#### V009-01-01/SFC

## **SPECIFICATIONS**

P.1/4

This product is not intended for operation by itself or without series operation unit.

Please connect the series operation unit before operation.

Model Name				EZA11K-320240SFC		
	Item			Battery side	Grid side	
1	Rated Voltage		-	240VDC	320VDC	
2	Voltage Range	(*1,*2)	-	150VDC - 300VDC	240VDC - 400VDC	
3	Rated Current		-	±45.8A	±34.4A	
4	Constant Current Setting Range	(*1,*2)	-	1.0A - 50A	1.0A - 40A	
5	Maximum Output Power		-	±11,000W	±11,000W	
6	Maximum Current		-	±50A	±40A	
7	Efficiency (typ)	(*3)	-	95%	95%	
8	Required Pre-charge Voltage	(*1)	-	More than output lower limit voltage	More than output lower limit voltage	
9	Inrush Current (typ)	(*4)	-	3.6A	3.6A	
10	Maximum Line Regulation		-	1.2V	1.6V	
11	Maximum Load Regulation		-	2.4V	3.2V	
12	Maximum Temperature Regulation		-	1.5V	2.0V	
13	Output Ripple and Noise		-	Less than 3Vp-p	Less than 4Vp-p	
14	Sink Current (typ)	(*5)	-	1.6A	1.2A	
Prote	ection					
1	Output Over Current Protection (typ)	(*6,*7)	-	70A (Output shut down)	60A (Output shut down)	
2	Over Power Protection (typ)	(*6)	-	12,000W (Constant power)	12,000W (Constant power)	
3	Input Current Limitation (typ)	(*6)	-	52A(Constant current)	42A(Constant current)	
4	Over Voltage Protection	(*2)	-	Possible (Setting range: 144V - 306V)	Possible (Setting range : 230V - 410V)	
5	Under Voltage Protection	(*2)	-	Possible (Setting range : 144V - 306V)	Possible (Setting range : 230V - 410V)	
Func	tion					
1	Remote ON/OFF		1	Possible (Control via RS	S-485 or Extra signal)	
2	Remote Reset		-	Possible (Latch off via RS-485, F	RESET SW or External Signal)	
	External Signal	(*8)		RUN: Operate at short, Stop at open		
				STOP: Stop at falling edge		
				ALMCLR: Alarm clear and Run at rising ed	lge	
3			-	ALM: Open under Alarm condition (O	pen Drain)	
				PG: Short under Operation (Open Di	rain)	
			ļ	5Vs: 5V Output (5V, 0.2A)		
				24Vi: 24V Input for RS-485 communi	cation	
4	Parallel operation	(*9)	-	Possible (Dro		
	Series operation	(*10)	-	Possible (Maximum of 6 units in series w	hen connected to series operation unit)	
	rnal Function (RS-485 )					
1	Voltage Setting Accuracy		-	Less than	±6.0V	
2	Current Setting Accuracy		-	Less than	±1.0A	
3	Voltage Setting Resolution		-	Less than	1 0.6V	
4	Current Setting Resolution		-	Less than 100mA		
5	Voltage Reading Accuracy		-	Less than ±6.0V		
6	Current Reading Accuracy		-	Less than	±1.0A	
7	Voltage Reading Resolution		-	Less than	1 0.6V	
8	Current Reading Resolution		-	Less than	100mA	
9	RS-485 Baud Rate		-	9600bps / 19.2kbps / 33.6kbps	/ 57.6kbps (Set by DIP-SW)	
10	RS-485 Maximum Connection		-	14		

#### V009-01-01/SFC **SPECIFICATIONS** P.2/4

	Model Name		EZA11K-320240SFC	
	Item		Battery side Grid side	
Env	ironmental		•	
1	Operating Temperature	-	-10°C - +50°C	
2	Operating Humidity	-	30 - 85%RH (No Condensing)	
3	Storage Temperature	-	-20°C - +70°C	
4	Storage Humidity	-	20 - 85%RH (No Condensing)	
5	Vibration	-	No Operation, 10-55Hz (Sweep 1min) 19.6m/s <sup>2</sup> Constant, X, Y, Z Each Direction 1hour	
6	Shock	-	196.1m/s <sup>2</sup> maximum	
7	Cooling	-	Forced Air Cooling by built-in FAN (Air Intake)	
8	Installation Location	-	Indoor use	
9	Altitude	-	Less than 3,000m	
Isol	ation			
1	Withstand Voltage	-	Primary(320V) - Secondary(240V) : 2.2kVAC(50mA) 1min Primary(320V) - Signals : 3kVAC(50mA) 1min Secondary(240V) - Signals : 3kVAC(50mA) 1min Primary(320V) - Chassis : 2kVAC(50mA) 1min Secondary(240V) - Chassis : 2kVAC(50mA) 1min Signals - Chassis : 400VAC(100mA) 1min	
2	Insulation Resistance	-	Primary(320V) - Chassis More than 100MΩ at 1kVDC 25°C, 70%RH Secondary(240V) - Chassis More than 100MΩ at 1kVDC 25°C, 70%RH Signals - Chassis More than 100MΩ at 500VDC 25°C, 70%RH	
Phy	sical Characteristics			
1	Weight	-	Less than 20 kg	
2	Size (W x H x D)	mm	422.8 x 43.6 x 530 (Refer to outline drawing)	
Oth	1			
1	PCB Coating materials	-	HumiSeal 1B59LU	
2	PCB Coating areas	-	Mounting surface and solder surface of six internal boards.  (Excluding discrete parts, screw holes, and connectors)	
3	Cooling Fan	-	High speed, dustproof and long life	

Please read instruction manual Carefully, before using the unit.

#### =Notes=

- \*1. Please refer to Derating Curve.
- \*2. It can be set via RS-485.
- \*3. Ta=25°C, rated voltage and rated current.
- \*4. Not applicable for the inrush current to Noise filter for less than 0.2ms.
- \*5. Current sink appear when applied voltage is greater than output target voltage.
- \*6. Parameter is fixed.
- \*7. Shut down method, manual reset.(Latch off via RS-485, RESET SW or External Signal)
- \*8. The external signal connector is connected to the series operation unit.
  - This product is not intended to be operated directly by external signals.
  - Operation by external signals is performed via the series operation unit.
- \*9. Droop ratio can be set via RS-485.
- \*10. Be sure to connect the series operation unit.

For details, please refer to the instruction manual of the series operation unit.


## V009-01-01/SFC SPECIFICATIONS P.3/4

Model Name			EZA11K-320240SFC	
Item			Operation Mode (*11)	
Battery Autonomy CV mode				
1 Power Conversion mode		-	Control battery voltage constant.	
2 Dead Zone set	(*12)	1	Possible	
3 Battery 0V Ramp up	(*13)	-	Possible	
4 Grid CC mode	(*11)	-	Possible (Control grid side current with constant current mode)	
5 Grid Over Charge Protection	(*12)	-	Possible	
6 Grid Over Discharge Protection	(*12)	-	Possible	
Grid Autonomy CV mode				
1 Power Conversion mode		-	Control Grid voltage constant.	
2 Dead Zone set	(*12)	-	Possible	
3 Grid 0V Ramp up	(*13)	-	Possible	
4 Battery CC mode	(*11)	-	Possible (Control battery side current with constant current mode)	
5 Battery Over Charge Protection	(*12)	-	Possible	
6 Battery Over Discharge Protection	(*12)	-	Possible	

Please read instruction manual Carefully, before using.

#### =Note=

- \*11. Control mode can be set via RS-485 or DIP-SW setting.
- \*12. It can be set via RS-485.
- \*13. It can start up under pre-charge voltage (Battery side : less than 150V, Grid side : less than 240V).



Direction of Generation and Regeneration

V009-01-01/SFC P.4/4

# **Derating Curve**




Fig. 1





Fig. 2



Please read instruction manual Carefully, before using.

#### =Note=

\*14. Limit maximum current by half (Battery side: 25.0A, Grid side: 20.0A).

\*15. Output shut down.




Fig. 4