


**NOTES**

- A: 9- $\phi$ 3.5 HOLES ARE FOR CUSTOMER'S CHASSIS MOUNTING HOLES. ALL MUST BE SCREWED IN ORDER TO CONFORM THE VIBRATION.
- B: MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE, AND MAXIMUM OUTPUT CURRENT ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.
- C: COUNTRY OF MANUFACTURE WILL BE SHOWN HERE.
- D:  $\oplus$  IS FOR SAFETY GROUND CONNECTION.
- E: TO KEEP THE DISTANCE MORE THAN 50mm BETWEEN PCB EDGE AND CUSTOMER'S CHASSIS FOR AIR VENTILATION.
- F: GIVE 10mm SPACING FOR COVER FIXING.

**NAME PLATE**

SCALE FOR NAME PLATE : 1/1

SEE NOTE B



SEE NOTE C

(unit : mm)

MODEL NAME	TEP200-280
<b>TDK-Lambda</b>	
B094-02-01B	