


DEMKO CERTIFICATE

Certificate No.	D-08879
Page	1/4
Date of Issue	2021-11-09
Certificate Holder	TDK-LAMBDA CORP NAGAOKA TECHNICAL CENTER 2704-1 SETTAYA-MACHI NAGAOKA-SHI, NIIGATA-KEN, 940-1195 JAPAN
Manufacturer	TDK-LAMBDA CORP NAGAOKA TECHNICAL CENTER 2704-1 SETTAYA-MACHI NAGAOKA-SHI, NIIGATA-KEN, 940-1195 JAPAN
Production site	TDK-LAMBDA CORP 2704-1 SETTAYA-MACHI NAGAOKA-SHI, NIIGATA-KEN, 940-1195 JAPAN
Certified Product	DC-DC Converter
Model	CC10-wwxyz#-E See page 2 for additional Information
Trademark	
Ratings	Input: 4.5 - 9 Vdc (for Model ww: 05) 9 - 18 Vdc (for Model ww: 12) 18 - 36 Vdc (for Model ww: 24) 36 - 76 Vdc (for Model ww: 48) See page 2 for additional ratings
Tested according to	EN IEC 62368-1:2020, EN IEC 62368-1:2020/A11:2020
Test Report No.	E132035-A6017-CB-1 issued on 2021-10-20
Additional	
Expire date	2031-11-08

Certification Manager
Jan-Erik Storgaard

This is to certify that representative sample(s) of the Product described herein ("Certified Product") have been investigated and found in compliance with the Standard(s) indicated on this Certificate, in accordance with the D-Mark Requirements. As specified in the respective appendix below the Designated Certificate holder is entitled to use the D-Mark, or its alternative for cables, for the Certified Product manufactured at the production site(s) identified above, in accordance with the D-Mark Service Agreement, including without limitation the D-Mark Testing and Certification Services Service Terms. Only those Products bearing the D-Mark should be considered as being covered by UL's D-Mark Service. This Certificate shall remain valid through the expiration date, unless terminated earlier in accordance with the Service Agreement including without limitation if the Standard identified on this Certificate is amended or withdrawn prior the expiration date.

Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65,
info.dk@ul.com
www.UL.com



Appendix DEMKO CERTIFICATE

Certificate No. D-08879
Page 2/4
Date of Issue 2021-11-09

Additional Model(s):

Series: CC10-wwxyz#-E, (ww: 05, 12, 24 or 48, xx: 03, 05 or 12, y: S, z: F or R, #: A to Z or blank) or (ww: 05, 12, 24 or 48, xx: 12, y: D, z: F or R, #: A to Z or blank)

Ratings:

Output:

3.3 - 3.6 Vdc, 2500 mA

(for Models CC10-ww03Sz#-E)

5 - 6 Vdc, 2000 mA

(for Models CC10-ww05Sz#-E)

12 - 15 Vdc, 800 mA

(for Model CC10-0512Sz#-E)

12 - 15 Vdc, 1000 mA

(for Models CC10-ww12Sz#-E, ww = 12, 24, 48)

±12 - ±15 Vdc, 400 mA

(for Model CC10-0512Dz#-E)

±12 - ±15 Vdc, 450 mA

(for Models CC10-ww12Dz#-E, except for ww = 05)

for building-in, Not Classified, IPX0

Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65, info.dk@ul.com
www.UL.com




Appendix DEMKO CERTIFICATE

Certificate No. D-08879
Page 3/4
Date of Issue 2021-11-09

Certification Mark D-Mark

The D-Mark, as displayed below, shall appear on certified products only. Except as specified below the Mark shall be legible and no Minimum size is specified.



The size of the Mark may be reduced or enlarged on the condition that it remains readable and that the proportions of width and height are kept. The use of dark text for the D-Mark on light backgrounds and light text on dark backgrounds is permitted.

The D-Mark may appear on a label, nameplate, or may be cast, stamped or molded into the product. When appearing on a label or nameplate, the Manufacturer's name or trademark along with a model number are also required on that same label or nameplate. If cast, stamped or molded, the Certificate Manufacturer's name or trademark and model number shall also appear elsewhere on the product

When putting the product on the EU market, the manufacturer's name, trademark or mark of origin must be affixed in a clearly visible location and position on the product, on the package and in the user manual. It can be affixed by label, be directly imprinted, or cast or molded into the product.

Where the size of the product does not allow the Mark, the manufacturer's name, trademark, mark of origin and model number to be legible, and appearance on a label is not desired, it is allowed to cast, stamp or mold the Mark into the product, in a size which is not visible to the naked eye, provided the legible Mark, the manufacturer's name, trademark or mark of origin and model number appears on the package and in the user manual

Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65, info.dk@ul.com
www.UL.com



Appendix DEMKO CERTIFICATE

Certificate No. D-08879
Page 4/4
Date of Issue 2021-11-09

Alternate certification Mark for cables

As an alternative to the D-Mark specified above the alternate D-Mark, displayed below, can appear on certified cables only. Minimum size is not specified, as long as the mark is legible.

<DEMKO>

The alternate D-Mark may be cast, stamped or molded into the cable and continue throughout the length of the cable as specified in the applicable cable standard.

All content shall be in accordance with the details provided on this D-Mark Certificate.

Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65, info.dk@ul.com
www.UL.com

