



TEST REPORT IEC 62368-1

Audio/video, information and communication technology equipment Part 1: Safety requirements

Report Number: E220248-A6025-CB-1

Date of issue: 2021-12-07

Total number of pages: 57

Name of Testing Laboratory UL RTP

Applicant's name...... TDK-LAMBDA AMERICAS INC

Address 3000 TECHNOLOGY DR, SUITE 100

PLANO TX 75074 UNITED STATES

Test specification:

Standard: IEC 62368-1: 2018

Test procedure...... CB Scheme

Non-standard test method.....: N/A

TRF template used IECEE OD-2020-F1:2020, Ed.1.3

Test Report Form No.....: IEC62368_1E

Test Report Form(s) Originator...: UL(US)

Master TRF...... Dated 2021-02-04

Copyright © 2021 IEC System of Conformity Assessment Schemes for Electrotechnical Equipment and Components (IECEE System). All rights reserved.

This publication may be reproduced in whole or in part for non-commercial purposes as long as the IECEE is acknowledged as copyright owner and source of the material. IECEE takes no responsibility for and will not assume liability for damages resulting from the reader's interpretation of the reproduced material due to its placement and context.

If this Test Report Form is used by non-IECEE members, the IECEE/IEC logo and the reference to the CB Scheme procedure shall be removed.

This report is not valid as a CB Test Report unless signed by an approved CB Testing Laboratory and appended to a CB Test Certificate issued by an NCB in accordance with IECEE 02.

General disclaimer:

The test results presented in this report relate only to the object tested.

This report shall not be reproduced, except in full, without the written approval of the Issuing CB Testing Laboratory. The authenticity of this Test Report and its contents can be verified by contacting the NCB, responsible for this Test Report.

Issue Date: 2021-12-07 Page 2 of 57 Report Reference # E220248-A6025-CB-1

Test Item Description:	DC-DC Converter	
Trade Mark(s):	TDK	
	公TDK	
Manufacturer:	TDK-LAMBDA AMERICAS	INC
	3000 TECHNOLOGY DR, S	SUITE 100
	PLANO TX 75074 US	
Model/Type reference:	i3A4W***A%%V-0xx(-R)	
	Where 4W represents input Max input current	Voltage between 9 - 53 VDC 10 A
	*** represents rated output of	current between 0 A - 10A,
	·	out voltage between 0 V dc to 30 Vdc.
	and 0xx indicates a number non safety features.	of alphanumeric characters to denote
	It may also be followed by o compliance.	ptional "-R " to denote RoHS
	Model examples:	
	i3A4W005A150V-0xx(-R)	
	i3A4W008A033V-0xx(-R)	
Ratings::	Optional:	
	Rated input Voltage 9-53 VI	DC
	Rated Input Current 10 A	
	Rated Power 100 W	
	Rated outputs 20 VDC mays	10 A may
	Rated output: 30 VDC max;	TO A Max.
Responsible Testing Laboratory (as applica	ble), testing procedure and	d testing location(s):
☐ CB Testing Laboratory:		
Testing location/ address:	UL RTP, 12 Laboratory D 27709, USA	rive, Research Triangle Park , NC,
Tested by (name, function, signature):	Mengis Tesfay / Project Handler	Mery's Tosfay
Approved by (name, function, signature):	Scott Shepler / Reviewer	Mery's Tosfay Scott Sheplen
☐ Testing procedure: CTF Stage 1:		
Testing location/ address:		
resumy rocations address		
Tested by (name, function, signature):		

Issue Date: 2021-12-07 Page 3 of 57 Report Reference # E220248-A6025-CB-1

Approved by (name, function, signature):			
Approved by (flame, function, signature)			
\boxtimes	Testing procedure: CTF Stage 2:		
Testing location/ address:		TDK-LAMBDA AMERICAS INC	
		SUITE 100	
		3320 MATRIX DR	
		RICHARDSON TX 75082	2
		UNITED STATES	
Test	ed by (name, function, signature):	Steve McKitrick / Tester	See original CBTR for signatures
Witnessed by (name, function, signature).:		P. Mobs / Project	See original CBTR for signatures
		Handler	
Approved by (name, function, signature):		K. Kreuzer / Reviewer	See original CBTR for signatures
	Testing procedure: CTF Stage 3:		
	Testing procedure: CTF Stage 4:		
Test	ing location/ address:		
Test	ed by (name, function, signature):		
Witnessed by (name, function, signature).:			
Approved by (name, function, signature):			
Supervised by (name, function, signature) :			

Issue Date: 2021-12-07 Page 4 of 57 Report Reference # E220248-A6025-CB-1

List of Attachments (including a total number of pages in each attachment):

National Differences (29 pages) Enclosures (58 pages)

Summary of testing:

Tests performed (name of test and test clause):

Testing Location:

CTF Stage 2: TDK-LAMBDA AMERICAS INC

SUITE 100

3320 MATRIX DR

RICHARDSON TX 75082

UNITED STATES

B.2.5 - INPUT TEST: SINGLE PHASE

Testing conducted in accordance with IEC 60950-1:2005 (Second Edition), Am1:2009 + Am2:2013; UL 60950-1, 2nd Edition, 2014-10-14; and CAN/CSA C22.2 No. 60950-1-07, 2nd Edition, 2014-10, and was deemed equivalent to the test required by IEC62368-1, 2nd Edition, CAN/CSA-C22.2 NO. 62368-1 2nd Ed, Issued December 1, 2014, and UL 62368-1 2nd Ed, Issued December 1, 2014. This test was also considered representative to the test required per UL62368-1, 3rd Ed December 13, 2019; CAN/CSA-C22.2 No. 62368-1, 3rd Ed December 13, 2019; and IEC62368-1:2018, 3rd Ed.

B.1.5, B.2.6, 5.4.1.4, 6.3, 9.3 - NORMAL OPERATING CONDITIONS TEMPERATURE MEASUREMENT

Testing conducted in accordance with IEC 60950-1:2005 (Second Edition), Am1:2009 + Am2:2013; UL 60950-1, 2nd Edition, 2014-10-14; and CAN/CSA C22.2 No. 60950-1-07, 2nd Edition, 2014-10, and was deemed equivalent to the test required by IEC62368-1, 2nd Edition, CAN/CSA-C22.2 NO. 62368-1 2nd Ed, Issued December 1, 2014, and UL 62368-1 2nd Ed, Issued December 1, 2014. This test was also considered representative to the test required per UL62368-1, 3rd Ed December 13, 2019; CAN/CSA-C22.2 No. 62368-1, 3rd Ed December 13, 2019; and IEC62368-1:2018, 3rd Ed.

B.3 - SIMULATED ABNORMAL OPERATING CONDITIONS

Testing conducted in accordance with IEC 60950-1:2005 (Second Edition), Am1:2009 + Am2:2013; UL 60950-1, 2nd Edition, 2014-10-14; and CAN/CSA C22.2 No. 60950-1-07, 2nd Edition, 2014-10, and was deemed equivalent to the test required by IEC62368-1, 2nd Edition, CAN/CSA-C22.2 NO. 62368-1 2nd Ed, Issued December 1, 2014, and UL 62368-1 2nd Ed, Issued December 1, 2014. This test was also considered representative to the test required per UL62368-1, 3rd Ed December 13, 2019; CAN/CSA-C22.2 No. 62368-1, 3rd Ed December 13, 2019; and IEC62368-1:2018, 3rd Ed.

B.4 - SIMULATED SINGLE FAULT CONDITIONS

Testing conducted in accordance with IEC 60950-1:2005 (Second Edition), Am1:2009 + Am2:2013; UL 60950-1, 2nd Edition, 2014-10-14; and CAN/CSA C22.2 No. 60950-1-07, 2nd Edition, 2014-10, and was deemed equivalent to the test required by IEC62368-1, 2nd Edition, CAN/CSA-C22.2 NO. 62368-1 2nd Ed, Issued December 1, 2014, and UL 62368-1 2nd Ed, Issued December 1, 2014. This test was also considered representative to the test required per UL62368-1, 3rd Ed

Issue Date: 2021-12-07 Page 5 of 57 Report Reference # E220248-A6025-CB-1

	December 13, 2019; CAN/CSA-C22.2 No. 62368-1, 3rd Ed December 13, 2019; and IEC62368-1:2018, 3rd Ed.			
Summary of compliance with National Differences (List of countries addressed):				
EU Group and National Differences, USA / Canada				
☐ The product fulfils the requirements of EN IEC 62368-1:2020+A11:2020				
Statement concerning the uncertainty of the measurement systems used for the tests				
☐ Internal procedure used for type testing through which traceability of the measuring uncertainty has been established:				
Procedure number, issue date and title:				
	e with the NCB and testing laboratory that conducted the			
testing.				
Statement not required by the oter land west	for them a toption of			
Statement not required by the standard used □	for type testing			
(Note: When IEC or ISO standard requires a statement concerning be reported above. The informative text in parenthesis should be	ng the uncertainty of the measurement systems used for tests, this should delete in both cases after selecting the applicable option)			

Issue Date: 2021-12-07 Page 6 of 57 Report Reference # E220248-A6025-CB-1

Copy of marking plate:

The artwork below may be only a draft. The use of certification marks on a product must be authorized by the respective NCBs that own these marks.

TDK-Lambda Americas Inc.



i3A4W005A150V-0xx(-R)

Note: The above markings are the minimum requirements required by the safety lab. For the final production samples, the additional markings which do not give rise to misunderstanding may be added.

Issue Date: 2021-12-07 Page 7 of 57 Report Reference # E220248-A6025-CB-1

Test item particulars:			
Product group			
Classification of use by	Instructed person		
Supply Connection	not mains connected: ES1		
Supply tolerance	None		
Supply connection – type	For building in. To be considered in end system		
Considered current rating of protective device	N/A		
Equipment mobility	for building-in		
Over voltage category (OVC)	OVC I		
Class of equipment	Not Classified		
Special installation location	N/A		
	0		
Pollution degree (PD)	PD 2		
Manufacturer's specified Tma (°C)	25		
IP protection class	IPX0		
Power systems			
Altitude during operation (m)	2000 m or less		
Altitude of test laboratory (m)	180 m m		
Mass of equipment (kg)	0.1		
Possible test case verdicts:			
- test case does not apply to the test object:	N/A		
- test object does meet the requirement:	P (Pass)		
- test object does not meet the requirement:	F (Fail)		
Testing:			
Date of receipt of test item:	2017-02-20, 2019-09-04		
Date (s) of performance of tests:	2017-02-20 to 2017-05-16, 2019-09-04		
General remarks:			
"(See Enclosure #)" refers to additional information appended to the report. "(See appended table)" refers to a table appended to the report.			
Throughout this report a \square comma / \boxtimes point is used as the decimal separator.			
Manufacturer's Declaration per sub-clause 4.2.5 of IECEE 02:			

Issue Date: 2021-12-07 Page 8 of 57 Report Reference # E220248-A6025-CB-1

The application for obtaining a CB Test Certificate includes more than one factory location and a declaration from the Manufacturer stating that the sample(s) submitted for evaluation is (are) representative of the products from each factory has been provided	✓ Yes☐ Not applicable			
When differences exist; they shall be identified in the General product information section.				
Name and address of factory (ies):	TDK-LAMBDA AMERICAS INC			
	3000 TECHNOLOGY DR, SUITE 100			
	PLANO TX 75074 US			
	TDK-LAMBDA MALAYSIA SDN BHD			

PLO33 KAWASAN PERINDUSTRIAN SENAI

SENAI JOHOR 81400 Malaysia

General product information and other remarks:

Product Description

EUT is high density non-Isolated DC-DC Converter modules. The converters are provided with input terminal pins for factory installation onto a printed wiring board with a connection to a dc source of supply and output terminal pins.

Model Differences

All models are identical except for minor changes to the components based upon the output voltage rating of the unit.

Additional Information

This report is based on CB report references E220248-A6005-CB-1 and CB Test Certificate Ref. US-34429-UL respectively which was previously evaluated to UL 62368-1, 2nd Edition, 2014-12-01, CSA C22.2 No. 62368-1-14, 2nd Edition, 2014-12, and IEC 62368-1:2014. Testing conducted in accordance with UL 62368-1, 2nd Edition, 2014-12-01, CSA C22.2 No. 62368-1-14, 2nd Edition, 2014-12, and IEC 62368-1:2014, was deemed equivalent to the test required per UL62368-1, 3rd Ed December 13, 2019; CAN/CSA-C22.2 No. 62368-1, 3rd Ed December 13, 2019; and IEC62368-1:2018, 3rd Ed.

Marking label provided represents all models in series.

Technical Considerations

- The product was submitted and evaluated for use at the maximum ambient temperature (Tma) permitted by the manufacturer's specification of : 25 °C
- The product is intended for use on the following power systems : No direct connection
- Considered current rating of protective device as part of the building installation (A): For building in. To be considered in end system. Device was evaluated with a 20 A external overcurrent protective device.
- Mains supply tolerance (%) or absolute mains supply: No direct connection
- The equipment disconnect device is considered to be : To be considered in end system
- The following are available from the Applicant upon request: Installation (Safety) Instructions / Manual
- The product was investigated to the following additional standard: EN IEC 62368-1:2020+A11:2020

Issue Date: 2021-12-07 Page 9 of 57 Report Reference # E220248-A6025-CB-1

Engineering Conditions of Acceptability

When installed in an end-product, consideration must be given to the following:

- The following output circuits are at ES1 energy levels : All input and output
- The following output circuits are at PS3 energy levels: Outputs: 1.8 Vdc, 2.5 Vdc and 3.3 Vdc
- The maximum investigated branch circuit rating is: For building in. To be considered in end system. Device was evaluated with a 20 A external overcurrent protective device.
- The investigated Pollution Degree is: 2
- The following end-product enclosures are required: Fire, Electrical
- A heating test shall be considered in the end product. The PWB is rated 130°C.