

UL TEST REPORT AND PROCEDURE

Standard:	UL 62368-1, 2nd Ed, 2014-12-01 (Audio/video, information and communication technology equipment Part 1: Safety requirements) CAN/CSA C22.2 No. 62368-1-14, 2nd Ed-(Audio/video, information and communication technology equipment Part 1: Safety requirements)
Certification Type:	Component Recognition
CCN:	QQJQ2, QQJQ8 (Power Supplies for Use in Audio/Video, Information and Communication Technology Equipment)
Complementary CCN:	N/A
Product:	DC-To-DC Converters
Model:	i7Czz***A%%V-xxx-R where zz represents input voltage where it may be 2W (9-36 VDC input), or 4W (9-53 VDC input), 30A max input current. *** represents rated output current between 0.8 A - 30A, where *** may be 1 to 3 digits. %%V represents rated output voltage between 0.8Vdc - 56Vdc, where %%% may be 1 to 3 digits. Note that the third digit is preceded by a decimal point. Example 120 implies 12.0 Volts. xxx indicates a number or alphanumeric character which affects non safety related features. -R is optional and indicates RoHS compliance.
Rating:	Not required. Optional. Input: 9-53Vdc, 30A Max Output: 0.8 VDC to 56VDC; Max 30A, 439 W maximum.
Applicant Name and Address:	TDK-LAMBDA AMERICAS INC SUITE 100 3320 MATRIX DR RICHARDSON TX 75082 UNITED STATES

This is to certify that representative samples of the products covered by this Test Report have been investigated in accordance with the above referenced Standards. The products have been found to comply with the requirements covering the category and the products are judged to be eligible for Follow-Up Service under the indicated Test Procedure. The manufacturer is authorized to use the UL Mark on such products which comply with this Test Report and any other applicable requirements of UL LLC ('UL') in accordance with the Follow-Up Service Agreement. Only those products which properly bear the UL Mark are considered as being covered by UL's Follow-Up Service under the indicated Test Procedure.

The applicant is authorized to reproduce the referenced Test Report provided it is reproduced in its entirety.

UL authorizes the applicant to reproduce the latest pages of the referenced Test Report consisting of the first page of the Specific Technical Criteria through to the end of the Conditions of Acceptability.

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL.

Prepared By: Mengis Tesfay / Project Handler Reviewed By: Scott Shepler / Reviewer

Supporting Documentation

The following documents located at the beginning of this Procedure supplement the requirements of this Test Report:

- A. Authorization - The Authorization page may include additional Factory Identification Code markings.
- B. Generic Inspection Instructions -
 - i. Part AC details important information which may be applicable to products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of this Test Report.
 - ii. Part AE details any requirements which may be applicable to all products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of each Test Report.
 - iii. Part AF details the requirements for the UL Certification Mark which is not controlled by the technical standard used to investigate these products. Products are permitted to bear only the Certification Mark(s) corresponding to the countries for which it is certified, as indicated in each Test Report.

Product Description

The i7C product family consists of non-isolated DC-DC power modules intended to be used as a component in an end-user’s power system. The modules will be offered in multiple input voltage and output voltage ranges. The input ranges from 9 - 53Vdc input at 30 A max. The output voltage will be adjustable between 0.8V to 56V. The rated output power will be 439W or less

Model Differences

All models within the series are similar except for input rating, output rating, and size of inductor.

Test Item Particulars

Classification of use by	Instructed person
Supply Connection	External Circuit - not Mains connected ES1
Supply % Tolerance	None
Supply Connection – Type	No direct connection to Mains. Considered in the end-product
Considered current rating of protective device as part of building or equipment installation	N/A A; N/A
Equipment mobility	for building-in
Over voltage category (OVC)	OVC I
Class of equipment	Not classified
Access location	N/A
Pollution degree (PD)	PD 2
Manufacturer’s specified maximum operating ambient (°C)	25
IP protection class	IPX0
Power Systems	N/A
Altitude during operation (m)	2000 m or less
Altitude of test laboratory (m)	2000 m or less
Mass of equipment (kg)	0.08

Technical Considerations

- The product was submitted and evaluated for use at the maximum ambient temperature (T_{ma}) permitted by the manufacturer's specification of : 25°C
- The product is intended for use on the following power systems : No direct connection
- Considered current rating of protective device as part of the building installation (A) : N/A. For building in.
- Mains supply tolerance (%) or absolute mains supply values : No direct connection
- The equipment disconnect device is considered to be : N/A
- The following are available from the Applicant upon request : Installation (Safety) Instructions / Manual
- The product was investigated to the following additional standard : EN 62368-1:2014 + A11:2017, AS/NZS 62368.1:2018

Engineering Conditions of Acceptability

For use only in or with complete equipment where the acceptability of the combination is determined by UL LLC. When installed in an end-product, consideration must be given to the following:

- The following output circuits are at ES1 energy levels : All
- The following output circuits are at PS3 energy levels : Output Terminal
- The investigated Pollution Degree is : 2
- An investigation of the protective bonding terminals has : not been conducted
- The following end-product enclosures are required : Electrical, Fire
- The units provide Functional Insulation only between input and output circuits.
- Heating Test shall be evaluated in end product. The following components require special consideration during end-product Thermal (Heating) tests due to the indicated maximum temperature measurements during component-level testing: PWB.
Rated 130 C.
- This component has been evaluated in 'control of fire spread' method assuming appropriate fire enclosure is provided in end product. Unless the fire enclosure is made of non-combustible or V-0 material, the separation from the PIS shall be considered
- Classification of PIS has not been conducted. Therefore, all electrical components and conductors including printed wirings were assumed to be arcing/resistive PIS.
- Power to the DC-DC Converter is intended to be supplied by isolated secondary circuitry in an end use application.
- All Units were tested with an external 30A fuse during Abnormal Operation and Component Fault testing.
- Output voltage may be adjusted for up the maximum fixed output power (i.e. maximum output current is decreased). When the output voltage is adjusted down, the maximum output current is fixed (i.e. available output power is decreased).

Additional Information

This report is based on CB report E220248-A42-CB-1, and CB Test Certificate Ref. US-32823-UL and US-32823-A1-UL, and was previously evaluated to UL/CSA/IEC 60950-1, 2nd edition, + Amendment 1, and Amendment 2. Testing was conducted in accordance with IEC 60950-1:2005 (Second Edition), Am1:2009 + Am2:2013; UL 60950-1, 2nd Edition, 2014- 10-14; and CAN/CSA C22.2 No. 60950-1-07, 2nd Edition, 2014-10, and was deemed equivalent to the test required by IEC62368-1, 2nd Edition, CAN/CSA-C22.2 NO. 62368-1 2nd Ed, Issued December 1, 2014, and UL 62368-1 2nd Ed, Issued December 1, 2014. Testing correlation explanation provided in Enclosure. All required testing took place in original report.

All original sample and test dates are noted in the testing portion of this report. Test date noted 2019-10-24 is for construction review only.

Models i7C4W008A120V-xxx(-R), i7C2W020A120V-xxx(-R) of i7C series were used for test purposes and are considered representative of the entire series. Model i7C4W008A120V-xxx is the highest output voltage and

highest power module within the series.

The nameplate included in the report is representative of all models covered under this report.

Additional Standards

The product fulfills the requirements of: EN 62368-1:2014 + A11:2017

Markings and Instructions

Clause Title	Marking or Instruction Details
Equipment identification marking – Manufacturer identification	Listees or Recognized companys name, Trade Name, Trademark or File Number
Equipment identification marking – model identification	Model Number

Special Instructions to UL Representative

N/A