

UL TEST REPORT AND PROCEDURE

Standard:	UL 62368-1, 2nd Ed, 2014-12-01 (Audio/video, information and communication technology equipment Part 1: Safety requirements) CAN/CSA C22.2 No. 62368-1-14, 2nd Ed-(Audio/video, information and communication technology equipment Part 1: Safety requirements)
Certification Type:	Component Recognition
CCN:	QQJQ2, QQJQ8 (Power Supplies for Use in Audio/Video, Information and Communication Technology Equipment)
Complementary CCN:	N/A
Product:	DC-To-DC Converters
Model:	<p>Model iAH-, iAF-, iBF-, iBH-, iCF-, iCG-, iCH -series</p> <p>Model structure i&&!!***A%%V-###(-R) eg.iCF05003A006V-###-R where: && represents a two letter mechanical form factor and pin out, e.g. CF means 0.5"x 0.5" with a particular terminal pattern. !! represents a two digit input voltage, e.g. "05" means 5Vdc *** represents a three digit current, eg."003" means 3A %%% represents a three digit voltage, eg."006" means 0.6V, ### Or xxx represents a three digit combination of numbers and/or letters which indicate the feature set (see below) -R optional, designates ROHS compliance</p> <p>See model Matrix, under miscellaneous enclosure</p>
Rating:	<p>Input: 3 – 17 VDC, Max. 35 A, Max.</p> <p>Output: 0.7 - 5 VDC, 40 A, 150 W,</p> <p>See model Matrix, for details</p>

Applicant Name and Address:

TDK-LAMBDA AMERICAS INC
SUITE 100
3320 MATRIX DR
RICHARDSON TX 75082
UNITED STATES

This is to certify that representative samples of the products covered by this Test Report have been investigated in accordance with the above referenced Standards. The products have been found to comply with the requirements covering the category and the products are judged to be eligible for Follow-Up Service under the indicated Test Procedure. The manufacturer is authorized to use the UL Mark on such products which comply with this Test Report and any other applicable requirements of UL LLC ('UL') in accordance with the Follow-Up Service Agreement. Only those products which properly bear the UL Mark are considered as being covered by UL's Follow-Up Service under the indicated Test Procedure.

The applicant is authorized to reproduce the referenced Test Report provided it is reproduced in its entirety.

UL authorizes the applicant to reproduce the latest pages of the referenced Test Report consisting of the first page of the Specific Technical Criteria through to the end of the Conditions of Acceptability.

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL.

Prepared By: Mengis Tesfay / Project Handler Reviewed By: Scott Shepler / Reviewer

Supporting Documentation

The following documents located at the beginning of this Procedure supplement the requirements of this Test Report:

- A. Authorization - The Authorization page may include additional Factory Identification Code markings.
- B. Generic Inspection Instructions -
 - i. Part AC details important information which may be applicable to products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of this Test Report.
 - ii. Part AE details any requirements which may be applicable to all products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of each Test Report.
 - iii. Part AF details the requirements for the UL Certification Mark which is not controlled by the technical standard used to investigate these products. Products are permitted to bear only the Certification Mark(s) corresponding to the countries for which it is certified, as indicated in each Test Report.

Product Description

iAH12 power modules perform local voltage conversion from either a 5V or 12V bus. The iAH12040A007V utilizes a low component count that results in both a low cost structure and a high level of performance. The open-frame, compact, surface mountable design features a low profile and weight that allow for extremely flexible and robust manufacturing processes.

Model Differences

All models with iAH-, iAF-, iBF-, iBH-, iCF-, iCG-, iCH -series covered within this series are similar as they share same power train, consisting of two Mosfets, power inductor and input/output filtering capacitors.

Test Item Particulars

Classification of use by	Instructed person
Supply Connection	External Circuit - not Mains connected ES1
Supply % Tolerance	None
Supply Connection – Type	No direct connection to Mains
Considered current rating of protective device as part of building or equipment installation	N/A, No direct connection to Mains A; N/A
Equipment mobility	for building-in
Over voltage category (OVC)	OVC I
Class of equipment	Not classified
Access location	N/A
Pollution degree (PD)	PD 2
Manufacturer's specified maximum operating ambient (°C)	25
IP protection class	IPX0
Power Systems	N/A
Altitude during operation (m)	2000 m or less
Altitude of test laboratory (m)	App 180 m
Mass of equipment (kg)	0.08

Technical Considerations

- The product was submitted and evaluated for use at the maximum ambient temperature (Tma) permitted by the manufacturer's specification of : 25°C
- The product is intended for use on the following power systems : No direct connection
- Considered current rating of protective device as part of the building installation (A) : An external input line normal blow fuse with a max. value 10 A for iCF, iCG Series, 15 A for iBF, iCH Series and 20A for iAF, iBH Series are required.
- Mains supply tolerance (%) or absolute mains supply values : No direct connection
- The equipment disconnect device is considered to be : N/A
- The following are available from the Applicant upon request : Installation (Safety) Instructions / Manual
- The product was investigated to the following additional standard : EN 62368-1:2014 + A11:2017

Engineering Conditions of Acceptability

For use only in or with complete equipment where the acceptability of the combination is determined by UL LLC. When installed in an end-product, consideration must be given to the following:

- The following output circuits are at ES1 energy levels : All
- The following output circuits are at PS3 energy levels : Output Terminal
- The maximum investigated branch circuit rating is : An external input line normal blow fuse with a max. value 10 A for iCF, iCG Series, 15 A for iBF, iCH Series and 20A for iAF, iBH Series are required.
- The investigated Pollution Degree is : 2
- The following end-product enclosures are required : Fire
- The power supply was evaluated to be used at altitudes up to : "2,000 m"
- The output circuit is considered PS3
- Heating Test shall be evaluated in end product.
- Classification of PIS has not been conducted. Therefore, all electrical components and conductors including printed wirings were assumed to be arcing/resistive PIS.
- Unit intended for building-in and supplied power from secondary circuit which is isolated from primary circuit by double or reinforced insulation.

Additional Information

This report is based on VDE CB report 2520400-3336-0025/158205, and its amendments 2520400-3336-0025/182234, 2520400-3336-0025/199270, 2520400-3336-0025/200890, 2520400-3336-0025/204318, 207809-CI3-2 and CB Test Certificate Ref.DE1-49619, DE1-49619/M1, DE1-49619/A1/B1, DE1-49619/A1/B1/M2, DE1-49619/A2/B1/M2 respectively which was previously evaluated to UL/CSA/IEC 60950-1, 2nd edition, + Amendment 1, and Amendment 2. Testing conducted in accordance with IEC 60950-1:2005 (Second Edition), Am1:2009 + Am2:2013; UL 60950-1, 2nd Edition, 2014-10-14; and CAN/CSA C22.2 No. 60950-1-07, 2nd Edition, 2014-10, and was deemed equivalent to test required by IEC62368-1, 2nd Edition, CAN/CSA-C22.2 NO. 62368-1 2nd Ed, Issued December 1, 2014, and UL 62368-1 2nd Ed, Issued December 1, 2014. Testing correlation explanation is provided in Enclosure.

All original sample and test dates are noted in the testing portion of this report.

The nameplate included in the report is representative of all models covered under this report.

Additional Standards

The product fulfills the requirements of: EN 62368-1:2014 + A11:2017

Markings and Instructions

Clause Title	Marking or Instruction Details
--------------	--------------------------------

Equipment identification marking – Manufacturer identification	Listees or Recognized companys name, Trade Name, Trademark or File Number
Equipment identification marking – model identification	Model Number
Special Instructions to UL Representative N/A	