Issue Date: 2021-12-07 Page 1 of 8 Report Reference # E220248-A6025-UL

Revision Date: 2023-05-23

UL TEST REPORT AND PROCEDURE

Standard: UL 62368-1, 3rd Ed, 2021-10-22 (Audio/video, information and

communication technology equipment Part 1: Safety requirements) CAN/CSA C22.2 No. 62368-1:19, 3rd Ed, 2021-10-22 (Audio/video, information and communication technology equipment Part 1: Safety

requirements)

Certification Type: Component Recognition

CCN: QQJQ2, QQJQ8 (Power Supplies for Use in Audio/Video, Information

and Communication Technology Equipment)

Complementary CCN: N/A

Model:

Rating:

Applicant Name and Address:

Product: DC-DC Converter

i3A4W***A%%%V-0xx(-R)

Where 4W represents input Voltage between 9 - 53 VDC 10 A Max input

current

*** represents rated output current between 0 A - 10A,

%%% represents rated output voltage between 0 V dc to 30 Vdc.

and 0xx indicates a number of alphanumeric characters to denote non

safety features.

It may also be followed by optional "-R " to denote RoHS compliance.

Model examples:

i3A4W005A150V-0xx(-R) i3A4W008A033V-0xx(-R)

Optional:

Rated input Voltage 9-53 VDC

Rated Input Current 10 A

Rated Power 100 W

Rated output: 30 VDC max; 10 A max.

TDK-LAMBDA AMERICAS INC

3000 TECHNOLOGY DR, SUITE 100

PLANO TX 75074

UNITED STATES

Issue Date: 2021-12-07 Page 2 of 8 Report Reference # E220248-A6025-UL

Revision Date: 2023-05-23

This is to certify that representative samples of the products covered by this Test Report have been investigated in accordance with the above referenced Standards. The products have been found to comply with the requirements covering the category and the products are judged to be eligible for Follow-Up Service under the indicated Test Procedure. The manufacturer is authorized to use the UL Mark on such products which comply with this Test Report and any other applicable requirements of UL LLC ('UL') in accordance with the Follow-Up Service Agreement. Only those products which properly bear the UL Mark are considered as being covered by UL's Follow-Up Service under the indicated Test Procedure.

The applicant is authorized to reproduce the referenced Test Report provided it is reproduced in its entirety.

UL authorizes the applicant to reproduce the latest pages of the referenced Test Report consisting of the first page of the Specific Technical Criteria through to the end of the Conditions of Acceptability.

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL.

Prepared By: Oliver Trinh/Mengis Tesfay / Reviewed By: Michael Lockhart / Reviewer

Project Handler

Issue Date: 2021-12-07 Page 3 of 8 Report Reference # E220248-A6025-UL

Revision Date: 2023-05-23

Supporting Documentation

The following documents located at the beginning of this Procedure supplement the requirements of this Test Report:

A. Authorization - The Authorization page may include additional Factory Identification Code markings.

- B. Generic Inspection Instructions
 - i. Part AC details important information which may be applicable to products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of this Test Report.
 - ii. Part AE details any requirements which may be applicable to all products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of each Test Report.
 - iii. Part AF details the requirements for the UL Certification Mark which is not controlled by the technical standard used to investigate these products. Products are permitted to bear only the Certification Mark(s) corresponding to the countries for which it is certified, as indicated in each Test Report.

Product Description

EUT is high density non-Isolated DC-DC Converter modules. The converters are provided with input terminal pins for factory installation onto a printed wiring board with a connection to a dc source of supply and output terminal pins.

Model Differences

All models are identical except for minor changes to the components based upon the output voltage rating of the unit.

Test Item Particulars	
Product group	
Classification of use by	Instructed person
Supply Connection	not mains connected: ES1
Supply tolerance	None
Supply connection – type	For building in. To be considered in end system
Considered current rating of protective device	N/A
Equipment mobility	for building-in
Over voltage category (OVC)	OVC I
Class of equipment	Not Classified
Special installation location	N/A
	0
Pollution degree (PD)	PD 2
Manufacturer's specified Tma (°C)	25
IP protection class	IPX0
Power systems	
Altitude during operation (m)	2000 m or less
Altitude of test laboratory (m)	180 m m
Mass of equipment (kg)	0.1

Technical Considerations

Issue Date: 2021-12-07 Page 4 of 8 Report Reference # E220248-A6025-UL

Revision Date: 2023-05-23

· · · · · · · · · · · · · · · · · · ·
permitted by the manufacturer's specification of : 25 °C
be considered in end system. Device was evaluated with a 20 A external overcurrent protective device.
Mains supply tolerance (%) or absolute mains supply : No direct connection
The equipment disconnect device is considered to be : To be considered in end system
The following are available from the Applicant upon request: Installation (Safety) Instructions / Manual
The product was investigated to the following additional standard: EN IEC 62368-1:2020+A11:2020
se only in or with complete equipment where the acceptability of the combination is determined by UL When installed in an end-product, consideration must be given to the following:
The following output circuits are at ES1 energy levels : All input and output
The following output circuits are at PS3 energy levels : Outputs: 1.8 Vdc, 2.5 Vdc and 3.3 Vdc
The maximum investigated branch circuit rating is: For building in. To be considered in end system.
Device was evaluated with a 20 A external overcurrent protective device.
The investigated Pollution Degree is : 2
The following end-product enclosures are required : Fire, Electrical
A heating test shall be considered in the end product. The PWB is rated 130°C.

Additional Information

This report is based on CB report references E220248-A6005-CB-1 and CB Test Certificate Ref. US-34429-UL respectively which was previously evaluated to UL 62368-1, 2nd Edition, 2014-12-01, CSA C22.2 No. 62368-1-14, 2nd Edition, 2014-12, and IEC 62368-1:2014. Testing conducted in accordance with UL 62368-1, 2nd Edition, 2014-12-01, CSA C22.2 No. 62368-1-14, 2nd Edition, 2014-12, and IEC 62368-1:2014, was deemed equivalent to the test required per UL62368-1, 3rd Ed December 13, 2019; CAN/CSA-C22.2 No. 62368-1, 3rd Ed December 13, 2019; and IEC62368-1:2018, 3rd Ed.

Marking label provided represents all models in series.

Additional Standards

The product fulfills the requirements of: EN IEC 62368-1:2020+A11:2020

Markings and Instructions

Clause Title	Marking or Instruction Details
Equipment identification marking – Manufacturer identification	Listee's or Recognized Company's name, Trade Name, Trademark or File Number
Equipment identification marking – model identification	Model Number

Special Instructions to UL Representative

Units can be fully manufactured in either the Malaysia or Plano, TX location; however, it is also possible that completed units can go back to either factory for rework where a new product label can be applied based on the location that completed the rework.

Issue Date: 2021-12-07 Page 5 of 8 Report Reference # E220248-A6025-UL

Revision Date: 2023-05-23

The Field Inspector should verify that the reworked units came from the original manufacturer (the Factory ID (if any) should be verified). The Field Inspector should verify that the new product label includes all required markings as shown in the Markings and Instructions section.