



TEST REPORT IEC 62368-1

Audio/video, information and communication technology equipment Part 1: Safety requirements

Report Number E220248-A6033-CB-1

Date of issue: 2022-02-07

Total number of pages.....: 59

Name of Testing Laboratory UL RTP

Applicant's name...... TDK-LAMBDA AMERICAS INC

Address 3000 TECHNOLOGY DR, SUITE 100

PLANO TX 75074 UNITED STATES

Test specification:

Standard: IEC 62368-1: 2018

Test procedure...... CB Scheme

Non-standard test method.....: N/A

TRF template used IECEE OD-2020-F1:2020, Ed.1.3

Test Report Form No.....: IEC62368_1E

Test Report Form(s) Originator...: UL(US)

Master TRF...... Dated 2021-02-04

Copyright © 2021 IEC System of Conformity Assessment Schemes for Electrotechnical Equipment and Components (IECEE System). All rights reserved.

This publication may be reproduced in whole or in part for non-commercial purposes as long as the IECEE is acknowledged as copyright owner and source of the material. IECEE takes no responsibility for and will not assume liability for damages resulting from the reader's interpretation of the reproduced material due to its placement and context.

If this Test Report Form is used by non-IECEE members, the IECEE/IEC logo and the reference to the CB Scheme procedure shall be removed.

This report is not valid as a CB Test Report unless signed by an approved CB Testing Laboratory and appended to a CB Test Certificate issued by an NCB in accordance with IECEE 02.

General disclaimer:

The test results presented in this report relate only to the object tested.

This report shall not be reproduced, except in full, without the written approval of the Issuing CB Testing Laboratory. The authenticity of this Test Report and its contents can be verified by contacting the NCB, responsible for this Test Report.

Issue Date: 2022-02-07 Page 2 of 59 Report Reference # E220248-A6033-CB-1

Test Item Description:	Component DC-DC Power S	Supply
Trade Mark(s):	None	
Manufacturer:	TDK-LAMBDA AMERICAS	INC
	3000 Technology Dr, Suite	100
	Plano TX 75074	
	UNITED STATES	
Model/Type reference:	i7Azz***A%%%V-#xx(-R)	
	\\/\bar{\bar{\bar{\bar{\bar{\bar{\bar{	/ OM h
		I or 2W or can be any two alpha resents input voltage between 4.5-
	60Vdc input, 60A max input	current,
	*** represents rated output of	current between 0A - 70A,
	%%% represents rated outp	out voltage between 0.8Vdc – 32Vdc,
		c character and xx indicates a number which do not affect safety related
		I –R indicating RoHS compliance
	,	g
Ratings:	Optional	
	Input: 4.5 - 60 VDC, 60 A M	
	Output: 0.8 - 32 VDC, 70 A	Max
	750 Watts Max	
Responsible Testing Laboratory (as applica	ble), testing procedure and	d testing location(s):
Testing location/ address:	UL RTP, 12 Laboratory D	rive, Research Triangle Park , NC,
	27709, USA	
Total but to and function simulature)	Manaja Taafay / Drajaat	
Tested by (name, function, signature):	Mengis Tesfay / Project Handler	Money Toway
		Modes lates
Approved by (name, function, signature):	Scott Shepler /	8 - 01
	Reviewer	Menys Toufay Scott Shepler
		2.2
☐ Testing procedure: CTF Stage 1:		
Testing location/ address:		
roding roddion address		
Tested by (name, function, signature):		
Approved by (name, function, signature):		
Approved by (name, function, signature)		

Issue Date: 2022-02-07 Page 3 of 59 Report Reference # E220248-A6033-CB-1

\boxtimes	Testing procedure: CTF Stage 2:		
Testing location/ address:		TDK-LAMBDA AMERICAS INC	
		3320 MATRIX DR, SUITE	≣ 100
		RICHARDSON TX 75082	2
		UNITED STATES	
Test	ed by (name, function, signature):	Steve McKitrick / Tester	See original CBTR for signatures
Witr	nessed by (name, function, signature).:	Mengis Tesfay / Project	See original CBTR for signatures
		Handler	
App	roved by (name, function, signature):	Scott Shepler / Reviewer	See original CBTR for signatures
		Reviewei	
	Testing procedure: CTF Stage 3:		
	Testing procedure: CTF Stage 4:		
Test	ing location/ address:		
Test	ed by (name, function, signature):		
Witr	nessed by (name, function, signature).:		
App	roved by (name, function, signature):		
Sup	ervised by (name, function, signature) :		

Issue Date: 2022-02-07 Page 4 of 59 Report Reference # E220248-A6033-CB-1

List of Attachments (including a total number of pages in each attachment):

National Differences (29 pages) Enclosures (35 pages)

Summary of testing:

Tests performed (name of test and test clause):

Testing Location:

CTF Stage 2: TDK-LAMBDA AMERICAS INC 3320 MATRIX DR, SUITE 100 RICHARDSON TX 75082 UNITED STATES

B.2.5 - INPUT TEST: SINGLE PHASE

Testing conducted in accordance with IEC62368-1, 2nd Edition, CAN/CSA-C22.2 NO. 62368-1 2nd Ed, Issued December 1, 2014, and UL 62368-1 2nd Ed, Issued December 1, 2014, was considered representative to the test required per UL62368-1, 3rd Ed December 13, 2019; CAN/CSA-C22.2 No. 62368-1, 3rd Ed December 13, 2019; and IEC62368-1:2018, 3rd Ed. Test was covered under E220248-A6002-CB.

B.1.5, B.2.6, 5.4.1.4, 6.3, 9.3 - NORMAL OPERATING CONDITIONS TEMPERATURE MEASUREMENT

Testing conducted in accordance with IEC62368-1, 2nd Edition, CAN/CSA-C22.2 NO. 62368-1 2nd Ed, Issued December 1, 2014, and UL 62368-1 2nd Ed, Issued December 1, 2014, was considered representative to the test required per UL62368-1, 3rd Ed December 13, 2019; CAN/CSA-C22.2 No. 62368-1, 3rd Ed December 13, 2019; and IEC62368-1:2018, 3rd Ed. Test was covered under E220248-A6002-CB.

B.3 - SIMULATED ABNORMAL OPERATING CONDITIONS

Testing conducted in accordance with IEC62368-1, 2nd Edition, CAN/CSA-C22.2 NO. 62368-1 2nd Ed, Issued December 1, 2014, and UL 62368-1 2nd Ed, Issued December 1, 2014, was considered representative to the test required per UL62368-1, 3rd Ed December 13, 2019; CAN/CSA-C22.2 No. 62368-1, 3rd Ed December 13, 2019; and IEC62368-1:2018, 3rd Ed. Test was covered under E220248-A6002-CB.

B.4 - SIMULATED SINGLE FAULT CONDITIONS

Testing conducted in accordance with IEC62368-1, 2nd Edition, CAN/CSA-C22.2 NO. 62368-1 2nd Ed, Issued December 1, 2014, and UL 62368-1 2nd Ed, Issued December 1, 2014, was considered representative to the test required per UL62368-1, 3rd Ed December 13, 2019; CAN/CSA-C22.2 No. 62368-1, 3rd Ed December 13, 2019; and IEC62368-1:2018, 3rd Ed. Test was covered under E220248-A6002-CB.

ANNEX F.3.10 – TEST FOR THE PERMANENCE OF MARKINGS

Testing conducted in accordance with IEC62368-1, 2nd Edition, CAN/CSA-C22.2 NO. 62368-1 2nd Ed, Issued December 1, 2014, and UL 62368-1 2nd Ed, Issued December 1, 2014, was considered representative to the test required per UL62368-1, 3rd Ed December 13, 2019; CAN/CSA-C22.2 No. 62368-1, 3rd Ed December 13, 2019; and IEC62368-1:2018, 3rd Ed. Test was covered under E220248-A6002-CB.


Issue Date: 2022-02-07 Page 5 of 59 Report Reference # E220248-A6033-CB-1

Summary of compliance with National Differences (List of countries addressed): EU Group and National Differences, USA / Canada		
☐ The product fulfils the requirements of EN IEC 62368-1:2020+A11:2020		
Statement concerning the uncertainty of the measurement systems used for the tests		
☐ Internal procedure used for type testing through which traceability of the measuring uncertainty has been established:		
Procedure number, issue date and title:		
Calculations leading to the reported values are on file with the NCB and testing laboratory that conducted the testing.		
Statement not required by the standard used for type testing		
(Note: When IEC or ISO standard requires a statement concerning the uncertainty of the measurement systems used for tests, this should be reported above. The informative text in parenthesis should be delete in both cases after selecting the applicable option)		

Issue Date: 2022-02-07 Page 6 of 59 Report Reference # E220248-A6033-CB-1

Copy of marking plate:

The artwork below may be only a draft. The use of certification marks on a product must be authorized by the respective NCBs that own these marks.



Note: The above markings are the minimum requirements required by the safety lab. For the final production samples, the additional markings which do not give rise to misunderstanding may be added.

Issue Date: 2022-02-07 Page 7 of 59 Report Reference # E220248-A6033-CB-1

Test item particulars:				
Product group	built-in component			
Classification of use by	Instructed person			
Supply Connection	not mains connected:			
Supply tolerance	None			
Supply connection – type	Not connected to Mains			
Considered current rating of protective device	40 A. External fuse to be provided in the end product. A; Location: equipment			
Equipment mobility	for building-in			
Over voltage category (OVC)	OVC II			
Class of equipment	Not Classified			
Special installation location	N/A 0			
Pollution degree (PD)	PD 2			
Manufacturer's specified Tma (°C)	25°C, per client's provided de-rating curve			
IP protection class	IPX0			
Power systems	not AC mains			
Altitude during operation (m)	2000 m or less			
Altitude of test laboratory (m)	2000 m or less			
Mass of equipment (kg)	0.10			
Possible test case verdicts:				
- test case does not apply to the test object:	N/A			
- test object does meet the requirement:	P (Pass)			
- test object does not meet the requirement:	F (Fail)			
Testing:				
Date of receipt of test item:	2019-05-06, 2021-08-09			
Date (s) of performance of tests:	2019-05-14, 2021-08-09			
General remarks:				
"(See Enclosure #)" refers to additional information appended to the report. "(See appended table)" refers to a table appended to the report. Throughout this report a ☐ comma / ☒ point is used as the decimal separator.				
- · · · · · · · · · · · · · · · · · · ·				
Manufacturer's Declaration per sub-clause 4.2.5 of I	ECEE 02:			

Issue Date: 2022-02-07 Page 8 of 59 Report Reference # E220248-A6033-CB-1

The application for obtaining a CB Test Certificate includes more than one factory location and a declaration from the Manufacturer stating that the sample(s) submitted for evaluation is (are) representative of the products from each factory has been provided	⊠ Yes ☐ Not applicable	
When differences exist; they shall be identified in the General product information section.		
Name and address of factory (ies):	TDK-LAMBDA AMERICAS INC 3000 Technology Dr, Suite 100 Plano TX 75074	
	UNITED STATES	
	TDK-LAMBDA MALAYSIA SDN BHD PLO33 KAWASAN PERINDUSTRIAN SENAI 81400 SENAI JOHOR MALAYSIA	
General product information and other remarks:		
Product Description		
Product Description The i7A product family consists of non-isolated DC-DC power modules intended to be used as a component in an end-user's power system. The modules will be offered in multiple input voltage and output voltage ranges not exceeding ES1 level. The input ranges from 4.5 - 60Vdc input at 60 A max. The output voltage will be adjustable between 0.8V to 32Vdc.		
Model Differences		
All models within the series are similar except for input rating, output rating, and size of inductor.		
Additional Information		
This report is based on CB report references E220248-A6002-CB-1, and Amendment 1, with CB Test Certificate Ref. US-33723-UL, and US-33723-M1-UL respectively, which was previously evaluated to UL 62368-1, 2nd Edition, 2014-12-01, CSA C22.2 No. 62368-1- 14, 2nd Edition, 2014-12, and IEC 62368-1:2014.		
Testing conducted in accordance with UL 62368-1, 2nd Edition, 2014-12-01, CSA C22.2 No. 62368-1-14, 2nd Edition, 2014-12, and IEC 62368-1:2014, was deemed equivalent to the test required per UL62368-1, 3rd Ed December 13, 2019; CAN/CSA-C22.2 No. 62368-1, 3rd Ed December 13, 2019; and IEC62368-1:2018, 3rd Ed.		

All original sample and test dates are noted in the testing portion of this report.

The nameplate included in the report is representative of all models covered under this report.

Technical Considerations

Issue Date: 2022-02-07 Page 9 of 59 Report Reference # E220248-A6033-CB-1

- The product was submitted and evaluated for use at the maximum ambient temperature (Tma) permitted by the manufacturer's specification of : 25°C. See derating curve for more details
- The product is intended for use on the following power systems: No direct connection
- Considered current rating of protective device as part of the building installation (A): External fast blow 40 A fuse to be provided in the end product.
- Mains supply tolerance (%) or absolute mains supply : No direct connection
- The equipment disconnect device is considered to be : For building in
- The following are available from the Applicant upon request: Installation (Safety) Instructions / Manual
- The product was investigated to the following additional standard: EN IEC 62368-1:2020+A11:2020

Engineering Conditions of Acceptability

When installed in an end-product, consideration must be given to the following:

- The following output circuits are at ES1 energy levels : All
- The following output circuits are at PS3 energy levels : All
- The investigated Pollution Degree is: 2
- An investigation of the protective bonding terminals has : Not been conducted
- The following end-product enclosures are required: Fire
- The maximum continuous power supply output (Watts) relied on forced air cooling from : Ranging from
 5.2 to 70 CFM depending on ambient, and load. See Derating Curve
- The power supply was evaluated to be used at altitudes up to : "2,000 m"
- Test was conducted using fast blow external fuse rated 40 A. External fuse employed shall comply with IEC 60127.
- Heating Test need to re-conducted as part of an end product evaluation to ensure the max temperature of 130 C is not exceeded.