



Ref. Certif. No.

JP-20624-M2-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

DC-DC Converters

Name and address of the applicant

TDK-LAMBDA CORP
NAGAOKA TECHNICAL CENTER R&D DIV
2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA 940-1195
JAPAN

Name and address of the manufacturer

TDK-LAMBDA CORP
NAGAOKA TECHNICAL CENTER R&D DIV
2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA 940-1195
JAPAN

Name and address of the factory

TDK-LAMBDA CORP
2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA-KEN
940-1195
JAPAN


Note: When more than one factory, please report on page 2

Additional Information on page 2

Ratings and principal characteristics

- 1) Input: 20-36Vdc, 43A, Output: 12Vdc, 50A
- 2) Input: 19-36Vdc, 43A, Output: 28Vdc, 21.5A
- 3) Input: 36-76Vdc, 21A, Output: 12Vdc, 50A
- 4) Input: 36-76Vdc, 21A, Output: 28Vdc, 21.5A

Trademark / Brand (if any)



Type of Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

See Page 2

Additional information (if necessary may also be reported on page 2)

(Technical Modification)
Additionally evaluated to EN 62368-1:2014/ A11:2017.
National Differences specified in the CB Test Report.

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

E122103-A6055-CB-1 issued on 2020-07-21

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2020-07-22

Signature:

Original Issue Date: 2019-01-16

Masamichi Takagi



Ref. Certif. No.

JP-20624-M2-UL

Model Details:

- 1) PAF600F24-12
- 2) PAF600F24-28
- 3) PAF600F48-12
- 4) PAF600F48-28

Models may be followed by optional suffix denoting minor variations which are not related to safety aspects : "/" and any alphanumeric characters.

Factories:

TDK-LAMBDA MALAYSIA SDN BHD
PLO33 KAWASAN PERINDUSTRIAN SENAI 81400 SENAI JOHOR
MALAYSIA

TDK-LAMBDA (CHINA) ELECTRONICS CO LTD
NO.95,ZHUJIANG RD, XINWU DISTRICT WUXI JIANGSU 214028
CHINA

TDK-LAMBDA MALAYSIA SDN BHD
LOT 2 & 3, BATU 9 3/4 KAWASAN PERINDUSTRIAN BANDAR BARU JAYA GADING 26070 KUANTAN PAHANG
MALAYSIA

ZHANGJIAGANG HUA YANG ELECTRONICS CO LTD
NO.15 TONGXIN RD, ZHAOFENG ECONOMIC DEVELOPMENT ZONE, LEYU TOWN ZHANGJIAGANG JIANGSU
215622
CHINA

Additional Information:

The original report was modified to include the following changes/additions:

- Addition of alternate Opto coupler (PC1, PC2), Toshiba Electronic Devices & Storage Corporation, Type TLP291.

Additional information (if necessary)



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/names

Date: 2020-07-22
Original Issue Date: 2019-01-16

Signature:
Masamichi Takagi