

DEMKO CERTIFICATE

Certificate No. D-07470-A1
Page 1/3
Date of Issue 2020-06-22

Certificate Holder TDK-LAMBDA CORP
NAGAOKA TECHNICAL CENTER R&D DIV 2704-1 SETTAYA-
MACHI NAGAOKA-SHI NIIGATA 940-1195 JAPAN

Manufacturer TDK-LAMBDA CORP
NAGAOKA TECHNICAL CENTER R&D DIV 2704-1 SETTAYA-
MACHI NAGAOKA-SHI NIIGATA 940-1195 JAPAN

Production site TDK-LAMBDA CORP
2704-1 SETTAYA-MACHI NAGAOKA-SHI NIIGATA-KEN 940-1195
JAPAN

See Page 2

Certified Product Model DC-DC Converter
PAH300S24-12, PAH300S24-28, PAH350S24-28, PAH350S24-48
See Page 2

Trademark

TDK-Lambda

Rated Voltage / Frequency

See Page 2

Rated Current / Power

See Page 2

Insulation Class

Class I

Degree of protection (IP)

IP is not classified (for building-in)

Tested acc. to

EN 62368-1:2014/A11:2017, EN 62368-1:2014

Test Report No.

E122103-A6082-CB-1 issued on 2020-06-16

Additional

for building-in

The report was revised to include administrative modifications

Expire date

2029-08-29

Certification Manager
Jan-Erik Storgaard

This is to certify that representative sample(s) of the Product described herein ("Certified Product") have been investigated and found in compliance with the Standard(s) indicated on this Certificate, in accordance with the D-Mark Requirements. As specified in the respective appendix below the Designated Certificate holder is entitled to use the D-Mark, or its alternative for cables, for the Certified Product manufactured at the production site(s) identified above, in accordance with the D-Mark Service Agreement, including without limitation the D-Mark Testing and Certification Services Service Terms. Only those Products bearing the D-Mark should be considered as being covered by UL's D-Mark Service. This Certificate shall remain valid through the expiration date, unless terminated earlier in accordance with the Service Agreement including without limitation if the Standard identified on this Certificate is amended or withdrawn prior the expiration date.

Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65,
info.dk@ul.com
www.UL.com



Appendix DEMKO CERTIFICATE

Certificate No. D-07470-A1
Page 2/3
Date of Issue 2020-06-22

Model Details:

PAH300S24-12, PAH300S24-28, PAH350S24-28, PAH350S24-48 (Models may be followed by optional suffix denoting minor variations which are not related to safety aspects : "/" and any alphanumeric characters.)

Production Sites:

TDK-LAMBDA MALAYSIA SDN BHD
PLO33 KAWASAN PERINDUSTRIAN SENAI 81400 SENAI JOHOR
MALAYSIA

TDK-LAMBDA (CHINA) ELECTRONICS CO LTD
NO.95,ZHUJIANG RD, XINWU DISTRICT WUXI JIANGSU 214028
CHINA

Ratings:

Input:

18-36 Vdc, 22 A (for Model PAH300S24) and 30 A (for Model PAH350S24)

Output:

12 Vdc, 25 A, 300 W (for Model PAH300S24-12)
28 Vdc, 11 A, 308 W (for Model PAH300S24-28)
28 Vdc, 12.5 A, 350 W (for Model PAH350S24-28)
48 Vdc, 7.3 A, 350.4 W (for Model PAH350S24-48)

Additional Information:

This certificate replaces the certificate No. D-07470, issued on 2019-08-30 due to:

- Change address of one factory.
- Change of one factory.

Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65, info.dk@ul.com
www.UL.com



Appendix DEMKO CERTIFICATE

Certificate No. D-07470-A1
Page 3/3
Date of Issue 2020-06-22

Certification Mark D-Mark

The D-Mark, as displayed below, shall appear on certified products only. Minimum size is not specified, as long as the Mark is legible.



The size of the Mark may be reduced or enlarged on the condition that it remains readable and that the proportions of width and height are kept. The use of dark text for the D-Mark on light backgrounds and light text on dark backgrounds is permitted.

When putting the product on the EU market, the manufacturer's name, trademark or mark of origin must be affixed in a clearly visible location and position on the product, on the package and in the user manual. It can be affixed by label, be directly imprinted, or cast or molded into the product.

Alternate certification Mark for cables

As an alternative to the D-Mark specified above the alternate D-Mark, displayed below, can appear on certified cables only. Minimum size is not specified, as long as the mark is legible.

◁DEMKO▷

The alternate D-Mark may be cast, stamped or moulded into the cable and continue throughout the length of the cable as specified in the applicable cable standard.

All content shall be in accordance with the details provided on this D-Mark Certificate.

Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65, info.dk@ul.com
www.UL.com

