



Test Report issued under the responsibility of:



TEST REPORT

IEC 62368-1

Audio/video, information and communication technology equipment Part 1: Safety requirements

Report Number: E220248-A6036-CB-1

Date of issue: 2024-10-18

Total number of pages: 53

Name of Testing Laboratory
preparing the Report: UL Solutions RTP

Applicant's name: TDK-LAMBDA AMERICAS INC
Address: 3000 TECHNOLOGY DR, SUITE 100
PLANO TX 75074
UNITED STATES

Test specification:

Standard: IEC 62368-1:2014

Test procedure: CB Scheme

Non-standard test method: N/A

TRF template used: IECEE OD-2020-F1:2021, Ed.1.4

Test Report Form No.: IEC62368_1D

Test Report Form(s) Originator: UL(US)

Master TRF: Dated 2022-04-14

Copyright © 2022 IEC System of Conformity Assessment Schemes for Electrotechnical Equipment and Components (IECEE System). All rights reserved.

This publication may be reproduced in whole or in part for non-commercial purposes as long as the IECEE is acknowledged as copyright owner and source of the material. IECEE takes no responsibility for and will not assume liability for damages resulting from the reader's interpretation of the reproduced material due to its placement and context.


If this Test Report Form is used by non-IECEE members, the IECEE/IEC logo and the reference to the CB Scheme procedure shall be removed.



This report is not valid as a CB Test Report unless signed by an approved CB Testing Laboratory and appended to a CB Test Certificate issued by an NCB in accordance with IECEE 02.

General disclaimer:

The test results presented in this report relate only to the object tested.

This report shall not be reproduced, except in full, without the written approval of the Issuing CB Testing Laboratory. The authenticity of this Test Report and its contents can be verified by contacting the NCB, responsible for this Test Report.

Test Item description	DC-To-DC Converters
Trade Mark(s)	TDK, TDK-Lambda 
Manufacturer	TDK-LAMBDA AMERICAS INC 3000 Technology Dr, Suite 100 Plano TX 75074 UNITED STATES
Model/Type reference	<p>i9Czz***A%%%V-xxx(-R)</p> <p>Where "zz" may be 4W or 2W OR can be any two alphanumeric characters that represents input voltage between 9 to 80 VDC, 60 A max current</p> <p>Where "****" may be rated output current up to max 30 A.</p> <p>Where "%%%%" represent rated output voltage between 9.5 to 60 VDC</p> <p>and 'xxx" indicates a number of alphanumeric characters for non safety features.</p> <p>Optional "-R" may be to denote RoHS compliance</p>
Ratings	Not required. Optional.
Responsible Testing Laboratory (as applicable), testing procedure and testing location(s):	
<input checked="" type="checkbox"/> CB Testing Laboratory:	
Testing location/ address	UL Solutions RTP 12 Laboratory Drive, Research Triangle Park , NC, 27709, USA
Tested by (name, function, signature).....:	Mengis Tesfay / Project Handler 
Approved by (name, function, signature).....:	Gregory A. Ray / Reviewer 
<input type="checkbox"/> Testing procedure: CTF Stage 1:	
Testing location/ address.....:	
Tested by (name, function, signature).....:	
Approved by (name, function, signature).....:	
<input checked="" type="checkbox"/> Testing procedure: CTF Stage 2:	
Testing location/ address.....:	TDK-LAMBDA AMERICAS INC 3000 Technology Dr. Suite 100 Plano, TX 75074

		USA
Tested by (name, function, signature)		Ketan Patel / Tester 
Witnessed by (name, function, signature) ...:		Mengis Tesfay / Project Handler 
Approved by (name, function, signature).....:		Gregory A. Ray / Reviewer 
<input type="checkbox"/>	Testing procedure: CTF Stage 3:	
<input type="checkbox"/>	Testing procedure: CTF Stage 4:	
Testing location/ address.....:		
Tested by (name, function, signature)		
Witnessed by (name, function, signature) ...:		
Approved by (name, function, signature).....:		
Supervised by (name, function, signature) ...:		

List of Attachments (including a total number of pages in each attachment):

National Differences (31 pages)

Enclosures (41 pages)

Summary of testing:

Tests performed (name of test and test clause): B.2.5 – INPUT TEST: SINGLE PHASE B.2.6, 5.4.1.4, 6.3, 9.2, B.1.6 – NORMAL OPERATING CONDITIONS TEMPERATURE MEASUREMENT B.3 – SIMULATED ABNORMAL OPERATING CONDITIONS B.4 – SIMULATED SINGLE FAULT CONDITIONS	Testing Location: Unless otherwise noted, test are all conducted in CBTL: UL Solutions RTP 12 Laboratory Drive, Research Triangle Park , NC, 27709, USA
Tests performed (name of test and test clause): B.2.5 – INPUT TEST: SINGLE PHASE B.2.6, 5.4.1.4, 6.3, 9.2, B.1.6 – NORMAL OPERATING CONDITIONS TEMPERATURE MEASUREMENT B.3 – SIMULATED ABNORMAL OPERATING CONDITIONS B.4 – SIMULATED SINGLE FAULT CONDITIONS	Testing Location: CTF Stage 2: TDK-LAMBDA AMERICAS INC 3000 Technology Dr. Suite 100 Plano, TX 75074 USA

Summary of compliance with National Differences:

List of countries addressed: Australia - AU, New Zealand - NZ, EU Group Differences, Japan - JP, United States of America - US, Canada - CA

The product fulfils the requirements of: AS/NZS 62368.1:2018,
EN 62368-1:2014+A11:2017,
J62368-1 (2020),
CSA/UL 62368-1:2014

Use of uncertainty of measurement for decisions on conformity (decision rule) :

No decision rule is specified by the IEC standard, when comparing the measurement result with the applicable limit according to the specification in that standard. The decisions on conformity are made without applying the measurement uncertainty ("simple acceptance" decision rule, previously known as "accuracy method").

Other:.... (to be specified, for example when required by the standard or client, or if national accreditation requirements apply)

Information on uncertainty of measurement:

The uncertainties of measurement are calculated by the laboratory based on application of criteria given by OD-5014 for test equipment and application of test methods, decision sheets and operational procedures of IECEE. IEC Guide 115 provides guidance on the application of measurement uncertainty principles and applying the decision rule when reporting test results within IECEE scheme, noting that the reporting of the measurement uncertainty for measurements is not necessary unless required by the test standard or customer.

Calculations leading to the reported values are on file with the NCB and testing laboratory that conducted the testing.

Copy of marking plate:

The artwork below may be only a draft. The use of certification marks on a product must be authorized by the respective NCBs that own these marks.



Note: The above markings are the minimum requirements required by the safety lab. For the final production samples, the additional markings which do not give rise to misunderstanding may be added.

TEST ITEM PARTICULARS:	
Classification of use by	Instructed person
Supply Connection	External Circuit - not Mains connected ES2
Supply % Tolerance	None
Supply Connection – Type	No direct connection to Mains. Considered in the end-product
Considered current rating of protective device as part of building or equipment installation	60 A; equipment
Equipment mobility	for building-in
Over voltage category (OVC)	OVC I
Class of equipment	Not classified
Access location	N/A
Pollution degree (PD)	PD 2
Manufacturer's specified maximum operating ambient (°C)	125 C at base plate
IP protection class	IPX0
Power Systems	N/A
Altitude during operation (m)	2000 m or less
Altitude of test laboratory (m)	2000 m or less
Mass of equipment (kg)	0.08
POSSIBLE TEST CASE VERDICTS:	
- test case does not apply to the test object.....	N/A
- test object does meet the requirement	P (Pass)
- test object does not meet the requirement	F (Fail)
TESTING:	
Date of receipt of test item.....	2024-07-15
Date (s) of performance of tests	2024-09-25 to 2024-10-04
GENERAL REMARKS:	
<p>"(See Enclosure #)" refers to additional information appended to the report. "(See appended table)" refers to a table appended to the report.</p>	
<p>Throughout this report a <input type="checkbox"/> comma / <input checked="" type="checkbox"/> point is used as the decimal separator.</p>	
Manufacturer's Declaration per sub-clause 4.2.5 of IECEE 02:	

The application for obtaining a CB Test Certificate includes more than one factory location and a declaration from the Manufacturer stating that the sample(s) submitted for evaluation is (are) representative of the products from each factory has been provided :	<input checked="" type="checkbox"/> Yes <input type="checkbox"/> Not applicable
When differences exist; they shall be identified in the General product information section.	
Name and address of factory (ies) :	TDK-LAMBDA AMERICAS INC 3000 Technology Dr, Suite 100 Plano TX 75074 UNITED STATES TDK-LAMBDA MALAYSIA SDN BHD PLO33 KAWASAN PERINDUSTRIAN SENAI 81400 SENAI Johor MALAYSIA
GENERAL PRODUCT INFORMATION:	
Report Summary All applicable tests according to the referenced standard(s) have been carried out.	
Product Description The i9C product family consists of non-isolated DC-DC power modules intended to be used as a component in an end-user's power system. The modules will be offered in multiple input voltage and output voltage ranges. The input ranges from 9 - 80Vdc input at 60 A max. The output voltage will be adjustable between 9.5V to 60V. The rated output power will be 1500W or less.	
Model Differences All models within the series are similar except for input rating, output rating, and size of inductor.	
Additional application considerations – (Considerations used to test a component or sub-assembly) - All original sample and test dates are noted in the testing portion of this report.	
The nameplate included in the report is representative of all models covered under this report.	
Technical Considerations <ul style="list-style-type: none"> The product was submitted and evaluated for use at the maximum ambient temperature (Tma) permitted by the manufacturer's specification of : 125°C at faceplate The product is intended for use on the following power systems : No direct connection Considered current rating of protective device as part of the building installation (A) : N/A. For building in. Mains supply tolerance (%) or absolute mains supply values : No direct connection The equipment disconnect device is considered to be : N/A The following are available from the Applicant upon request : Installation (Safety) Instructions / Manual The product was investigated to the following additional standards : EN 62368-1:2014 + A11:2017 	

Engineering Conditions of Acceptability

When installed in an end-product, consideration must be given to the following:

- The following output circuits are at ES2 energy levels : All
- The following output circuits are at PS3 energy levels : Output Terminal
- The investigated Pollution Degree is : 2
- An investigation of the protective bonding terminals has : not been conducted
- The following end-product enclosures are required : Electrical, Fire
- The units provide Functional Insulation only between input and output circuits.
- Tests conducted in wind tunnel with 900 Ifm (550CFM). Heating Test shall be evaluated in end product. The following components require special consideration during end-product Thermal (Heating) tests.
- This component has been evaluated in 'control of fire spread' method assuming appropriate fire enclosure is provided in end product. Unless the fire enclosure is made of non-combustible or V-0 material, the separation from the PIS shall be considered
- Classification of PIS has not been conducted. Therefore, all electrical components and conductors including printed wirings were assumed to be arcing/resistive PIS.
- Power to the DC-DC Converter is intended to be supplied by isolated secondary circuitry in an end use application.
- Output voltage may be adjusted for up the maximum fixed output power (i.e. maximum output current is decreased). When the output voltage is adjusted down, the maximum output current is fixed (i.e. available output power is decreased).
- ES Classification of EUT is to be verified during end product. Declared ES2, but the converter is non-isolating and it is to be used by Instructed or Skilled person.

ENERGY SOURCE IDENTIFICATION AND CLASSIFICATION TABLE:

(Note 1: Identify the following six (6) energy source forms based on the origin of the energy.)

(Note 2: The identified classification e.g., ES2, TS1, should be with respect to its ability to cause pain or injury on the body or its ability to ignite a combustible material. Any energy source can be declared Class 3 as a worse case classification e.g. PS3, ES3.)

Electrically-caused injury (Clause 5):

(Note: Identify type of source, list sub-assembly or circuit designation and corresponding energy source classification)

Example: +5 V dc input

ES1

Source of electrical energy	Corresponding classification (ES)
All circuits (Input, Internal Output circuits)	ES2

Electrically-caused fire (Clause 6):

(Note: List sub-assembly or circuit designation and corresponding energy source classification)

Example: Battery pack (maximum 85 watts):

PS2

Source of power or PIS	Corresponding classification (PS)
All circuits (Input, Internal Output circuits)	PS3, Arcing PIS, Resistive PIS

Injury caused by hazardous substances (Clause 7)

(Note: Specify hazardous chemicals, whether produces ozone or other chemical construction not addressed as part of the component evaluation.)

Example: Liquid in filled component

Glycol

Source of hazardous substances	Corresponding chemical
N/A	-

Mechanically-caused injury (Clause 8)

(Note: List moving part(s), fan, special installations, etc. & corresponding MS classification based on Table 35.)

Example: Wall mount unit

MS2

Source of kinetic/mechanical energy	Corresponding classification (MS)
N/A	-

Thermal burn injury (Clause 9)

(Note: Identify the surface or support, and corresponding energy source classification based on type of part, location, operating temperature and contact time in Table 38.)

Example: Hand-held scanner – thermoplastic enclosure

TS1

Source of thermal energy	Corresponding classification (TS)
PWB and Components	TS3 (EUT is for building in. Enclosure to be provided in end product.)

Radiation (Clause 10)

(Note: List the types of radiation present in the product and the corresponding energy source classification.)

Example: DVD – Class 1 Laser Product

RS1

Type of radiation	Corresponding classification (RS)
N/A	-

ENERGY SOURCE DIAGRAM

Indicate which energy sources are included in the energy source diagram. Insert diagram below

ES **PS** **MS** **TS** **RS**

See ENERGY SOURCE IDENTIFICATION AND CLASSIFICATION TABLE