

US-34799-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)

CB TEST CERTIFICATE

Product DC-To-DC Converters

Name and address of the applicant TDK-LAMBDA AMERICAS INC

> SUITE 100 3320 MATRIX DR **RICHARDSON TX 75082 UNITED STATES**

Name and address of the manufacturer TDK-LAMBDA AMERICAS INC

> SUITE 100 3320 MATRIX DR **RICHARDSON TX 75082 UNITED STATES**

Name and address of the factory TDK-LAMBDA AMERICAS INC

SUITE 100 Note: When more than one factory, please report on page 2 3320 MATRIX DR

RICHARDSON TX 75082 UNITED STATES

Additional Information on page 2

Ratings and principal characteristics See Page 2

TDK or TDK-Lambda Trademark / Brand (if any)

ATOK TDK-Lambda

Type of Customer's Testing Facility (CTF) Stage used CTF Stage 2

Model / Type Ref. iEH48***A%%%V-xxx, iEH4N***A%%%V-xxx

See Page 2

Additional information (if necessary may also be Additionally evaluated to EN 62368-1:2014 / A11:2017;

reported on page 2) National Differences specified in the CB Test Report. Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part

of this Certificate

E220248-A6011-CB-1 issued on 2019-11-20

This CB Test Certificate is issued by the National Certification Body



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2019-11-20 Signature:

Jolanta M. Wroblewska



US-34799-UL

Model Details:

iEH Series:

Model: iEH48***A%%%V-xxx or iEH4N***A%%%V-xxx where

*** represents rated output current between 20A - 40A, (Note that the first digit is always "0");

%%% represents rated output voltage between 9.6V - 12V (Note that the third digit is preceded by a decimal point.

Example 120 implies 12.0 Volts.) and

xxx represents any alphanumeric characters denoting non-safety related features.

It may also be followed by optional '-R' to denote RoHS compliance.

Examples:

iEH48025A120V-xxx(-R), iEH48020A120V-xxx(-R), iEH4N028A108V-xxx(-R), iEH4N033A096V-xxx(-R),

iEH4N031A096V-xxx(-R), iEH4N040A120V-xxx(-R), iEH4N042A108V-xxx(-R)

where xxx represents any alphanumeric characters denoting non-safety related features

Factories:

TDK-LAMBDA MALAYSIA SDN BHD PLO33 KAWASAN PERINDUSTRIAN SENAI 81400 SENAI JOHOR MALAYSIA

Ratings: Optional:

Input DC 36 -75 VDC, 10.5 max

Output 9.6 - 12.0 VDC max, 42 A max, 480 W max

See model list

iEH48025A120V-xxx(-R) Input: 36-75Vdc, 9A

Output: 12Vdc, 25A, 300W max

iEH48028A108V-xxx(-R) Input: 36-75Vdc, 9A

Output: 10.8Vdc, 28A, 300W max

iEH48020A120V-xxx(-R) Input: 36-75Vdc, 7.5A

Output: 12Vdc, 20A, 240W max

iEH4N028A108V-xxx(-R) Input: 51-55Vdc, 6.5A

Output: 10.8Vdc, 28A, 302W max

iEH4N033A096V-xxx(-R) Input: 38-55Vdc, 8.5A

Output: 9.6Vdc, 33.3A, 320W max

iEH4N031A096V-xxx(-R) Input: 38-55Vdc, 8A

Output: 9.6Vdc, 31.3A, 300W max

iEH4N040A120V-xxx(-R) Input: 49-56Vdc, 10.5A Output: 12Vdc, 40A, 480W IEH4N042A108V-xxx(-R) Input: 49-56Vdc, 9.8A Output: 10.8Vdc, 42A, 454W

Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

Jolaska Ja Wie

For full legal entity names see www.ul.com/ncbnames

Date: 2019-11-20

Signature:

Jolanta M. Wroblewska