## CCG3-48-xxDxC

C297-01-01/C-A

## SPECIFICATIONS (1/2)

MODEL				CCG3-48-12DxC	CCG3-48-15DxC
INPU					
	Input Voltage Range VDC		18 - 76		
	Efficiency (Typ)	(*1)	%	83	83
	Input Current (Typ)	(*1)	Α	0.078	0.075
OUT	PUT	. ,	l l		
	Nominal Output Voltage		VDC	±12	±15
	Output Voltage Accuracy	(*1)	%	±:	2
	Maximum Output Current		Α	0.13	0.1
	Maximum Output Power		W	3.12	3
	Maximum Line Regulation	(*2)	mV	60	75
	Maximum Load Regulation	(*3)	mV	120	150
	Maximum Load Regulation	(*10)	mV	480	600
	Temperature Coefficient		-	0.029	%/°C
	Maximum Ripple & Noise	(*4)	mV	200	200
	Output Voltage Range		-	Fix	red
	Over Current Protection	(*5)	-	105% min.	
	Over Voltage Protection		-	No	ne
FUN	CTION				
	Remote ON/OFF Control	(*6)	Possible		ible
	Remote Sensing			No	ne
	Parallel Operation - Series Operation (*6) -		None		
			Possible		
ENV	TRONMENT				
	Operating Temperature	(*7)	-	-40°C	+100°C
	Storage Temperature55°C - +125°C  Operating Humidity - 5 - 95%RH (Non Condensing)		-55°C	-55°C - +125°C	
			on Condensing)		
	Storage Humidity		-	5 - 95%RH (Non Condensing)	
	Vibration	(*8)	-	At No Operating, 10 - 55Hz (Sweep for 1min.)  Amplitude 1.65 mm Constant (Maximum 98m/s²), X,Y,Z 1 hour each	
	Shock	(*8)	-	490.3	3m/s <sup>2</sup>
	Cooling		-	Convection Cooling /	Forced Air Cooling
ISOLATION					
	Withstand Voltage	(*9)	-	Input - Output : 1.5kVDC (20mA)	1min. or 1.0kVAC (20mA) 1min.
	Isolation Resistance		-	More than $100M\Omega$ at $25^{\circ}C$ and $7$	70%RH, Input - Output 500VDC
STA	NDARD AND COMPLIANCE				
Safety -		Approved by IEC/EN/UL/CSA62368-1 (Altitude ≤ 5,000m)			
MECHANICAL					
	Weight (Typ.)		g	3	3
	Size (W x H x D)		mm	DIP: 15.7 x 11.5 x 10.4 / SMD: 15.7 x	11.8 x 10.4 (Refer to Outline Drawing)
OTHERS					
	Coating	ating (*11) - Coating on both sides of PCB			

C297-01-01/C-A

## SPECIFICATIONS (2/2)

*Read Instruction Manual carefully, before using the power supply unit.
=NOTES=
*1. At 48VDC input voltage and maximum output current. (Ambient Temperature = +25°C.)
*2. 18 - 76VDC input voltage, constant load.
*3. No Load - Full Load, constant input voltage. (Balanced load)
*4. External components are needed for operation. (Refer to Instruction Manual.)
*5. OCP TYPE : Hiccup, Automatic recovery.
*6. Refer to Instruction Manual.
*7. Rating - Refer to Derating Curve in Instruction Manual.
*8. The result is evaluated by TDK-Lambda standard measurement conditions.
The final equipment should be evaluated to meet its requirements.  *9. This specification applies to power supply module as stand-alone.
*10. One side fixed Full Load, the other side 20% - Full Load, Constant input voltage. (Asymmetrical load)
*11. This product is with coating on both sides of PCB that is objective to improve resistance against humidity and dust.
The coating is not to prevent moisture absorption and dust ingress completely
since there is non coating area such as the shadowed part of component.