

UL TEST REPORT AND PROCEDURE

Standard:	UL 60950-1, 1st Edition, 2007-10-31 (Information Technology Equipment - Safety - Part 1: General Requirements) CSA C22.2 No. 60950-1-03, 1st Edition, 2006-07 (Information Technology Equipment - Safety - Part 1: General Requirements)
Certification Type:	Component Recognition
CCN:	QQGQ2, QQGQ8 (Power Supplies for Information Technology Equipment Including Electrical Business Equipment)
Product:	Power Supply DC-DC
Model:	iQE4W***A%%V-0##(-R), iQE4W***A%%V-1##(-R). where *** represents a three digit current less than or equal to 35 A. Values will be expressed in 1A increments. where %% represents a three digit voltage less than or equal to 20 V. Values will be expressed in 100mV increments, followed by ##, where 0## or 1## is a three digit alphanumeric indicating a mechanical or control function modification. The 1 in 1## indicates option for baseplate.
Rating:	The total maximum output power is less than or equal to 120W iQE4W***A%%V-0##(-R), iQE4W***A%%V-1## (-R) Input - 18-75 VDC, 20A Output: 1.2 - 20 VDC, 35 - 1A, Max 120 Watts
Applicant Name and Address:	TDK INNOVETA INC SUITE 100 3320 MATRIX DR RICHARDSON TX 75082 UNITED STATES

This is to certify that representative samples of the products covered by this Test Report have been investigated in accordance with the above referenced Standards. The products have been found to comply with the requirements covering the category and the products are judged to be eligible for Follow-Up Service under the indicated Test Procedure. The manufacturer is authorized to use the UL Mark on such products which comply with this Test Report and any other applicable requirements of UL LLC ('UL') in accordance with the Follow-Up Service Agreement. Only those products which properly bear the UL Mark are considered as being covered by UL's Follow-Up Service under the indicated Test Procedure.

The applicant is authorized to reproduce the referenced Test Report provided it is reproduced in its entirety.

Issue Date: 2007-06-15
2012-01-25

Page 2 of 7

Report Reference #

E220248-A17-UL

UL authorizes the applicant to reproduce the latest pages of the referenced Test Report consisting of the first page of the Specific Technical Criteria through to the end of the Conditions of Acceptability.

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL.

Prepared by: Can Nguyen

Reviewed by: Rick Duran

Supporting Documentation

The following documents located at the beginning of this Procedure supplement the requirements of this Test Report:

- A. Authorization - The Authorization page may include additional Factory Identification Code markings.
- B. Generic Inspection Instructions -
 - i. Part AC details important information which may be applicable to products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of this Test Report.
 - ii. Part AE details any requirements which may be applicable to all products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of each Test Report.
 - iii. Part AF details the requirements for the UL Certification Mark which is not controlled by the technical standard used to investigate these products. Products are permitted to bear only the Certification Mark(s) corresponding to the countries for which it is certified, as indicated in each Test Report.

Product Description

The product is a component type DC/DC converter power module with a planar type power transformer. The converter is provided with input terminal pins for factory installation onto a printed wiring board with a connection to a dc source of supply and output terminal pins.

Model Differences

Models covered within this series are identical except for output electrical rating and optional baseplate.

Technical Considerations

- Equipment mobility : for building-in
- Operating condition : continuous
- Mains supply tolerance (%) : No direct connection
- Tested for IT power systems : No
- IT testing, phase-phase voltage (V) : N/A
- Class of equipment : Special Application - TNV-2
- Mass of equipment (kg) : < 18
- Protection against ingress of water : IP X0
- The product was submitted and evaluated for use at the maximum ambient temperature (T_{ma}) permitted by the manufacturer's specification of: 25°C

- The power supply wiring means are meant for building in.

Engineering Conditions of Acceptability

For use only in or with complete equipment where the acceptability of the combination is determined by UL LLC. When installed in an end-product, consideration must be given to the following:

- The power supply terminals and/or connectors are: Suitable for factory wiring only
- The investigated Pollution Degree is: 2
- The following end-product enclosures are required: Mechanical , Fire , Electrical , ,
- The following components require special consideration during end-product Thermal (Heating) tests due to the indicated maximum temperature measurements during component-level testing: T101 Winding, Transformer (T101) winding trace is integrated within the PWB, rated 130 C. ,
-

Testing on similar Models is conducted with a Listed 20A fuse on the input. If a higher rated fuse is used, additional testing such as Output Short Circuit and Component Faults shall be repeated.

-

The power supply is intended to be supplied by isolated secondary circuitry in an end-use appliance.

-

For the output to be considered SELV, the input must be from a source that is isolated from the mains (utility) by reinforced insulation.

Additional Information

- These models have been evaluated as having Basic insulation from input to output.
- The product employs a planar transformer and a multilayer PWB.
- The products may optionally provide a suffix [R] which indicates a non-safety related function.

This report was revise to add suffix "-1##" which indicates option for baseplate.

Additional Standards

The product fulfills the requirements of: -

Markings and instructions

Clause Title	Marking or Instruction Details
Power rating - Ratings	Ratings (voltage, frequency/dc, current)
Power rating - Company identification	Listee's or Recognized company's name, Trade Name, Trademark or File Number

Power rating - Model	Model Number
Special Instructions to UL Representative	
N/A	

Production-Line Testing Requirements

Electric Strength Test Special Constructions - Refer to Generic Inspection Instructions, Part AC for further information.

Model	Component	Removable Parts	Test probe location	V rms	V dc	Test Time, s
N/A						

Earthing Continuity Test Exemptions - This test is not required for the following models:

Electric Strength Test Exemptions - This test is not required for the following models:

--

Electric Strength Test Component Exemptions - The following solid-state components may be disconnected from the remainder of the circuitry during the performance of this test:

--

Sample and Test Specifics for Follow-Up Tests at UL

Model	Component	Material	Test	Sample(s)	Test Specifics
N/A					