CCG1R5-24-xxSxC

C287-01-01/C-A

SPECIFICATIONS (1/2)

MODEL			GGG1P5 24 029 G	GGG1P5 24 050 G	GGG1P5 24 126 G	GGG1P5 24 150 G	
ITEMS			CCG1R5-24-03SxC	CCG1R5-24-05SxC	CCG1R5-24-12SxC	CCG1R5-24-15SxC	
INPUT							
Input Voltage Range VDC		9 - 36					
Efficiency (Typ)	(*1)	%	73	78	82	82	
Input Current (Typ)	(*1)	A	0.075	0.080	0.079	0.076	
OUTPUT							
Nominal Output Voltage		VDC	3.3	5	12	15	
Output Voltage Accuracy	(*1)	%	±2				
Maximum Output Current		Α	0.4	0.3	0.13	0.1	
Maximum Output Power		W	1.32	1.5	1.56	1.5	
Maximum Line Regulation	(*2)	mV	20	20	48	60	
Maximum Load Regulation	(*3)	mV	20	20	48	60	
Temperature Coefficient		-	0.02%/°C				
Maximum Ripple & Noise	(*4)	mV	200	200	200	200	
Output Voltage Range	(*4)	VDC	3.135 - 3.63	4.75 - 5.5	11.4 - 13.2	14.25 - 16.5	
Over Current Protection	(*5)	-	105% min.				
Over Voltage Protection	Over Voltage Protection -			None			
FUNCTION							
Remote ON/OFF Control	(*6)	-	Possible				
Remote Sensing		-	None				
Parallel Operation		-		No	ne		
Series Operation	(*6)	-	Possible				
ENVIRONMENT							
Operating Temperature	(*7)	-		-40°C -	+100°C		
Storage Temperature		-	-55°C - +125°C				
Operating Humidity		-	5 - 95%RH (Non Condensing)				
Storage Humidity		-	5 - 95%RH (Non Condensing)				
Vibration	(*8)	-	At No Operating, 10 - 55Hz (Sweep for 1min.)				
	Amplitude 1.65 mm Constant (Maximum 98m/s ²), X,Y,Z		,Z 1 hour each				
Shock	(*8)	-	490.3m/s ²				
Cooling		-	Convection Cooling / Forced Air Cooling				
ISOLATION							
Withstand Voltage	(*9)	-	Input - Output: 1.5kVDC (20mA) 1min. or 1.0kVAC (20mA) 1min.				
Isolation Resistance		-	More than $100 \text{M}\Omega$ at 25°C and $70\%\text{RH}$, Input - Output 500VDC				
STANDARD AND COMPLIAN	CE						
Safety		-	Approved by IEC/EN/UL/CSA62368-1 (Altitude ≤ 5,000m)				
MECHANICAL							
Weight (Typ.)		g	3				
Size (W x H x D) mm			DIP: 15.7 x 11.5 x 10.4 / SMD: 15.7 x 11.8 x 10.4 (Refer to Outline Drawing)				
OTHERS							
Coating	Coating (*10) - Coating on both sides of PCB						

C287-01-01/C-A

SPECIFICATIONS (2/2)

*Dard Lateration Monard annihilla Information the name annulus site
*Read Instruction Manual carefully, before using the power supply unit.
=NOTES=
*1. At 24VDC input voltage and maximum output current. (Ambient Temperature = +25°C.)
*2. 9 - 36VDC input voltage, constant load. *3. No Load - Full Load, constant input voltage.
*4. External components are needed for operation. (Refer to Instruction Manual.)
*5. OCP TYPE : Hiccup, Automatic recovery.
*6. Refer to Instruction Manual.
*7. Rating - Refer to Output Derating Curve in Instruction Manual.
*8. The result is evaluated by TDK-Lambda standard measurement conditions. The final equipment should be evaluated to meet its requirements.
*9. This specification applies to power supply module as stand-alone.
*10. This product is with coating on both sides of PCB that is objective to improve resistance against humidity and dust.
The coating is not to prevent moisture absorption and dust ingress completely
since there is non coating area such as the shadowed part of component.