CCG1R5-48-xxDxC

C291-01-01/C-A

SPECIFICATIONS (1/2)

MODEL			CCG1R5-48-12DxC	CCG1R5-48-15DxC
INPUT				
Input Voltage Range		VDC	18 -	76
Efficiency (Typ)	(*1)	%	78	76
Input Current (Typ)	(*1)	Α	0.042	0.041
OUTPUT				
Nominal Output Voltage		VDC	±12	±15
Output Voltage Accuracy	(*1)	%	±.	2
Maximum Output Current		A	0.065	0.05
Maximum Output Power		W	1.56	1.5
Maximum Line Regulation	(*2)	mV	60	75
Maximum Load Regulation	(*3)	mV	120	150
Maximum Load Regulation	(*10)	mV	480	600
Temperature Coefficient		-	0.029	%/°C
Maximum Ripple & Noise	(*4)	mV	200	200
Output Voltage Range		-	Fix	ed
Over Current Protection	(*5)	-	105%	min.
Over Voltage Protection		-	No	ne
FUNCTION				
Remote ON/OFF Control	(*6)	-	Poss	ible
Remote Sensing		-	No	ne
Parallel Operation		-	No	ne
Series Operation	(*6)	-	Poss	ible
ENVIRONMENT				
Operating Temperature	(*7)	-	-40°C	+100°C
Storage Temperature		-	-55°C	+125°C
Operating Humidity		-	5 - 95%RH (No	on Condensing)
Storage Humidity		-	5 - 95%RH (No	on Condensing)
Vibration	(*8)	-	At No Operating, 10 - 5	5Hz (Sweep for 1min.)
			Amplitude 1.65 mm Constant (Max	
Shock	(*8)	-	490.3	sm/s ²
Cooling		-	Convection Cooling /	Forced Air Cooling
ISOLATION				
Withstand Voltage	(*9)	-	Input - Output : 1.5kVDC (20mA)	
Isolation Resistance		-	More than 100MΩ at 25°C and 7	0%RH, Input - Output 500VDC
STANDARD AND COMPLIANCE				
Safety		_	Approved by IEC/EN/UL/CSA	A62368-1 (Altitude \leq 5,000m)
MECHANICAL				
Weight (Typ.)		g	3	
Size (W x H x D)		mm	DIP: 15.7 x 11.5 x 10.4 / SMD: 15.7 x	11.8 x 10.4 (Refer to Outline Drawing)
OTHERS				-
Coating	(*11)	-	Coating on both	h sides of PCB

C291-01-01/C-A SPECIFICATIONS (2/2)
*Read Instruction Manual carefully, before using the power supply unit.
=NOTES=
*1. At 48VDC input voltage and maximum output current. (Ambient Temperature = +25°C.) *2. 18 - 76VDC input voltage, constant load.
*3. No Load - Full Load, constant input voltage. (Balanced load)
*4. External components are needed for operation. (Refer to Instruction Manual.) *5. OCP TYPE: Hiccup, Automatic recovery.
*6. Refer to Instruction Manual.
*7. Rating - Refer to Derating Curve in Instruction Manual.
*8. The result is evaluated by TDK-Lambda standard measurement conditions. The final equipment should be evaluated to meet its requirements.
*9. This specification applies to power supply module as stand-alone.
*10. One side fixed Full Load, the other side 20% - Full Load, Constant input voltage. (Asymmetrical load)
*11. This product is with coating on both sides of PCB that is objective to improve resistance against humidity and dust.
The coating is not to prevent moisture absorption and dust ingress completely since there is non coating area such as the shadowed part of component.
since there is non-counting their distinct smaller may be component.