

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT  
(IECEE) CB SCHEME

## CB TEST CERTIFICATE

Product	Programmable AC/DC and AC/AC power supply
Name and address of the applicant	TDK-Lambda Ltd. 56 Haharoshet St., P.O.B. 500 Karmiel Industrial Zone, 2161401 Karmiel, Israel
Name and address of the manufacturer	TDK-Lambda Ltd. 56 Haharoshet St., P.O.B. 500 Karmiel Industrial Zone, 2161401 Karmiel, Israel
Name and address of the factory	TDK-Lambda Ltd. 56 Haharoshet St., P.O.B. 500 Karmiel Industrial Zone, 2161401 Karmiel, Israel
Ratings and principal characteristics	Input ratings:100-240 Va.c., 16 A, 50/60Hz for 1-phase 208Vac models with 2kVA output; 100-240 Va.c., 22.5 A, 50/60Hz for 1-phase 208Vac models models with 3kVA output; additional ratings see page 2.
Trademark (if any)	TDK-Lambda, TDK·Lambda
Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	GAC-xyzuw-mmoppq;GAC-xyzuw-mmoppq/aaaaaa; GAC-PRO-xyzuw-mmoppq;GAC-PRO-xyzuw-mmoppq/aaaaaa x=0-9;y=A-Z;z=A-Z;u=0-9;w=A-Z;m=0-9;o=A-Z;p=0-9;q=A-Z; a=A-Z, or 0-9, or BLANK.
Additional information (if necessary may also be reported on page 2)	
A sample of the product was tested and found to be in conformity with	IEC 61010-1:2010+A1 See Test Report for National Differences
As shown in the Test Report Ref. No. which forms part of this Certificate	CN231DTM 001

This CB Test Certificate is issued by the National Certification Body



TÜVRheinland®

TÜV Rheinland Japan Ltd.  
Global Technology Assessment Center  
4-25-2 Kita-Yamata, Tsuzuki-ku  
Yokohama 224-0021, Japan  
Phone + 81 45 914-3888  
Fax + 81 45 914-3354  
Mail: info@jpn.tuv.com  
Web : www.tuv.com

Date: 2024-06-03

Signature:

Miao Mai

## Input ratings:

190-240 Va.c., 8.6 A, 50/60Hz for 3-phase 208Vac models with 2kVA output;  
190-240 Va.c., 12.5 A, 50/60Hz for 3-phase 208Vac models with 3kVA output;  
380-480 Va.c., 4.5 A, 50/60Hz for 3-phase 480Vac models with 2kVA output;  
380-480 Va.c., 6.5 A, 50/60Hz for 3-phase 480Vac models with 3kVA output;

## Output ratings:

AC 0-350 V, 20 A, for 2kVA output (GAC-02 series)  
AC 0-350 V, 30 A, for 3kVA output (GAC-03 series)  
AC 0-350 V or DC -500 to +500 V, 20 A for 2kVA output (GAC-PRO-02 series)  
AC 0-350 V or DC -500 to +500 V, 30 A for 3kVA output (GAC-PRO-03 series)