

CCGS15-48-xxD/DIN

SPECIFICATIONS

C318-01-01/DIN-A

ITEMS		MODEL	CCGS15-48-12D/DIN	CCGS15-48-15D/DIN
INPUT				
Input Voltage Range (DC)		V	18-76	
Efficiency (Typ.)		(*1) %	87	89
Input Current (Typ.)		(*1) A	0.37	0.35
OUTPUT				
Nominal Output Voltage(DC)		V	+/-12	+/-15
Output Voltage Initial Set Accuracy		(*1) -	11.39 - 12.60	14.24 - 15.75
Maximum Output Current		A	0.65	0.5
Maximum Output Power		W	15.6	15
Maximum Line Regulation		(*2) mV	60	75
Maximum Load Regulation	(*3) Balanced load	mV	120	150
	(*7) Asymmetrical load	mV	480	600
Temperature Coefficient		-	Less than 0.02% / °C	
Maximum Ripple & Noise	0≤Ta<70°C	mV	130	130
	(*4) -20≤Ta<0°C	mV	180	180
PROTECTIVE FUNCTION				
Over Current Protection		(*5) -	105% minimum	
Over Voltage Protection		-	None	
FUNCTION				
Remote ON/OFF Control		(*4) -	Possible	
Remote Sensing		-	None	
Parallel Operation		-	None	
Series Operation		(*4) -	Possible	
ENVIRONMENT				
Operating Temperature		(*6) -	-20 to +70°C	
Storage Temperature		-	-30 to +85°C	
Operating Humidity		-	20 to 95%RH (Non Condensing)	
Storage Humidity		-	10 to 95%RH (Non Condensing)	
Vibration		-	At no operating, 10 - 55Hz (Sweep for 3min) 19.6m/s ² Constant, X,Y,Z 1hour each.	
Shock		-	Less than 196.1m/s ²	
Cooling		-	Convection Cooling	
ISOLATION				
Withstand Voltage		-	Input - FG : 1.5kVDC (10mA), Input - Output : 1.5kVDC (10mA), Output - FG : 1.0kVDC (10mA) for 1min	
Isolation Resistance		-	More than 100MΩ at 25°C and 70%RH Output - FG : 500VDC	
STANDARD AND COMPLIANCE				
Safety		-	Approved by IEC/EN/UL/CSA 62368-1 (Altitude ≤ 5,000m)	
MECHANICAL				
Weight (Typ.)		g	115	
Size (W x H x D)		mm	52.0 x 31.9 x 93.0	

*Read instruction manual carefully, before using the power supply unit.

=NOTES=

*1. At 48VDC input voltage and maximum output current. (Ambient Temperature = +25°C.)

*2. 18 - 76VDC input voltage, constant load.

*3. No-Load - Full Load, constant input voltage. (Balanced load)

*4. Refer to Instruction Manual.

*5. OCP TYPE : Hiccup, Automatic recovery.

*6. Rating - Refer to Output Derating Curve in Instruction Manual.

*7. One side fixed Full Load, the other side 20% - Full Load, Constant input voltage. (Asymmetrical load)