



Ref. Certif. No.

JPTUV-132384

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Programmable AC/DC power supply

Name and address of the applicant

TDK-Lambda Ltd.
56 Haharoshet St., P.O.B. 500
Karmiel Industrial Zone, 2161401 Karmiel, Israel

Name and address of the manufacturer

TDK-Lambda Ltd.
56 Haharoshet St., P.O.B. 500
Karmiel Industrial Zone, 2161401 Karmiel, Israel

Name and address of the factory

TDK-Lambda Ltd.
56 Haharoshet St., P.O.B. 500
Karmiel Industrial Zone, 2161401 Karmiel, Israel

Ratings and principal characteristics

Ratings for input: Option 1: AC 190-240 V; 47-63 Hz; 3 W+PE.
1a), 1b): Rated input current: 27.8 A max.
2a), 2b): Rated input current: 18.5 A max. Class I
For other ratings, refer to the test report.

Trademark (if any)

TDK-Lambda

Customer's Testing Facility (CTF) Stage used

CTF Stage 3

Model / Type Ref.

GENESYS+ 7500W series: 1a) Gxxxx-yyy-z-v/uuuuuu/w or
Gxxxx-yyy-z-v-uuuuuu/w; 1b) GBxxxx-yyy-z-v/uuuuuu/w or
GBxxxx-yyy-z-v-uuuuuu/w
GENESYS+ 5000W series: 2a) G1000-5-z-v/uuuuuu/w or
G1000-5-z-v-uuuuuu/w , Additional models see Page 2

Additional information (if necessary may also be reported on page 2)

For model differences, refer to the test report.

A sample of the product was tested and found to be in conformity with

IEC 61010-1:2010+A1
See Test Report for National Differences

As shown in the Test Report Ref. No. which forms part of this Certificate

CN224X04 001

This CB Test Certificate is issued by the National Certification Body



TÜV Rheinland Japan Ltd.
Global Technology Assessment Center
4-25-2 Kita-Yamata, Tsuzuki-ku
Yokohama 224-0021, Japan
Phone + 81 45 914-3888
Fax + 81 45 914-3354
Mail: info@jpn.tuv.com
Web : www.tuv.com

Date: 2022-03-24

Signature:

Miao Mai

1. TDK-Lambda Ltd.
56 Haharoshet St., P.O.B. 500
Karmiel Industrial Zone
2161401 Karmiel
Israel

Additional information (if necessary)

Report Ref. No. : CN224X04 001

Additional models:

2b) GB1000-5-z-v/uuuuuu/w or GB1000-5-z-v-uuuuuu/w

3a) G1500-3.4-z-v/uuuuuu/w or G1500-3.4-z-v-uuuuuu/w

3b) GB1500-3.4-z-v/uuuuuu/w or GB1500-3.4-z-v-uuuuuu/w

xxxx=020 - 1500; yyy=005 - 375; z=GPIB (IEEE),MDBS,ECAT,
IS420,IS010 or Blank; v=3P200 or 3P480;

uuuuuu=Various letters and/or numbers or Blank;

w=CO or Blank



Date: 2022-03-24

Signature:

Miao Mai