

PSS6-5-*

SPECIFICATIONS


C188-01-01C

ITEMS		MODEL	PSS6-5-3R3	PSS6-5-5	PSS6-5-12
1	Nominal Output Voltage	V	3.3	5	12 (15)
2	Maximum Output Current	A	1.2	1	0.5 (0.4)
3	Maximum Output Power	W	3.96	5.0	6.0
4	Efficiency (Typ.)	(*1) %	72	78	80
5	Input Voltage Range	-		4.5 ~ 9.0VDC	
6	Input Current (Typ.)	(*1) A	1.13	1.29	1.5
7	Output Voltage Accuracy	(*1) %		±5	
8	Output Voltage Range (Typ.)	V	2.84 ~ 3.67	4.3 ~ 6.0	12 ~ 15
9	Maximum Ripple & Noise	(*2) mV	100	100	120
10	Maximum Line Regulation	(*3) mV		20	
11	Maximum Load Regulation	(*4) mV		40	
12	Over Current Protection	(*5)	-	Yes	
13	Over Voltage Protection	-		No	
14	Parallel Operation	-		-	
15	Remote ON/OFF Control	-		Yes	
16	Series Operation	-		Possible	
17	Operating Temperature	(*6)	-	-40°C ~ 85°C	
18	Operating Humidity	-		5% - 95%RH (No Dewdrop)	
19	Storage Temperature	-		-40°C ~ 85°C	
20	Storage Humidity	-		5% - 95%RH (No Dewdrop)	
21	Cooling	-		Convection Cooling / Forced air cooling	
22	Temperature Coefficient (%)	-		Less than 0.02%/ $^{\circ}$ C	
23	Withstand Voltage	-		Input-Output, Input-Case : 500VAC for 1min (20mA)	
24	Isolation Resistance	-		More than 100M Ω at 25°C and 70%RH Output-Case : 500VDC	
25	Vibration	-		At No Operating, 10-55Hz Amplitude (Sweep for 1min.) 1.52mm Constant (Maximum 88.3m/s ²) X,Y,Z 2 hour each	
26	Shock	-		196.1m/s ²	
27	Weight (Typ.)	g		8	
28	Size (WxHxD)	mm		28.5 x 8.0 x 20.5 (Refer to Outline Drawing)	


= NOTES =

- *1. At 5VDC and maximum output power and Ta=+25°C.
- *2. This is specified at the output terminals by JEITA RC-9141 measuring method.
- *3. From 4.5 ~ 9.0VDC, constant load.
- *4. From No load - Full load, constant input voltage.
- *5. Constant current limiting with automatic recovery.
Avoid to operate over load or dead short for longer than 30 sec.
(Refer to instruction manual for details.)
- *6. Rating - Refer to derating curve (C188-01-02__).
- Load(%) is percent of maximum output current.

1. DERATING CURVE



2. BASIC CONNECTION



==NOTES==

- *1. Put input capacitors.
 $C_1: 470\mu F$
- *2. Put output capacitors.
 $C_2: 1\mu F$ ceramic capacitor.
- *3. Refer to instruction manual for further details.