

HFE2500-S1U SERIES RACK SPECIFICATIONS

			Rev.	
1	Number of power supply modules	(*1) (*7) ---	Maximum 4 units HFE2500 of the same output voltage rating.	E
2	Maximum output power	W	Refer to HFE2500 specifications	B
3	Maximum output current	---	320A per output (Total 640A)	D
4	Input voltage / frequency range	(*2) ---	85~265Vac continuous, 47~63Hz, Single phase, separate input for each PS module.	
5	Maximum input current (at 115/230Vac)	A	15/12 for each HFE2500 power supply module	
6	Maximum line regulation	(*4) %	Less than 0.25 of rated output voltage	E
7	Maximum load regulation	(*5) %	Less than 0.8 of rated output voltage	E
8	AC input connector	(*6) ---	Separate for each power supply. HFE2500-S1U: IEC inlet, (C20); HFE2500-S1U/TB: Terminal Block.	E
9	Output terminals	---	Two bus-bars outputs for each output terminal (two sides). Refer to outline drawing.	E
10	Remote sensing	(*3) V	Possible. Refer to Instruction Manual.	
11	Parallel operation	---	Possible. Refer to Instruction Manual.	
12	Series operation	---	Possible. Refer to Instruction Manual.	
13	Remote On/Off control (INHIBIT)	---	Separate control for each PS unit, by electrical signal or dry contact. "OFF": 0~0.6V or short. "ON": 2~15V or open.	
14	Remote On/Off control (ENABLE)	---	Common for all PS units, by electrical signal or dry contact. "ON": 0~0.6V or short. "OFF": 2~15V or open.	
15	DC OK signal	---	Separate signal for each PS unit, open collector signal. Maximum sink current: 10mA, Max 15V Tracking output setting, "LOW" when $V_{out} > 90 \pm 5\%$ of output voltage setting	E
16	AC fail signal	---	Separate signal for each PS unit, open collector signal. Maximum sink current: 10mA, Max 15V "LOW" when input voltage $85Vac < V_{in} < 270Vac$.	E
17	Over Temperature alarm signal	---	Separate signal for each PS unit, open collector signal. Maximum sink current: 10mA, Max 15V Refer to Instruction Manual	E
18	Output voltage trimming	---	Common for all PS units, by built-in potentiometer. Refer to Instruction Manual.	
19	Output voltage programming	---	Possible, Common for all PS units, by 0~5V signal. Refer to Instruction Manual.	
20	Output voltage programming via I ² C interface	---	Possible, Common for all PS units. Refer to Instruction Manual.	
21	OCP programming by external voltage	---	Possible, Common for all PS units, by 0~5V signal. Refer to Instruction Manual.	
22	OCP programming via I ² C interface	---	Possible, Common for all PS units. Refer to Instruction Manual.	
23	Auxiliary power supply	---	11.2~12.5VDC. Maximum output current: 0.5A	A
24	Operating temperature	---	-10~50°C: 100% load. +50°C to +60°C: Derate 2%/°C of load +60°C to +70°C: Derate 2.5%/°C of load	E
25	Storage temperature	---	-30~85°C	
26	Operating humidity	---	10~90% RH, no condensation.	
27	Storage humidity	---	10~95% RH, no condensation.	
28	Vibration	---	Built to meet IEC60068-2-64 (Basic Transportation)	
29	Shock	---	Built to meet IEC60068-2-27 (Basic Transportation)	B
30	Applicable safety standards	---	IEC 62368-1 UL62368-1 CSA22.2 No.62368-1 EN62368-1.	F
31	Withstand voltage	Input-Output:	3000Vrms, 1min.	
		Input-Ground:	2000Vrms, 1min.	
		Output-Ground:	12, 24V models - 500Vrms, 1min 48V model - 2250VDC, 1min.	
32	Isolation resistance	---	More than 100Mohm at 25°C and 70% RH. Output-Ground: 500Vdc	F
33	Weight (Typ) (with accessories)	kg	5.0	
34	Size (W*H*D)	---	445x43.6x401mm. Refer to Outline Drawing.	

Notes:

- *1 Mixing of PMBus option units ("HFE2500-xx/S") and standard units ("HFE2500-xx") is not allowed.
- *2 For cases where conformance to various safety standards (UL, EN etc.) is required, Input Voltage to be described as 100-240Vac (50/60Hz).
- *3 Maximum voltage drop on load wires: HFE2500-12: 0.25V/wire, HFE2500-24: 0.5V/wire, HFE2500-48: 1V/wire.
- *4 From 85~132Vac or 170~265Vac, constant load.
- *5 From No-load to Rated load, constant input voltage. Measured at the sensing point in Remote sense.
- *6 Use UL approved Insulated terminal lugs
- *7 The output of all HFE2500 modules are connected in parallel in the Rack

E
E

DRAWING NO:	IA706-01-01F	
DRAW:	<i>Stano</i>	<i>SK</i>
ENGR:	<i>Ashie-sh</i>	<i>9/11/2020</i>
CHECK:	<i>Boris K.</i>	<i>10/11/2020</i>
APPR:	<i>J</i>	<i>11/11/20</i>