

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST
CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

SYSTEME CEI D'ACCEPTATION MUTUELLE DE
CERTIFICATS D'ESSAIS DES EQUIPEMENTS
ELECTRIQUES (IECEE) METHODE OC

CB TEST CERTIFICATE**CERTIFICAT D'ESSAI OC**

Product
Produit

Name and address of the applicant
Nom et adresse du demandeur

Name and address of the manufacturer
Nom et adresse du fabricant

Name and address of the factory
Nom et adresse de l'usine

Note: When more than one factory, please report on page 2
Note: Lorsque il y plus d'une usine, veuillez utiliser la 2^{ème} page

Ratings and principal characteristics
Valeurs nominales et caractéristiques principales

Trademark (if any)
Marque de fabrique (si elle existe)

Type of Manufacturer's Testing Laboratories used
Type de programme du laboratoire d'essais
constructeur

Model / Type Ref.
Ref. De type

Additional information (if necessary may also be
reported on page 2)
Les informations complémentaires (si nécessaire,,
peuvent être indiqués sur la 2^{ème} page

A sample of the product was tested and found
to be in conformity with
Un échantillon de ce produit a été essayé et a été
considéré conforme à la

As shown in the Test Report Ref. No. which forms
part of this Certificate
Comme indiqué dans le Rapport d'essais numéro de
référence qui constitue partie de ce Certificat

Power Supply


TDK-LAMBDA AMERICAS INC
405 ESSEX RD
TINTON FALLS NJ 07753-7701 USA

TDK-LAMBDA AMERICAS INC
405 ESSEX RD
TINTON FALLS NJ 07753-7701 USA

TDK-LAMBDA AMERICAS INC
405 ESSEX RD TINTON FALLS NJ 07753-7701
USA

Additional Information on page 2

See Page 2



GEN AAA-BBBB-KKK-Z, QS AAA-BBBB-KKK-Z
See Page 2

Additionally evaluated to EN 60950-1: 2006 / A11: 2009 / A1:
2010 / A12: 2011 / A2:2013; National Differences specified in
the CB Test Report.

Additional Information on page 2

IEC 60950-1(ed.2), IEC 60950-1(ed.2);am1,
IEC 60950-1(ed.2);am2

E113160-A5-CB-8 issued on 2016-06-22

This CB Test Certificate is issued by the National Certification Body

Ce Certificat d'essai OC est établi par l'Organisme **National de Certification**



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2016-06-23

Signature:

Jolanta M. Wroblewska

Model Details:

GEN AAA-BBBB-KKK-Z, QS AAA-BBBB-KKK-Z,

Where:

AAA is the output voltage ranging from 0 to 600V. (additionally marked with 00530XXXX or 00531XXXX number)

-BBBB is the output current ranging from 0 to 1000A depending on voltage.

-KKK represents other non-safety related options. See General Product Information - Additional Information.

-Z represents the 3 phase input voltage.

See General Product Information in Report - Additional Information for additional suffixes that indicate special options/markings.

Ratings:

Input Ratings:

Models GEN AAA-BBBB-KKK-Z, QS AAA-BBBB-KKK-Z:

208Vac, 45A, 50-60Hz (For 7.5kW and 10kW Units);

208Vac, 58A, 50-60Hz (For 15kW Units);

400Vac, 24A, 50-60Hz (For 7.5kW and 10kW Units);

400Vac, 32A, 50-60Hz (For 15kW Units);

480Vac, 20A, 50-60Hz (For 7.5kW and 10kW Units);

480Vac, 28A, 50-60Hz (For 15kW Units).

Additional information (if necessary)**Information complémentaire (si nécessaire)**

UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA



UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK



UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN




UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2016-06-23

Signature:



Jolanta M. Wroblewska