

**ROHS COMPLIANCE**


CONTROLLED COPY  
08.06.12  
N.L.I. R&D

15A 250V OPEN CORD SET  $\triangle 1$

1. UNSHIELDED, 3 CONDUCTORS
2. RATING MIN.: 15A, 250V
3. POWER CORD LENGTH: 2m TYP.
4. JACKET COLOR: BLACK.
5. TEMPERATURE RATING MIN.: 75°C.  $\triangle 8$
6. COMPONENTS DESCRIPTION:

- $\triangle 2$  1. CABLE:
  - TYPE: HARMONIZED, H05RR-F, H05RN-F OR H05VV-F;  $\triangle 5$   $\triangle 9$
  - CONDUCTORS CROSS-SECTION AREA MIN.: 14AWG;  $\triangle 6$
  - RATED MIN.: 15A, 250V;
  - SAFETY MARKING: <HAR>, CERTIFICATION AGENCY MARK(S), CE MARK.
- $\triangle 3$  2. CONNECTOR:
  - IEC 60320-1 CERTIFIED TYPE C19;  $\triangle 11$
  - RATED MIN.: 15A, 250V;
  - SAFETY MARKING: CERTIFICATION AGENCY MARK(S),  $\triangle 10$

$\triangle 7$



NOTE:  
ROHS COMPLIANCE  
REFER TO D-L GROUP  
GREEN PROCUREMENT  
GUIDELINE : DL-EMS-010\_

D	$\triangle 8 \sim \triangle 11$	REV. B5	29.APR.2012			
C	$\triangle 5 \sim \triangle 7$	REV. B3	28.FEB.2012			
B	$\triangle 1 \sim \triangle 4$	REV. B2	26.JAN.2012			
A	NEW DRAWING		17.JAN.2012			
D	CONTENTS		DATE	ENGR	CHK	APPD

DWG	S.MIKI	29.11.2012	SHEET OF	
ENGR	S.MIKI	29.11.2012	1	1
CHK		29.11.2012	SCALE	NONE
APPD	Kotani S.	Apr. 29. 12	UNITS	mm
ISSUED				75°C

MATERIALS	TITLE	15A 250V OPEN CORD SET
FINISH	DRAWING No.	$\triangle 1$ IA706-81-11 - $\square D$
<b>TDK-Lambda</b>		