


Multilayer Ceramic Chip Capacitors

Feb. 27, 2026
Simple Model

Commercial Grade High Temperature Application / C1608 series (1/4)

Circuit Diagram



Circuit Parameters


Part No.	C1[pF]	L1[nH]	R1[ohm]	R2[Gohm]
C1608NP01H010C080AA	1	0.420	0.9827	10.0
C1608NP01H020C080AA	2	0.420	0.9188	10.0
C1608NP01H030C080AA	3	0.420	0.7233	10.0
C1608NP01H040C080AA	4	0.420	0.5992	10.0
C1608NP01H050C080AA	5	0.420	0.3921	10.0
C1608NP01H060D080AA	6	0.420	0.3985	10.0
C1608NP01H070D080AA	7	0.420	0.4918	10.0
C1608NP01H080D080AA	8	0.420	0.3141	10.0
C1608NP01H090D080AA	9	0.420	0.4633	10.0
C1608NP01H100D080AA	10	0.420	0.3084	10.0
C1608NP01H150J080AA	15	0.420	0.3727	10.0
C1608NP01H220J080AA	22	0.420	0.2911	10.0
C1608NP01H330J080AA	33	0.420	0.2471	10.0
C1608NP01H470J080AA	47	0.420	0.2173	10.0
C1608NP01H680J080AA	68	0.420	0.1473	10.0
C1608NP01H101J080AA	100	0.420	0.1402	10.0
C1608NP01H151J080AA	150	0.420	0.0807	10.0
C1608NP01H221J080AA	220	0.420	0.0681	10.0
C1608NP01H331J080AA	330	0.420	0.0770	10.0
C1608NP01H471J080AA	470	0.420	0.0560	10.0
C1608NP01H681J080AA	680	0.420	0.0473	10.0
C1608NP01H102J080AA	1,000	0.420	0.0396	10.0
C1608NP01H122J080AA	1,200	0.420	0.0366	10.0
C1608NP01H152J080AA	1,500	0.420	0.0284	10.0
C1608NP01H182J080AA	1,800	0.420	0.0256	10.0
C1608NP01H222J080AA	2,200	0.420	0.0310	10.0
C1608NP01H272J080AA	2,700	0.420	0.0249	10.0
C1608NP01H332J080AA	3,300	0.420	0.0218	10.0
C1608NP01H392J080AA	3,900	0.420	0.0233	10.0
C1608NP01H472J080AA	4,700	0.420	0.0255	10.0
C1608NP01H562J080AA	5,600	0.420	0.0263	10.0
C1608NP01H682J080AA	6,800	0.420	0.0173	10.0
C1608NP01H822J080AA	8,200	0.420	0.0237	10.0
C1608NP01H103J080AA	10,000	0.420	0.0160	10.0
C1608NP02A010C080AA	1	0.420	1.1407	10.0
C1608NP02A020C080AA	2	0.420	1.0049	10.0

Multilayer Ceramic Chip Capacitors

Feb. 27, 2026
Simple Model

Commercial Grade High Temperature Application / C1608 series (2/4)

Circuit Diagram



Circuit Parameters


Part No.	C1[pF]	L1[nH]	R1[ohm]	R2[Gohm]
C1608NP02A030C080AA	3	0.420	0.8279	10.0
C1608NP02A040C080AA	4	0.420	0.6683	10.0
C1608NP02A050C080AA	5	0.420	0.4904	10.0
C1608NP02A060D080AA	6	0.420	0.4810	10.0
C1608NP02A070D080AA	7	0.420	0.4387	10.0
C1608NP02A080D080AA	8	0.420	0.3963	10.0
C1608NP02A090D080AA	9	0.420	0.3734	10.0
C1608NP02A100D080AA	10	0.420	0.3177	10.0
C1608NP02A150J080AA	15	0.420	0.3337	10.0
C1608NP02A220J080AA	22	0.420	0.2911	10.0
C1608NP02A330J080AA	33	0.420	0.2683	10.0
C1608NP02A470J080AA	47	0.420	0.3899	10.0
C1608NP02A680J080AA	68	0.420	0.1176	10.0
C1608NP02A101J080AA	100	0.420	0.0919	10.0
C1608NP02A151J080AA	150	0.420	0.0779	10.0
C1608NP02A221J080AA	220	0.420	0.0552	10.0
C1608NP02A331J080AA	330	0.420	0.0659	10.0
C1608NP02A471J080AA	470	0.420	0.0607	10.0
C1608NP02A681J080AA	680	0.420	0.0463	10.0
C1608NP02A102J080AA	1,000	0.420	0.0369	10.0
C1608NP02A122J080AA	1,200	0.420	0.0290	10.0
C1608NP02A152J080AA	1,500	0.420	0.0284	10.0
C1608NP02A182J080AA	1,800	0.420	0.0288	10.0
C1608NP02A222J080AA	2,200	0.420	0.0214	10.0
C1608NP02A272J080AA	2,700	0.420	0.0220	10.0
C1608NP02A332J080AA	3,300	0.420	0.0209	10.0
C1608NP02E102J080AA	1,000	0.420	0.0653	10.0
C1608NP02E122J080AA	1,200	0.420	0.0627	10.0
C1608NP02E152J080AA	1,500	0.420	0.0591	10.0
C1608NP02E182J080AA	1,800	0.420	0.0460	10.0
C1608NP02E222J080AA	2,200	0.420	0.0422	10.0
C1608X8L0J155K080AC	1,500,000	0.420	0.0058	0.0660
C1608X8L0J225K080AC	2,200,000	0.420	0.0037	0.0450
C1608X8L1C684K080AC	680,000	0.420	0.0102	0.147
C1608X8L1C105K080AC	1,000,000	0.420	0.0083	0.100
C1608X8R1C334K080AB	330,000	0.420	0.0139	0.303

Multilayer Ceramic Chip Capacitors

Feb. 27, 2026
Simple Model

Commercial Grade High Temperature Application / C1608 series (3/4)

Circuit Diagram



Circuit Parameters


Part No.	C1[pF]	L1[nH]	R1[ohm]	R2[Gohm]
C1608X8R1C334M080AB	330,000	0.420	0.0139	0.303
C1608X8R1C474K080AB	470,000	0.420	0.0103	0.212
C1608X8R1C474M080AB	470,000	0.420	0.0103	0.212
C1608X8R1E683K080AA	68,000	0.420	0.0180	7.35
C1608X8R1E683M080AA	68,000	0.420	0.0180	7.35
C1608X8R1E104K080AA	100,000	0.420	0.0130	5.00
C1608X8R1E104M080AA	100,000	0.420	0.0130	5.00
C1608X8R1E154K080AB	150,000	0.420	0.0169	3.33
C1608X8R1E154M080AB	150,000	0.420	0.0169	3.33
C1608X8R1E224K080AB	220,000	0.420	0.0282	2.27
C1608X8R1E224M080AB	220,000	0.420	0.0282	2.27
C1608X8R1E334K080AC	330,000	0.420	0.0139	1.52
C1608X8R1E334M080AC	330,000	0.420	0.0139	1.52
C1608X8R1H102K080AA	1,000	0.420	0.1886	10.0
C1608X8R1H102M080AA	1,000	0.420	0.1886	10.0
C1608X8R1H152K080AA	1,500	0.420	0.1868	10.0
C1608X8R1H152M080AA	1,500	0.420	0.1868	10.0
C1608X8R1H222K080AA	2,200	0.420	0.1359	10.0
C1608X8R1H222M080AA	2,200	0.420	0.1359	10.0
C1608X8R1H332K080AA	3,300	0.420	0.0945	10.0
C1608X8R1H332M080AA	3,300	0.420	0.0945	10.0
C1608X8R1H472K080AA	4,700	0.420	0.0969	10.0
C1608X8R1H472M080AA	4,700	0.420	0.0969	10.0
C1608X8R1H682K080AA	6,800	0.420	0.0681	10.0
C1608X8R1H682M080AA	6,800	0.420	0.0681	10.0
C1608X8R1H103K080AA	10,000	0.420	0.0509	10.0
C1608X8R1H103M080AA	10,000	0.420	0.0509	10.0
C1608X8R1H153K080AA	15,000	0.420	0.0378	10.0
C1608X8R1H153M080AA	15,000	0.420	0.0378	10.0
C1608X8R1H223K080AA	22,000	0.420	0.0396	10.0
C1608X8R1H223M080AA	22,000	0.420	0.0396	10.0
C1608X8R1H333K080AA	33,000	0.420	0.0298	10.0
C1608X8R1H333M080AA	33,000	0.420	0.0298	10.0
C1608X8R1H473K080AA	47,000	0.420	0.0195	10.0
C1608X8R1H473M080AA	47,000	0.420	0.0195	10.0
C1608X8R1H683K080AB	68,000	0.420	0.0290	7.35

Multilayer Ceramic Chip Capacitors

Feb. 27, 2026
Simple Model

Commercial Grade High Temperature Application / C1608 series (4/4)

Circuit Diagram



Circuit Parameters

Part No.	C1[pF]	L1[nH]	R1[ohm]	R2[Gohm]
C1608X8R1H683M080AB	68,000	0.420	0.0290	7.35
C1608X8R1H104K080AB	100,000	0.420	0.0190	5.00
C1608X8R1H104M080AB	100,000	0.420	0.0190	5.00
C1608X8R2A102K080AA	1,000	0.420	0.1886	10.0
C1608X8R2A102M080AA	1,000	0.420	0.1886	10.0
C1608X8R2A152K080AA	1,500	0.420	0.1868	10.0
C1608X8R2A152M080AA	1,500	0.420	0.1868	10.0
C1608X8R2A222K080AA	2,200	0.420	0.1359	10.0
C1608X8R2A222M080AA	2,200	0.420	0.1359	10.0
C1608X8R2A332K080AA	3,300	0.420	0.0945	10.0
C1608X8R2A332M080AA	3,300	0.420	0.0945	10.0
C1608X8R2A472K080AA	4,700	0.420	0.0969	10.0
C1608X8R2A472M080AA	4,700	0.420	0.0969	10.0
C1608X8R2A682K080AA	6,800	0.420	0.0681	10.0
C1608X8R2A682M080AA	6,800	0.420	0.0681	10.0
C1608X8R2A103K080AA	10,000	0.420	0.0509	10.0
C1608X8R2A103M080AA	10,000	0.420	0.0509	10.0
C1608X8R2A153K080AA	15,000	0.420	0.0378	10.0
C1608X8R2A153M080AA	15,000	0.420	0.0378	10.0
C1608X8R2A223K080AB	22,000	0.420	0.0522	10.0
C1608X8R2A223M080AB	22,000	0.420	0.0522	10.0
C1608X8R2A333K080AB	33,000	0.420	0.0273	10.0
C1608X8R2A333M080AB	33,000	0.420	0.0273	10.0