


## Multilayer Ceramic Chip Capacitors

Feb. 27, 2026  
Simple Model

### Commercial Grade Soft Termination / C3216 series (1/4)

#### Circuit Diagram



#### Circuit Parameters


Part No.	C1[pF]	L1[nH]	R1[ohm]	R2[Gohm]
C3216C0G1H473J115AE	47,000	0.750	0.0091	10.0
C3216C0G1H683J160AE	68,000	0.750	0.0102	7.35
C3216C0G1H104J160AE	100,000	0.750	0.0072	5.00
C3216C0G2A473J115AE	47,000	0.750	0.0091	10.0
C3216C0G2A683J160AE	68,000	0.750	0.0102	7.35
C3216C0G2A104J160AE	100,000	0.750	0.0072	5.00
C3216C0G2E103J115AE	10,000	0.750	0.0134	10.0
C3216C0G2E153J160AE	15,000	0.750	0.0109	10.0
C3216C0G2W682J115AE	6,800	0.750	0.0132	10.0
C3216C0G2W822J115AE	8,200	0.750	0.0131	10.0
C3216C0G2W103J160AE	10,000	0.750	0.0145	10.0
C3216C0G2J392G085AE	3,900	0.750	0.0187	10.0
C3216C0G2J392J085AE	3,900	0.750	0.0187	10.0
C3216C0G2J562G115AE	5,600	0.750	0.0153	10.0
C3216C0G2J562J115AE	5,600	0.750	0.0153	10.0
C3216C0G2J682G115AE	6,800	0.750	0.0132	10.0
C3216C0G2J682J115AE	6,800	0.750	0.0132	10.0
C3216C0G2J822G160AE	8,200	0.750	0.0124	10.0
C3216C0G2J822J160AE	8,200	0.750	0.0124	10.0
C3216C0G2J103G160AE	10,000	0.750	0.0145	10.0
C3216C0G2J103J160AE	10,000	0.750	0.0145	10.0
C3216X7R1C106K160AE	10,000,000	0.750	0.0048	0.0100
C3216X7R1C106M160AE	10,000,000	0.750	0.0048	0.0100
C3216X7R1E225K160AE	2,200,000	0.750	0.0164	0.227
C3216X7R1E225M160AE	2,200,000	0.750	0.0164	0.227
C3216X7R1E475K160AE	4,700,000	0.750	0.0037	0.106
C3216X7R1E475M160AE	4,700,000	0.750	0.0037	0.106
C3216X7R1E106K160AE	10,000,000	0.750	0.0037	0.0500
C3216X7R1E106M160AE	10,000,000	0.750	0.0037	0.0500
C3216X7R1V225K160AE	2,200,000	0.750	0.0055	0.227
C3216X7R1V225M160AE	2,200,000	0.750	0.0141	0.227
C3216X7R1V475K160AE	4,700,000	0.750	0.0037	0.106
C3216X7R1V475M160AE	4,700,000	0.750	0.0037	0.106
C3216X7R1V106K160AE	10,000,000	0.750	0.0034	0.0500
C3216X7R1V106M160AE	10,000,000	0.750	0.0034	0.0500
C3216X7R1H105K160AE	1,000,000	0.750	0.0110	0.500

## Multilayer Ceramic Chip Capacitors

Feb. 27, 2026  
Simple Model

### Commercial Grade Soft Termination / C3216 series (2/4)

#### Circuit Diagram



#### Circuit Parameters


Part No.	C1[pF]	L1[nH]	R1[ohm]	R2[Gohm]
C3216X7R1H105M160AE	1,000,000	0.750	0.0110	0.500
C3216X7R1H225K160AE	2,200,000	0.750	0.0055	0.227
C3216X7R1H225M160AE	2,200,000	0.750	0.0055	0.227
C3216X7R1H475K160AE	4,700,000	0.750	0.0048	0.106
C3216X7R1H475M160AE	4,700,000	0.750	0.0048	0.106
C3216X7R1H106K160AE	10,000,000	0.750	0.0042	0.0500
C3216X7R2A104K160AE	100,000	0.750	0.0254	5.00
C3216X7R2A104M160AE	100,000	0.750	0.0254	5.00
C3216X7R2A224K115AE	220,000	0.750	0.0195	2.27
C3216X7R2A224M115AE	220,000	0.750	0.0195	2.27
C3216X7R2A474K160AE	470,000	0.750	0.0148	1.06
C3216X7R2A474M160AE	470,000	0.750	0.0148	1.06
C3216X7R2A105K160AE	1,000,000	0.750	0.0071	0.500
C3216X7R2A105M160AE	1,000,000	0.750	0.0108	0.500
C3216X7R2E223K115AE	22,000	0.750	0.0633	10.0
C3216X7R2E223M115AE	22,000	0.750	0.0633	10.0
C3216X7R2E473K160AE	47,000	0.750	0.0350	10.0
C3216X7R2E473M160AE	47,000	0.750	0.0350	10.0
C3216X7R2E104K160AE	100,000	0.750	0.0266	5.00
C3216X7R2E104M160AE	100,000	0.750	0.0266	5.00
C3216X7R2J102K115AE	1,000	0.750	0.2588	10.0
C3216X7R2J102M115AE	1,000	0.750	0.2588	10.0
C3216X7R2J222K115AE	2,200	0.750	0.1524	10.0
C3216X7R2J222M115AE	2,200	0.750	0.1524	10.0
C3216X7R2J332K115AE	3,300	0.750	0.1592	10.0
C3216X7R2J332M115AE	3,300	0.750	0.1592	10.0
C3216X7R2J472K115AE	4,700	0.750	0.0979	10.0
C3216X7R2J472M115AE	4,700	0.750	0.0979	10.0
C3216X7R2J103K115AE	10,000	0.750	0.1061	10.0
C3216X7R2J103M115AE	10,000	0.750	0.1061	10.0
C3216X7R2J223K130AE	22,000	0.750	0.0604	10.0
C3216X7R2J223M130AE	22,000	0.750	0.0604	10.0
C3216X7R2J333K160AE	33,000	0.750	0.0372	10.0
C3216X7R2J333M160AE	33,000	0.750	0.0372	10.0
C3216X7S2A225K160AE	2,200,000	0.750	0.0175	0.227
C3216X7S2A225M160AE	2,200,000	0.750	0.0175	0.227

## Multilayer Ceramic Chip Capacitors

Feb. 27, 2026  
Simple Model

### Commercial Grade Soft Termination / C3216 series (3/4)

#### Circuit Diagram



#### Circuit Parameters


Part No.	C1[pF]	L1[nH]	R1[ohm]	R2[Gohm]
C3216X7T2E224K160AE	220,000	0.750	0.0159	2.27
C3216X7T2E224M160AE	220,000	0.750	0.0159	2.27
C3216X7T2W104K160AE	100,000	0.750	0.0175	5.00
C3216X7T2W104M160AE	100,000	0.750	0.0175	5.00
C3216X7T2J473K160AE	47,000	0.750	0.0304	10.0
C3216X7T2J473M160AE	47,000	0.750	0.0304	10.0
C3216X8L1E106K160AE	10,000,000	0.750	0.0042	0.0500
C3216X8R1C335K160AE	3,300,000	0.750	0.0056	0.0300
C3216X8R1C335M160AE	3,300,000	0.750	0.0056	0.0300
C3216X8R1C475K160AE	4,700,000	0.750	0.0059	0.0210
C3216X8R1C475M160AE	4,700,000	0.750	0.0059	0.0210
C3216X8R1E105K160AE	1,000,000	0.750	0.0093	0.500
C3216X8R1E105M160AE	1,000,000	0.750	0.0093	0.500
C3216X8R1E155K160AE	1,500,000	0.750	0.0091	0.333
C3216X8R1E155M160AE	1,500,000	0.750	0.0091	0.333
C3216X8R1E225K160AE	2,200,000	0.750	0.0068	0.227
C3216X8R1E225M160AE	2,200,000	0.750	0.0068	0.227
C3216X8R1E335K160AE	3,300,000	0.750	0.0056	0.0300
C3216X8R1E335M160AE	3,300,000	0.750	0.0056	0.0300
C3216X8R1E475K160AE	4,700,000	0.750	0.0059	0.0210
C3216X8R1E475M160AE	4,700,000	0.750	0.0059	0.0210
C3216X8R1H334K160AE	330,000	0.750	0.0137	1.52
C3216X8R1H334M160AE	330,000	0.750	0.0137	1.52
C3216X8R1H474K160AE	470,000	0.750	0.0093	1.06
C3216X8R1H474M160AE	470,000	0.750	0.0093	1.06
C3216X8R1H684K160AE	680,000	0.750	0.0102	0.735
C3216X8R1H684M160AE	680,000	0.750	0.0102	0.735
C3216X8R1H105K160AE	1,000,000	0.750	0.0077	0.500
C3216X8R1H105M160AE	1,000,000	0.750	0.0077	0.500
C3216X8R2A104K115AE	100,000	0.750	0.0233	5.00
C3216X8R2A104M115AE	100,000	0.750	0.0233	5.00
C3216X8R2A154K160AE	150,000	0.750	0.0182	3.33
C3216X8R2A154M160AE	150,000	0.750	0.0182	3.33
C3216X8R2A224K160AE	220,000	0.750	0.0180	2.27
C3216X8R2A224M160AE	220,000	0.750	0.0180	2.27
C3216X8R2A334K160AE	330,000	0.750	0.0149	1.52

## Multilayer Ceramic Chip Capacitors

Feb. 27, 2026  
Simple Model

Commercial Grade Soft Termination / C3216 series (4/4)

### Circuit Diagram



### Circuit Parameters

Part No.	C1[pF]	L1[nH]	R1[ohm]	R2[Gohm]
C3216X8R2A334M160AE	330,000	0.750	0.0149	1.52