


Multilayer Ceramic Chip Capacitors

Feb. 27, 2026
Simple Model

Commercial Grade Soft Termination / C3225 series (1/3)

Circuit Diagram



Circuit Parameters


Part No.	C1[pF]	L1[nH]	R1[ohm]	R2[Gohm]
C3225C0G2A683J230AE	68,000	0.600	0.0127	7.35
C3225C0G2E223J160AE	22,000	0.600	0.0130	10.0
C3225C0G2W333J250AE	33,000	0.600	0.0200	10.0
C3225C0G2J153G160AE	15,000	0.600	0.0145	10.0
C3225C0G2J153J160AE	15,000	0.600	0.0145	10.0
C3225C0G2J333G250AE	33,000	0.600	0.0117	10.0
C3225C0G2J333J250AE	33,000	0.600	0.0117	10.0
C3225C0G3A102G200AE	1,000	0.600	0.0279	10.0
C3225C0G3A102J200AE	1,000	0.600	0.0279	10.0
C3225C0G3A122G200AE	1,200	0.600	0.0218	10.0
C3225C0G3A122J200AE	1,200	0.600	0.0218	10.0
C3225C0G3A152G200AE	1,500	0.600	0.0241	10.0
C3225C0G3A152J200AE	1,500	0.600	0.0241	10.0
C3225C0G3A182G200AE	1,800	0.600	0.0198	10.0
C3225C0G3A182J200AE	1,800	0.600	0.0198	10.0
C3225C0G3A222G200AE	2,200	0.600	0.0255	10.0
C3225C0G3A222J200AE	2,200	0.600	0.0255	10.0
C3225C0G3A272G200AE	2,700	0.600	0.0171	10.0
C3225C0G3A272J200AE	2,700	0.600	0.0171	10.0
C3225C0G3A332G200AE	3,300	0.600	0.0250	10.0
C3225C0G3A332J200AE	3,300	0.600	0.0250	10.0
C3225C0G3A392G200AE	3,900	0.600	0.0141	10.0
C3225C0G3A392J200AE	3,900	0.600	0.0141	10.0
C3225C0G3A472G200AE	4,700	0.600	0.0210	10.0
C3225C0G3A472J200AE	4,700	0.600	0.0210	10.0
C3225C0G3A562G200AE	5,600	0.600	0.0082	10.0
C3225C0G3A562J200AE	5,600	0.600	0.0082	10.0
C3225C0G3A682G200AE	6,800	0.600	0.0193	10.0
C3225C0G3A682J200AE	6,800	0.600	0.0193	10.0
C3225C0G3A822G230AE	8,200	0.600	0.0086	10.0
C3225C0G3A822J230AE	8,200	0.600	0.0086	10.0
C3225X7R1H225K200AE	2,200,000	0.600	0.0080	0.227
C3225X7R1H225M200AE	2,200,000	0.600	0.0080	0.227
C3225X7R1H475K250AE	4,700,000	0.600	0.0042	0.106
C3225X7R2A474K200AE	470,000	0.600	0.0107	1.06
C3225X7R2A474M200AE	470,000	0.600	0.0107	1.06

Multilayer Ceramic Chip Capacitors

Feb. 27, 2026
Simple Model

Commercial Grade Soft Termination / C3225 series (2/3)

Circuit Diagram



Circuit Parameters


Part No.	C1[pF]	L1[nH]	R1[ohm]	R2[Gohm]
C3225X7R2A105K200AE	1,000,000	0.600	0.0110	0.500
C3225X7R2A105M200AE	1,000,000	0.600	0.0110	0.500
C3225X7R2A225K230AE	2,200,000	0.600	0.0047	0.227
C3225X7R2A225M230AE	2,200,000	0.600	0.0047	0.227
C3225X7R2E104K200AE	100,000	0.600	0.0208	5.00
C3225X7R2E104M200AE	100,000	0.600	0.0208	5.00
C3225X7R2E224K200AE	220,000	0.600	0.0151	2.27
C3225X7R2E224M200AE	220,000	0.600	0.0151	2.27
C3225X7R2J473K200AE	47,000	0.600	0.0374	10.0
C3225X7R2J473M200AE	47,000	0.600	0.0374	10.0
C3225X7R2J683K200AE	68,000	0.600	0.0230	7.35
C3225X7R2J683M200AE	68,000	0.600	0.0230	7.35
C3225X7S1H475K230AE	4,700,000	0.600	0.0068	0.106
C3225X7S1H475M230AE	4,700,000	0.600	0.0068	0.106
C3225X7S1H106K250AE	10,000,000	0.600	0.0041	0.0500
C3225X7S1H106M250AE	10,000,000	0.600	0.0041	0.0500
C3225X7S2A335K200AE	3,300,000	0.600	0.0054	0.151
C3225X7S2A335M200AE	3,300,000	0.600	0.0054	0.151
C3225X7S2A475K200AE	4,700,000	0.600	0.0086	0.106
C3225X7S2A475M200AE	4,700,000	0.600	0.0086	0.106
C3225X7T2E334K200AE	330,000	0.600	0.0101	1.52
C3225X7T2E334M200AE	330,000	0.600	0.0101	1.52
C3225X7T2W224K200AE	220,000	0.600	0.0160	2.27
C3225X7T2W224M200AE	220,000	0.600	0.0160	2.27
C3225X7T2J104K160AE	100,000	0.600	0.0165	5.00
C3225X7T2J104M160AE	100,000	0.600	0.0165	5.00
C3225X7T2J154K200AE	150,000	0.600	0.0117	3.33
C3225X7T2J154M200AE	150,000	0.600	0.0117	3.33
C3225X8R1C106K250AE	10,000,000	0.600	0.0037	0.0100
C3225X8R1C106M250AE	10,000,000	0.600	0.0037	0.0100
C3225X8R1E335K250AE	3,300,000	0.600	0.0060	0.151
C3225X8R1E335M250AE	3,300,000	0.600	0.0060	0.151
C3225X8R1E475K250AE	4,700,000	0.600	0.0054	0.106
C3225X8R1E475M250AE	4,700,000	0.600	0.0054	0.106
C3225X8R1E106K250AE	10,000,000	0.600	0.0037	0.0100
C3225X8R1E106M250AE	10,000,000	0.600	0.0037	0.0100

Multilayer Ceramic Chip Capacitors

Feb. 27, 2026
Simple Model

Commercial Grade Soft Termination / C3225 series (3/3)

Circuit Diagram



Circuit Parameters

Part No.	C1[pF]	L1[nH]	R1[ohm]	R2[Gohm]
C3225X8R2A474K200AE	470,000	0.600	0.0109	1.06
C3225X8R2A474M200AE	470,000	0.600	0.0109	1.06
C3225X8R2A684K250AE	680,000	0.600	0.0081	0.735
C3225X8R2A684M250AE	680,000	0.600	0.0081	0.735