



Ref. Certif. No.

DK-100369-M1-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Buffer Module
Name and address of the applicant	TDK-LAMBDA SINGAPORE PTE LTD #06-01/08 1008 TOA PAYOH NORTH SINGAPORE 318996 SINGAPORE
Name and address of the manufacturer	TDK-LAMBDA SINGAPORE PTE LTD #06-01/08 1008 TOA PAYOH NORTH SINGAPORE 318996 SINGAPORE
Name and address of the factory	TDK-LAMBDA MALAYSIA SDN BHD PLO33 KAWASAN PERINDUSTRIAN SENAI SENAI, JOHOR, 81400 MALAYSIA
Note: When more than one factory, please report on page 2	<input checked="" type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	Input: 23.0 - 30.0 VDC, 20 A <input checked="" type="checkbox"/> Additional Information on page 2
Trademark (if any)	
Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	DBM20abcxxxxx <input checked="" type="checkbox"/> Additional Information on page 2
Additional information (if necessary may also be reported on page 2)	Additionally evaluated to: EN 62368-1:2014/A11:2017, EN 62368-1:2014 National Difference specified in the CB Test Report The report was revised to include technical modifications. <input checked="" type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 62368-1:2014
As shown in the Test Report Ref. No. which forms part of this Certificate	E252373-A6016-CB-1 issued on 2021-11-01

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2021-11-02
Original Issue Date: 2020-07-24

Signature: Jan-Erik Storgaard



Ref. Certif. No.

DK-100369-M1-UL

Factories:

TDK-LAMBDA MALAYSIA SDN BHD
LOT 2 & 3, BATU 9 3/4 KAWASAN PERINDUSTRIAN BANDAR BARU JAYA GADING KUANTAN, PAHANG, 26070
MALAYSIA

TDK-LAMBDA (CHINA) ELECTRONICS CO LTD
NO.95,ZHUJIANG RD, XINWU DISTRICT WUXI, JIANGSU, 214028
CHINA

PANYU TRIO MICROTRONICS CO LTD
SHIJI INDUSTRIAL ESTATE DONGYONG NANSHA GUANGZHOU, GUANGDONG, 511453
CHINA

Additional Model Detail(s):

DBM20abcxxxxx, where
a can be "/" or blank,
b can be E or blank,
c can be CO or CO2 or blank,
x can be blank or any alphanumeric character that is non safety related information

Additional Ratings:

Output (Ready Mode): 23.0 - 30.0 VDC, 20 A
Output (Buffer Mode): 22.4 VDC/VIN-1, 20 A
Buffer Time: 20A/0.25s (typ)

Summary of Modifications:

Change of minor surface mount components;
Editorial change of Ratings;
See test report for details.

Additional information (if necessary)



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2021-11-02
Original Issue Date: 2020-07-24

Signature:

Jan-Erik Storgaard