

UL TEST REPORT AND PROCEDURE

Standard: Certification Type: CCN:	UL 60950-1, 2nd Edition, 2014-10-14 (Information Technology Equipment - Safety - Part 1: General Requirements) CAN/CSA C22.2 No. 60950-1-07, 2nd Edition, 2014-10 (Information Technology Equipment - Safety - Part 1: General Requirements) Component Recognition NWGQ2, NWGQ8 (Information Technology Equipment Including Electrical Business Equipment)
Product: Model: Rating:	Dual Redundancy Module DRM40xyyyyy, DRM40x/Eyyyyy, DRM40x/Fyyyyy where: x can be B or blank, y can be CO, CO2, blank or any alphanumeric character that is non safety related information. Input 1: 12-28 Vdc, 20A. Input 2: 12-28 Vdc, 20A. Output: 12-28 Vdc, 40A.
Applicant Name and Address:	TDK-LAMBDA SINGAPORE PTE LTD #06-01/08 1008 TOA PAYOH NORTH SINGAPORE 318996 SINGAPORE

This is to certify that representative samples of the products covered by this Test Report have been investigated in accordance with the above referenced Standards. The products have been found to comply with the requirements covering the category and the products are judged to be eligible for Follow-Up Service under the indicated Test Procedure. The manufacturer is authorized to use the UL Mark on such products which comply with this Test Report and any other applicable requirements of UL LLC ('UL') in accordance with the Follow-Up Service Agreement. Only those products which properly bear the UL Mark are considered as being covered by UL's Follow-Up Service under the indicated Test Procedure.

The applicant is authorized to reproduce the referenced Test Report provided it is reproduced in its entirety.

UL authorizes the applicant to reproduce the latest pages of the referenced Test Report consisting of the first page of the Specific Technical Criteria through to the end of the Conditions of Acceptability.

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL.

Prepared by: Chai Ming Yuo, Project Handler

Reviewed by: Jim Kao, Reviewer

Supporting Documentation

The following documents located at the beginning of this Procedure supplement the requirements of this Test Report:

- A. Authorization - The Authorization page may include additional Factory Identification Code markings.
- B. Generic Inspection Instructions -
 - i. Part AC details important information which may be applicable to products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of this Test Report.
 - ii. Part AE details any requirements which may be applicable to all products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of each Test Report.
 - iii. Part AF details the requirements for the UL Certification Mark which is not controlled by the technical standard used to investigate these products. Products are permitted to bear only the Certification Mark(s) corresponding to the countries for which it is certified, as indicated in each Test Report.

Product Description

The equipment is a Dual Redundancy Module having 2 inputs and 1 output consists of electronic components mounted on PWB intended for building-in.

Model Differences

Models DRM40xyyyyy, DRM40x/Eyyyyy and DRM40x/Fyyyyy are similar except the following:

- DRM40xyyyyy using 4 pins terminal block and 2 pins terminal block for output;
- DRM40x/Eyyyyy using spring type terminal block for input and output;
- DRM40x/Fyyyyy using 4 pins terminal block for input and output;

Options:

B = No LED and no DC-OK signal

CO = Conformal coating apply on one side of the PCB

CO2 = Conformal coating apply on both sides of the PCB

Technical Considerations

- Equipment mobility : for building-in
- Connection to the mains : not directly connected to the mains
- Operating condition : continuous
- Access location : N/A
- Over voltage category (OVC) : N/A
- Mains supply tolerance (%) or absolute mains supply values : N/A
- Tested for IT power systems : No
- IT testing, phase-phase voltage (V) : N/A
- Class of equipment : Class III (supplied by SELV)
- Considered current rating of protective device as part of the building installation (A) : 20
- Pollution degree (PD) : PD 2
- IP protection class : IP X0
- Altitude of operation (m) : 5000

- Altitude of test laboratory (m) : less than 2000 meters
- Mass of equipment (kg) : 0.3 (Approximately)
- The product was submitted and evaluated for use at the maximum ambient temperature (Tma) permitted by the manufacturer's specification of: 70 °C for 100% load at Mounting Position A, 60 °C for 100% load at Mounting B, C, 70 °C for 75% load at Mounting B, C
- The product was investigated to the following additional standards: EN 60950-1:2006 + A11:2009 + A1:2010 + A12:2011 + A2:2013 (which includes all European national differences, including those specified in this test report).
- The following are available from the Applicant upon request: Installation (Safety) Instructions / Manual
- LEDs provided in the product are considered low power devices: Yes
- Heating test was performed at different mounting position. See Enclosure Id 7-03 for details.

Engineering Conditions of Acceptability

For use only in or with complete equipment where the acceptability of the combination is determined by UL LLC. When installed in an end-product, consideration must be given to the following:

- The investigated Pollution Degree is: 2
- The following end-product enclosures are required: Fire

Additional Information

Manufacturer requested to perform verification on end-product peak loading conditions as following:
 Loading 1 - output loaded 60 A for 4 seconds and rest at 22.87 A for 7.4 seconds;
 Loading 2 - output loaded 45 A for 4 seconds and rest at 17.14 A for 7.4 seconds.
 See Enclosure ID 7-04 for details.

Additional Standards

The product fulfills the requirements of: EN 60950-1:2006 + A1:2010 + A11:2009 + A12:2011 + A2:2013

Markings and instructions

Clause Title	Marking or Instruction Details
Power rating - Ratings	Ratings (voltage, frequency/dc, current)
Power rating - Company identification	Listee's or Recognized company's name, Trade Name, Trademark or File Number
Power rating - Model	Model Number

Special Instructions to UL Representative

N/A