

HFE2500-S1U SERIES RACK SPECIFICATIONS

				Rev	
1	Number of power supply modules (*1) (*7)		Maximum 4 units HFE2500 of the same output voltage rating.		
2	Maximum output power		Refer to HFE2500 specifications	В	
3	Maximum output current		320A per output (Total 640A)	D	
4	Input voltage / frequency range (*2)		85~265Vac continuous, 47~63Hz, Single phase, separate input for each PS module.		
5	Maximum input current (at 115/230Vac)	Α	15/12 for each HFE2500 power supply module	\top	
6	Maximum line regulation (*4)	%	Less than 0.25 of rated output voltage		
7			Less than 0.8 of rated output voltage		
8	AC input connector (*6)		Separate for each power supply. HFE2500-S1U: IEC inlet, (C20); HFE2500-S1U/TB: Terminal Block.	E	
9	Output terminals		Two bus-bars outputs for each output terminal (two sides). Refer to outline drawing.	E	
10	Remote sensing (*3)		Possible. Refer to Instruction Manual.	 -	
11	Parallel operation		Possible. Refer to Instruction Manual.		
12	Series operation		Possible. Refer to Instruction Manual.		
13	Remote On/Off control (INHIBIT)		Separate control for each PS unit, by electrical signal or dry contact. 'OFF": 0~0.6V or short. "ON": 2~15V or open.		
14	Remote On/Off control (ENABLE)		Common for all PS units, by electrical signal or dry contact. 'ON": 0~0.6V or short. "OFF": 2~15V or open.		
15	DC OK signal		Separate signal for each PS unit, open collector signal. Maximum sink current: 10mA, Max 15V Tracking output setting, "LOW" when Vout>90+/-5% of output voltage setting		
16	Over Temperature alarm signal		Separate signal for each PS unit, open collector signal. Maximum sink current: 10mA, Max 15V "LOW" when input voltage 85Vac <vin<270vac. 10ma,="" 15v="" collector="" current:="" each="" for="" instruction="" manual<="" max="" maximum="" open="" ps="" refer="" separate="" signal="" signal.="" sink="" td="" to="" unit,=""></vin<270vac.>		
17					
18	3		Common for all PS units, by built-in potentiometer. Refer to Instruction Manual.		
	Output voltage programming		Possible, Common for all PS units, by 0~5V signal. Refer to Instruction Manual.		
20	· · · · · · · · · · · · · · · · · · ·		Possible, Common for all PS units. Refer to Instruction Manual.		
21			Possible, Common for all PS units, by 0~5V signal. Refer to Instruction Manual.		
22	1 9 0		Possible, Common for all PS units. Refer to Instruction Manual.		
23	Auxiliary power supply		11.2~12.5VDC. Maximum output current: 0.5A	Α	
24	Operating temperature		10~50°C: 100% load. +50°C to +60°C: Derate 2%/°C of load +60°C to +70°C: Derate 2.5%/°C of load		
25	Storage temperature		-30~85°C	+	
26			10~90% RH, no condensation.		
27			10~95% RH, no condensation.		
28			Built to meet IEC60068-2-64 (Basic Transportation)		
29			Built to meet IEC60068-2-27 (Basic Transportation)		
30			IEC 62368-1 UL62368-1 CSA22.2 No.62368-1 EN62368-1.		
	Input-Output:		3000Vrms, 1min.	F	
31	Withstand voltage Input-Ground: Output-Ground:		2000Vrms, 1min.	+-	
01			12, 24V models - 500Vrms, 1min 48V model - 2250VDC, 1min.		
32	2 Isolation resistance		More than 100Mohm at 25°C and 70% RH. Output-Ground: 500Vdc	F	
	Weight (Typ) (with accessories)	kg	5.0	- '	
34	9 , 11 , ,		445x43.6x401mm. Refer to Outline Drawing.		
	JOIZE (VV 11 D)		Trox to ox to think resol to outline brawing.		

Notes:

- *1 Mixing of PMBus option units ("HFE2500-xx/S") and standard units ("HFE2500-xx") is <u>not allowed</u>.
- *2 For cases where conformance to various safety standards (UL, EN etc.) is required, Input Voltage to be described as 100-240Vac (50/60Hz).
- $^{\star}3~~\text{Maximum voltage drop on load wires: HFE2500-12: 0.25V/wire, HFE2500-24: 0.5V/wire, HFE2500-48: 1V/wire.}$
- *4 From 85~132Vac or 170~265Vac, constant load.
- *5 From No-load to Rated load, constant input voltage. Measured at the sensing point in Remote sense.
- *6 Use UL approved Insulated terminal lugs
 *7 The output of all HFE2500 modules are connected in parallel in the Rack

DRAWING NO:	IA706-01-01F , ,				
DRAW:	Suno	25C	9/11/2020		
ENGR:	Ashe-Sh.		10-11-2020		
CHECK:	Borrs K.		19.11.2020		
APPR:	7		11/11/120		