

Group	Series, Type	Part No.	Property	S-para meter	Equivalent Circuit Model			
				Touch- stone	Simple Model		Precise Model	V-I Model
					PDF	SPICE	SPICE	HSPICE,LT spice,PSpice
AVRM	AVRM0402	AVRM0402C6R8NT101N	V1mA=6.8V	–	–	–	✓	✓
AVRM	AVRM0402	AVRM0402C120MT330N	V1mA=12V	✓	–	–	✓	✓
AVRM	AVRM0603	AVRM0603C6R8NT101N	V1mA=6.8V	✓	–	–	✓	✓
AVRM	AVRM0603	AVRM0603C6R8NT331N	V1mA=6.8V	–	–	–	✓	✓
AVRM	AVRM0603	AVRM0603C080MT101N	V1mA=8V	✓	–	–	✓	✓
AVRM	AVRM0603	AVR-M0603C120MTAAB	V1mA=12V	✓	–	–	✓	✓
AVRM	AVRM0603	AVRM0603C120MT101N	V1mA=12.8V	✓	–	–	✓	✓
AVRM	AVRM0603	AVRM0603C120MT150N	V1mA=12.8V	✓	–	–	✓	✓
AVRM	AVRM0603	AVRM0603C200MT150N	V1mA=20V	–	–	–	✓	✓
AVRM	AVRM1005	AVRM1005C6R8NT101N	V1mA=6.8V	✓	–	–	✓	✓
AVRM	AVRM1005	AVRM1005C6R8NT331N	V1mA=6.8V	–	–	–	✓	✓
AVRM	AVRM1005	AVR-M1005C080MTAAB	V1mA=8V	✓	–	–	✓	✓
AVRM	AVRM1005	AVR-M1005C080MTABB	V1mA=8V	✓	–	–	✓	✓
AVRM	AVRM1005	AVR-M1005C080MTACB	V1mA=8V	✓	–	–	✓	✓
AVRM	AVRM1005	AVR-M1005C080MTADB	V1mA=8V	✓	–	–	✓	✓
AVRM	AVRM1005	AVR-M1005C120MTAAB	V1mA=12V	✓	–	–	✓	✓
AVRM	AVRM1005	AVR-M1005C120MTACC	V1mA=12V	–	–	–	✓	✓
AVRM	AVRM1005	AVR-M1005C180MTAAB	V1mA=18V	–	–	–	✓	✓
AVRM	AVRM1005	AVRM1005C270KT101N	V1mA=27V	✓	–	–	✓	✓
AVRM	AVRM1005	AVR-M1005C270MTAAB	V1mA=27V	✓	–	–	✓	✓
AVRM	AVRM1005	AVR-M1005C270MTABB	V1mA=27V	✓	–	–	✓	✓
AVRM	AVRM1608	AVR-M1608C080MTAAB	V1mA=8V	✓	–	–	✓	✓
AVRM	AVRM1608	AVR-M1608C120MT2AB	V1mA=12V	✓	–	–	✓	✓
AVRM	AVRM1608	AVR-M1608C120MT6AB	V1mA=12V	✓	–	–	✓	✓
AVRM	AVRM1608	AVR-M1608C180MT6AB	V1mA=18V	✓	–	–	✓	✓
AVRM	AVRM1608	AVR-M1608C220KT2AB	V1mA=22V	✓	–	–	✓	✓
AVRM	AVRM1608	AVR-M1608C220KT6AB	V1mA=22V	✓	–	–	✓	✓
AVRM	AVRM1608	AVR-M1608C270KT2AB	V1mA=27V	✓	–	–	✓	✓
AVRM	AVRM1608	AVR-M1608C270KT6AB	V1mA=27V	✓	–	–	✓	✓
AVRM	AVRM1608	AVRM1608C270KT800M	V1mA=27V	–	–	–	✓	✓
AVRM	AVRM1608	AVR-M1608C270KTACB	V1mA=27V	✓	–	–	✓	✓
AVRM	AVRM1608	AVR-M1608C270MTAAB	V1mA=27V	✓	–	–	✓	✓
AVRM	AVRM1608	AVR-M1608C270MTABB	V1mA=27V	✓	–	–	✓	✓
AVRM	AVRM1608	AVRM1608C390KT271N	V1mA=39V	✓	–	–	✓	✓
AVRM	AVRM2012	AVR-M2012C120MT6AB	V1mA=12V	✓	–	–	✓	✓
AVRM	AVRM2012	AVR-M2012C220KT6AB	V1mA=22V	✓	–	–	✓	✓
AVRM	AVRM2012	AVR-M2012C390KT6AB	V1mA=39V	✓	–	–	✓	✓
AVRL	AVRL04	AVRL041E1R1NTA	V1mA=39V	✓	–	–	✓	✓
AVRL	AVRL06	AVRL061E1R1NTA	V1mA=39V	✓	–	–	✓	✓
AVRL	AVRL10	AVRL101A1R1NTA	V1mA=90V	✓	–	–	✓	✓
AVRL	AVRL16	AVRL161A1R1NTB	V1mA=39V	✓	–	–	✓	✓
AVRL	AVRL16	AVRL161A1R1NTA	V1mA=90V	✓	–	–	✓	✓
AVRH	AVRH10	AVRH10C270KT150NA8	V1mA=27V	–	–	–	✓	✓
AVRH	AVRH10	AVRH10C390KT500NA8	V1mA=39V	–	–	–	✓	✓
AVRH	AVRH10	AVRH10C101KT4R7FA8	V1mA=100V	–	–	–	✓	✓