

Group	Series, Type	Part No.	Property	S-parameter	Equivalent Circuit Model			
					Simple Model		Precise Model	V-I Model
				Touch-stone	PDF	SPICE	SPICE	HSPICE,LT spice,PSpice
Commercial Grade	AVRM0402	AVRM0402C6R8NT101N	V1mA=6.8V	—	—	—	✓	✓
Commercial Grade	AVRM0402	AVRM0402C120MT330N	V1mA=12V	✓	—	—	✓	✓
Commercial Grade	AVRM0603	AVRM0603C6R8NT101N	V1mA=6.8V	✓	—	—	✓	✓
Commercial Grade	AVRM0603	AVRM0603C6R8NT331N	V1mA=6.8V	—	—	—	✓	✓
Commercial Grade	AVRM0603	AVRM0603C080MT101N	V1mA=8V	✓	—	—	✓	✓
Commercial Grade	AVRM0603	AVR-M0603C120MTAAB	V1mA=12V	✓	—	—	✓	✓
Commercial Grade	AVRM0603	AVRM0603C120MT101N	V1mA=12.8V	✓	—	—	✓	✓
Commercial Grade	AVRM0603	AVRM0603C120MT150N	V1mA=12.8V	✓	—	—	✓	✓
Commercial Grade	AVRM0603	AVRM0603C200MT150N	V1mA=20V	—	—	—	✓	✓
Commercial Grade	AVRM1005	AVRM1005C6R8NT101N	V1mA=6.8V	✓	—	—	✓	✓
Commercial Grade	AVRM1005	AVRM1005C6R8NT331N	V1mA=6.8V	—	—	—	✓	✓
Commercial Grade	AVRM1005	AVR-M1005C080MTAAB	V1mA=8V	✓	—	—	✓	✓
Commercial Grade	AVRM1005	AVR-M1005C080MTABB	V1mA=8V	✓	—	—	✓	✓
Commercial Grade	AVRM1005	AVR-M1005C080MTACB	V1mA=8V	✓	—	—	✓	✓
Commercial Grade	AVRM1005	AVR-M1005C080MTADB	V1mA=8V	✓	—	—	✓	✓
Commercial Grade	AVRM1005	AVR-M1005C120MTAAB	V1mA=12V	✓	—	—	✓	✓
Commercial Grade	AVRM1005	AVR-M1005C120MTACC	V1mA=12V	—	—	—	✓	✓
Commercial Grade	AVRM1005	AVR-M1005C180MTAAB	V1mA=18V	—	—	—	✓	✓
Commercial Grade	AVRM1005	AVRM1005C270KT101N	V1mA=27V	✓	—	—	✓	✓
Commercial Grade	AVRM1005	AVR-M1005C270MTAAB	V1mA=27V	✓	—	—	✓	✓
Commercial Grade	AVRM1005	AVR-M1005C270MTABB	V1mA=27V	✓	—	—	✓	✓
Commercial Grade	AVRM1608	AVR-M1608C080MTAAB	V1mA=8V	✓	—	—	✓	✓
Commercial Grade	AVRM1608	AVR-M1608C120MT2AB	V1mA=12V	✓	—	—	✓	✓
Commercial Grade	AVRM1608	AVR-M1608C120MT6AB	V1mA=12V	✓	—	—	✓	✓
Commercial Grade	AVRM1608	AVR-M1608C180MT6AB	V1mA=18V	✓	—	—	✓	✓
Commercial Grade	AVRM2012	AVR-M2012C120MT6AB	V1mA=12V	✓	—	—	✓	✓
Commercial Grade	AVRL04	AVRL041E1R1NTA	V1mA=39V	✓	—	—	✓	✓
Commercial Grade	AVRL06	AVRL061E1R1NTA	V1mA=39V	✓	—	—	✓	✓
Commercial Grade	AVRL06	AVRL061FR50ETA	V1mA=140V	—	—	—	—	—
Commercial Grade	AVRL10	AVRL101E1R1NTB	V1mA=39V	—	—	—	—	—
Commercial Grade	AVRL10	AVRL101A1R1NTA	V1mA=90V	✓	—	—	✓	✓
Commercial Grade	AVRL16	AVRL161A1R1NTB	V1mA=39V	✓	—	—	✓	✓
Commercial Grade	AVRL16	AVRL161A1R1NTA	V1mA=90V	✓	—	—	✓	✓
Automotive Grade	AVRM1608	AVR-M1608C220KT2AB	V1mA=22V	✓	—	—	✓	✓
Automotive Grade	AVRM1608	AVR-M1608C220KT6AB	V1mA=22V	✓	—	—	✓	✓
Automotive Grade	AVRM1608	AVRM1608C270KT221M	V1mA=27V	✓	—	—	—	—
Automotive Grade	AVRM1608	AVR-M1608C270KT2AB	V1mA=27V	✓	—	—	✓	✓
Automotive Grade	AVRM1608	AVR-M1608C270KT6AB	V1mA=27V	✓	—	—	✓	✓
Automotive Grade	AVRM1608	AVRM1608C270KT800M	V1mA=27V	—	—	—	✓	✓
Automotive Grade	AVRM1608	AVR-M1608C270KTACB	V1mA=27V	✓	—	—	✓	✓
Automotive Grade	AVRM1608	AVR-M1608C270MTAAB	V1mA=27V	✓	—	—	✓	✓
Automotive Grade	AVRM1608	AVR-M1608C270MTABB	V1mA=27V	✓	—	—	✓	✓
Automotive Grade	AVRM1608	AVR-M1608G270KT6AB	V1mA=27V	—	—	—	—	—
Automotive Grade	AVRM1608	AVRM1608C390KT271N	V1mA=39V	✓	—	—	✓	✓
Automotive Grade	AVRM1608	AVRM1608C560KT101M	V1mA=56V	—	—	—	✓	✓
Automotive Grade	AVRM1608	AVRM1608C720KT750M	V1mA=72V	—	—	—	✓	✓
Automotive Grade	AVRM2012	AVR-M2012C220KT6AB	V1mA=22V	✓	—	—	✓	✓
Automotive Grade	AVRM2012	AVRM2012C330KT801N	V1mA=33V	—	—	—	—	—
Automotive Grade	AVRM2012	AVR-M2012C390KT6AB	V1mA=39V	✓	—	—	✓	✓
Automotive Grade	AVRM2012	AVRM2012C560KT251M	V1mA=56V	—	—	—	✓	✓
Automotive Grade	AVRM2012	AVRM2012C720KT201M	V1mA=72V	—	—	—	✓	✓
Automotive Grade	AVRL10	AVRL101D3R3FTA	V1mA=27V	—	—	—	—	—
Automotive Grade	AVRL10	AVRL101D6R8GTA	V1mA=27V	—	—	—	—	—
Automotive Grade	AVRL16	AVRL161D3R3FTA	V1mA=27V	—	—	—	—	—
Automotive Grade	AVRL16	AVRL161D6R8GTA	V1mA=27V	—	—	—	—	—
Automotive Grade	AVRH10	AVRH10C220YT201MA8	V1mA=22V	✓	—	—	✓	✓
Automotive Grade	AVRH10	AVRH10C270KT150NA8	V1mA=27V	✓	—	—	✓	✓
Automotive Grade	AVRH10	AVRH10C270KT350NA8	V1mA=27V	✓	—	—	✓	✓
Automotive Grade	AVRH10	AVRH10C390KT500NA8	V1mA=39V	✓	—	—	✓	✓
Automotive Grade	AVRH10	AVRH10C101KT4R7FA8	V1mA=100V	✓	—	—	✓	✓
Automotive Grade	AVRH10	AVRH10C101KT4R7YA8	V1mA=115V	✓	—	—	✓	✓
Automotive Grade	AVRH10	AVRH10C101KT1R1NE8	V1mA=110V	✓	—	—	✓	✓
Automotive Grade	AVRH10	AVRH10C101KT1R2YE8	V1mA=110V	✓	—	—	✓	✓
Automotive Grade	AVRH10	AVRH10C221KT1R5YA8	V1mA=220V	✓	—	—	✓	✓
Automotive Grade	AVRSP16	AVRSP16C270KT431N	V1mA=27V	—	—	—	—	—
Automotive Grade(Array)	AVRH16	AVRH16A2C270KT200NA8	V1mA=27V	—	—	—	—	—