

DELIVERY SPECIFICATION

SPEC. No. A-ESD-f

D A T E : March, 2021

To

Non-Controlled Copy

CUSTOMER'S PRODUCT NAME

TDK PRODUCT NAME

MULTILAYER CERAMIC CHIP CAPACITORS
Bulk and Tape packaging 【RoHS compliant】
CGA3EA ESD Protection Series

Please return this specification to TDK representatives with your signature.
If orders are placed without returned specification, please allow us to judge that specification is accepted by your side.

RECEIPT CONFIRMATION

DATE: _____ YEAR _____ MONTH _____ DAY _____

Test conditions in this specification based on AEC-Q200 for automotive application.

TDK Corporation
Sales
Electronic Components
Sales & Marketing Group

Engineering
Electronic Components Business Company
Ceramic Capacitors Business Group

APPROVED	Person in charge

APPROVED	CHECKED	Person in charge

■ CATALOG NUMBER CONSTRUCTION

CGA	3	E	A	NP0	2A	103	J	080	A	C
(1)	(2)	(3)	(4)	(5)	(6)	(7)	(8)	(9)	(10)	(11)

(1) Series

(2) Dimensions L x W (mm)

Code	EIA	Length	Width	Terminal width
3	CC0603	1.60	0.80	0.20

(3) Thickness code

Code	Thickness
E	0.80mm

(4) Voltage condition for life test

Symbol	Condition
A	ESD protection

(5) Temperature characteristics

Temperature characteristics	Temperature coefficient	Temperature range
C0G	0±30 ppm/°C	-55 to +125°C
NP0	0±30 ppm/°C	-55 to +150°C

(6) Rated voltage (DC)

Code	Voltage (DC)
2A	100V

(7) Nominal capacitance (pF)

The capacitance is expressed in three digit codes and in units of pico Farads (pF). The first and second digits identify the first and second significant figures of the capacitance. The third digit identifies the multiplier. R designates a decimal point.

(Example) 0R5 = 0.5pF
101 = 100pF
225 = 2,200,000pF = 2.2μF

(8) Capacitance tolerance

Code	Tolerance
J	±5%

(9) Thickness

Code	Thickness
080	0.80mm

(10) Packaging style

Code	Style
A	178mm reel, 4mm pitch

(11) Special reserved code

Code	Description
A,C	TDK internal code

SCOPE

This delivery specification shall be applied to Multilayer ceramic chip capacitors to be delivered to _____.

PRODUCTION PLACES

Production places defined in this specification shall be TDK Corporation, TDK(Suzhou)Co.,Ltd and TDK Components U.S.A.,Inc.

PRODUCT NAME

The name of the product to be defined in this specifications shall be CGA3EA00002A□□□×.

REFERENCE STANDARD

JIS C 5101-1 : 2010	Fixed capacitors for use in electronic equipment-Part 1: Generic specification
C 5101-21 : 2014	Fixed capacitors for use in electronic equipment-Part21 : Sectional specification : Fixed surface mount multilayer capacitors of ceramic dielectric,Class1
C 0806-3 : 2014	Packaging of components for automatic handling - Part 3: Packaging of surface mount components on continuous tapes
JEITA RCR-2335 C 2014	Safety application guide for fixed ceramic capacitors for use in electronic equipment

CONTENTS

1. CODE CONSTRUCTION
2. OPERATING TEMPERATURE RANGE
3. STORING CONDITION AND TERM
4. INDUSTRIAL WASTE DISPOSAL
5. PERFORMANCE
6. INSIDE STRUCTURE AND MATERIAL
7. PACKAGING
8. SETTING UP FOR ESD TEST
9. CAUTION
10. TAPE PACKAGING SPECIFICATION

<EXPLANATORY NOTE>

When the mistrust in the spec arises, this specification is given priority. And it will be confirmed by written spec change after conference of both posts involved.

This specification warrants the quality of the ceramic chip capacitor. Capacitors should be evaluated or confirmed a state of mounted on your product.

If the use of the capacitors goes beyond the bounds of this specification, we can not afford to guarantee.

Division	Date	SPEC. No.
Ceramic Capacitors Business Group	March, 2021	A-ESD-f


1. CODE CONSTRUCTION

(Example) $\frac{\text{CGA}}{(1)}$ $\frac{3}{(2)}$ $\frac{\text{E}}{(3)}$ $\frac{\text{A}}{(4)}$ $\frac{\text{COG}}{(5)}$ $\frac{2 \text{ A}}{(6)}$ $\frac{103}{(7)}$ $\frac{\text{J}}{(8)}$ $\frac{\text{T}}{(9)}$ $\frac{\text{OOOO}}{(10)}$

(1) Series

Symbol	Series
CGA	Ceramic chip capacitor for automotive application

(2) Case size



Symbol	Case size	Dimensions (Unit : mm)				
	TDK(EIA style)	L	W	T	B	G
3	CGA3(CC0603)	1.60±0.10	0.80±0.10	0.80±0.10	0.20 min.	0.30 min.

(3) Thickness

Symbol	Dimension(mm)
E	0.80

(4) Identification for ESD capacitor

* Details are shown in Table 1 No.16 at 5.PERFORMANCE.

※ As for applied ESD level, please refer to detail page on TDK web.

Symbol	Identification
A	ESD capacitor

(5) Temperature Characteristics

* Details are shown in Table 1 No.6 at 5.PERFORMANCE.

(6) Rated Voltage

Symbol	Rated Voltage
2 A	DC 100 V

(7) Rated Capacitance

Stated in three digits and in units of pico farads (pF).
The first and Second digits identify the first and second significant figures of the capacitance, the third digit identifies the multiplier.

(Example)

Symbol	Rated Capacitance
103	10,000 pF

(8) Capacitance tolerance

Symbol	Tolerance
J	± 5 %

(9) Packaging

Symbol	Packaging
B	Bulk
T	Taping

(10) TDK internal code

2. OPERATING TEMPERATURE RANGE

T.C.	Min. operating Temperature	Max. operating Temperature	Reference Temperature
C0G	-55°C	125°C	25°C
NP0	-55°C	150°C	25°C

3. STORING CONDITION AND TERM


Storing temperature	Storing humidity	Storing term
5~40°C	20~70%RH	Within 6 months upon receipt.

4. INDUSTRIAL WASTE DISPOSAL



Dispose this product as industrial waste in accordance with the Industrial Waste Law.

5. PERFORMANCE

Table 1

No.	Item	Performance	Test or inspection method										
1	External Appearance	No defects which may affect performance.	Inspect with magnifying glass(3×)										
2	Insulation Resistance	10,000MΩ min.	Measuring voltage : Rated voltage Voltage application time : 60s.										
3	Voltage Proof	Withstand test voltage without insulation breakdown or other damage.	Apply voltage : 3 × rated voltage Voltage application time : 1s. Charge/discharge current : 50mA or lower										
4	Capacitance	Within the specified tolerance.	<table border="1"> <thead> <tr> <th>Rated Capacitance</th> <th>Measuring frequency</th> <th>Measuring voltage</th> </tr> </thead> <tbody> <tr> <td>1000pF</td> <td>1MHz±10%</td> <td rowspan="2">0.5 ~ 5V rms.</td> </tr> <tr> <td>Over 1000pF</td> <td>1kHz±10%</td> </tr> </tbody> </table>	Rated Capacitance	Measuring frequency	Measuring voltage	1000pF	1MHz±10%	0.5 ~ 5V rms.	Over 1000pF	1kHz±10%		
Rated Capacitance	Measuring frequency	Measuring voltage											
1000pF	1MHz±10%	0.5 ~ 5V rms.											
Over 1000pF	1kHz±10%												
5	Q	Please refer to detail page on TDK web.	See No.4 in this table for measuring condition.										
6	Temperature Characteristics of Capacitance	<table border="1"> <thead> <tr> <th>T.C.</th> <th>Temperature Coefficient (ppm/°C)</th> </tr> </thead> <tbody> <tr> <td>C0G</td> <td>0 ± 30</td> </tr> <tr> <td>NP0</td> <td>0 ± 30</td> </tr> </tbody> </table> <table border="1"> <thead> <tr> <th>Capacitance drift</th> <th>Within ± 0.2% or ± 0.05pF, whichever larger.</th> </tr> </thead> <tbody> <tr> <td></td> <td></td> </tr> </tbody> </table>	T.C.	Temperature Coefficient (ppm/°C)	C0G	0 ± 30	NP0	0 ± 30	Capacitance drift	Within ± 0.2% or ± 0.05pF, whichever larger.			<p>Temperature coefficient shall be calculated based on values at 25°C and 85°C temperature.</p> <p>Measuring temperature below 25°C shall be -10°C and -25°C.</p>
T.C.	Temperature Coefficient (ppm/°C)												
C0G	0 ± 30												
NP0	0 ± 30												
Capacitance drift	Within ± 0.2% or ± 0.05pF, whichever larger.												
7	Robustness of Terminations	No sign of termination coming off, breakage of ceramic, or other abnormal signs.	<p>Reflow solder the capacitors on a P.C.Board shown in Appendix 2.</p> <p>Apply a pushing force gradually at the center of a specimen in a horizontal direction of P.C.board.</p> <p>Pushing force : 17.7N Holding time : 10±1s.</p> 										



(continued)



No.	Item	Performance	Test or inspection method				
8	Bending	No mechanical damage.	Reflow solder the capacitor on a P.C.Board shown in Appendix1.  (Unit : mm)				
9	Solderability	New solder to cover over 75% of termination. 25% may have pin holes or rough spots but not concentrated in one spot. Ceramic surface of A sections shall not be exposed due to melting or shifting of termination material.  A section	Solder : Sn-3.0Ag-0.5Cu Flux : Isopropyl alcohol (JIS K 8839) Rosin (JIS K 5902) 25% solid solution. Solder temp. : 245±5°C Dwell time : 3±0.3s. Solder position : Until both terminations are completely soaked.				
10	Resistance to solder heat	External appearance	No cracks are allowed and terminations shall be covered at least 60% with new solder.				
		Capacitance	<table border="1"> <thead> <tr> <th>Characteristics</th> <th>Change from the value before test</th> </tr> </thead> <tbody> <tr> <td>C0G NPO</td> <td>±2.5%</td> </tr> </tbody> </table>	Characteristics	Change from the value before test	C0G NPO	±2.5%
		Characteristics	Change from the value before test				
		C0G NPO	±2.5%				
		Q	Meet the initial spec.				
Insulation Resistance	Meet the initial spec.						
Voltage proof	No insulation breakdown or other damage.						
			Solder : Sn-3.0Ag-0.5Cu Flux : Isopropyl alcohol (JIS K 8839) Rosin (JIS K 5902) 25% solid solution. Solder temp. : 260±5°C Dwell time : 10±1s. Solder position : Until both terminations are completely soaked. Pre-heating : Temp. — 110~140°C Time — 30~60s. Leave the capacitors in ambient condition for 6~24h before measurement.				
11	Vibration	External appearance	No mechanical damage.				
		Capacitance	<table border="1"> <thead> <tr> <th>Characteristics</th> <th>Change from the value before test</th> </tr> </thead> <tbody> <tr> <td>C0G NPO</td> <td>±2.5%</td> </tr> </tbody> </table>	Characteristics	Change from the value before test	C0G NPO	±2.5%
		Characteristics	Change from the value before test				
C0G NPO	±2.5%						
Q	Meet the initial spec.						
			Applied force : 5G max. Frequency : 10~2,000Hz Reciprocating sweep time : 20 min. Cycle : 12 cycles in each 3 mutually perpendicular directions. Reflow solder the capacitors on a P.C.Board shown in Appendix 2 before testing.				

(continued)

No.	Item	Performance	Test or inspection method																
12	Temperature cycle	External appearance	No mechanical damage.																
		Capacitance	Characteristics	Change from the value before test															
			COG NPO	Please contact with our sales representative.															
		Q	Meet the initial spec.	Expose the capacitors in the condition step1 through step 4 listed in the following table. Temp. cycle : 1,000 cycles <table border="1"> <thead> <tr> <th>Step</th> <th>Temperature(°C)</th> <th>Time (min.)</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>Min. operating temp. ± 3</td> <td>30 \pm 3</td> </tr> <tr> <td>2</td> <td>Ambient Temp.</td> <td>2 ~ 5</td> </tr> <tr> <td>3</td> <td>Max. operating temp. ± 2</td> <td>30 \pm 2</td> </tr> <tr> <td>4</td> <td>Ambient Temp.</td> <td>2 ~ 5</td> </tr> </tbody> </table>	Step	Temperature(°C)	Time (min.)	1	Min. operating temp. ± 3	30 \pm 3	2	Ambient Temp.	2 ~ 5	3	Max. operating temp. ± 2	30 \pm 2	4	Ambient Temp.	2 ~ 5
		Step	Temperature(°C)		Time (min.)														
1	Min. operating temp. ± 3	30 \pm 3																	
2	Ambient Temp.	2 ~ 5																	
3	Max. operating temp. ± 2	30 \pm 2																	
4	Ambient Temp.	2 ~ 5																	
Insulation Resistance	Meet the initial spec.	As for Min./ Max. operating temp., please refer to "2.OPERATING TEMPERATURE RANGE".																	
Voltage proof	No insulation breakdown or other damage.	Leave the capacitors in ambient condition for 6~24h before measurement. Reflow solder the capacitors on a P.C.Board shown in Appendix 2 before testing.																	
13	Moisture Resistance (Steady State)	External appearance	No mechanical damage.																
		Capacitance	Characteristics	Change from the value before test															
			COG NPO	Please contact with our sales representative.															
		Q	350 min.	Test temp. : 40 \pm 2°C Test humidity : 90~95%RH Test time : 500 +24,0h Leave the capacitors in ambient condition for 6~24h before measurement. Reflow solder the capacitors on a P.C.Board shown in Appendix2 before testing.															
Insulation Resistance	1,000M Ω min.																		
14	Moisture Resistance	External appearance	No mechanical damage.																
		Capacitance	Characteristics	Change from the value before test															
			COG NPO	Please contact with our sales representative.															
		Q	200 min.	Test temp. : 85 \pm 2°C Test humidity : 85%RH Applied voltage : Rated voltage Test time : 1,000 +48,0h Charge/discharge current : 50mA or lower Leave the capacitors in ambient condition for 6~24h before measurement. Reflow solder the capacitors on a P.C.Board shown in Appendix2 before testing.															
Insulation Resistance	500M Ω min.																		

(continued)

No.	Item	Performance	Test or inspection method				
15	Life	No mechanical damage.	Test temp. : Maximum operating temperature $\pm 2^{\circ}\text{C}$ Applied voltage : Please contact with our sales representative. Test time : 1,000 +48,0h Charge/discharge current : 50mA or lower Leave the capacitors in ambient condition for 6~24h before measurement. Reflow solder the capacitors on a P.C.Board shown in Appendix2 before testing.				
	External appearance						
	Capacitance	<table border="1" data-bbox="512 331 954 510"> <thead> <tr> <th data-bbox="512 331 687 398">Characteristics</th> <th data-bbox="692 331 954 398">Change from the value before test</th> </tr> </thead> <tbody> <tr> <td data-bbox="512 405 687 510">COG NPO</td> <td data-bbox="692 405 954 510">Please contact with our sales representative.</td> </tr> </tbody> </table>		Characteristics	Change from the value before test	COG NPO	Please contact with our sales representative.
	Characteristics	Change from the value before test					
COG NPO	Please contact with our sales representative.						
Q	350 min.						
16	ESD	Withstand ESD voltage without insulation breakdown.  Rc : Charge current limit resistor Rd : Discharge resistor Cs : Energy storage capacitor 	Reflow Solder the capacitors on a P.C.Board shown in Appendix3 before testing. Circuit condition : IEC 61000-4-2 (Cs : 150pF / Rd : 330 Ω) Test method : Direct contact Number of ESD pulse : ± 10 times As for applied ESD level, please refer to detail page on TDK web. After each ESD pulse, dissipation of residual charge shall be done with applying 1M Ω resistance for 1 sec min.				



1. Material : Glass Epoxy
(As per JIS C6484 GE4)

2. Thickness : 1.6mm

- Copper(Thickness:0.035mm)
- Solder resist


Appendix 1, 2 (Unit : mm)

Case size	a	b	c
TDK(EIA style)			
CGA3(CC0603)	1.0	3.0	1.2

Appendix 3 (ESD TEST) (Unit : mm)

Case size	a	b	c
TDK(EIA style)			
CGA3(CC0603)	1.0	3.0	0.75

6. INSIDE STRUCTURE AND MATERIAL



No.	NAME	MATERIAL
1	Dielectric	CaZrO ₃
2	Electrode	Nickel (Ni)
3	Termination	Copper (Cu)
4		Nickel (Ni)
5		Tin (Sn)

7. PACKAGING

Packaging shall be done to protect the components from the damage during transportation and storing, and a label which has the following information shall be attached.

7.1 Each plastic bag for bulk packaging contains 1000pcs. And the minimum quantity for Bulk packaging is 1000pcs.

7.2 Tape packaging is as per 10. TAPE PACKAGING SPECIFICATION.

- 1) Inspection No.
- 2) TDK P/N
- 3) Customer's P/N
- 4) Quantity

*Composition of Inspection No.

Example $\frac{E}{(a)} \frac{1}{(b)} \frac{A}{(c)} - \frac{23}{(d)} - \frac{001}{(e)}$

- (a) Line code
- (b) Last digit of the year
- (c) Month and A for January and B for February and so on. (Skip I)
- (d) Inspection Date of the month.
- (e) Serial No. of the day

*Composition of new Inspection No.


(Implemented on and after May 1, 2019 in sequence)

Example $\frac{I}{(a)} \frac{F}{(b)} \frac{1}{(c)} \frac{E}{(d)} \frac{23}{(e)} \frac{A0}{(f)} \frac{01}{(g)}$


- (a) Prefix
- (b) Line code
- (c) Last digit of the year
- (d) Month and A for January and B for February and so on. (Skip I)
- (e) Inspection Date of the month.
- (f) Serial No. of the day(00 ~ ZZ)
- (g) Suffix(00 ~ ZZ)

















* It was shifted to the new inspection No. on and after May 2019, but the implementation timing may be different depending on shipment bases.
Until the shift is completed, either current or new composition of inspection No. will be applied.


8. SETTING UP FOR ESD TEST








































9. CAUTION













No.	Process	Condition
1	Operating Condition (Storage, Use, Transportation)	<p>1-1. Storage, Use</p> <p>The capacitors must be stored in an ambient temperature of 5 to 40°C with a relative humidity of 20 to 70%RH. JIS C 60721-3-1 Class 1K2 should be followed for the other climatic conditions.</p> <ol style="list-style-type: none"> 1) High temperature and humidity environment may affect a capacitor's solder ability because it accelerates terminal oxidization. They also deteriorate performance of taping and packaging. Therefore, SMD capacitors shall be used within 6 months. For capacitors with terminal electrodes consisting of silver or silver-palladium which tend to become oxidized or sulfurized, use as soon as possible, such as within one month after opening the bag. 2) When capacitors are stored for a longer time period than 6 months, confirm the solderability of the capacitors prior to use. During storage, keep the minimum packaging unit in its original packaging without opening it. Do not deviate from the above temperature and humidity conditions even for a short term. 3) Corrosive gasses in the air or atmosphere may result in deterioration of the reliability, such as poor solderability of the terminal electrodes. Do not store capacitors where they will be exposed to corrosive gas (e.g., hydrogen sulfide, sulfur dioxide, chlorine ammonia etc.) 4) Solderability and electrical performance may deteriorate due to photochemical change in the terminal electrode if stored in direct sunlight, or due to condensation from rapid changes in humidity. The capacitors especially which use resin material must be operated and stored in an environment free of dew condensation, as moisture absorption due to condensation may affect the performance. 5) Refer to JIS C 60721-3-1, class 1K2 for other climate conditions. <p>1-2. Handling in transportation</p> <p>In case of the transportation of the capacitors, the performance of the capacitors may be deteriorated depending on the transportation condition. (Refer to JEITA RCR-2335C 9.2 Handling in transportation)</p>
2	Circuit design  Caution	<p>2-1. Operating temperature</p> <ol style="list-style-type: none"> 1) Upper category temperature (maximum operating temperature) is specified. It is necessary to select a capacitor whose rated temperature is higher than the operating temperature. Also, it is necessary to consider the temperature distribution in the equipment and seasonal temperature variation. 2) Do not use capacitors above the maximum allowable operating temperature. Surface temperature including self heating should be below maximum operating temperature. (Due to dielectric loss, capacitors will heat itself when AC is applied. Especially for high frequency circuit, the heat might be so extreme that it may damage itself or the product mounted on. Please design the circuit so that the maximum temperature of the capacitors including the self heating to be below the maximum allowable operating temperature. Temperature rise at capacitor surface shall be below 20°C) 3) The electrical characteristics of the capacitors will vary depending on the temperature. The capacitors should be selected and designed in taking the temperature into consideration. <p>2-2. When overvoltage is applied</p> <p>Applying overvoltage to a capacitor may cause dielectric breakdown and result in a short circuit. The duration until dielectric breakdown depends on the applied voltage and the ambient temperature.</p>

No.	Process	Condition														
2	Circuit design  Caution	<p>2-3. Operating voltage</p> <p>1) Operating voltage across the terminals should be below the rated voltage. When AC and DC are super imposed, V_{0-P} must be below the rated voltage. — (1) and (2)</p> <p>AC or pulse with overshooting, V_{P-P} must be below the rated voltage. — (3), (4) and (5)</p> <p>When the voltage is started to apply to the circuit or it is stopped applying, the irregular voltage may be generated for a transit period because of resonance or switching. Be sure to use the capacitors within rated voltage containing these Irregular voltage.</p> <table border="1" data-bbox="472 517 1445 786"> <thead> <tr> <th data-bbox="472 517 660 555">Voltage</th> <th data-bbox="660 517 922 555">(1) DC voltage</th> <th data-bbox="922 517 1184 555">(2) DC+AC voltage</th> <th data-bbox="1184 517 1445 555">(3) AC voltage</th> </tr> </thead> <tbody> <tr> <td data-bbox="472 555 660 786">Positional Measurement (Rated voltage)</td> <td data-bbox="660 555 922 786">  </td> <td data-bbox="922 555 1184 786">  </td> <td data-bbox="1184 555 1445 786">  </td> </tr> </tbody> </table> <table border="1" data-bbox="472 819 1184 1088"> <thead> <tr> <th data-bbox="472 819 660 857">Voltage</th> <th data-bbox="660 819 922 857">(4) Pulse voltage (A)</th> <th data-bbox="922 819 1184 857">(5) Pulse voltage (B)</th> </tr> </thead> <tbody> <tr> <td data-bbox="472 857 660 1088">Positional Measurement (Rated voltage)</td> <td data-bbox="660 857 922 1088">  </td> <td data-bbox="922 857 1184 1088">  </td> </tr> </tbody> </table> <p>2) Even below the rated voltage, if repetitive high frequency AC or pulse is applied, the reliability of the capacitors may be reduced.</p> <p>3) The effective capacitance will vary depending on applied DC and AC voltages. The capacitors should be selected and designed in taking the voltages into consideration.</p> <p>4) Abnormal voltage (surge voltage, static electricity, pulse voltage, etc.) shall not exceed the rated voltage.</p> <p>5) When capacitors are used in a series connection, it is necessary to add a balancing circuit such as voltage dividing resistors in order to avoid an imbalance in the voltage applied to each capacitor.</p> <p>2-4. Frequency When the capacitors (Class 2) are used in AC and/or pulse voltages, the capacitors may vibrate themselves and generate audible sound.</p>	Voltage	(1) DC voltage	(2) DC+AC voltage	(3) AC voltage	Positional Measurement (Rated voltage)				Voltage	(4) Pulse voltage (A)	(5) Pulse voltage (B)	Positional Measurement (Rated voltage)		
Voltage	(1) DC voltage	(2) DC+AC voltage	(3) AC voltage													
Positional Measurement (Rated voltage)																
Voltage	(4) Pulse voltage (A)	(5) Pulse voltage (B)														
Positional Measurement (Rated voltage)																


No.	Process	Condition																								
3	Designing P.C.board	<p>The amount of solder at the terminations has a direct effect on the reliability of the capacitors.</p> <ol style="list-style-type: none"> 1) The greater the amount of solder, the higher the stress on the chip capacitors, and the more likely that it will break. When designing a P.C.board, determine the shape and size of the solder lands to have proper amount of solder on the terminations. 2) Avoid using common solder land for multiple terminations and provide individual solder land for each terminations. 3) Size and recommended land dimensions. <div style="text-align: center;">  <p>The diagram shows a top-down view of a chip capacitor mounted on a PCB. The capacitor is represented by two grey rectangular pads. Dimension 'A' is the length of the capacitor pads. Dimension 'B' is the width of the solder land between the pads. Dimension 'C' is the height of the solder land. The PCB is shown as a hatched area with 'Solder resist' indicated by an arrow. Labels 'Chip capacitors' and 'Solder land' also have arrows pointing to their respective parts.</p> </div> <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th colspan="2" style="text-align: left;">Reflow soldering (mm)</th> </tr> <tr> <th style="text-align: left;">Case size</th> <th style="text-align: left;">CGA3 (CC0603)</th> </tr> <tr> <th style="text-align: left;">Symbol</th> <th></th> </tr> </thead> <tbody> <tr> <td style="text-align: center;">A</td> <td style="text-align: center;">0.6 ~ 0.8</td> </tr> <tr> <td style="text-align: center;">B</td> <td style="text-align: center;">0.6 ~ 0.8</td> </tr> <tr> <td style="text-align: center;">C</td> <td style="text-align: center;">0.6 ~ 0.8</td> </tr> </tbody> </table> <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th colspan="2" style="text-align: left;">Flow soldering (Unrecommend) (mm)</th> </tr> <tr> <th style="text-align: left;">Case size</th> <th style="text-align: left;">CGA3 (CC0603)</th> </tr> <tr> <th style="text-align: left;">Symbol</th> <th></th> </tr> </thead> <tbody> <tr> <td style="text-align: center;">A</td> <td style="text-align: center;">0.7 ~ 1.0</td> </tr> <tr> <td style="text-align: center;">B</td> <td style="text-align: center;">0.8 ~ 1.0</td> </tr> <tr> <td style="text-align: center;">C</td> <td style="text-align: center;">0.6 ~ 0.8</td> </tr> </tbody> </table>	Reflow soldering (mm)		Case size	CGA3 (CC0603)	Symbol		A	0.6 ~ 0.8	B	0.6 ~ 0.8	C	0.6 ~ 0.8	Flow soldering (Unrecommend) (mm)		Case size	CGA3 (CC0603)	Symbol		A	0.7 ~ 1.0	B	0.8 ~ 1.0	C	0.6 ~ 0.8
Reflow soldering (mm)																										
Case size	CGA3 (CC0603)																									
Symbol																										
A	0.6 ~ 0.8																									
B	0.6 ~ 0.8																									
C	0.6 ~ 0.8																									
Flow soldering (Unrecommend) (mm)																										
Case size	CGA3 (CC0603)																									
Symbol																										
A	0.7 ~ 1.0																									
B	0.8 ~ 1.0																									
C	0.6 ~ 0.8																									




No.	Process	Condition												
3	Designing P.C.board	<p>4) Recommended chip capacitors layout is as following.</p> <table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th style="width: 20%;"></th> <th style="width: 40%;">Disadvantage against bending stress</th> <th style="width: 40%;">Advantage against bending stress</th> </tr> </thead> <tbody> <tr> <td style="text-align: center; vertical-align: middle;">Mounting face</td> <td style="text-align: center;"> <p>Perforation or slit</p>  <p>Break P.C.board with mounted side up.</p> </td> <td style="text-align: center;"> <p>Perforation or slit</p>  <p>Break P.C.board with mounted side down.</p> </td> </tr> <tr> <td style="text-align: center; vertical-align: middle;">Chip arrangement (Direction)</td> <td style="text-align: center;"> <p>Perforation or slit</p>  </td> <td style="text-align: center;"> <p>Perforation or slit</p>  </td> </tr> <tr> <td style="text-align: center; vertical-align: middle;">Distance from slit</td> <td style="text-align: center;"> <p>Closer to slit is higher stress</p>  <p style="text-align: right;">$(l_1 < l_2)$</p> </td> <td style="text-align: center;"> <p>Away from slit is less stress</p>  <p style="text-align: right;">$(l_1 < l_2)$</p> </td> </tr> </tbody> </table>		Disadvantage against bending stress	Advantage against bending stress	Mounting face	<p>Perforation or slit</p>  <p>Break P.C.board with mounted side up.</p>	<p>Perforation or slit</p>  <p>Break P.C.board with mounted side down.</p>	Chip arrangement (Direction)	<p>Perforation or slit</p> 	<p>Perforation or slit</p> 	Distance from slit	<p>Closer to slit is higher stress</p>  <p style="text-align: right;">$(l_1 < l_2)$</p>	<p>Away from slit is less stress</p>  <p style="text-align: right;">$(l_1 < l_2)$</p>
	Disadvantage against bending stress	Advantage against bending stress												
Mounting face	<p>Perforation or slit</p>  <p>Break P.C.board with mounted side up.</p>	<p>Perforation or slit</p>  <p>Break P.C.board with mounted side down.</p>												
Chip arrangement (Direction)	<p>Perforation or slit</p> 	<p>Perforation or slit</p> 												
Distance from slit	<p>Closer to slit is higher stress</p>  <p style="text-align: right;">$(l_1 < l_2)$</p>	<p>Away from slit is less stress</p>  <p style="text-align: right;">$(l_1 < l_2)$</p>												


No.	Process	Condition												
3	Designing P.C.board	<p>5) Mechanical stress varies according to location of chip capacitors on the P.C.board.</p>  <p>When dividing printed wiring boards, the intensities of mechanical stress applied to capacitors are different according to each dividing method in the order of : Push-back < Slit < V-groove < Perforation. Therefore consider not only position of capacitors, but also the way of the dividing the printed wiring boards.</p> <p>6) Layout recommendation</p> <table border="1"> <thead> <tr> <th data-bbox="379 1034 539 1151">Example</th> <th data-bbox="539 1034 842 1151">Use of common solder land</th> <th data-bbox="842 1034 1152 1151">Soldering with chassis</th> <th data-bbox="1152 1034 1489 1151">Use of common solder land with other SMD</th> </tr> </thead> <tbody> <tr> <td data-bbox="379 1151 539 1532">Need to avoid</td> <td data-bbox="539 1151 842 1532">  </td> <td data-bbox="842 1151 1152 1532">  </td> <td data-bbox="1152 1151 1489 1532">  </td> </tr> <tr> <td data-bbox="379 1532 539 1944">Recommendation</td> <td data-bbox="539 1532 842 1944">  </td> <td data-bbox="842 1532 1152 1944">  <p>$l_2 > l_1$</p> </td> <td data-bbox="1152 1532 1489 1944">  </td> </tr> </tbody> </table>	Example	Use of common solder land	Soldering with chassis	Use of common solder land with other SMD	Need to avoid				Recommendation		 <p>$l_2 > l_1$</p>	
Example	Use of common solder land	Soldering with chassis	Use of common solder land with other SMD											
Need to avoid														
Recommendation		 <p>$l_2 > l_1$</p>												


No.	Process	Condition									
4	Mounting	<p>4-1. Stress from mounting head If the mounting head is adjusted too low, it may induce excessive stress in the chip capacitors to result in cracking. Please take following precautions.</p> <ol style="list-style-type: none"> 1) Adjust the bottom dead center of the mounting head to reach on the P.C.board surface and not press it. 2) Adjust the mounting head pressure to be 1 to 3N of static weight. 3) To minimize the impact energy from mounting head, it is important to provide support from the bottom side of the P.C.board. See following examples. <table border="1" style="width: 100%; border-collapse: collapse;"> <thead> <tr> <th data-bbox="480 566 663 611"></th> <th data-bbox="663 566 1059 611">Not recommended</th> <th data-bbox="1059 566 1433 611">Recommended</th> </tr> </thead> <tbody> <tr> <td data-bbox="480 611 663 875">Single sided mounting</td> <td data-bbox="663 611 1059 875">  </td> <td data-bbox="1059 611 1433 875">  <p>A support pin is not to be underneath the capacitor.</p> </td> </tr> <tr> <td data-bbox="480 875 663 1140">Double-sides mounting</td> <td data-bbox="663 875 1059 1140">  <p>Solder peeling Crack</p> </td> <td data-bbox="1059 875 1433 1140">  <p>Support pin</p> </td> </tr> </tbody> </table> <p>When the centering jaw is worn out, it may give mechanical impact on the capacitors to cause crack. Please control the close up dimension of the centering jaw and provide sufficient preventive maintenance and replacement of it.</p>		Not recommended	Recommended	Single sided mounting		 <p>A support pin is not to be underneath the capacitor.</p>	Double-sides mounting	 <p>Solder peeling Crack</p>	 <p>Support pin</p>
	Not recommended	Recommended									
Single sided mounting		 <p>A support pin is not to be underneath the capacitor.</p>									
Double-sides mounting	 <p>Solder peeling Crack</p>	 <p>Support pin</p>									


No.	Process	Condition														
5	Soldering	<p>5-1. Flux selection</p> <p>Flux can seriously affect the performance of capacitors. Confirm the following to select the appropriate flux.</p> <ol style="list-style-type: none"> 1) It is recommended to use a mildly activated rosin flux (less than 0.1wt% chlorine). Strong flux is not recommended. 2) Excessive flux must be avoided. Please provide proper amount of flux. 3) When water-soluble flux is used, enough washing is necessary. <p>5-2. Recommended soldering profile : Reflow method</p> <p>Refer to the following temperature profile at Reflow soldering.</p> <div style="text-align: center;"> <p>Reflow soldering</p> </div> <p>5-3. Recommended soldering peak temp and peak temp duration for Reflow soldering</p> <p>Pb free solder is recommended, but if Sn-37Pb must be used, refer to below.</p> <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th rowspan="2" style="text-align: center;">Temp./Duration</th> <th colspan="2" style="text-align: center;">Reflow soldering</th> </tr> <tr> <th style="text-align: center;">Peak temp(°C)</th> <th style="text-align: center;">Duration(sec.)</th> </tr> </thead> <tbody> <tr> <td style="text-align: center;">Solder</td> <td></td> <td></td> </tr> <tr> <td style="text-align: center;">Lead Free Solder</td> <td style="text-align: center;">260 max.</td> <td style="text-align: center;">10 max.</td> </tr> <tr> <td style="text-align: center;">Sn-Pb Solder</td> <td style="text-align: center;">230 max.</td> <td style="text-align: center;">20 max.</td> </tr> </tbody> </table> <p>Recommended solder compositions Lead Free Solder : Sn-3.0Ag-0.5Cu</p>	Temp./Duration	Reflow soldering		Peak temp(°C)	Duration(sec.)	Solder			Lead Free Solder	260 max.	10 max.	Sn-Pb Solder	230 max.	20 max.
Temp./Duration	Reflow soldering															
	Peak temp(°C)	Duration(sec.)														
Solder																
Lead Free Solder	260 max.	10 max.														
Sn-Pb Solder	230 max.	20 max.														
























No.	Process	Condition																				
5	Soldering	<p>5-4. Soldering profile : Flow method (Unrecommend) Refer to the following temperature profile at Flow soldering.</p> <div style="text-align: center;">  <p>The graph shows a temperature profile for flow soldering. The y-axis is labeled 'Temp. (°C)' and the x-axis is labeled 'Peak Temp time'. The profile is divided into three phases: 'Preheating', 'Soldering', and 'Natural cooling'. The 'Preheating' phase shows a linear increase in temperature from 0 to a peak level, with a time duration of 'Over 60 sec.' and a temperature difference ΔT indicated. The 'Soldering' phase is a constant peak temperature plateau, also with a time duration of 'Over 60 sec.'. The 'Natural cooling' phase shows a non-linear decrease in temperature back to 0, with a time duration of 'Over 60 sec.'.</p> </div> <p>Reflow soldering is recommended.</p> <p>5-5. Recommended soldering peak temp and peak temp duration for Flow soldering Pb free solder is recommended, but if Sn-37Pb must be used, refer to below.</p> <table border="1" data-bbox="587 936 1332 1173"> <thead> <tr> <th rowspan="2" style="text-align: center;">Temp./Duration</th> <th colspan="2" style="text-align: center;">Flow soldering</th> </tr> <tr> <th style="text-align: center;">Peak temp(°C)</th> <th style="text-align: center;">Duration(sec.)</th> </tr> </thead> <tbody> <tr> <td style="text-align: center;">Solder</td> <td></td> <td></td> </tr> <tr> <td style="text-align: center;">Lead Free Solder</td> <td style="text-align: center;">260 max.</td> <td style="text-align: center;">5 max.</td> </tr> <tr> <td style="text-align: center;">Sn-Pb Solder</td> <td style="text-align: center;">250 max.</td> <td style="text-align: center;">3 max.</td> </tr> </tbody> </table> <p>Recommended solder compositions Lead Free Solder : Sn-3.0Ag-0.5Cu</p> <p>5-6. Avoiding thermal shock</p> <p>1) Preheating condition</p> <table border="1" data-bbox="587 1361 1161 1509"> <thead> <tr> <th style="text-align: center;">Soldering</th> <th style="text-align: center;">Temp. (°C)</th> </tr> </thead> <tbody> <tr> <td style="text-align: center;">Reflow soldering</td> <td style="text-align: center;">$\Delta T \leq 150$</td> </tr> <tr> <td style="text-align: center;">Flow soldering</td> <td style="text-align: center;">$\Delta T \leq 150$</td> </tr> </tbody> </table> <p>2) Cooling condition Natural cooling using air is recommended. If the chips are dipped into a solvent for cleaning, the temperature difference (ΔT) must be less than 100°C.</p>	Temp./Duration	Flow soldering		Peak temp(°C)	Duration(sec.)	Solder			Lead Free Solder	260 max.	5 max.	Sn-Pb Solder	250 max.	3 max.	Soldering	Temp. (°C)	Reflow soldering	$\Delta T \leq 150$	Flow soldering	$\Delta T \leq 150$
Temp./Duration	Flow soldering																					
	Peak temp(°C)	Duration(sec.)																				
Solder																						
Lead Free Solder	260 max.	5 max.																				
Sn-Pb Solder	250 max.	3 max.																				
Soldering	Temp. (°C)																					
Reflow soldering	$\Delta T \leq 150$																					
Flow soldering	$\Delta T \leq 150$																					









No.	Process	Condition
5	Soldering	<p>5-7. Amount of solder Excessive solder will induce higher tensile force in chip capacitors when temperature changes and it may result in chip cracking. In sufficient solder may detach the capacitors from the P.C.board.</p> <hr/> <div style="display: flex; justify-content: space-between;"> <div data-bbox="496 421 619 488">Excessive solder</div> <div data-bbox="683 405 1094 510">  </div> <div data-bbox="1121 405 1409 495">Higher tensile force in chip capacitors to cause crack</div> </div> <hr/> <div style="display: flex; justify-content: space-between;"> <div data-bbox="496 591 612 618">Adequate</div> <div data-bbox="683 551 1262 656">  </div> </div> <hr/> <div style="display: flex; justify-content: space-between;"> <div data-bbox="496 725 627 792">Insufficient solder</div> <div data-bbox="683 710 1094 815">  </div> <div data-bbox="1121 696 1409 815">Low robustness may cause contact failure or chip capacitors come off the P.C.board.</div> </div> <hr/> <p>5-8. Sn-Zn solder Sn-Zn solder affects product reliability. Please contact TDK in advance when utilize Sn-Zn solder.</p> <p>5-9. Countermeasure for tombstone The misalignment between the mounted positions of the capacitors and the land patterns should be minimized. The tombstone phenomenon may occur especially the capacitors are mounted (in longitudinal direction) in the same direction of the reflow soldering. (Refer to JEITA RCR-2335C Annex A (Informative), Recommendations to prevent the tombstone phenomenon.)</p>


No.	Process	Condition												
6	Solder repairing	<p>Solder repairing is unavoidable, refer to below.</p> <p>6-1.Soldering rework using spot heater Heat stress during rework may possibly be reduced by using a spot heater (also called a “blower”) rather than a soldering iron. It is applied only to adding solder in the case of insufficient solder amount.</p> <p>1) Reworking using a spot heater may suppress the occurrence of cracks in the capacitor compared to using a soldering iron. A spot heater can heat up a capacitor uniformly with a small heat gradient which leads to lower thermal stress caused by quick heating and cooling or localized heating. Moreover, where ultra-small capacitors are mounted close together on a printed circuit board, reworking with a spot heater can eliminate the risk of direct contact between the tip of a soldering iron and a capacitor.</p> <p>2) Rework condition If the blower nozzle of a spot heater is too close to a capacitor, a crack in the capacitor may occur due to heat stress. Below are recommendations for avoiding such an occurrence. Keep more than 5mm between a capacitor and a spot heater nozzle. The blower temperature of the spot heater shall be lower than 400°C. The airflow shall be set as weak as possible. The diameter of the nozzle is recommended to be 2mm(one-outlet type).The size is standard and common. Duration of blowing hot air is recommended to be 10s or less, considering surface area of the capacitor and melting temperature of solder. The angle between the nozzle and the capacitor is recommended to be 45degrees in order to work easily and to avoid partial area heating. As is the case when using a soldering iron, preheating reduces thermal stress on capacitors and improves operating efficiency.</p> <ul style="list-style-type: none"> Recommended rework condition (Consult the component manufactures for details.) <table border="1" data-bbox="507 1160 1453 1491"> <tbody> <tr> <td>Distance from nozzle</td> <td>5mm and over</td> </tr> <tr> <td>Nozzle angle</td> <td>45degrees</td> </tr> <tr> <td>Nozzle temp.</td> <td>400°C and less</td> </tr> <tr> <td>Airflow</td> <td>Set as weak as possible (The airflow shall be the minimum value necessary for solder to melt in the conditions mentioned above.)</td> </tr> <tr> <td>Nozzle diameter</td> <td>φ2mm (one-outlet type)</td> </tr> <tr> <td>Blowing duration</td> <td>10s and less</td> </tr> </tbody> </table> <ul style="list-style-type: none"> Example of recommended spot heater use  <p>3) Amount of solder should be suitable to form a proper fillet shape. Excess solder causes mechanical and thermal stress on a capacitor and results in cracks. Insufficient solder causes weak adherence of the capacitor to the substrate and may result in detachment of a capacitor and deteriorate reliability of the printed wiring board. See the example of appropriate solder fillet shape for 5-5.Amount of solder.</p>	Distance from nozzle	5mm and over	Nozzle angle	45degrees	Nozzle temp.	400°C and less	Airflow	Set as weak as possible (The airflow shall be the minimum value necessary for solder to melt in the conditions mentioned above.)	Nozzle diameter	φ2mm (one-outlet type)	Blowing duration	10s and less
Distance from nozzle	5mm and over													
Nozzle angle	45degrees													
Nozzle temp.	400°C and less													
Airflow	Set as weak as possible (The airflow shall be the minimum value necessary for solder to melt in the conditions mentioned above.)													
Nozzle diameter	φ2mm (one-outlet type)													
Blowing duration	10s and less													

No.	Process	Condition																		
6	Solder repairing	<p>6-2. Solder repair by solder iron</p> <p>1) Selection of the soldering iron tip Tip temperature of solder iron varies by its type, P.C.board material and solder land size. The higher the tip temperature, the quicker the operation. However, heat shock may cause a crack in the chip capacitors. Please make sure the tip temp. before soldering and keep the peak temp and time in accordance with following recommended condition.</p> <div style="text-align: center;"> <p>Manual soldering (Solder iron)</p>  </div> <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th colspan="4" style="text-align: center;">Recommended solder iron condition (Sn-Pb Solder and Lead Free Solder)</th> </tr> <tr> <th style="text-align: center;">Temp. (°C)</th> <th style="text-align: center;">Duration (sec.)</th> <th style="text-align: center;">Wattage (W)</th> <th style="text-align: center;">Shape (mm)</th> </tr> </thead> <tbody> <tr> <td style="text-align: center;">350 max.</td> <td style="text-align: center;">3 max.</td> <td style="text-align: center;">20 max.</td> <td style="text-align: center;">Ø 3.0 max.</td> </tr> </tbody> </table> <p>* Please preheat the chip capacitors with the condition in 6-3 to avoid the thermal shock.</p> <p>2) Direct contact of the soldering iron with ceramic dielectric of chip capacitors may cause crack. Do not touch the ceramic dielectric and the terminations by solder iron.</p> <p>6-3. Avoiding thermal shock</p> <table border="1" style="margin-left: auto; margin-right: auto;"> <thead> <tr> <th colspan="2" style="text-align: center;">Preheating condition</th> </tr> <tr> <th style="text-align: center;">Soldering</th> <th style="text-align: center;">Temp. (°C)</th> </tr> </thead> <tbody> <tr> <td style="text-align: center;">Manual soldering</td> <td style="text-align: center;">$\Delta T \leq 150$</td> </tr> </tbody> </table>	Recommended solder iron condition (Sn-Pb Solder and Lead Free Solder)				Temp. (°C)	Duration (sec.)	Wattage (W)	Shape (mm)	350 max.	3 max.	20 max.	Ø 3.0 max.	Preheating condition		Soldering	Temp. (°C)	Manual soldering	$\Delta T \leq 150$
Recommended solder iron condition (Sn-Pb Solder and Lead Free Solder)																				
Temp. (°C)	Duration (sec.)	Wattage (W)	Shape (mm)																	
350 max.	3 max.	20 max.	Ø 3.0 max.																	
Preheating condition																				
Soldering	Temp. (°C)																			
Manual soldering	$\Delta T \leq 150$																			

No.	Process	Condition
7	Cleaning	<p>1) If an unsuitable cleaning fluid is used, flux residue or some foreign articles may stick to chip capacitors surface to deteriorate especially the insulation resistance.</p> <p>2) If cleaning condition is not suitable, it may damage the chip capacitors.</p> <p>2)-1. Insufficient washing</p> <p>(1) Terminal electrodes may corrode by Halogen in the flux.</p> <p>(2) Halogen in the flux may adhere on the surface of capacitors, and lower the insulation resistance.</p> <p>(3) Water soluble flux has higher tendency to have above mentioned problems (1) and (2).</p> <p>2)-2. Excessive washing When ultrasonic cleaning is used, excessively high ultrasonic energy output can affect the connection between the ceramic chip capacitor's body and the terminal electrode. To avoid this, following is the recommended condition.</p> <p style="padding-left: 40px;">Power : 20W/ ℓ max. Frequency : 40kHz max. Washing time : 5 minutes max.</p> <p>2)-3. If the cleaning fluid is contaminated, density of Halogen increases, and it may bring the same result as insufficient cleaning.</p>
8	Coating and molding of the P.C.board	<p>1) When the P.C.board is coated, please verify the quality influence on the product.</p> <p>2) Please verify carefully that there is no harmful decomposing or reaction gas emission during curing which may damage the chip capacitors.</p> <p>3) Please verify the curing temperature.</p>
9	Handling after chip mounted ⚠ Caution	<p>1) Please pay attention not to bend or distort the P.C.board after soldering in handling otherwise the chip capacitors may crack.</p> <div style="text-align: center;">  </div>

No.	Process	Condition																
9	Handling after chip mounted  Caution	<p>2) Printed circuit board cropping should not be carried out by hand, but by using the proper tooling. Printed circuit board cropping should be carried out using a board cropping jig as shown in the following figure or a board cropping apparatus to prevent inducing mechanical stress on the board.</p> <p>(1) Example of a board cropping jig Recommended example: The board should be pushed from the back side, close to the cropping jig so that the board is not bent and the stress applied to the capacitor is compressive. Unrecommended example: If the pushing point is far from the cropping jig and the pushing direction is from the front side of the board, large tensile stress is applied to the capacitor, which may cause cracks.</p> <div style="display: flex; justify-content: space-around;"> <div data-bbox="459 577 758 855"> <p>Outline of jig</p>  </div> <div data-bbox="762 568 1439 831"> <table border="1"> <thead> <tr> <th data-bbox="762 568 1098 622">Recommended</th> <th data-bbox="1098 568 1439 622">Unrecommended</th> </tr> </thead> <tbody> <tr> <td data-bbox="762 622 1098 831">  </td> <td data-bbox="1098 622 1439 831">  </td> </tr> </tbody> </table> </div> </div> <p>(2) Example of a board cropping machine</p> <p>An outline of a printed circuit board cropping machine is shown below. The top and bottom blades are aligned with one another along the lines with the V-grooves on printed circuit board when cropping the board.</p> <p>Unrecommended example: Misalignment of blade position between top and bottom, right and left, or front and rear blades may cause a crack in the capacitor.</p> <div style="display: flex; justify-content: space-around; margin-top: 20px;"> <div data-bbox="555 1167 965 1429"> <p>Outline of machine</p>  </div> <div data-bbox="965 1167 1407 1413"> <p>Principle of operation</p>  </div> </div> <div style="text-align: center; margin-top: 20px;"> <p>Cross-section diagram</p>  </div> <div style="margin-top: 20px;"> <table border="1" style="width: 100%; text-align: center;"> <thead> <tr> <th data-bbox="641 1646 821 1731">Recommended</th> <th colspan="3" data-bbox="821 1646 1353 1697">Unrecommended</th> </tr> <tr> <th></th> <th data-bbox="821 1697 1002 1771">Top-bottom misalignment</th> <th data-bbox="1002 1697 1166 1771">Left-right misalignment</th> <th data-bbox="1166 1697 1353 1771">Front-rear misalignment</th> </tr> </thead> <tbody> <tr> <td data-bbox="641 1731 821 2072">  </td> <td data-bbox="821 1771 1002 2072">  </td> <td data-bbox="1002 1771 1166 2072">  </td> <td data-bbox="1166 1771 1353 2072">  </td> </tr> </tbody> </table> </div>	Recommended	Unrecommended			Recommended	Unrecommended				Top-bottom misalignment	Left-right misalignment	Front-rear misalignment				
Recommended	Unrecommended																	
																		
Recommended	Unrecommended																	
	Top-bottom misalignment	Left-right misalignment	Front-rear misalignment															
																		

No.	Process	Condition						
9	Handling after chip mounted ⚠ Caution	<p>3) When functional check of the P.C.board is performed, check pin pressure tends to be adjusted higher for fear of loose contact. But if the pressure is excessive and bend the P.C.board, it may crack the chip capacitors or peel the terminations off. Please adjust the check pins not to bend the P.C.board.</p> <table border="1" data-bbox="475 383 1433 680"> <thead> <tr> <th data-bbox="475 383 616 443">Item</th> <th data-bbox="616 383 1034 443">Not recommended</th> <th data-bbox="1034 383 1433 443">Recommended</th> </tr> </thead> <tbody> <tr> <td data-bbox="475 443 616 680">Board bending</td> <td data-bbox="616 443 1034 680">  <p>Termination peeling Check pin</p> </td> <td data-bbox="1034 443 1433 680">  <p>Support pin Check pin</p> </td> </tr> </tbody> </table>	Item	Not recommended	Recommended	Board bending	 <p>Termination peeling Check pin</p>	 <p>Support pin Check pin</p>
Item	Not recommended	Recommended						
Board bending	 <p>Termination peeling Check pin</p>	 <p>Support pin Check pin</p>						
10	Handling of loose chip capacitors	<p>1) If dropped the chip capacitors may crack. Once dropped do not use it. Especially, the large case sized chip capacitors are tendency to have cracks easily, so please handle with care.</p>  <p>Floor</p> <p>Crack</p> <p>2) Piling the P.C.board after mounting for storage or handling, the corner of the P.C. board may hit the chip capacitors of another board to cause crack.</p>  <p>P.C.board</p> <p>Crack</p>						
11	Capacitance aging	The capacitors (Class 2) have aging in the capacitance. They may not be used in precision time constant circuit. In case of the time constant circuit, the evaluation should be done well.						
12	Estimated life and estimated failure rate of capacitors	As per the estimated life and the estimated failure rate depend on the temperature and the voltage. This can be calculated by the equation described in JEITA RCR-2335C Annex F (Informative) Calculation of the estimated lifetime and the estimated failure rate (Voltage acceleration coefficient : 3 multiplication rule, Temperature acceleration coefficient : 10°C rule) The failure rate can be decreased by reducing the temperature and the voltage but they will not be guaranteed.						

No.	Process	Condition
13	Caution during operation of equipment	<p>1) A capacitor shall not be touched directly with bare hands during operation in order to avoid electric shock. Electric energy held by the capacitor may be discharged through the human body when touched with a bare hand. Even when the equipment is off, a capacitor may stay charged. The capacitor should be handled after being completely discharged using a resistor.</p> <p>2) The terminals of a capacitor shall not be short-circuited by any accidental contact with a conductive object. A capacitor shall not be exposed to a conductive liquid such as an acid or alkali solution. A conductive object or liquid, such as acid and alkali, between the terminals may lead to the breakdown of a capacitor due to short circuit</p> <p>3) Confirm that the environment to which the equipment will be exposed during transportation and operation meets the specified conditions. Do not to use the equipment in the following environments.</p> <p>(1) Environment where a capacitor is splattered with water or oil (2) Environment where a capacitor is exposed to direct sunlight (3) Environment where a capacitor is exposed to Ozone, ultraviolet rays or radiation (4) Environment where a capacitor exposed to corrosive gas(e.g. hydrogen sulfide, sulfur dioxide, chlorine. ammonia gas etc.) (5) Environment where a capacitor exposed to vibration or mechanical shock exceeding the specified limits. (6) Atmosphere change with causes condensation</p>
14	Others  Caution	<p>The product listed in this specification is intended for use in automotive applications under-normal operation and usage conditions.</p> <p>The product is not designed or warranted to meet the requirements of application listed below, whose performance and/or quality requires a more stringent level of safety or reliability, or whose failure, malfunction or defect could cause serious damage to society, person or property. Please understand that we are not responsible for any damage or liability caused by use of the products in any of the applications below or for any other use exceeding the range or conditions set forth in this specification sheet. If you intend to use the products in the applications listed below or if you have special requirements exceeding the range or conditions set forth in this specification, please contact us.</p> <p>(1) Aerospace/Aviation equipment (2) Transportation equipment (electric trains, ships etc.) (3) Medical equipment (Excepting Pharmaceutical Affairs Law classification Class1, 2) (4) Power-generation control equipment (5) Atomic energy-related equipment (6) Seabed equipment (7) Transportation control equipment (8) Public information-processing equipment (9) Military equipment (10) Electric heating apparatus, burning equipment (11) Disaster prevention/crime prevention equipment (12) Safety equipment (13) Other applications that are not considered general-purpose applications</p> <p>When designing your equipment even for general-purpose applications, you are kindly requested to take into consideration securing protection circuit/device or providing backup circuits in your equipment. In addition, although the products listed in this specification is intended for use in automotive application as described above, it is not prohibited to use for general electronic equipment, whose performance and/or quality doesn't require a more stringent level of safety or reliability, or whose failure, malfunction or defect could not cause serious damage to society, person or property. Therefore, the description of this caution will be applied, when the products are used in general electronic equipment under a normal operation and usage conditions.</p>


10. TAPE PACKAGING SPECIFICATION

1. CONSTRUCTION AND DIMENSION OF TAPING

1-1. Dimensions of carrier tape

Dimensions of paper tape shall be according to Appendix 4.

1-2. Bulk part and leader of taping




1-3. Dimensions of reel

Dimensions of $\phi 178$ reel shall be according to Appendix 5.

Dimensions of $\phi 330$ reel shall be according to Appendix 6.

1-4. Structure of taping




2. CHIP QUANTITY

Please refer to detail page on TDK web.

3. PERFORMANCE SPECIFICATIONS

3-1. Fixing peeling strength (top tape)

$0.05\text{N} < \text{Peeling strength} < 0.7\text{N}$



3-2. Carrier tape shall be flexible enough to be wound around a minimum radius of 30mm with components in tape.


3-3. The missing of components shall be less than 0.1%

3-4. Components shall not stick to fixing tape.

3-5. When removing the cover tape, there shall not be difficulties by unfitting clearance gap, burrs and crushes of cavities. Also the sprocket holes shall not be covered by absorbing dust into the suction nozzle.

Appendix 4

Paper Tape



(Unit : mm)


Symbol Case size	A	B	C	D	E	F
CGA3 (CC0603)	(1.10)	(1.90)	8.00 ± 0.30	3.50 ± 0.05	1.75 ± 0.10	4.00 ± 0.10

Symbol Case size	G	H	J	T
CGA3 (CC0603)	2.00 ± 0.05	4.00 ± 0.10	$\phi 1.50 \begin{matrix} +0.10 \\ 0 \end{matrix}$	1.20 max.

() Reference value.

Appendix 5

Dimensions of reel (Material : Polystyrene)




(Unit : mm)

Symbol	A	B	C	D	E	W1
Dimension	$\phi 178 \pm 2.0$	$\phi 60 \pm 2.0$	$\phi 13 \pm 0.5$	$\phi 21 \pm 0.8$	2.0 ± 0.5	9.0 ± 0.3
Symbol	W2	R				
Dimension	13.0 ± 1.4	1.0				

Appendix 6

Dimensions of reel (Material : Polystyrene)



(Unit : mm)

Symbol	A	B	C	D	E	W
Dimension	$\phi 382$ max. (Nominal $\phi 330$)	$\phi 50$ min.	$\phi 13 \pm 0.5$	$\phi 21 \pm 0.8$	2.0 ± 0.5	10.0 ± 1.5
Symbol	t	R				
Dimension	2.0 ± 0.5	1.0				