

PML12030A007V

EVALUATION DATA

型式データ

DWG.NO. C261-53-01		
承認	査閲	担当
<i>T. Uozumi</i>	<i>H. Inokawa</i>	<i>T. Masuda</i>
24. Oct. '12	24. Oct. '12	24. Oct. '12

INDEX


1. 評価方法	Evaluation Method	PAGE
1.1	測定回路 Measurement Circuits	T-1
	(1) 静特性、過電流保護特性、出力リップル・ノイズ波形 Steady state characteristics, Over current protection (OCP) characteristics, and Output ripple and noise waveform	
	(2) 過渡応答、その他 Dynamic response characteristics, and Other characteristics	
1.2	使用測定機器 List of equipment used	T-2
2.	特性データ Characteristics	
2.1	静特性 Steady state data	
	(1) 入力変動、負荷変動、温度変動 Line regulation, Load regulation, Temperature drift	T-3
	(2) 出力電圧、出力リップル・ノイズ電圧 対 入力電圧 Output voltage and Output ripple and noise voltage vs. Input voltage	T-4
	(3) 入力電流、効率 対 出力電流 Input current and Efficiency vs. Output current	T-5
	(4) 効率 対 入力電圧 Efficiency vs. Input voltage	T-6
	(5) 効率 対 ケース温度 Efficiency vs. Case temperature	T-7
	(6) 起動、停止電圧特性 Start and Stop voltage characteristics	T-8
2.2	待機電力特性 Standby power characteristics	T-9
2.3	通電ドリフト特性 Warm up voltage drift characteristics	T-9
2.4	過電流保護特性 Over current protection (OCP) characteristics	T-10
2.5	出力立ち上がり、立ち下がり特性 Output rise and fall characteristics	T-11
2.6	過渡応答(負荷急変)特性 Dynamic load response characteristics	T-15
2.7	出力リップル・ノイズ波形 Output ripple and noise waveform	T-16

使用記号 Terminology used


	Definition	
V_{in} 入力電圧	Input voltage
V_o 出力電圧	Output voltage
$V_{ON/OFF}$ ON/OFF 電圧	ON/OFF voltage
I_{in} 入力電流	Input current
I_o 出力電流	Output current
T_a 周囲温度	Ambient temperature
T_c ケース温度	Case temperature
f 周波数	Frequency

1. 評価方法 **Evaluation Method**
 1.1 測定回路 **Measurement Circuits**

- (1) 静特性、過電流保護特性、出力リップル・ノイズ波形
 Steady state characteristics, Over current protection (OCP) characteristics,
 and Output ripple and noise waveform



- (2) 過渡応答、その他
 Dynamic response characteristics, and Other characteristics



1.2 使用測定機器 List of equipment used

	EQUIPMENT USED	MANUFACTURER	MODEL NO.
1	DC POWER SUPPLY	KIKUSUI	PWR800L
2	CARBON PLATE RHEOSTATS	YAMABISHI ELECTRIC	RC-3
3	DYNAMIC DUMMY LOAD	KEISOKU GIKEN	ELL-1005
4	DATA ACQUISITION / SWITCH UNIT	AGILENT	34970A
5	SHUNT RESISTER	YOKOGAWA ELECT.	2215
6	CONTROLLED TEMP. CHAMBER	ESPEC CORP.	SU-261
7	DIGITAL PHOSPHOR OSCILLOSCOPE	TEKTRONIX	TDS3012
8	DIGITAL STORAGE OSCILLOSCOPE	YOKOGAWA ELECT.	DL9040L
9	CURRENT PROBE	YOKOGAWA ELECT.	701930
10	HYBRID RECORDER	YOKOGAWA ELECT.	MV230

2. 特性データ Characteristics

2.1 静特性 Steady state data

(1) 入力変動、負荷変動、温度変動 Line regulation, Load regulation, Temperature drift

 $V_o = 0.7\text{ V}$

1. Line regulation and Load regulation

Conditions $T_c : 25^\circ\text{C}$
Air Velocity : 1m/s

$I_o \setminus V_{in}$	8VDC	12VDC	14VDC	Line regulation	
0%	0.7003V	0.7004V	0.7004V	0.1mV	0.014%
50%	0.7001V	0.7001V	0.7001V	0.0mV	0.000%
100%	0.6996V	0.6997V	0.6998V	0.2mV	0.029%
Load regulation	0.7mV	0.7mV	0.6mV		
	0.100%	0.100%	0.086%		

2. Temperature drift

Conditions $V_{in} : 12\text{VDC}$
 $I_o : 100\%$
Air Velocity : 1m/s

T_c	-40°C	+25°C	+115°C	Temperature stability	
V_o	0.7006V	0.6997V	0.6982V	2.4mV	0.343%

 $V_o = 1.2\text{ V}$

1. Line regulation and Load regulation

Conditions $T_c : 25^\circ\text{C}$
Air Velocity : 1m/s

$I_o \setminus V_{in}$	8VDC	12VDC	14VDC	Line regulation	
0%	1.2075V	1.2076V	1.2076V	0.1mV	0.008%
50%	1.2071V	1.2071V	1.2071V	0.0mV	0.000%
100%	1.2065V	1.2067V	1.2068V	0.3mV	0.025%
Load regulation	1.0mV	0.9mV	0.8mV		
	0.083%	0.075%	0.067%		

2. Temperature drift

Conditions $V_{in} : 12\text{VDC}$
 $I_o : 100\%$
Air Velocity : 1m/s

T_c	-40°C	+25°C	+115°C	Temperature stability	
V_o	1.2079V	1.2067V	1.2068V	1.1mV	0.092%

 $V_o = 2.0\text{ V}$

1. Line regulation and Load regulation

Conditions $T_c : 25^\circ\text{C}$
Air Velocity : 1m/s

$I_o \setminus V_{in}$	8VDC	12VDC	14VDC	Line regulation	
0%	1.9978V	1.9977V	1.9978V	0.1mV	0.005%
50%	1.9976V	1.9977V	1.9978V	0.2mV	0.010%
100%	1.9968V	1.9974V	1.9975V	0.7mV	0.035%
Load regulation	1.0mV	0.3mV	0.3mV		
	0.050%	0.015%	0.015%		

2. Temperature drift

Conditions $V_{in} : 12\text{VDC}$
 $I_o : 100\%$
Air Velocity : 1m/s


T_c	-40°C	+25°C	+115°C	Temperature stability	
V_o	1.9991V	1.9974V	2.0001V	2.7mV	0.135%

(2) 出力電圧、出力リップル・ノイズ電圧 対 入力電圧


Output voltage and Output ripple and noise voltage vs. Input voltage

Conditions I_o : 100 %
 T_c : -40 °C -----
 : 25 °C - · - · - · -
 : 115 °C —————
 Air Velocity : 1 m/s


$V_o = 0.7$ V



$V_o = 1.2$ V



$V_o = 2.0$ V




(3) 入力電流、効率 対 出力電流


Input current and Efficiency vs. Output current

Conditions Vin : 8 VDC -----
 : 12 VDC -.-.-.-
 : 14 VDC _____
 Tc : 25 °C
 Air Velocity : 1 m/s


Vo= 0.7 V



Vo= 1.2 V




Vo= 2.0 V




(4) 効率 対 入力電圧
Efficiency vs. Input voltage

Conditions I_o : 50 % ----
 : 100 % ——
 T_c : 25 °C
 Air Velocity : 1 m/s


$V_o = 0.7$ V



$V_o = 1.2$ V




$V_o = 2.0$ V




(5) 効率対ケース温度
Efficiency vs. Case temperature

Conditions Vin : 12 VDC
Io : 50 %
: 100 %
Air Velocity : 1 m/s


Vo= 0.7 V



Vo= 1.2 V




Vo= 2.0 V



(6) 起動、停止電圧特性
Start and Stop voltage characteristics


出力電圧 対 入力電圧
Output voltage vs. Input voltage

Conditions I_o : 100 %
 T_c : 25 °C
 V_o : 0.7 V ———
 : 1.2 V - - - -
 : 2.0 V - · - · -
 Air Velocity : 1 m/s




入力電流 対 入力電圧
Input current vs. Input voltage

Conditions I_o : 100 %
 T_c : 25 °C
 V_o : 0.7 V ———
 : 1.2 V - - - -
 : 2.0 V - · - · -
 Air Velocity : 1 m/s




2.2 待機電力特性
Standby power characteristics

Conditions T_c : 25 °C
 V_o : 0.7 V ———
 : 1.2 V - - - -
 : 2.0 V - · - · -
 Air Velocity : 1 m/s



2.3 通電ドリフト特性
Warm up voltage drift characteristics

Conditions V_{in} : 12 VDC
 V_o : 1.2 V
 I_o : 100 %
 T_a : 25 °C
 Air Velocity : 1 m/s



2.4 過電流保護特性

Over current protection (OCP) characteristics

入力電圧依存性

Input voltage dependence


Conditions Vin : 8 VDC -----
 : 12 VDC - - - - -
 : 14 VDC _____
 Tc : 25 °C
 Air Velocity : 1 m/s

ケース温度依存性


Case temperature dependence

Conditions Vin : 12 VDC
 Tc : -40 °C -----
 : 25 °C - - - - -
 : 115 °C _____
 Air Velocity : 1 m/s


$V_o = 0.7\text{ V}$




$V_o = 0.7\text{ V}$




$V_o = 1.2\text{ V}$




$V_o = 1.2\text{ V}$



$V_o = 2.0\text{ V}$





$V_o = 2.0\text{ V}$





2.5 出力立ち上がり、立ち下がり特性
Output rise and fall characteristics

Conditions Vin : 12 VDC
Io : 0 %
Tc : 25 °C
Air Velocity : 1 m/s



Vo = 0.7 V



Vo = 1.2 V





Vo = 2.0 V





2.5 出力立ち上がり、立ち下がり特性
Output rise and fall characteristics

Conditions Vin : 12 VDC
Io : 100 %
Tc : 25 °C
Air Velocity : 1 m/s



Vo= 0.7 V



Vo= 1.2 V





Vo= 2.0 V





2.5 出力立ち上がり、立ち下がり特性 (リモートON/OFF時)
Output rise and fall characteristics with Remote ON/OFF

Conditions V_{in} : 12 VDC
 I_o : 0 %
 T_c : 25 °C
 Air Velocity : 1 m/s



$V_o = 0.7$ V



$V_o = 1.2$ V





$V_o = 2.0$ V





2.5 出力立ち上がり、立ち下がり特性 (リモートON/OFF時)
Output rise and fall characteristics with Remote ON/OFF

Conditions V_{in} : 12 VDC
 I_o : 100 %
 T_c : 25 °C
 Air Velocity : 1 m/s



$V_o = 0.7$ V



$V_o = 1.2$ V






$V_o = 2.0$ V



2.6 過渡応答（負荷急変）特性
Dynamic load response characteristics


Conditions Vin : 12 VDC
Tc : 25 °C
Air Velocity : 1 m/s




2.7 出力リップル・ノイズ波形
Output ripple and noise waveform

Conditions V_{in} : 12 VDC
 I_o : 100 %
 T_c : 25 °C
 Air Velocity : 1 m/s

$V_o = 0.7\text{ V}$



$V_o = 1.2\text{ V}$



$V_o = 2.0\text{ V}$

