

EMI Suppression Capacitors

Series/Type: B32911*5 ... B32918*5

The following products presented in this data sheet are being withdrawn.

Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B32916B5105M003		2016-05-20	2016-08-31	2016-11-30
B32916B5105M000		2016-05-20	2016-08-31	2016-11-30
B32913A5823K289		2016-05-20	2016-08-31	2016-11-30



Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B32913A5823K189		2016-05-20	2016-08-31	2016-11-30
B32913A5823K003		2016-05-20	2016-08-31	2016-11-30
B32913A5823K000		2016-05-20	2016-08-31	2016-11-30
B32913A5224M289		2016-05-20	2016-08-31	2016-11-30
B32913A5224M189		2016-05-20	2016-08-31	2016-11-30
B32913A5224M003		2016-05-20	2016-08-31	2016-11-30
B32913A5224M000		2016-05-20	2016-08-31	2016-11-30
B32913A5104M289		2016-05-20	2016-08-31	2016-11-30
B32913A5104M189		2016-05-20	2016-08-31	2016-11-30
B32913A5104M003		2016-05-20	2016-08-31	2016-11-30
B32913A5104M000		2016-05-20	2016-08-31	2016-11-30
B32912A5823M289		2016-05-20	2016-08-31	2016-11-30
B32912A5823M255		2016-05-20	2016-08-31	2016-11-30
B32912A5823M189		2016-05-20	2016-08-31	2016-11-30
B32912A5823M155		2016-05-20	2016-08-31	2016-11-30
B32912A5823M003		2016-05-20	2016-08-31	2016-11-30
B32912A5823M000		2016-05-20	2016-08-31	2016-11-30
B32912A5822M289		2016-05-20	2016-08-31	2016-11-30
B32912A5822M255		2016-05-20	2016-08-31	2016-11-30
B32912A5822M189		2016-05-20	2016-08-31	2016-11-30
B32912A5822M155		2016-05-20	2016-08-31	2016-11-30
B32912A5822M003		2016-05-20	2016-08-31	2016-11-30
B32912A5822M000		2016-05-20	2016-08-31	2016-11-30
B32912A5822K289		2016-05-20	2016-08-31	2016-11-30
B32912A5822K255		2016-05-20	2016-08-31	2016-11-30
B32912A5822K189		2016-05-20	2016-08-31	2016-11-30
B32912A5822K155		2016-05-20	2016-08-31	2016-11-30
B32912A5822K003		2016-05-20	2016-08-31	2016-11-30
B32912A5822K000		2016-05-20	2016-08-31	2016-11-30
B32912A5682M289		2016-05-20	2016-08-31	2016-11-30
B32912A5682M255		2016-05-20	2016-08-31	2016-11-30
B32912A5682M189		2016-05-20	2016-08-31	2016-11-30
B32912A5682M155		2016-05-20	2016-08-31	2016-11-30
B32912A5682M003		2016-05-20	2016-08-31	2016-11-30
B32912A5682M000		2016-05-20	2016-08-31	2016-11-30
B32912A5682K289		2016-05-20	2016-08-31	2016-11-30
B32912A5682K255		2016-05-20	2016-08-31	2016-11-30
B32912A5682K189		2016-05-20	2016-08-31	2016-11-30



Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B32912A5682K155		2016-05-20	2016-08-31	2016-11-30
B32912A5682K003		2016-05-20	2016-08-31	2016-11-30
B32912A5682K000		2016-05-20	2016-08-31	2016-11-30
B32912A5563K289		2016-05-20	2016-08-31	2016-11-30
B32912A5563K255		2016-05-20	2016-08-31	2016-11-30
B32912A5563K189		2016-05-20	2016-08-31	2016-11-30
B32912A5563K155		2016-05-20	2016-08-31	2016-11-30
B32912A5563K003		2016-05-20	2016-08-31	2016-11-30
B32912A5563K000		2016-05-20	2016-08-31	2016-11-30
B32912A5333M289		2016-05-20	2016-08-31	2016-11-30
B32912A5333M255		2016-05-20	2016-08-31	2016-11-30
B32912A5333M189		2016-05-20	2016-08-31	2016-11-30
B32912A5333M155		2016-05-20	2016-08-31	2016-11-30
B32912A5333M003		2016-05-20	2016-08-31	2016-11-30
B32912A5333M000		2016-05-20	2016-08-31	2016-11-30
B32912A5223K289		2016-05-20	2016-08-31	2016-11-30
B32912A5223K255		2016-05-20	2016-08-31	2016-11-30
B32912A5223K189		2016-05-20	2016-08-31	2016-11-30
B32912A5223K155		2016-05-20	2016-08-31	2016-11-30
B32912A5223K003		2016-05-20	2016-08-31	2016-11-30
B32912A5223K000		2016-05-20	2016-08-31	2016-11-30
B32912A5153M289		2016-05-20	2016-08-31	2016-11-30
B32912A5153M255		2016-05-20	2016-08-31	2016-11-30
B32912A5153M189		2016-05-20	2016-08-31	2016-11-30
B32912A5153M155		2016-05-20	2016-08-31	2016-11-30
B32912A5153M003		2016-05-20	2016-08-31	2016-11-30
B32912A5153M000		2016-05-20	2016-08-31	2016-11-30
B32912A5153K289		2016-05-20	2016-08-31	2016-11-30
B32912A5153K255		2016-05-20	2016-08-31	2016-11-30
B32912A5153K189		2016-05-20	2016-08-31	2016-11-30
B32912A5153K155		2016-05-20	2016-08-31	2016-11-30
B32912A5153K003		2016-05-20	2016-08-31	2016-11-30
B32912A5153K000		2016-05-20	2016-08-31	2016-11-30
B32912A5124M189		2016-05-20	2016-08-31	2016-11-30
B32912A5124M155		2016-05-20	2016-08-31	2016-11-30
B32912A5124M003		2016-05-20	2016-08-31	2016-11-30
B32912A5124M000		2016-05-20	2016-08-31	2016-11-30
B32912A5103M289		2016-05-20	2016-08-31	2016-11-30



Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B32912A5103M255		2016-05-20	2016-08-31	2016-11-30
B32912A5103M189		2016-05-20	2016-08-31	2016-11-30
B32912A5103M155		2016-05-20	2016-08-31	2016-11-30
B32912A5103M003		2016-05-20	2016-08-31	2016-11-30
B32912A5103M000		2016-05-20	2016-08-31	2016-11-30
B32911B5103M289		2016-05-20	2016-08-31	2016-11-30
B32911B5103M240		2016-05-20	2016-08-31	2016-11-30
B32911B5103M189		2016-05-20	2016-08-31	2016-11-30
B32911B5103M140		2016-05-20	2016-08-31	2016-11-30
B32911B5103M003		2016-05-20	2016-08-31	2016-11-30
B32911B5103M000		2016-05-20	2016-08-31	2016-11-30
B32911B5103K289		2016-05-20	2016-08-31	2016-11-30
B32911B5103K240		2016-05-20	2016-08-31	2016-11-30
B32911B5103K189		2016-05-20	2016-08-31	2016-11-30
B32911B5103K140		2016-05-20	2016-08-31	2016-11-30
B32911B5103K003		2016-05-20	2016-08-31	2016-11-30
B32911B5103K000		2016-05-20	2016-08-31	2016-11-30
B32911A5822M289		2016-05-20	2016-08-31	2016-11-30
B32911A5822M240		2016-05-20	2016-08-31	2016-11-30
B32911A5822M189		2016-05-20	2016-08-31	2016-11-30
B32911A5822M140		2016-05-20	2016-08-31	2016-11-30
B32911A5822M003		2016-05-20	2016-08-31	2016-11-30
B32911A5822M000		2016-05-20	2016-08-31	2016-11-30
B32911A5822K289		2016-05-20	2016-08-31	2016-11-30
B32911A5822K240		2016-05-20	2016-08-31	2016-11-30
B32911A5822K189		2016-05-20	2016-08-31	2016-11-30
B32911A5822K140		2016-05-20	2016-08-31	2016-11-30
B32911A5822K003		2016-05-20	2016-08-31	2016-11-30
B32911A5822K000		2016-05-20	2016-08-31	2016-11-30
B32911A5682M289		2016-05-20	2016-08-31	2016-11-30
B32911A5682M240		2016-05-20	2016-08-31	2016-11-30
B32911A5682M189		2016-05-20	2016-08-31	2016-11-30
B32911A5682M140		2016-05-20	2016-08-31	2016-11-30
B32911A5682M003		2016-05-20	2016-08-31	2016-11-30
B32911A5682M000		2016-05-20	2016-08-31	2016-11-30
B32911A5682K289		2016-05-20	2016-08-31	2016-11-30
B32911A5682K240		2016-05-20	2016-08-31	2016-11-30
B32911A5682K189		2016-05-20	2016-08-31	2016-11-30



Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B32911A5682K140		2016-05-20	2016-08-31	2016-11-30
B32911A5682K003		2016-05-20	2016-08-31	2016-11-30
B32911A5682K000		2016-05-20	2016-08-31	2016-11-30
B32911A5562M289		2016-05-20	2016-08-31	2016-11-30
B32911A5562M240		2016-05-20	2016-08-31	2016-11-30
B32911A5562M189		2016-05-20	2016-08-31	2016-11-30
B32911A5562M140		2016-05-20	2016-08-31	2016-11-30
B32911A5562M003		2016-05-20	2016-08-31	2016-11-30
B32911A5562M000		2016-05-20	2016-08-31	2016-11-30
B32911A5562K289		2016-05-20	2016-08-31	2016-11-30
B32911A5562K240		2016-05-20	2016-08-31	2016-11-30
B32911A5562K189		2016-05-20	2016-08-31	2016-11-30
B32911A5562K140		2016-05-20	2016-08-31	2016-11-30
B32911A5562K003		2016-05-20	2016-08-31	2016-11-30
B32911A5562K000		2016-05-20	2016-08-31	2016-11-30
B32911A5472M289		2016-05-20	2016-08-31	2016-11-30
B32911A5472M240		2016-05-20	2016-08-31	2016-11-30
B32911A5472M189		2016-05-20	2016-08-31	2016-11-30
B32911A5472M140		2016-05-20	2016-08-31	2016-11-30
B32911A5472M003		2016-05-20	2016-08-31	2016-11-30
B32911A5472M000		2016-05-20	2016-08-31	2016-11-30
B32911A5472K289		2016-05-20	2016-08-31	2016-11-30
B32911A5472K240		2016-05-20	2016-08-31	2016-11-30
B32911A5472K189		2016-05-20	2016-08-31	2016-11-30
B32911A5472K140		2016-05-20	2016-08-31	2016-11-30
B32911A5472K003		2016-05-20	2016-08-31	2016-11-30
B32911A5472K000		2016-05-20	2016-08-31	2016-11-30
B32911A5332M289		2016-05-20	2016-08-31	2016-11-30
B32911A5332M240		2016-05-20	2016-08-31	2016-11-30
B32911A5332M189		2016-05-20	2016-08-31	2016-11-30
B32911A5332M140		2016-05-20	2016-08-31	2016-11-30
B32911A5332M003		2016-05-20	2016-08-31	2016-11-30
B32911A5332M000		2016-05-20	2016-08-31	2016-11-30
B32911A5332K289		2016-05-20	2016-08-31	2016-11-30
B32911A5332K240		2016-05-20	2016-08-31	2016-11-30
B32911A5332K189		2016-05-20	2016-08-31	2016-11-30
B32911A5332K140		2016-05-20	2016-08-31	2016-11-30
B32911A5332K003		2016-05-20	2016-08-31	2016-11-30



Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B32911A5332K000		2016-05-20	2016-08-31	2016-11-30
B32911A5222M289		2016-05-20	2016-08-31	2016-11-30
B32911A5222M240		2016-05-20	2016-08-31	2016-11-30
B32911A5222M189		2016-05-20	2016-08-31	2016-11-30
B32911A5222M140		2016-05-20	2016-08-31	2016-11-30
B32911A5222M003		2016-05-20	2016-08-31	2016-11-30
B32911A5222M000		2016-05-20	2016-08-31	2016-11-30
B32911A5222K289		2016-05-20	2016-08-31	2016-11-30
B32911A5222K240		2016-05-20	2016-08-31	2016-11-30
B32911A5222K189		2016-05-20	2016-08-31	2016-11-30
B32911A5222K140		2016-05-20	2016-08-31	2016-11-30
B32911A5222K003		2016-05-20	2016-08-31	2016-11-30
B32911A5222K000		2016-05-20	2016-08-31	2016-11-30
B32911A5152M289		2016-05-20	2016-08-31	2016-11-30
B32911A5152M240		2016-05-20	2016-08-31	2016-11-30
B32911A5152M189		2016-05-20	2016-08-31	2016-11-30
B32911A5152M140		2016-05-20	2016-08-31	2016-11-30
B32911A5152M003		2016-05-20	2016-08-31	2016-11-30
B32911A5152M000		2016-05-20	2016-08-31	2016-11-30
B32911A5152K289		2016-05-20	2016-08-31	2016-11-30
B32911A5152K240		2016-05-20	2016-08-31	2016-11-30
B32911A5152K189		2016-05-20	2016-08-31	2016-11-30
B32911A5152K140		2016-05-20	2016-08-31	2016-11-30
B32911A5152K003		2016-05-20	2016-08-31	2016-11-30
B32911A5152K000		2016-05-20	2016-08-31	2016-11-30
B32911A5123M289		2016-05-20	2016-08-31	2016-11-30
B32911A5123M240		2016-05-20	2016-08-31	2016-11-30
B32911A5123M189		2016-05-20	2016-08-31	2016-11-30
B32911A5123M140		2016-05-20	2016-08-31	2016-11-30
B32911A5123M003		2016-05-20	2016-08-31	2016-11-30
B32911A5123M000		2016-05-20	2016-08-31	2016-11-30
B32911A5123K289		2016-05-20	2016-08-31	2016-11-30
B32911A5123K240		2016-05-20	2016-08-31	2016-11-30
B32911A5123K189		2016-05-20	2016-08-31	2016-11-30
B32911A5123K140		2016-05-20	2016-08-31	2016-11-30
B32911A5123K003		2016-05-20	2016-08-31	2016-11-30
B32911A5123K000		2016-05-20	2016-08-31	2016-11-30
B32911A5103M289		2016-05-20	2016-08-31	2016-11-30



Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B32911A5103M240		2016-05-20	2016-08-31	2016-11-30
B32911A5103M189		2016-05-20	2016-08-31	2016-11-30
B32911A5103M140		2016-05-20	2016-08-31	2016-11-30
B32911A5103M003		2016-05-20	2016-08-31	2016-11-30
B32911A5103M000		2016-05-20	2016-08-31	2016-11-30
B32911A5102M289		2016-05-20	2016-08-31	2016-11-30
B32911A5102M240		2016-05-20	2016-08-31	2016-11-30
B32911A5102M189		2016-05-20	2016-08-31	2016-11-30
B32911A5102M140		2016-05-20	2016-08-31	2016-11-30
B32911A5102M003		2016-05-20	2016-08-31	2016-11-30
B32911A5102M000		2016-05-20	2016-08-31	2016-11-30
B32911A5102K289		2016-05-20	2016-08-31	2016-11-30
B32911A5102K240		2016-05-20	2016-08-31	2016-11-30
B32911A5102K189		2016-05-20	2016-08-31	2016-11-30
B32911A5102K140		2016-05-20	2016-08-31	2016-11-30
B32911A5102K003		2016-05-20	2016-08-31	2016-11-30
B32911A5102K000		2016-05-20	2016-08-31	2016-11-30

For further information please contact your nearest EPCOS sales office, which will also support you in selecting a suitable substitute. The addresses of our worldwide sales network are presented at www.epcos.com/sales.

Typical applications

- X1 class for interference suppression
- "Across the line" applications

Climatic

- Max. operating temperature: 110 °C
- Climatic category (IEC 60068-1): 40/110/56

Construction

- Dielectric: polypropylene (MKP)
- Plastic case (UL 94 V-0)
- Epoxy resin sealing (UL 94 V-0)

Features

- Small dimensions
- Good self-healing properties
- High voltage capability
- RoHS-compatible
- Halogen-free capacitors available on request

Terminals

- Parallel wire leads, lead-free tinned
- Special lead lengths available on request

Marking

Manufacturer's logo, lot number, date code, rated capacitance (coded), capacitance tolerance (code letter), rated AC voltage (IEC), series number, sub-class (X1), dielectric code (MKP), climatic category, passive flammability category, approvals.



Delivery mode

Bulk (untaped)

Taped (Ammo pack or reel)

For taping details, refer to chapter

"Taping and packing".

Dimensional drawing
Drawing 1

Drawing 2


$P_1 = 20.3 \text{ mm}$

Dimensions in mm

Pin	Lead spacing $e \pm 0.4$	Lead diameter $d_1 \pm 0.05$	Type	Drawing
2	10	0.6	B32911*5	1
2	15	0.8	B32912*5	1
2	22.5	0.8	B32913*5	1
2	27.5	0.8	B32914*5	1
2	37.5	1.0	B32916*5	1 / 2 ¹⁾
4	52.5	1.2	B32918*5	2

1) A few individual types only

B32911*5 ... B32918*5


X1 / 530 V AC



Approvals

Marking examples

(position of marks may vary):



KMK1718-J



KMK1719-K

Approvals

Approval marks	Standards	Certificate
	EN 60384-14, IEC 60384-14	ENEC- 00955 (approved by UL Demko)
	UL 60384-14, CSA E60384-14	E97863

Notes:	<p>Effective January 2014, only for EMI suppression capacitors:</p> <ul style="list-style-type: none"> – UL 60384-14 certification replaces both UL 1414 and UL 1283 standards. – CSA C22.2 No. 1 and CSA C22.s No. 8 are replaced by CSA E60384-14. – References like 1414, 1283 are removed from the capacitor marking
--------	---



B32911*5 ... B32918*5

X1 / 530 V AC

Overview of available types

Lead spacing	10 mm	15 mm	22.5 mm	27.5 mm	37.5 mm	52.5 mm
Type	B32911*5	B32912*5	B32913*5	B32914*5	B32916*5	B32918*5
C _R (μF)						
0.0010						
0.0015						
0.0022						
0.0033						
0.0047						
0.0056						
0.0068						
0.0082						
0.010						
0.012						
0.015						
0.022						
0.033						
0.047						
0.056						
0.068						
0.082						
0.10						
0.12						
0.15						
0.22						
0.33						
0.47						
0.56						
0.68						
0.82						
1.0						
1.5						
1.8						
2.2						
3.3						
4.7						
5.6						


Ordering codes and packing units

Lead spacing	C _R	Max. dimensions w × h × l mm	Ordering code (composition see below)	Straight terminals, Ammo pack pcs./MOQ	Straight terminals, Reel pcs./MOQ	Straight terminals, Untaped pcs./MOQ	Pins
mm	μF						
10	0.0010	4.0 × 9.0 × 13.0	B32911A5102+***	4000	6800	4000	2
	0.0015	4.0 × 9.0 × 13.0	B32911A5152+***	4000	6800	4000	2
	0.0022	4.0 × 9.0 × 13.0	B32911A5222+***	4000	6800	4000	2
	0.0033	4.0 × 9.0 × 13.0	B32911A5332+***	4000	6800	4000	2
	0.0047	4.0 × 9.0 × 13.0	B32911A5472+***	4000	6800	4000	2
	0.0056	5.0 × 11.0 × 13.0	B32911A5562+***	3320	5200	4000	2
	0.0068	5.0 × 11.0 × 13.0	B32911A5682+***	3320	5200	4000	2
	0.0082	5.0 × 11.0 × 13.0	B32911A5822+***	3320	5200	4000	2
	0.010	5.0 × 11.0 × 13.0	B32911A5103M***	3320	5200	4000	2
	0.010	6.0 × 12.0 × 13.0	B32911B5103+***	2720	4400	4000	2
	0.012	6.0 × 12.0 × 13.0	B32911A5123+***	2720	4400	4000	2
15	0.0068	5.0 × 10.5 × 18.0	B32912B5682+***	4680	5200	4000	2
	0.0068	5.5 × 8.5 × 18.0	B32912A5682+***	4280	4800	4000	2
	0.0082	5.0 × 10.5 × 18.0	B32912B5822+***	4680	5200	4000	2
	0.0082	5.5 × 8.5 × 18.0	B32912A5822+***	4280	4800	4000	2
	0.010	5.0 × 10.5 × 18.0	B32912B5103+***	4680	5200	4000	2
	0.010	5.5 × 8.5 × 18.0	B32912A5103M***	4280	4800	4000	2
	0.015	5.0 × 10.5 × 18.0	B32912A5153+***	4680	5200	4000	2
	0.022	5.5 × 11.0 × 18.0	B32912A5223+***	4280	4800	4000	2

MOQ = Minimum Order Quantity, consisting of 4 packing units.

Further intermediate capacitance values on request.

Composition of ordering code

+ = Capacitance tolerance code:

M = ±20%

K = ±10%

*** = Packaging code:

289 = Straight terminals, Ammo pack

189 = Straight terminals, Reel

240 = Crimped down from lead spacing 10 mm to 7.5 mm, Ammo pack


140 = Crimped down from lead spacing 10 mm to 7.5 mm, Reel

255 = Crimped down from lead spacing 15 mm to 7.5 mm, Ammo pack

155 = Crimped down from lead spacing 15 mm to 7.5 mm, Reel

003 = Straight terminals, untaped (lead length 3.2 ±0.3 mm)

000 = Straight terminals, untaped (lead length 6 - 1 mm)



B32911*5 ... B32918*5

X1 / 530 V AC

Ordering codes and packing units

Lead spacing	C _R	Max. dimensions w × h × l mm	Ordering code (composition see below)	Straight terminals, Ammo pack pcs./MOQ	Straight terminals, Reel pcs./MOQ	Straight terminals, Untaped pcs./MOQ	Pins
mm	μF						
15	0.033	6.0 × 12.0 × 18.0	B32912A5333M***	3840	4400	4000	2
	0.033	7.0 × 12.5 × 18.0	B32912B5333+***	3320	3600	4000	2
	0.047	8.0 × 14.0 × 18.0	B32912A5473+***	2920	3000	2000	2
	0.056	8.0 × 14.0 × 18.0	B32912A5563+***	2920	3000	2000	2
	0.068	9.0 × 17.5 × 18.0	B32912A5683+***	2560	2800	2000	2
	0.082	9.0 × 17.5 × 18.0	B32912A5823M***	2560	2800	2000	2
	0.10	11.0 × 18.5 × 18.0	B32912A5104+***	–	2200	1200	2
	0.12	11.0 × 18.5 × 18.0	B32912A5124M***	–	2200	1200	2
22.5	0.033	6.0 × 15.0 × 26.5	B32913A5333+***	2720	2800	2880	2
	0.047	6.0 × 15.0 × 26.5	B32913A5473+***	2720	2800	2880	2
	0.056	6.0 × 15.0 × 26.5	B32913A5563+***	2720	2800	2880	2
	0.068	6.0 × 15.0 × 26.5	B32913A5683+***	2720	2800	2880	2
	0.082	6.0 × 15.0 × 26.5	B32913A5823+***	2720	2800	2880	2
	0.10	6.0 × 15.0 × 26.5	B32913A5104M***	2720	2800	2880	2
	0.10	7.0 × 16.0 × 26.5	B32913C5104+***	2320	2400	2520	2
	0.10	7.5 × 14.0 × 26.5	B32913B5104+***	2200	2000	2280	2
	0.15	8.5 × 16.5 × 26.5	B32913A5154+***	1920	2000	2040	2
	0.22	10.5 × 16.5 × 26.5	B32913A5224M***	1560	1600	2160	2
	0.22	10.5 × 18.5 × 26.5	B32913B5224+***	1560	1600	2160	2

MOQ = Minimum Order Quantity, consisting of 4 packing units.

Further intermediate capacitance values on request.

Composition of ordering code

+ = Capacitance tolerance code:

M = ±20%

K = ±10%

*** = Packaging code:

289 = Straight terminals, Ammo pack

189 = Straight terminals, Reel

240 = Crimped down from lead spacing 10 mm to 7.5 mm, Ammo pack


140 = Crimped down from lead spacing 10 mm to 7.5 mm, Reel

255 = Crimped down from lead spacing 15 mm to 7.5 mm, Ammo pack

155 = Crimped down from lead spacing 15 mm to 7.5 mm, Reel

003 = Straight terminals, untaped (lead length 3.2 ±0.3 mm)

000 = Straight terminals, untaped (lead length 6 - 1 mm)


Ordering codes and packing units

Lead spacing	C _R	Max. dimensions w × h × l mm	Ordering code (composition see below)	Straight terminals, Ammo pack pcs./MOQ	Straight terminals, Reel pcs./MOQ	Straight terminals, Untaped pcs./MOQ	Pins
mm	μF						
22.5	0.33	11.0 × 20.5 × 26.5	B32913A5334M***	1480	1400	2040	2
	0.33	12.0 × 22.0 × 26.5	B32913B5334+***	—	—	1800	2
	0.47	14.5 × 29.5 × 26.5	B32913A5474+***	—	—	1040	2
27.5	0.15	11.0 × 19.0 × 31.5	B32914A5154+***	—	1400	1280	2
	0.22	11.0 × 19.0 × 31.5	B32914A5224+***	—	1400	1280	2
	0.33	11.0 × 19.0 × 31.5	B32914A5334M***	—	1400	1280	2
	0.47	12.5 × 21.5 × 31.5	B32914A5474M***	—	1200	1120	2
	0.47	13.5 × 23.0 × 31.5	B32914B5474+***	—	1000	1040	2
	0.56	13.5 × 23.0 × 31.5	B32914A5564M***	—	1000	1040	2
	0.56	14.0 × 24.5 × 31.5	B32914B5564+***	—	1000	1040	2
	0.68	14.0 × 24.5 × 31.5	B32914A5684M***	—	1000	1040	2
	0.68	16.0 × 32.0 × 31.5	B32914C5684+***	—	—	880	2
	0.68	18.0 × 27.5 × 31.5	B32914B5684+***	—	—	800	2
	0.82	16.0 × 32.0 × 31.5	B32914B5824+***	—	—	880	2
	0.82	18.0 × 27.5 × 31.5	B32914A5824+***	—	—	800	2
	1.0	16.0 × 32.0 × 31.5	B32914B5105+***	—	—	880	2
	1.0	18.0 × 27.5 × 31.5	B32914A5105M***	—	—	800	2
	1.5	22.0 × 36.5 × 31.5	B32914A5155+***	—	—	640	2
1.8	22.0 × 36.5 × 31.5	B32914A5185M***	—	—	640	2	

MOQ = Minimum Order Quantity, consisting of 4 packing units.

Further intermediate capacitance values on request.

Composition of ordering code

+ = Capacitance tolerance code:

M = ±20%

K = ±10%

*** = Packaging code:

289 = Straight terminals, Ammo pack

189 = Straight terminals, Reel

240 = Crimped down from lead spacing 10 mm to 7.5 mm, Ammo pack


140 = Crimped down from lead spacing 10 mm to 7.5 mm, Reel

255 = Crimped down from lead spacing 15 mm to 7.5 mm, Ammo pack

155 = Crimped down from lead spacing 15 mm to 7.5 mm, Reel

003 = Straight terminals, untaped (lead length 3.2 ±0.3 mm)

000 = Straight terminals, untaped (lead length 6 - 1 mm)



B32911*5 ... B32918*5

X1 / 530 V AC

Ordering codes and packing units

Lead spacing	C _R	Max. dimensions w × h × l mm	Ordering code (composition see below)	Straight terminals, Ammo pack pcs./MOQ	Straight terminals, Reel pcs./MOQ	Straight terminals, Untaped pcs./MOQ	Pins
mm	μF						
37.5	0.22	12.0 × 22.0 × 41.5	B32916A5224+***	—	—	1620	2
	0.33	12.0 × 22.0 × 41.5	B32916A5334+***	—	—	1620	2
	0.47	12.0 × 22.0 × 41.5	B32916A5474+***	—	—	1620	2
	0.56	12.0 × 22.0 × 41.5	B32916A5564+***	—	—	1620	2
	0.56	24.0 × 15.0 × 41.5	B32916B5564+***	—	—	1040	2
	0.68	12.0 × 22.0 × 41.5	B32916A5684+***	—	—	1620	2
	0.68	24.0 × 15.0 × 41.5	B32916B5684+***	—	—	1040	2
	0.82	14.0 × 25.0 × 41.5	B32916A5824M***	—	—	1380	2
	0.82	24.0 × 15.0 × 41.5	B32916B5824+***	—	—	1040	2
	1.0	14.0 × 25.0 × 41.5	B32916A5105M***	—	—	1380	2
	1.0	16.0 × 28.5 × 41.5	B32916C5105+***	—	—	800	2
	1.0	24.0 × 15.0 × 41.5	B32916B5105M***	—	—	1040	2
	1.0	24.0 × 19.0 × 41.5	B32916D5105+***	—	—	780	2
	1.5	16.0 × 28.5 × 41.5	B32916A5155M***	—	—	800	2
	1.5	17.0 × 32.0 × 41.5	B32916B5155+***	—	—	760	2
	2.2	20.0 × 39.5 × 41.5	B32916A5225+***	—	—	640	2
	2.2	31.0 × 26.5 × 42.0	B32916B5225+***	—	—	600	2
	3.3	28.0 × 37.0 × 42.0	B32916A5335M***	—	—	440	2
	3.3	28.0 × 42.5 × 42.0	B32916B5335+***	—	—	440	2

MOQ = Minimum Order Quantity, consisting of 4 packing units.

Further intermediate capacitance values on request.

Composition of ordering code

+ = Capacitance tolerance code:

M = ±20%

K = ±10%

*** = Packaging code:

289 = Straight terminals, Ammo pack

189 = Straight terminals, Reel

240 = Crimped down from lead spacing 10 mm to 7.5 mm, Ammo pack

140 = Crimped down from lead spacing 10 mm to 7.5 mm, Reel

255 = Crimped down from lead spacing 15 mm to 7.5 mm, Ammo pack


155 = Crimped down from lead spacing 15 mm to 7.5 mm, Reel

003 = Straight terminals, untaped (lead length 3.2 ±0.3 mm)

000 = Straight terminals, untaped (lead length 6 - 1 mm)

B32911*5 ... B32918*5

X1 / 530 V AC



Ordering codes and packing units

Lead spacing	C _R	Max. dimensions w × h × l mm	Ordering code (composition see below)	Straight terminals, Ammo pack pcs./MOQ	Straight terminals, Reel pcs./MOQ	Straight terminals, Untaped pcs./MOQ	Pins
mm	μF						
37.5	4.7	30.0 × 45.0 × 42.0	B32916A5475M***	–	–	400	4
	4.7	33.0 × 48.0 × 42.0	B32916B5475+***	–	–	180	4
	5.6	33.0 × 48.0 × 42.0	B32916A5565M***	–	–	180	4
52.5	4.7	30.0 × 45.0 × 57.5	B32918A5475+***	–	–	280	4
	5.6	30.0 × 45.0 × 57.5	B32918A5565+***	–	–	280	4
	5.6	35.0 × 50.0 × 57.5	B32918B5565+***	–	–	108	4

MOQ = Minimum Order Quantity, consisting of 4 packing units.

Further intermediate capacitance values on request.

Composition of ordering code

+ = Capacitance tolerance code:

M = ±20%

K = ±10%

*** = Packaging code:

289 = Straight terminals, Ammo pack

189 = Straight terminals, Reel

240 = Crimped down from lead spacing 10 mm to 7.5 mm, Ammo pack


140 = Crimped down from lead spacing 10 mm to 7.5 mm, Reel

255 = Crimped down from lead spacing 15 mm to 7.5 mm, Ammo pack

155 = Crimped down from lead spacing 15 mm to 7.5 mm, Reel

003 = Straight terminals, untaped (lead length 3.2 ±0.3 mm)

000 = Straight terminals, untaped (lead length 6 - 1 mm)



B32911*5 ... B32918*5

X1 / 530 V AC

Technical data

Reference standard: IEC / UL 60384-14. All data given at T = 20 °C unless otherwise specified.

Rated AC voltage (IEC 60384-14)	530 V (50/60 Hz)
Maximum continuous DC voltage V_{DC}	1000 V
Max. operating temperature $T_{op,max}$	+110 °C
DC test voltage	2700 V, 2 s

The repetition of this DC voltage test may damage the capacitor. Special care must be taken in case of use several capacitors in a parallel configuration.

Dissipation factor $\tan \delta$ (in 10^{-3}) at 20 °C (upper limit values)		$C_R \leq 2.2 \mu F$	$C_R > 2.2 \mu F$
	at 1 kHz	1	2
Insulation resistance R_{ins} or time constant $\tau = C_R \cdot R_{ins}$ at 100 V DC, 20 °C, rel. humidity $\leq 65\%$ and for 60 s (minimum as-delivered values)	$C_R \leq 0.33 \mu F$	$C_R > 0.33 \mu F$	
	30 000 M Ω	10 000 s	
Passive flammability category	B		
Capacitance tolerances (measured at 1 kHz)	$\pm 10\%$ (K), $\pm 20\%$ (M)		

Pulse handling capability

"dV/dt" represents the maximum permissible voltage change per unit of time for non-sinusoidal voltages, expressed in V/ μ s.

" k_0 " represents the maximum permissible pulse characteristic of the waveform applied to the capacitor, expressed in V²/ μ s.

Note:

The values of dV/dt and k_0 provided below must not be exceeded in order to avoid damaging the capacitor.


dV/dt and k_0 values

Lead spacing	10 mm	15 mm	22.5 mm	27.5 mm	37.5 mm	52.5 mm
dV/dt in V/ μ s	550	400	200	150	100	40
k_0 in V ² / μ s	473 000	344 000	172 000	129 000	86 000	34 400



Impedance Z versus frequency f

(typical values)





B32911*5 ... B32918*5

X1 / 530 V AC

Testing and Standards

Test	Reference	Conditions of test	Performance requirements
Electrical Parameters	IEC 60384-14	Voltage Proof: Between terminals, 4.3 V _R , 1 min. Terminals and enclosure: 2 V _R + 1500 V AC Insulation resistance, R _{INS} Capacitance, C Dissipation factor, tan δ	Within specified limits
Robustness of terminations	IEC 60068-2-21	Tensile strength (test Ua1)	Capacitance and tan δ within specified limits
		Wire diameter	
		0.5 < d ₁ ≤ 0.8 mm	10 N
		0.8 < d ₁ ≤ 1.25 mm	20 N
Resistance to soldering heat	IEC 60068-2-20, test Tb, method 1A	Solder bath temperature at 260 ± 5 °C, immersion for 10 seconds	ΔC/C ₀ ≤ 5% tan δ within specified limits
Rapid change of temperature	IEC 60384-16	T _A = lower category temperature T _B = upper category temperature Five cycles, duration t = 30 min.	No visible damage ΔC/C ₀ ≤ 5% tan δ within specified limits
Vibration	IEC 60384-14	Test F _C : vibration sinusoidal Displacement: 0.75 mm Acceleration: 98 m/s ² Frequency: 10 Hz ... 500 Hz Test duration: 3 orthogonal axes, 2 hours each axe	No visible damage
Bump	IEC 60384-14	Test Eb: Total 4000 bumps with 400 m/s ² mounted on PCB 6 ms duration	No visible damage ΔC/C ₀ ≤ 5% tan δ within specified limits
Climatic sequence	IEC 60384-14	Dry heat – T _B / 16 h. Damp heat cyclic, 1st cycle + 55 °C / 24h / 95% ... 100% RH Cold – T _A / 2h Damp heat cyclic, 5 cycles + 55 °C / 24h / 95% ... 100% rh	No visible damage ΔC/C ₀ ≤ 5% Δ tan δ ≤ 0.008, C ≤ 1 μF Δ tan δ > 0.005, C > 1 μF Voltage proof R _{INS} ≥ 50% of initial limit

Damp Heat Steady State	IEC 60384-14	Test Ca 40 °C / 93% RH / 56 days	No visible damage $ \Delta C/C_0 \leq 5\%$ $ \Delta \tan \delta \leq 0.008$, $C \leq 1 \mu\text{F}$ $ \Delta \tan \delta > 0.005$, $C > 1 \mu\text{F}$ Voltage proof $R_{\text{INS}} \geq 50\%$ of initial limit
Impulse test Endurance	IEC 60384-14	3 impulses $T_B / 1.25 V_R / 1000$ hours, 1000 V_{rms} for 0.1 s every hour	No visible damage $ \Delta C/C_0 \leq 10\%$ $ \Delta \tan \delta \leq 0.008$, $C \leq 1 \mu\text{F}$ $ \Delta \tan \delta > 0.005$, $C > 1 \mu\text{F}$ Voltage proof $R_{\text{INS}} \geq 50\%$ of initial limit
Passive flammability	IEC 60384-14	Flame applied for a period of time depending on capacitor volume	B
Active flammability	IEC 60384-14	20 discharges at 2.5 kV + V_R	The cheesecloth shall not burn with a flame

Mounting guidelines

1 Soldering

1.1 Solderability of leads

The solderability of terminal leads is tested to IEC 60068-2-20, test Ta, method 1.

Before a solderability test is carried out, terminals are subjected to accelerated ageing (to IEC 60068-2-2, test Ba: 4 h exposure to dry heat at 155 °C). Since the ageing temperature is far higher than the upper category temperature of the capacitors, the terminal wires should be cut off from the capacitor before the ageing procedure to prevent the solderability being impaired by the products of any capacitor decomposition that might occur.

Solder bath temperature	235 ±5 °C
Soldering time	2.0 ±0.5 s
Immersion depth	2.0 +0/−0.5 mm from capacitor body or seating plane
Evaluation criteria:	
Visual inspection	Wetting of wire surface by new solder ≥90%, free-flowing solder



B32911*5 ... B32918*5


X1 / 530 V AC

1.2 Resistance to soldering heat


Resistance to soldering heat is tested to IEC 60068-2-20, test Tb, method 1A.

Conditions:

Series	Solder bath temperature	Soldering time
MKT boxed (except $2.5 \times 6.5 \times 7.2$ mm) coated uncoated (lead spacing > 10 mm)	260 ± 5 °C	10 ± 1 s
MFP MKP (lead spacing > 7.5 mm)		
MKT boxed (case $2.5 \times 6.5 \times 7.2$ mm)		5 ± 1 s
MKP (lead spacing ≤ 7.5 mm) MKT uncoated (lead spacing ≤ 10 mm) insulated (B32559)		< 4 s recommended soldering profile for MKT uncoated (lead spacing ≤ 10 mm) and insulated (B32559)



Immersion depth	2.0 +0/−0.5 mm from capacitor body or seating plane
Shield	Heat-absorbing board, (1.5 ± 0.5) mm thick, between capacitor body and liquid solder
Evaluation criteria:	
Visual inspection	No visible damage
$\Delta C/C_0$	2% for MKT/MKP/MFP 5% for EMI suppression capacitors
$\tan \delta$	As specified in sectional specification



1.3 General notes on soldering

Permissible heat exposure loads on film capacitors are primarily characterized by the upper category temperature T_{\max} . Long exposure to temperatures above this type-related temperature limit can lead to changes in the plastic dielectric and thus change irreversibly a capacitor's electrical characteristics. For short exposures (as in practical soldering processes) the heat load (and thus the possible effects on a capacitor) will also depend on other factors like:

- Pre-heating temperature and time
- Forced cooling immediately after soldering
- Terminal characteristics:
 - diameter, length, thermal resistance, special configurations (e.g. crimping)
- Height of capacitor above solder bath
- Shadowing by neighboring components
- Additional heating due to heat dissipation by neighboring components
- Use of solder-resist coatings

The overheating associated with some of these factors can usually be reduced by suitable countermeasures. For example, if a pre-heating step cannot be avoided, an additional or reinforced cooling process may possibly have to be included.

EPCOS recommends the following conditions:

- Pre-heating with a maximum temperature of 110 °C
- Temperature inside the capacitor should not exceed the following limits:
 - MKP/MFP 110 °C
 - MKT 160 °C
- When SMD components are used together with leaded ones, the leaded film capacitors should not pass into the SMD adhesive curing oven. The leaded components should be assembled after the SMD curing step.
- Leaded film capacitors are not suitable for reflow soldering.

Uncoated capacitors

For uncoated MKT capacitors with lead spacings ≤ 10 mm (B32560/B32561) the following measures are recommended:

- pre-heating to not more than 110 °C in the preheater phase
- rapid cooling after soldering



B32911*5 ... B32918*5

X1 / 530 V AC


Application note for the different possible X1 / X2 positions

In series with the powerline (i.e. capacitive power supply)

Typical Applications:

- Power meters
- ECUs for white goods and household appliances
- Different sensor applications
- Severe ambient conditions

Basic circuit



Required features

- High capacitance stability over the lifetime
- Narrow tolerances for a controlled current supply

Recommended EPCOS product series


- B3293* (305 V AC) heavy duty with EN approval for X2 (UL Q1/2010)
- B3265* MKP series standard MKP capacitor without safety approvals
- B3267*L MKP series standard MKP capacitor without safety approvals
- B3292*H/J (305 V AC), severe ambient condition, approved as X2

In parallel with the powerline

Typical Applications:

Standard X2 are used parallel over the mains for reducing electromagnetic interferences coming from the grid. For such purposes they must meet the applicable EMC directives and standards.

Basic circuit




Required features

- Standard safety approvals (ENEC, UL, CSA, CQC)
- High pulse load capability
- Withstand surge voltages

Recommended EPCOS product series

- B3292*C/D (305 V AC) standard series, approved as X2
- B3291* (330 V AC), approved as X1
- B3291* (530 V AC), approved as X1
- B3292*H/J (305 V AC), severe ambient condition, approved as X2




Cautions and warnings

- Do not exceed the upper category temperature (UCT).
- Do not apply any mechanical stress to the capacitor terminals.
- Avoid any compressive, tensile or flexural stress.
- Do not move the capacitor after it has been soldered to the PC board.
- Do not pick up the PC board by the soldered capacitor.
- Do not place the capacitor on a PC board whose PTH hole spacing differs from the specified lead spacing.
- Do not exceed the specified time or temperature limits during soldering.
- Avoid external energy inputs, such as fire or electricity.
- Avoid overload of the capacitors.

The table below summarizes the safety instructions that must always be observed. A detailed description can be found in the relevant sections of the chapters "General technical information" and "Mounting guidelines".

Topic	Safety information	Reference chapter "General technical information"
Storage conditions	Make sure that capacitors are stored within the specified range of time, temperature and humidity conditions.	4.5 "Storage conditions"
Flammability	Avoid external energy, such as fire or electricity (passive flammability), avoid overload of the capacitors (active flammability) and consider the flammability of materials.	5.3 "Flammability"
Resistance to vibration	Do not exceed the tested ability to withstand vibration. The capacitors are tested to IEC 60068-2-6. EPCOS offers film capacitors specially designed for operation under more severe vibration regimes such as those found in automotive applications. Consult our catalog "Film Capacitors for Automotive Electronics".	5.2 "Resistance to vibration"



B32911*5 ... B32918*5

X1 / 530 V AC

Topic	Safety information	Reference chapter "Mounting guidelines"
Soldering	Do not exceed the specified time or temperature limits during soldering.	1 "Soldering"
Cleaning	Use only suitable solvents for cleaning capacitors.	2 "Cleaning"
Embedding of capacitors in finished assemblies	When embedding finished circuit assemblies in plastic resins, chemical and thermal influences must be taken into account. Caution: Consult us first, if you also wish to embed other uncoated component types!	3 "Embedding of capacitors in finished assemblies"

Design of EMI Capacitors

EPCOS EMI capacitors use polypropylene (PP) film metalized with a thin layer of Zinc (Zn). The following key points have made this design suitable to IEC/UL testing, holding a minimum size.

- Overvoltage AC capability with very high temperature Endurance test of IEC60384-14 (3rd edition, 2005-07) / UL60384-14 (1st edition, 2009-04) must be performed at $1.25 \times V_R$ at maximum temperature, during 1000 hours, with a capacitance drift less than 10%.
- Higher breakdown voltage withstanding if compared to other film metallizations, like Aluminum. IEC60384-14 (3rd edition, 2005-07) / UL60384-14 (1st edition, 2009-04) establishes high voltage tests performed at $4.3 \times V_R$ – 1 minute, impulse testing at 2500 V for $C = 1 \mu\text{F}$ and active flammability tests.
- Damp heat steady state: 40 °C/ 93% RH / 56 days. (without voltage or current load)

Effect of humidity on capacitance stability


Long contact of a film capacitor with humidity can produce irreversible effects. Direct contact with liquid water or excess exposure to high ambient humidity or dew will eventually remove the film metallization and thus destroy the capacitor. Plastic boxed capacitors must be properly tested in the final application at the worst expected conditions of temperature and humidity in order to check if any parameter drift may provoke a circuit malfunction.

In case of penetration of humidity through the film, the layer of Zinc can be degraded, specially under AC operation (change of polarity), accelerated by the temperature, provoking an increment of the serial resistance of the electrode and eventually a reduction of the capacitance value. For DC operation, the parameter drift is much less.

Plastic boxes and resins can not protect 100% against humidity. Metal enclosures, resin potting or coatings or similar measures by customers in their applications will offer additional protection against humidity penetration.


B32911*5 ... B32918*5

X1 / 530 V AC



Display of ordering codes for EPCOS products

The ordering code for one and the same product can be represented differently in data sheets, data books, other publications and the website of EPCOS, or in order-related documents such as shipping notes, order confirmations and product labels. **The varying representations of the ordering codes are due to different processes employed and do not affect the specifications of the respective products.** Detailed information can be found on the Internet under www.epcos.com/orderingcodes.



B32911*5 ... B32918*5

X1 / 530 V AC

Symbols and terms

Symbol	English	German
α	Heat transfer coefficient	Wärmeübergangszahl
α_C	Temperature coefficient of capacitance	Temperaturkoeffizient der Kapazität
A	Capacitor surface area	Kondensatoroberfläche
β_C	Humidity coefficient of capacitance	Feuchtekoeffizient der Kapazität
C	Capacitance	Kapazität
C_R	Rated capacitance	Nennkapazität
ΔC	Absolute capacitance change	Absolute Kapazitätsänderung
$\Delta C/C$	Relative capacitance change (relative deviation of actual value)	Relative Kapazitätsänderung (relative Abweichung vom Ist-Wert)
$\Delta C/C_R$	Capacitance tolerance (relative deviation from rated capacitance)	Kapazitätstoleranz (relative Abweichung vom Nennwert)
dt	Time differential	Differentielle Zeit
Δt	Time interval	Zeitintervall
ΔT	Absolute temperature change (self-heating)	Absolute Temperaturänderung (Selbsterwärmung)
$\Delta \tan \delta$	Absolute change of dissipation factor	Absolute Änderung des Verlustfaktors
ΔV	Absolute voltage change	Absolute Spannungsänderung
dV/dt	Time differential of voltage function (rate of voltage rise)	Differentielle Spannungsänderung (Spannungsflankensteilheit)
$\Delta V/\Delta t$	Voltage change per time interval	Spannungsänderung pro Zeitintervall
E	Activation energy for diffusion	Aktivierungsenergie zur Diffusion
ESL	Self-inductance	Eigeninduktivität
ESR	Equivalent series resistance	Ersatz-Serienwiderstand
f	Frequency	Frequenz
f_1	Frequency limit for reducing permissible AC voltage due to thermal limits	Grenzfrequenz für thermisch bedingte Reduzierung der zulässigen Wechselspannung
f_2	Frequency limit for reducing permissible AC voltage due to current limit	Grenzfrequenz für strombedingte Reduzierung der zulässigen Wechselspannung
f_r	Resonant frequency	Resonanzfrequenz
F_D	Thermal acceleration factor for diffusion	Therm. Beschleunigungsfaktor zur Diffusion
F_T	Derating factor	Deratingfaktor
i	Current (peak)	Stromspitze
I_C	Category current (max. continuous current)	Kategoriestrom (max. Dauerstrom)

Symbol	English	German
I_{RMS}	(Sinusoidal) alternating current, root-mean-square value	(Sinusförmiger) Wechselstrom
i_z	Capacitance drift	Inkonstanz der Kapazität
k_0	Pulse characteristic	Impuls Kennwert
L_S	Series inductance	Serieninduktivität
λ	Failure rate	Ausfallrate
λ_0	Constant failure rate during useful service life	Konstante Ausfallrate in der Nutzungsphase
λ_{test}	Failure rate, determined by tests	Experimentell ermittelte Ausfallrate
P_{diss}	Dissipated power	Abgegebene Verlustleistung
P_{gen}	Generated power	Erzeugte Verlustleistung
Q	Heat energy	Wärmeenergie
ρ	Density of water vapor in air	Dichte von Wasserdampf in Luft
R	Universal molar constant for gases	Allg. Molarkonstante für Gas
R	Ohmic resistance of discharge circuit	Ohmscher Widerstand des Entladekreises
R_i	Internal resistance	Innenwiderstand
R_{ins}	Insulation resistance	Isolationswiderstand
R_P	Parallel resistance	Parallelwiderstand
R_S	Series resistance	Serienwiderstand
S	severity (humidity test)	Schärfegrad (Feuchtest)
t	Time	Zeit
T	Temperature	Temperatur
τ	Time constant	Zeitkonstante
$\tan \delta$	Dissipation factor	Verlustfaktor
$\tan \delta_D$	Dielectric component of dissipation factor	Dielektrischer Anteil des Verlustfaktors
$\tan \delta_P$	Parallel component of dissipation factor	Parallelanteil des Verlustfaktors
$\tan \delta_S$	Series component of dissipation factor	Serienanteil des Verlustfaktors
T_A	Temperature of the air surrounding the component	Temperatur der Luft, die das Bauteil umgibt
T_{max}	Upper category temperature	Obere Kategorietemperatur
T_{min}	Lower category temperature	Untere Kategorietemperatur
t_{OL}	Operating life at operating temperature and voltage	Betriebszeit bei Betriebstemperatur und -spannung
T_{op}	Operating temperature	Betriebstemperatur
T_R	Rated temperature	Nenntemperatur
T_{ref}	Reference temperature	Referenztemperatur
t_{SL}	Reference service life	Referenz-Lebensdauer



B32911*5 ... B32918*5

X1 / 530 V AC

Symbol	English	German
V_{AC}	AC voltage	Wechselspannung
V_C	Category voltage	Kategoriespannung
$V_{C,RMS}$	Category AC voltage	(Sinusförmige) Kategorie-Wechselspannung
V_{CD}	Corona-discharge onset voltage	Teilentlade-Einsatzspannung
V_{ch}	Charging voltage	Ladespannung
V_{DC}	DC voltage	Gleichspannung
V_{FB}	Fly-back capacitor voltage	Spannung (Flyback)
V_i	Input voltage	Eingangsspannung
V_o	Output voltage	Ausgangssspannung
V_{op}	Operating voltage	Betriebsspannung
V_p	Peak pulse voltage	Impuls-Spitzenspannung
V_{pp}	Peak-to-peak voltage Impedance	Spannungshub
V_R	Rated voltage	Nennspannung
\hat{V}_R	Amplitude of rated AC voltage	Amplitude der Nenn-Wechselspannung
V_{RMS}	(Sinusoidal) alternating voltage, root-mean-square value	(Sinusförmige) Wechselspannung
V_{SC}	S-correction voltage	Spannung bei Anwendung "S-correction"
V_{sn}	Snubber capacitor voltage	Spannung bei Anwendung "Beschaltung"
Z	Impedance	Scheinwiderstand
e	Lead spacing	Rastermaß

Important notes

The following applies to all products named in this publication:

1. Some parts of this publication contain **statements about the suitability of our products for certain areas of application**. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out **that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application**. As a rule we are either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether a product with the properties described in the product specification is suitable for use in a particular customer application.
2. We also point out that **in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified**. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
3. **The warnings, cautions and product-specific notes must be observed.**
4. In order to satisfy certain technical requirements, **some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous)**. Useful information on this will be found in our Material Data Sheets on the Internet (www.tdk-electronics.tdk.com/material). Should you have any more detailed questions, please contact our sales offices.
5. We constantly strive to improve our products. Consequently, **the products described in this publication may change from time to time**. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order.

We also **reserve the right to discontinue production and delivery of products**. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
6. Unless otherwise agreed in individual contracts, **all orders are subject to our General Terms and Conditions of Supply**.
7. **Our manufacturing sites serving the automotive business apply the IATF 16949 standard**. The IATF certifications confirm our compliance with requirements regarding the quality management system in the automotive industry. Referring to customer requirements and customer specific requirements ("CSR") TDK always has and will continue to have the policy of respecting individual agreements. Even if IATF 16949 may appear to support the acceptance of unilateral requirements, we hereby like to emphasize that **only requirements mutually agreed upon can and will be implemented in our Quality Management System**. For clarification purposes we like to point out that obligations from IATF 16949 shall only become legally binding if individually agreed upon.

Important notes

8. The trade names EPCOS, CeraCharge, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CTVS, DeltaCap, DigiSiMic, ExoCore, FilterCap, FormFit, LeaXield, MiniBlue, MiniCell, MKD, MKK, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PowerHap, PQSine, PQvar, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, ThermoFuse, WindCap are **trademarks registered or pending** in Europe and in other countries. Further information will be found on the Internet at www.tdk-electronics.tdk.com/trademarks.

Release 2018-10