

DRB15-1

EVALUATION DATA

型式データ

DWG No. CA798-53-01		
APPD	CHK	DWG
 25/July/13	K. Iida Komatsu 25.Jul.13	Komatsu 25.Jul.13

INDEX

1. 測定方法	Evaluation Method	PAGE
1.1 測定回路	Circuit used for determination	
測定回路 1	Circuit 1 used for determination	T-1
静特性	Steady state data	
過電流保護特性	Over current protection (OCP) characteristics	
過電圧保護特性	Over voltage protection (OVP) characteristics	
出力立ち上がり特性	Output rise characteristics	
出力立ち下がり特性	Output fall characteristics	
出力保持時間特性	Hold up time characteristics	
測定回路 2	Circuit 2 used for determination	T-1
過渡応答（負荷急変）特性	Dynamic load response characteristics	
測定回路 3	Circuit 3 used for determination	T-1
入力サージ電流（突入電流）波形	Inrush current waveform	
測定回路 4	Circuit 4 used for determination	T-2
リーク電流特性	Leakage current characteristics	
測定回路 5	Circuit 5 used for determination	T-2
出力リップル、ノイズ波形	Output ripple and noise waveform	
測定構成	Configuration used for determination	T-2
EMI特性	Electro-Magnetic Interference characteristics	
(a) 雑音端子電圧（帰還ノイズ）	Conducted Emission	
(b) 雑音電界強度（放射ノイズ）	Radiated Emission	
1.2 使用測定機器	List of equipment used	T-3
2. 特性データ	Characteristics	
2.1 静特性	Steady state data	
(1) 入力・負荷・温度変動／出力起動・遮断電圧	Regulation - line and load, Temperature drift / Start up voltage and Drop out voltage	T-4
(2) 効率対出力電流	Efficiency vs. Output current	T-4
(3) 入力電流対出力電流	Input current vs. Output current	T-5
(4) 入力電力対出力電流	Input power vs. Output current	T-5
2.2 過電流保護特性	Over current protection (OCP) characteristics	T-6
2.3 過電圧保護特性	Over voltage protection (OVP) characteristics	T-6
2.4 出力立ち上がり特性	Output rise characteristics	T-7
2.5 出力立ち下がり特性	Output fall characteristics	T-7
2.6 出力保持時間特性	Hold up time characteristics	T-8
2.7 過渡応答（負荷急変）特性	Dynamic load response characteristics	T-9
2.8 入力電圧瞬停特性	Response to brown out characteristics	T-10
2.9 入力サージ電流（突入電流）波形	Inrush current waveform	T-11
2.10 リーク電流特性	Leakage current characteristics	T-12
2.11 出力リップル、ノイズ波形	Output ripple and noise waveform	T-13
2.12 E M I 特性	Electro-Magnetic Interference characteristics	T-14~17

使用記号 Terminology used

	定義	Definition
Vin	入力電圧 Input voltage
Vout	出力電圧 Output voltage
Iin	入力電流 Input current
Iout	出力電流 Output current
Ta	周囲温度 Ambient temperature
f	周波数 Frequency

1. 測定方法


Evaluation Method

1.1 測定回路



Circuit used for determination

測定回路1 Circuit 1 used for determination


- ・静特性 Steady state data
- ・過電流保護特性 Over current protection (OCP) characteristics
- ・過電圧保護特性 Over voltage protection (OVP) characteristics
- ・出力立ち上がり特性 Output rise characteristics
- ・出力立ち下がり特性 Output fall characteristics
- ・出力保持時間特性 Hold up time characteristics

測定回路2 Circuit 2 used for determination

- ・過渡応答(負荷急変) 特性 Dynamic load response characteristics

測定回路3 Circuit 3 used for determination


- ・入力サージ電流(突入電流) 波形 Inrush current waveform



測定回路4 Circuit 4 used for determination


- リーコンダクタ特性

Leakage current characteristics

測定回路5 Circuit 5 used for determination


- 出力リップル、ノイズ波形

Output ripple and noise waveform


測定構成 Configuration used for determination

- E M I 特性 Electro-Magnetic Interference characteristics

(a) 雑音端子電圧 (帰還ノイズ) Conducted Emission



(b) 雑音電界強度 (放射ノイズ) Radiated Emission



1.2 使用測定機器 List of equipment used

	EQUIPMENT USED	MANUFACTURER	MODEL NO.
1	DIGITAL STORAGE OSCILLOSCOPE	YOKOGAWA ELECT.	DL2054
2	DIGITAL MULTIMETER	AGILENT	34970A
3	DIGITAL POWER METER	YOKOGAWA ELECT.	WT210
4	CURRENT PROBE	YOKOGAWA ELECT.	701933
5	DYNAMIC DUMMY LOAD	TAKASAGO	FK-200L
6	AC SOURCE	KIKUSUI	PCR2000L
7	LEAKAGE CURRENT METER	SIMPSON	228
8	CONTROLLED TEMP. CHAMBER	TABAI-ESPEC	SH661
9	EMI TEST RECEIVER	ROHDE & SCHWARZ	ESCI-03
10	LISN	ROHDE & SCHWARZ	ENV216
11	BICONICAL ANTENNA	EMCO	63208

2. 特性データ Characteristics

2.1 静特性 Steady state data

(1) 入力・負荷・温度変動／出力起動・遮断電圧

Regulation - line and load, Temperature drift / Start up voltage and Drop out voltage

24V		1. Regulation - line and load					Condition	Ta : 25 °C
Iout \ Vin		85VAC	115VAC	230VAC	265VAC	line regulation		
0%		24.049V	24.051V	24.051V	24.051V	2mV	0.008%	
50%		24.043V	24.043V	24.043V	24.043V	0mV	0.000%	
100%		24.034V	24.034V	24.034V	24.034V	0mV	0.000%	
load		15mV	17mV	17mV	17mV			
regulation		0.063%	0.071%	0.071%	0.071%			

2. Temperature drift

Conditions Vin : 115 VAC

Iout : 100 %

Ta	-10°C	+25°C	+55°C	temperature stability
Vout	24.032V	24.035V	24.038V	6mV

3. Start up voltage and Drop out voltage

Conditions Ta : 25 °C

Iout : 100 %

Start up voltage (Vin)	39VAC
Drop out voltage (Vin)	42VAC


(2) 効率対出力電流

Efficiency vs. Output current

Conditions Vin : 85 VAC -----
: 115 VAC - - - -
: 230 VAC —————
: 265 VAC - - - -

Ta : 25 °C

24V




(3) 入力電流対出力電流

Input current vs. Output current

24V

Io: 0%	
Vin	Input current
85VAC	0.010A
115VAC	0.011A
230VAC	0.019A
265VAC	0.022A

Conditions Vin : 85 VAC -----
 : 115 VAC - - - - -
 : 230 VAC ——————
 : 265 VAC - - - - -
 Ta : 25 °C




(4) 入力電力対出力電流

Input power vs. Output current

24V


Io: 0%	
Vin	Input power
115VAC	0.09W
230VAC	0.13W

Conditions Vin : 85 VAC -----
 : 115 VAC - - - - -
 : 230 VAC ——————
 : 265 VAC - - - - -
 Ta : 25 °C



2.2 過電流保護特性

Over current protection (OCP) characteristics




2.3 過電壓保護特性

Over voltage protection (OVP) characteristics


Conditions Vin : 115 VAC
 Iout : 0 %
 Ta : 25 °C

Conditions Vin : 230 VAC
 Iout : 0 %
 Ta : 25 °C




2.4 出力立ち上がり特性
Output rise characteristics

Conditions Vin : 85 VAC (A)
 115 VAC (B)
 230 VAC (C)
 265 VAC (D)
Ta : 25 °C





2.5 出力立ち下がり特性
Output fall characteristics

Conditions Vin : 85 VAC (A)
 115 VAC (B)
 230 VAC (C)
 265 VAC (D)
Ta : 25 °C



2.6 出力保持時間特性
Hold up time characteristics


Conditions Vin : 115 VAC -----
230 VAC —————
Ta : 25 °C




2.7 過渡応答（負荷急変）特性

Dynamic load response characteristics

Conditions
 Vin : 115 VAC
 Iout : 25 % \leftrightarrow 75 %
 (tr = tf = 50us)
 Ta : 25 °C



Conditions Vin : 230 VAC
 Iout : 25 % \leftrightarrow 75 %
 (tr = tf = 50us)
 Ta : 25 °C




2.8 入力電圧瞬停特性

Response to brown out characteristics


Conditions
 Vin : 115 VAC
 Iout : 100 %
 Ta : 25 °C

24V



Conditions
 Vin : 230 VAC
 Iout : 100 %
 Ta : 25 °C

24V




2.9 入力サージ電流（突入電流）波形
Inrush current waveform


24V

Conditions Vin : 115 VAC
Iout : 100 %
Ta : 25 °C

Switch on phase angle of input AC voltage
 $\phi = 0^\circ$




Switch on phase angle of input AC voltage
 $\phi = 90^\circ$




Conditions Vin : 230 VAC
Iout : 100 %
Ta : 25 °C

Switch on phase angle of input AC voltage
 $\phi = 0^\circ$



Switch on phase angle of input AC voltage
 $\phi = 90^\circ$




2.10 リーク電流特性

Leakage current characteristics


Conditions Iout : 0 % -----
 100 % ———
 Ta : 25 °C
 Equipment used : 228 (Simpson)

24V

f : 50 Hz




f : 60 Hz




2.11 出力リップル、ノイズ波形
Output ripple and noise waveform

Conditions Vin : 115 VAC
 Ta : 25 °C



Conditions Vin : 230 VAC
 Ta : 25 °C



2.12 EMI 特性

Electro-Magnetic Interference characteristics

Conditions

Vin : 115 VAC

Iout : 100 %


Ta : 25 °C

雜音端子電壓


Conducted Emission

24V

Point A (0.204MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	63.5	55.5
AV	53.5	40.8



Point B (0.204MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	63.5	55.5
AV	53.5	40.9



EN55011-B,VCCI-B,FCC-Bの限界値はEN55022 class Bの限界値と同じ
Limit of EN55011-B,VCCI-B,FCC-B are same as its EN55022 class B.

2.12 EMI特性

Electro-Magnetic Interference characteristics


Conditions Vin : 230 VAC
 Iout : 100 %
 Ta : 25 °C

雜音端子電圧


Conducted Emission

24V

Point A (0.204MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	63.5	53.9
AV	53.5	35.7



Point B (0.191MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
QP	64.0	54.0
AV	54.0	34.2



EN55011-B,VCCI-B,FCC-Bの限界値はEN55022 class Bの限界値と同じ
 Limit of EN55011-B,VCCI-B,FCC-B are same as its EN55022 class B.

2.12 E M I 特性

Electro-Magnetic Interference characteristics


Conditions Vin : 115 VAC
 Io : 100 %
 Ta : 25 °C

雜音電界強度


Radiated Emission

24V

Point A (170.0MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
H	40.0	28.4



Point B (88.3MHz)		
Ref. Data	Limit (dBuV)	Measure (dBuV)
V	40.0	33.4



2.12 E M I 特性

Electro-Magnetic Interference characteristics

Conditions Vin : 230 VAC
 Io : 100 %
 Ta : 25 °C


雜音電界強度

Radiated Emission

24V

HORIZONTAL

Point A (138.9MHz)		
Ref.	Limit (dBuV)	Measure (dBuV)
Data	40.0	30.2



VERTICAL

Point B (55.3MHz)		
Ref.	Limit (dBuV)	Measure (dBuV)
Data	40.0	33.5

