

SWS300

EVALUATION DATA

DWG No. CA740-53-01		
APPD	CHK	DWG
<i>JM</i> 13-Oct-04 2004	<i>Jackson</i> 13-Oct-04	<i>Ryan</i> 13-Oct-04

INDEX


1. Evaluation Method	
1.1 Circuit used for determination	T-1~4
(1) Steady state data	
(2) Over current protection (OCP) characteristics	
(3) Over voltage protection (OVP) characteristics	
(4) Output rise characteristics	
(5) Output fall characteristics	
(6) Dynamic load response characteristics	
(7) Inrush current characteristics	
(8) Leakage current characteristics	
(9) Output ripple and noise waveform	
(10) Electro Magnetic Interference characteristics	
1.2 List of equipment used	T-5
2. Characteristics	
2.1 Steady state data	
(1) Regulation - line and load, temperature drift	T-6
(2) Output voltage and ripple voltage vs. input voltage	T-7
(3) Efficiency and input current vs. output current	T-8
(4) Power factor and input current vs. output current	T-9
2.2 Over current protection (OCP) characteristics	T-10
2.3 Over voltage protection (OVP) characteristics	T-11
2.4 Output rise characteristics	T-12~13
2.5 Output fall characteristics	T-14~15
2.6 Hold up time characteristics	T-16
2.7 Dynamic load response characteristics	T-17~22
2.8 Response to brown out characteristics	T-23~24
2.9 Inrush current waveform	T-25~26
2.10 Input current harmonics	T-27
2.11 Leakage current characteristics	T-28
2.12 Output ripple and noise waveform	T-29
2.13 Electro-Magnetic interference characteristics	T-30~41

Terminology used

Definition		
Vin	Input voltage
Vout	Output voltage
Iin	Input current
Iout	Output current
Ta	Ambient temperature

1.1 Circuit used for determination


(1) Steady state data




(2) Over current protection (O.C.P) characteristics

Same as steady state data.

(3) Over voltage protection (O.V.P) characteristics




(4) Output rise characteristics



(5) Output fall characteristics


Same as output rise characteristics.

(6) Dynamic load response characteristics




Output current waveform :

i_{out} 0% \longleftrightarrow 100%




Output current waveform :


i_{out} 50% \longleftrightarrow 100%



(7) Inrush current characteristics




(8) Leakage current characteristics



Note : Leakage current measured through a 1k ohm resistor.
 Range used : AC + DC (For SIMPSON MODEL 228)


(9) Output - ripple, noise waveform

Normal Mode




(10) Electro-Magnetic Interference characteristics

(a) Conducted Emission Noise



(b) Radiated Emission Noise



1.2 LIST OF EQUIPMENT USED

	EQUIPMENT USED	MANUFACTURER	MODEL NO.
1	Oscilloscope	HITACHI	V-1050F
2	Digital storage oscilloscope	TEKTRONIX	TDS 540A
3	Digital volt meter	FLUKE	45
4	Digital power meter	YOKOGAWA	WT110
5	DC ampere meter	YOKOGAWA	2051
6	Dynamic dummy load	CHROMA	63030
7	Current probe/amplifier	TEKTRONIX	A6303/AM503B
8	Controlled temperature chamber	TABAI-ESPEC	SU-240
9	Leakage current meter	SIMPSON	228
10	Digirush currenter	TAKAMIZAWA CYBERNETICS	PSA-200
11	EMI receiver	HEWLETT PACKARD	HP8546A
12	LISN	EMCO	3825/2
13	Biconical antenna	EMCO	3110B

2. Characteristics

2.1 Steady state data

(1) Regulation - line and load, temperature drift

5V

1. Regulation-line and load

Iout \ Vin	85VAC	115VAC	230VAC	265VAC	line regulation	
0%	5.010V	5.010V	5.010V	5.009V	0.001V	0.020%
50%	5.003V	5.000V	5.000V	4.999V	0.004V	0.080%
100%	4.994V	4.991V	4.991V	4.991V	0.003V	0.060%
load	0.016V	0.019V	0.019V	0.018V		
regulation	0.320%	0.380%	0.380%	0.360%		

2. Temperature drift

Conditions Vin =115VAC

Iout =100%

Ta	-10°C	+25°C	+50°C	temperature stability
Vout	4.993V	4.991V	4.986V	0.007V 0.140%

24V

1. Regulation-line and load

condition Ta : 25°C

Iout \ Vin	85VAC	115VAC	230VAC	265VAC	line regulation	
0%	23.996V	23.996V	23.997V	23.997V	0.001V	0.004%
50%	23.991V	23.991V	23.991V	23.991V	0.000V	0.000%
100%	23.987V	23.988V	23.988V	23.988V	0.001V	0.004%
load	0.009V	0.008V	0.009V	0.009V		
regulation	0.038%	0.033%	0.038%	0.038%		

2. Temperature drift

Conditions Vin =115VAC

Iout =100%

Ta	-10°C	+25°C	+50°C	temperature stability
Vout	23.970V	23.988V	23.976V	0.018V 0.075%

48V

1. Regulation-line and load

condition Ta : 25°C

Iout \ Vin	85VAC	115VAC	230VAC	265VAC	line regulation	
0%	48.049	48.058	48.062	48.062	0.013V	0.027%
50%	48.042	48.046	48.048	48.048	0.006V	0.013%
100%	48.031	48.035	48.036	48.036	0.005V	0.010%
load	0.018V	0.023V	0.026V	0.026V		
regulation	0.038%	0.048%	0.054%	0.054%		

2. Temperature drift

Conditions Vin =115VAC


Iout =100%

Ta	-10°C	+25°C	+50°C	temperature stability
Vout	47.996V	48.035V	48.005V	0.039V 0.081%


(2) Output voltage and ripple voltage v.s. input voltage

Conditions I_{out} : 100%
 T_a : -10°C -----
 : 25°C -----
 : 50°C -----


5V



24V




48V




(3) Efficiency and input current v.s. output current

Conditions Vin : 85VAC
 : 115VAC
 : 230VAC
 : 265VAC
 Ta : 25°C


5V



24V




48V




(4) Power factor and input current v.s output current

Conditions Vin : 85VAC
 : 115VAC
 : 230VAC
 : 265VAC
 Ta : 25°C


5V




24V



48V




2.2 Over current protection (OCP) characteristics




2.3 Over voltage protection (OVP) characteristics

Conditions Vin : 230VAC
 Iout : 0%
 Ta : 25°C


5V



24V






48V




2.4 Output rise characteristics

Conditions
 Vin : 85VAC (A)
 : 115VAC (B)
 : 230VAC (C)
 : 265VAC (D)
 Iout : 0%
 Ta : 25°C




2.4 Output rise characteristics

Conditions Vin : 85VAC (A)
 : 115VAC (B)
 : 230VAC (C)
 : 265VAC (D)
 Iout : 100%
 Ta : 25°C






2.5 Output fall characteristics

Conditions Vin : 85VAC (A)
 : 115VAC (B)
 : 230VAC (C)
 : 265VAC (D)
 Iout : 0%
 Ta : 25°C






2.5 Output fall characteristics

Conditions Vin : 85VAC (A)
 : 115VAC (B)
 : 230VAC (C)
 : 265VAC (D)
 Iout : 100%
 Ta : 25°C



2.6 Hold up time characteristics

Conditions Vin : 115VAC -----
 : 230VAC -----
 Ta : 25°C





2.7 Dynamic load response characteristics



Conditions Vin : 115VAC
 Ta : 25°C

5V

f=100Hz



f=1kHz




2.7 Dynamic load response characteristics


Conditions Vin : 230VAC
 Ta : 25°C

5V

f=100Hz



f=1kHz




2.7 Dynamic load response characteristics

Conditions V_{in} : 115VAC
 T_a : 25°C

24V

f=100Hz

Load current tr = tf = 50μs
 50% \longleftrightarrow 100%




200mV/DIV

+0.20%

2ms/DIV

-0.29%

Load current tr = tf = 50μs
 0% \longleftrightarrow 100%



200mV/DIV


+0.39%

2ms/DIV

-1.35%

f=1kHz

Load current tr = tf = 50μs
 50% \longleftrightarrow 100%




200mV/DIV

+0.23%

200μs/DIV

-0.36%

Load current tr = tf = 50μs
 0% \longleftrightarrow 100%



200mV/DIV

+0.56%





200μs/DIV

-1.24%

2.7 Dynamic load response characteristics

Conditions Vin : 230VAC
 Ta : 25°C



24V

f=100Hzf=1kHz

2.7 Dynamic load response characteristics

Conditions Vin : 115VAC
 Ta : 25°C

48V

f=100Hzf=1kHz


2.7 Dynamic load response characteristics

Conditions Vin : 230VAC
 Ta : 25°C


48V

f=100Hz


Load current tr = tf = 50μs
 50% \longleftrightarrow 100%




Load current tr = tf = 50μs
 0% \longleftrightarrow 100%

f=1kHz

Load current tr = tf = 50μs
 50% \longleftrightarrow 100%




Load current tr = tf = 50μs
 0% \longleftrightarrow 100%




2.8 Response to brown out characteristics

Conditions Vin : 115V
 Iout : 100%
 Ta : 25°C





2.8 Response to brown out characteristics



2.9 Inrush current waveform



Conditions

V_{in} : 115VAC
I_{out} : 100%
T_a : 25°C





2.9 Inrush current waveform

Conditions Vin : 230VAC
 Iout : 100%
 Ta : 25°C




2.10 Input current harmonics




2.11 Leakage current characteristics

Conditions I_{out} : 0% -----
 : 100% _____
 Ta : 25°C
 f : 50Hz
 Equipment used : MODEL 228 (Simpson)


5V



24V



48V




2.12 Output ripple and noise waveform


Conditions
Vin : 230VAC
Iout : 100%
Ta : 25°C

NORMAL MODE


5V



24V



48V



2.13 Electro-Magnetic interference characteristics

Conducted Emission


5V

Conditions


Vin : 115VAC

Iout : 100%

Point A (0.18MHz)			
Ref.	Data	Limit (dB μ V)	Measure (dB μ V)
QP	64.4	52.8	
AV	54.4	37.0	



Point B (0.18MHz)			
Ref.	Data	Limit (dB μ V)	Measure (dB μ V)
QP	64.4	52.2	
AV	54.4	37.4	



2.13 Electro-Magnetic interference characteristics

Conducted Emission


5V

Conditions


Vin : 230VAC

Iout : 100%

Point A (0.19MHz)			
Ref.	Data	Limit (dB μ V)	Measure (dB μ V)
QP	63.9	43.6	
AV	53.9	24.1	



Point B (0.19MHz)			
Ref.	Data	Limit (dB μ V)	Measure (dB μ V)
QP	63.9	42.5	
AV	53.9	33.9	



2.13 Electro-Magnetic interference characteristics

Conducted Emission


24V

Conditions


Vin : 115VAC

Iout : 100%

Point A (0.26MHz)			
Ref.	Data	Limit (dB μ V)	Measure (dB μ V)
QP	61.3	40.5	
AV	51.3	40.2	



Point B (0.26MHz)			
Ref.	Data	Limit (dB μ V)	Measure (dB μ V)
QP	61.3	41.0	
AV	51.3	41.4	



2.13 Electro-Magnetic interference characteristics

Conducted Emission

24V


Conditions

Vin : 230VAC

Iout : 100%


Point A (0.18MHz)			
Ref.	Data	Limit (dB μ V)	Measure (dB μ V)
QP	64.8	42.1	
AV	54.8	39.6	

Point B (0.26MHz)			
Ref.	Data	Limit (dB μ V)	Measure (dB μ V)
QP	61.3	38.0	
AV	51.3	38.6	



Point C (0.18MHz)			
Ref.	Data	Limit (dB μ V)	Measure (dB μ V)
QP	64.7	57.6	
AV	54.7	39.9	

Point D (11.77MHz)			
Ref.	Data	Limit (dB μ V)	Measure (dB μ V)
QP	60.0	44.7	
AV	50.0	39.5	



2.13 Electro-Magnetic interference characteristics

Conducted Emission


48V

Conditions


Vin : 115VAC

Iout : 100%

Point A (0.26MHz)			
Ref.	Data	Limit (dB μ V)	Measure (dB μ V)
QP	61.3	43.0	
AV	51.3	41.8	



Point B (11.75MHz)			
Ref.	Data	Limit (dB μ V)	Measure (dB μ V)
QP	60.0	44.0	
AV	50.0	41.4	



2.13 Electro-Magnetic interference characteristics

Conducted Emission


48V

Conditions


Vin : 230VAC

Iout : 100%

Point A (12.01MHz)			
Ref.	Data	Limit (dB μ V)	Measure (dB μ V)
QP	60.0	43.6	
AV	50.0	40.2	




Point B (12.01MHz)			
Ref.	Data	Limit (dB μ V)	Measure (dB μ V)
QP	60.0	44.5	
AV	50.0	41.1	




2.13 Electro-Magnetic interference characteristics

Radiated Emission




2.13 Electro-Magnetic interference characteristics

Radiated Emission




2.13 Electro-Magnetic interference characteristics

Radiated Emission




2.13 Electro-Magnetic interference characteristics

Radiated Emission



2.13 Electro-Magnetic interference characteristics

Radiated Emission



2.13 Electro-Magnetic interference characteristics

Radiated Emission

