

LS50

RELIABILITY DATA

DWG. No PA582-57-01		
APPD	CHK	DWG
<i>2888</i> 2 Apr 08	<i>Ramch</i> 2-Apr-08	<i>Amidoto</i> 02/04/08

I N D E X

	PAGE
1. Calculated Values of MTBF	R - 1
2. Component Derating	R - 2
3. Main Components Temperature Rise ΔT List	R - 5
4. Electrolytic Capacitor Life	R - 7
5. Vibration Test	R - 11
6. Noise Simulate Test	R - 12
7. Abnormal Test	R - 13
8. Thermal Shock Test	R - 16

※ The above data is typical value. As all units have nearly the same characteristics, the data to be considered as ability value.

1. Calculated values for MTBF

MODEL : LS50-5

1. Calculating Method

Calculated based on part count reliability projection of JEITA (RCR-9102A).

Individual failure rates λ_G is given to each part and MTBF is calculated by the count of each part.

Formula :

$$\text{MTBF} = \frac{1}{\lambda_{\text{equip}}} = \frac{1}{\sum_{i=1}^n N_i (\lambda_G \pi_Q)_i} \times 10^6 \text{ (HOURS)}$$

where :

λ_{equip} = Total Equipment Failure Rate (Failure / 106 Hours)

λ_G = Generic Failure Rate For The ith Generic Part (Failure / 106 Hours)

N_i = Quantity of ith Generic Part

n = Number of Different Generic Part Categories

π_Q = Generic Quality Factor for the ith Generic Part ($\pi_Q = 1$)

2. MTBF Values

G_F : (GROUND, FIXED)

MTBF = 712,890 (Hours)

2. Component derating

MODEL : LS50-5

(1) Calculating method

(a) Measuring Conditions

Input	:	115 , 230VAC	• Ambient temperature	:	50°C
Output	:	5V 10A(100%)	• Mounting method	:	Mounting A

(b) Semiconductors

Compared with maximum junction temperature and actual one which is calculated based on case temperature, power dissipation and thermal impedance.

(c) IC, Resistors, Capacitors, etc.

Ambient temperature, operating condition, power dissipation and so on are within derating criteria.

(d) Calculating Method of Thermal Impedance

$$\theta_{j-c} = \frac{T_{j(max)} - T_c}{P_{c(max)}} \quad \theta_{j-a} = \frac{T_{j(max)} - T_a}{P_{c(max)}} \quad \theta_{j-l} = \frac{T_{j(max)} - T_l}{P_{c(max)}}$$

T_c : Case temperature at start point of derating ; 25°C in general

T_a : Ambient temperature at start point of derating ; 25°C in general

T_j : Lead temperature at start point of derating ; 25°C in general

$P_{c(max)}$: Maximum collector(channel) dissipation
 $(P_{ch(max)})$

$T_{j(max)}$: Maximum junction(channel) temperature
 $(T_{ch(max)})$

(θ_{j-c}) : Thermal impedance between junction(channel) and case
 (θ_{ch-c})

θ_{j-a} : Thermal impedance between junction and air

θ_{j-l} : Thermal impedance between junction and lead

(2) Component Derating List

Location No.	Vin = 115VAC Load = 100% Ta = 50°C
Q3 STF11NM60N ST MICROELECTRONICS	Tchmax = 150°C, $\theta_{ch-c} = 3.57^{\circ}\text{C}/\text{W}$, Pch = 1.21W, $\Delta T_c = 47.8^{\circ}\text{C}$, Tch = Tc + ((θ_{ch-c}) × Pch) = 102.12°C D.F. = 68.08%
D8 STPS20L45CFP ST MICROELECTRONICS	Tjmax = 150°C, $\theta_{j-c} = 3.5^{\circ}\text{C}/\text{W}$, Pd = 5.3W, $\Delta T_c = 63.9^{\circ}\text{C}$, Tj = Tc + ((θ_{j-c}) × Pd) = 132.45°C D.F. = 88.3%
D1 RS405M RECTRON	Tjmax = 150°C, $\theta_{j-c} = 6.0^{\circ}\text{C}/\text{W}$ Pd = 1.81W, $\Delta T_c = 46.5^{\circ}\text{C}$ Tj = Tc + ((θ_{j-c}) × Pd) = 107.36°C D.F. = 71.57%
D2 CRF02 TOSHIBA	Tjmax = 150°C, $\theta_{j-l} = 20^{\circ}\text{C}/\text{W}$ Pd = 0.134W, $\Delta T_l = 62.1^{\circ}\text{C}$ Tj = Tl + ((θ_{j-l}) × Pd) = 114.78°C D.F. = 76.52%
D7 CRH01 TOSHIBA	Tjmax = 150°C, $\theta_{j-l} = 20^{\circ}\text{C}/\text{W}$ Pd = 4mW, $\Delta T_l = 35.8^{\circ}\text{C}$ Tj = Tl + ((θ_{j-l}) × Pd) = 85.88°C D.F. = 57.25%
PC1 PS2581L2-E3(D)-A (TRANSISTOR) NEC	Tjmax = 125°C, $\theta_{j-c} = 150^{\circ}\text{C}/\text{W}$, Pc = .02mW, $\Delta T_c = 34.6^{\circ}\text{C}$, Tj = Tc + ((θ_{j-c}) × Pc) = 84.6°C D.F. = 67.68%
PC1 PS2581L2-E3(D)-A (LED) NEC	Tjmax = 125°C, $\theta_{j-c} = 150^{\circ}\text{C}/\text{W}$, Pc = 12mW, $\Delta T_c = 34.6^{\circ}\text{C}$, Tj = Tc + ((θ_{j-c}) × Pc) = 86.4°C D.F. = 69.12%
PC2 PS2581L2-E3(D)-A (TRANSISTOR) NEC	Tjmax = 125°C, $\theta_{j-c} = 150^{\circ}\text{C}/\text{W}$, Pc = 0.0W, $\Delta T_c = 34.1^{\circ}\text{C}$, Tj = Tc + ((θ_{j-c}) × Pc) = 84.6°C D.F. = 67.28%
PC2 PS2581L2-E3(D)-A (LED) NEC	Tjmax = 125°C, $\theta_{j-c} = 150^{\circ}\text{C}/\text{W}$, Pc = 0.0W, $\Delta T_c = 34.1^{\circ}\text{C}$, Tj = Tc + ((θ_{j-c}) × Pc) = 84.1°C D.F. = 67.28%
A1 FA13842N-D1-TE1 FUJI-ELEC.	Tjmax = 150°C, $\theta_{j-c} = 72^{\circ}\text{C}/\text{W}$ Pd = 0.108W, $\Delta T_c = 32.5^{\circ}\text{C}$ Tj = Tc + ((θ_{j-c}) × Pd) = 90.276°C D.F. = 60.18%
A2 HA17L431AP-TZ-E RENESAS	Tjmax = 150°C, $\theta_{j-c} = 100^{\circ}\text{C}/\text{W}$, Pd = 8mW, $\Delta T_c = 13.7^{\circ}\text{C}$, Tj = Tc + ((θ_{j-c}) × Pd) = 64.5°C D.F. = 43.0%
PD1 WP1154GD KING BRIGHT	IF = 6mA, $\Delta T_c = 14.9^{\circ}\text{C}$ Allowable IF(max)= 13mA(at Ta = 64.9°C) D.F. = 46.15%

Component Derating List

Location No.	Vin = 230VAC Load = 100% Ta = 50°C
Q3 STF11NM60N ST MICROELECTRONICS	Tchmax = 150°C, $\theta_{ch-c} = 3.57^{\circ}\text{C}/\text{W}$, Pch = 1.73W, $\Delta T_c = 45^{\circ}\text{C}$, $T_c = 95^{\circ}\text{C}$ $T_{ch} = T_c + ((\theta_{ch-c}) \times Pch) = 101.18^{\circ}\text{C}$ D.F. = 67.45%
D8 STPS20L45CFP ST MICROELECTRONICS	Tjmax = 150°C, $\theta_{j-c} = 3.5^{\circ}\text{C}/\text{W}$, Pd = 5.3W, $\Delta T_c = 60.5^{\circ}\text{C}$, $T_c = 110.5^{\circ}\text{C}$ $T_j = T_c + ((\theta_{j-c}) \times Pd) = 129.05^{\circ}\text{C}$ D.F. = 86.03%
D1 RS405M RECTRON	Tjmax = 150°C, $\theta_{j-c} = 6.0^{\circ}\text{C}/\text{W}$, Pd = 1.10 W, $\Delta T_c = 39.3^{\circ}\text{C}$, $T_c = 89.3^{\circ}\text{C}$ $T_j = T_c + ((\theta_{j-c}) \times Pd) = 95.9^{\circ}\text{C}$ D.F. = 63.93%
D2 CRF02 TOSHIBA	Tjmax = 150°C, $\theta_{j-l} = 20^{\circ}\text{C}/\text{W}$, Pd = 0.126W, $\Delta T_l = 58.1^{\circ}\text{C}$, $T_l = 108.1^{\circ}\text{C}$ $T_j = T_l + ((\theta_{j-l}) \times Pd) = 110.62^{\circ}\text{C}$ D.F. = 73.75%
D7 CRH01 TOSHIBA	Tjmax = 150°C, $\theta_{j-l} = 20^{\circ}\text{C}/\text{W}$, Pd = 2.7mW, $\Delta T_l = 34.1^{\circ}\text{C}$, $T_l = 84.1^{\circ}\text{C}$ $T_j = T_l + ((\theta_{j-l}) \times Pd) = 84.154^{\circ}\text{C}$ D.F. = 56.10%
PC1 PS2581L2-E3(D)-A (TRANSISTOR) NEC	Tjmax = 125°C, $\theta_{j-c} = 150^{\circ}\text{C}/\text{W}$, Pc = .02mW, $\Delta T_c = 33.5^{\circ}\text{C}$, $T_c = 83.5^{\circ}\text{C}$ $T_j = T_c + ((\theta_{j-c}) \times P_c) = 83.51^{\circ}\text{C}$ D.F. = 66.80%
PC1 PS2581L2-E3(D)-A (LED) NEC	Tjmax = 125°C, $\theta_{j-c} = 150^{\circ}\text{C}/\text{W}$, Pc = 19mW, $\Delta T_c = 33.5^{\circ}\text{C}$, $T_c = 83.5^{\circ}\text{C}$ $T_j = T_c + ((\theta_{j-c}) \times P_c) = 86.35^{\circ}\text{C}$ D.F. = 69.08%
PC2 PS2581L2-E3(D)-A (TRANSISTOR) NEC	Tjmax = 125°C, $\theta_{j-c} = 150^{\circ}\text{C}/\text{W}$, Pc = 0.0W, $\Delta T_c = 33.8^{\circ}\text{C}$, $T_c = 83.8^{\circ}\text{C}$ $T_j = T_c + ((\theta_{j-c}) \times P_c) = 83.8^{\circ}\text{C}$ D.F. = 67.04%
PC2 PS2581L2-E3(D)-A (LED) NEC	Tjmax = 125°C, $\theta_{j-c} = 150^{\circ}\text{C}/\text{W}$, Pc = 0.0W, $\Delta T_c = 33.8^{\circ}\text{C}$, $T_c = 83.8^{\circ}\text{C}$ $T_j = T_c + ((\theta_{j-c}) \times P_c) = 83.8^{\circ}\text{C}$ D.F. = 67.04%
A1 FA13842N-D1-TE1 FUJI-ELEC.	Tjmax = 150°C, $\theta_{j-c} = 72^{\circ}\text{C}/\text{W}$, Pd = 0.103W, $\Delta T_c = 31.5^{\circ}\text{C}$, $T_c = 81.5^{\circ}\text{C}$ $T_j = T_c + ((\theta_{j-c}) \times Pd) = 88.916^{\circ}\text{C}$ D.F. = 59.28%
A2 HA17L431AP-TZ-E RENESAS	Tjmax = 150°C, $\theta_{j-c} = 100^{\circ}\text{C}/\text{W}$, Pd = 8mW, $\Delta T_c = 13.8^{\circ}\text{C}$, $T_c = 63.8^{\circ}\text{C}$ $T_j = T_c + ((\theta_{j-c}) \times Pd) = 64.6^{\circ}\text{C}$ D.F. = 43.1%
PD1 WP1154GD KING BRIGHT	IF = 6mA, $\Delta T_c = 14.9^{\circ}\text{C}$, Allowable IF(max)= 13mA(at Ta = 64.9°C) D.F. = 46.15%

3. Main components temperature rise ΔT list

MODEL : LS50-5

Condition:

Standard Mounting (Mounting Method (A))	(A)			
	Mounting A	Mounting B	Mounting C	Mounting D
Input Voltage (VAC)		115		
Output Voltage (VDC)		5		
Output Current (A)		10		

Output Derating $T_a = 50^\circ\text{C}$		ΔT Temperature rise ($^\circ\text{C}$)			
Location No	Parts Name	$Io=100\%$	$Io=100\%$	$Io=70\%$	$Io=100\%$
Mounting (A)	Mounting (B)	Mounting (C)	Mounting (D)		
Q3	MOSFET	47.8	60.3	44	52.6
D1	BRIDGE DIODE	46.5	58.3	43.4	49.5
D8	F.R. DIODE	63.9	59.4	59.9	60.1
A1	CHIP IC	32.5	43.3	27.5	39.5
A2	CHIP SHUNT REGULATOR	25.8	28.2	41.8	21.9
PC1	CHIP PHOTOCOUPLER	33.3	31.5	30.2	35.6
T1	TRANS. PULSE	48.2	44.6	41.7	48
L1	BALUN COIL	46.3	55.5	47	47.9
L5	CHOKE COIL	51.5	50.3	62.5	46.5
C3	CAP. FILM	25.5	32	38.5	21.3
C4	CAP. FILM	33.9	51	36	38.3
C8	CAP. ELECT.	28	37.7	23.8	32.2
C2	CAP. CERAMIC	32.8	37.9	39.2	25.3
C20	CAP. ELECT.	27.7	27.2	22	39.8
C21	CAP. ELECT.	26.7	25.1	21.7	39.4
C26	CAP. ELECT.	46.8	39.5	41.9	37.1
C27	CAP. ELECT.	48	44.5	43.9	40
C28	CAP. ELECT.	45.2	40.5	44.2	36.4
C29	CAP. ELECT.	43.5	37.7	43.6	35.8
C30	CAP. ELECT.	40.6	42.2	45.3	33.7

3. Main components temperature rise ΔT list

MODEL : LS50-5

Condition:


		(A)			
Standard Mounting (Mounting Method (A))		Mounting A	Mounting B	Mounting C	Mounting D
Input Voltage (VAC)		230			
Output Voltage (VDC)		5			
Output Current (A)		10			

		ΔT Temperature rise ($^{\circ}\text{C}$)			
Output Derating $T_a = 50^{\circ}\text{C}$		$I_o=100\%$	$I_o=100\%$	$I_o=70\%$	$I_o=100\%$
Location No	Parts Name	Mounting (A)	Mounting (B)	Mounting (C)	Mounting (D)
Q3	MOSFET	45	57.5	42.3	49
D1	BRIDGE DIODE	39.3	51	37.1	41.3
D8	F.R. DIODE	60.5	55.8	56.5	56.7
A1	CHIP IC	31.5	41.2	27	36.9
A2	CHIP SHUNT REGULATOR	24.9	27.2	39.2	21.1
PC1	CHIP PHOTOCOUPLER	31.4	29.6	28.5	33.5
T1	TRANS. PULSE	45.9	42.3	39.9	45.4
L1	BALUN COIL	32.6	41.9	31.9	31.3
L5	CHOKE COIL	49.9	49	59.5	45.3
C3	CAP. FILM	21.3	28.3	30.9	18
C4	CAP. FILM	27.1	42.4	29.6	29.8
C8	CAP. ELECT.	24.7	34.1	21.2	27.8
C2	CAP. CERAMIC	28.1	34.1	33.8	22.4
C20	CAP. ELECT.	26.1	25.4	20.9	37.2
C21	CAP. ELECT.	24.9	23.5	20.6	37.1
C26	CAP. ELECT.	43.7	36.8	39	34.6
C27	CAP. ELECT.	43.4	40.3	39.7	36.1
C28	CAP. ELECT.	41.5	37.4	40.5	33.7
C29	CAP. ELECT.	41	35.6	40.6	33.8
C30	CAP. ELECT.	37.6	39.7	41.6	31.8

4. Electrolytic capacitor lifetime

MODEL : LS50-5


Mounting A



Ta = 40°C	—
= 50°C	- - -
= 70°C	-----


Vin = 115VAC

Load (%)	Life Time (years)		
	Ta = 40°C	Ta = 50°C	Ta = 70°C
50	10.0	5.1	1.3
60	8.8	4.4	1.1
70	7.4	3.7	0.9
80	6.6	3.3	—
90	6.4	3.2	—
100	5.0	2.5	—



Vin = 230VAC


Load (%)	Life Time (years)		
	Ta = 40°C	Ta = 50°C	Ta = 70°C
50	10.0	10.0	3.8
60	10.0	10.0	3.3
70	10.0	10.0	3.0
80	10.0	10.0	—
90	10.0	9.6	—
100	10.0	6.9	—



Note : E-cap life calculation is based on 8hrs/day operation.


4. Electrolytic capacitor lifetime

MODEL : LS50-5




Vin = 115VAC

Load (%)	Life Time (years)		
	Ta = 40°C	Ta = 50°C	Ta = 70°C
50	9.0	4.5	1.1
60	7.3	3.6	0.9
70	5.7	2.9	0.7
80	4.5	2.2	—
90	3.4	1.7	—
100	2.6	1.3	—



Vin = 230VAC


Load (%)	Life Time (years)		
	Ta = 40°C	Ta = 50°C	Ta = 70°C
50	10.0	10.0	2.8
60	10.0	8.9	2.2
70	10.0	7.7	1.9
80	10.0	6.3	—
90	10.0	5.3	—
100	8.7	4.4	—




Note : E-cap life calculation is based on 8hrs/day operation.

4. Electrolytic capacitor lifetime

MODEL : LS50-5




Load (%)	Life Time (years)		
	Ta = 40°C	Ta = 50°C	Ta = 70°C
50	10.0	6.9	1.7
60	10.0	6.2	1.5
70	10.0	5.3	1.3
80	9.2	—	—
90	7.9	—	—
100	6.7	—	—



Vin = 230VAC


Load (%)	Life Time (years)		
	Ta = 40°C	Ta = 50°C	Ta = 70°C
50	10.0	10.0	4.4
60	10.0	10.0	3.9
70	10.0	10.0	3.1
80	10.0	—	—
90	10.0	—	—
100	10.0	—	—




Note : E-cap life calculation is based on 8hrs/day operation.

4. Electrolytic capacitor lifetime

MODEL : LS50-5




Load (%)	Life Time (years)		
	Ta = 40°C	Ta = 50°C	Ta = 70°C
50	10.0	5.5	1.4
60	9.2	4.6	1.1
70	7.4	3.7	0.9
80	6.0	3.0	—
90	4.7	2.4	—
100	3.7	1.9	—



Vin = 230VAC

Load (%)	Life Time (years)		
	Ta = 40°C	Ta = 50°C	Ta = 70°C
50	10.0	10.0	3.7
60	10.0	10.0	3.0
70	10.0	10.0	2.7
80	10.0	9.4	—
90	10.0	7.8	—
100	10.0	6.8	—



Note : E-cap life calculation is based on 8hrs/day operation.

5. Vibration Test

MODEL : LS50-5

(1) Vibration Test Class

Frequency Variable Endurance Test

(2) Equipment Used

Controller	:	F-400-BM-E47 (EMIC CORP.)
Vibrator	:	905-FN (EMIC CORP.)
Serial no.	:	22965


(3) The Number Of D.U.T. (Device Under Test)

1 Unit

(4) Test Conditions

Sweep Frequency	:	10 - 55Hz	Direction	:	X, Y, Z
Sweep Time	:	1 minute	Test Time	:	1 hour each axis
Acceleration	:	2G			Non-operation
Mounting	:	A and B			

(5) Test Method



Fix the PSUT on the universal plate via two M3 tapped holes on the chassis of the power supply.
Standard mounting position as per test specification.

(6) Test results - OK


Test Conditions :	Vin	= 230 Vac	Load Condition :
	Ambient Temp.	= +25 °C	Full Load

Check Item		Output Voltage (V)	PSUT State
Before Test		V _{o1}	
5.046			
After test	X	5.046	OK
	Y	5.046	OK
	Z	5.046	OK

6. Noise simulate test

MODEL : LS50-5

(1) Test circuit and equipment



Simulator : INS-400L Noise Laboratory Co.,LTD

(2) Test conditions

- | | | | | | |
|-----------------------|---|--------------|------------------|---|---------------|
| • Input voltage | : | 115, 230VAC | • Noise level | : | 0V~2.4kV |
| • Output voltage | : | Rated | • Phase shift | : | 0° ~ 360° |
| • Output current | : | 0%, 100% | • Polarity | : | +, - |
| • Ambient temperature | : | 25°C | • Mode | : | Normal Common |
| • Pulse Width | : | 0ns ~ 1000ns | • Trigger select | : | Line |

(3) Acceptable conditions

1. Not to be broken.
2. No output shutdown.
3. No other out of order.

(4) Test result O K

7. Abnormal test

MODEL : LS50-5

(1) Test Condition

Input Voltage : 230VAC Output Current : 100% Ta : 25°C, 70% RH

(2) Test Results

(Da: Damaged)

No.	Test Position		Test Mode		Test Results												NOTE
	LOCATION	TEST POINT	S H O R T	O P E N	1	2	3	4	5	6	7	8	9	10	11	12	
					F I R E	S M O R E	B U R S L	S M E R L	R A D M A	D A M S E	F U A G B	O . . C P . .	O V P P . .	O O U U T	N O O C H	N O O C H	O T H A N G E
1	D1	(+) - (-)	•								•	•			•		Da : F1
2	D2		•												•		
3	D3		•												•		
4	D4		•												•		
5	D5	D4/R24	•												•		
		R24		•											•		
		D4		•											•		
6	D7		•								•					•	Hiccup, Da : R31,R32
7	D8		•												•		No Damage Da : R35, A1
8	Q1	3 - 4	•												•	•	Latch
				•											•		
		1 - 6	•												•	•	Latch
					•										•		
		3 - 5	•												•	•	Latch
						•									•		
9	Q2	6 - 2	•												•	•	Latch
				•											•		
		C - E	•												•		
		B - E	•												•		Hiccup
10	Q3	C - B	•												•		Hiccup
		G - S	•								•				•		Da : R35
		D - G	•							•	•				•		Da : R35,Z1,Z2,F1
11	C8	D - S	•							•	•				•		Da : F1,R35,Z1
		(+)Bulk - (-)Bulk	•							•	•				•		Da : F1
12	C15		•												•		
13	C16		•												•		
14	C17/R24		•												•		
		C17	•												•		
		R24	•												•		

7. Abnormal test

MODEL : LS50-5

(1) Test Condition

Input Voltage : 230VAC Output Current : 100% Ta : 25°C, 70% RH

(2) Test Results

(Da: Damaged)

No.	Test Position		Test Mode		Test Results												NOTE
	LOCATION	TEST POINT	S H O R T	O P E N	1	2	3	4	5	6	7	8	9	10	11	12	
					F I M O R S E K T	S M U O R L E T	B U M S L H A O T	S E D L L G A O T	R E A M A G B L O W	D A M A G E B L O W	F U S C P B L O U	O .C V P .	O O V P .	N O O U T	N O C H A	N O C H A	O T H E R
15	C36 OR C37		•													•	
					•											•	Hissing sound
16	PC1	1 - 2	•												•	•	Latch
		3 - 4	•												•	•	
		1 - 2		•											•	•	Latch
		3 - 4		•											•	•	
17	PC2	3 - 4	•												•	•	
				•											•	•	
		1 - 2	•												•	•	
				•											•	•	
18	A1	Vcc - GND	•												•	•	
		Vref - GND	•												•	•	
		Isense - GND	•									•			•	•	Da : Q3,Z2
		RtCt - GND	•												•	•	
		FB - GND	•												•	•	
		Comp - GND	•												•	•	
		Out - GND	•												•	•	
19	A2	A - K	•												•	•	
		R - K	•												•	•	Vo = 3.68V
		R - A	•												•	•	Latch
20	T1	Np	•												•	•	
		Nbias	•												•	•	
		Ns	•												•	•	
21	PD1		•												•	•	
				•											•	•	
22	Z1		•												•	•	
				•											•	•	
23	Z2		•								•				•	•	Da : Q2
				•											•	•	
24	Z4		•												•	•	
				•											•	•	
25	R9/C10	R9/C10	•												•	•	
		R9	•												•	•	
		C10	•												•	•	
26	R18		•												•	•	
				•											•	•	

7. Abnormal test**MODEL : LS50-5****(1) Test Condition**

Input Voltage : 230VAC Output Current : 100% Ta : 25°C, 70% RH

(2) Test Results

(Da: Damaged)

No.	Test Position		Test Mode		Test Results												NOTE
	LOCATION	TEST POINT	S H O R T	O P E R E N	1	2	3	4	5	6	7	8	9	10	11	12	
					F I M O R K S E	S M U R E L T L	B U M R D M A G	S E D M A B L E	R E D M A B L W	D A M E A B L W	F U S C P B L O	O .C V P .	N O O U T T P U	N O O C H A N G	O T H E R		
27	R29		•													•	
																	Da : Z1,F1,Q3
28	R34		•														Da : Q3,Z1,R35
29	R35		•														Da : Q3
30	R53		•													•	Latch
31	R54		•													•	Latch
32	VR1		•													•	Hissing sound
																•	Vo = 5.95
																•	Vo = 3.09

8. Thermal shock test

MODEL : LS50

(1) Equipment used


THERMAL SHOCK CHAMBER TSA-101S-W (ESPEC CORP.)

(2) The number of D.U.T.(Device Under Test)

1 unit

(3) Test Conditions

- Ambient temperature : -45°C ↔ 90°C
- Test time : 30 mins each temp.
- Test cycle : 100 cycles
- Not operating



(4) Test Method

Before testing, check if there is no abnormal output, then put the D.U.T. in testing chamber, and test it according to the above cycle. 100 cycles later, leave it for 1 hour at the room temperature, then check if there is no abnormal output.

(5) Test Results **OK**

Vin : 230VAC Io : 100%			3.3V			
			From		To	
Ripple&Spike noise		mV	14.56		24	
Line regulation	Full load	mV	2		1	
Load regulation	Vin:115V	mV	9		10	
Efficiency	Pin	W	43.62		43.65	
	Vout	V	3.291	75.44%	3.284	75.23%
	Iout	A	10		10	
Solder condition • etc.			<hr/>		OK	