

SWS50

EVALUATION DATA

CA729-53-01			
QA APPD	APPD	CHK	DWG
	 23.May.03	 15.May03	 15/May/03

INDEX


1. Evaluation Method	PAGE
1.1 Circuit used for determination	T-1~4
(1) Steady state data	
(2) Over current protection (OCP) characteristics	
(3) Over voltage protection (OVP) characteristics	
(4) Output rise characteristics	
(5) Output fall characteristics	
(6) Dynamic load response characteristics	
(7) Inrush current characteristics	
(8) Leakage current characteristics	
(9) Output ripple and noise waveform	
(10) Electro Magnetic Interference characteristics	
1.2 List of equipment used	T-5
2. Characteristics	
2.1 Steady state data	
(1) Regulation - line and load, temperature drift	T-6
(2) Output voltage and ripple voltage vs. input voltage	T-7
(3) Efficiency and input current vs. output current	T-8
2.2 Over current protection (OCP) characteristics	T-9~11
2.3 Over voltage protection (OVP) characteristics	T-12
2.4 Output rise characteristics	T-13~14
2.5 Output fall characteristics	T-15~16
2.6 Hold up time characteristics	T-17
2.7 Dynamic load response characteristics	T-18~23
2.8 Response to brown out characteristics	T-24~25
2.9 Inrush current waveform	T-26~27
2.10 Leakage current characteristics	T-28
2.11 Output ripple and noise waveform	T-29~32
2.12 Electro Magnetic Interference characteristics	T-33~44

Terminology used

	Definition
Vin	Input voltage
Vout	Output voltage
Iin	Input current
Iout	Output current
Ta	Ambient temperature

1.1 Circuit used for determination


(1) Steady state data




(2) Over current protection (O.C.P) characteristics

Same as steady state data.

(3) Over voltage protection (O.V.P) characteristics




(4) Output rise characteristics



(5) Output fall characteristics


Same as output rise characteristics.

(6) Dynamic load response characteristics




Output current waveform :

I_{out} 0% $\longleftrightarrow$ 50%




Output current waveform :


I_{out} 50% $\longleftrightarrow$ 100%



(7) Inrush current characteristics




(8) Leakage current characteristics




Note : Leakage current measured through a 1k ohm resistor.
Range used : AC + DC (For SIMPSON MODEL 228)

(9) Output - ripple, noise waveform




(10) Electro-Magnetic Interference characteristics

(a) Conducted Emission Noise



(b) Radiated Emission Noise



1.2 LIST OF EQUIPMENT USED

	EQUIPMENT USED	MANUFACTURER	MODEL NO.
1	Oscilloscope	HITACHI	V-1050F
2	Digital storage oscilloscope	TEKTRONIX	TDS 540A
3	Digital volt meter	FLUKE	45
4	Digital power meter	YOKOGAWA	WT110
5	DC ampere meter	YOKOGAWA	2051
6	Dynamic dummy load	CHROMA	63030
7	Current probe/amplifier	TEKTRONIX	A6303/AM503B
8	Controlled temperature chamber	TABAI-ESPEC	SU-240
9	Leakage current meter	SIMPSON	228
10	Digirush currenter	TAKAMIZAWA CYBERNETICS	PSA-200
11	EMI receiver	HEWLETT PACKARD	HP8546A
12	LISN	EMCO	3825/2
13	Biconical antenna	EMCO	3110B

2. Characteristics

2.1 Steady state data

(1) Regulation - line and load, temperature drift

5V

1. Regulation-line and load

condition Ta : 25°C

Iout \ Vin	85VAC	115VAC	230VAC	265VAC	line regulation	
0%	5.009V	5.009V	5.009V	5.009V	0.000V	0.000%
50%	4.994V	4.995V	4.995V	4.995V	0.001V	0.020%
100%	4.982V	4.982V	4.982V	4.981V	0.001V	0.020%
load	0.027V	0.027V	0.027V	0.028V		
regulation	0.540%	0.540%	0.540%	0.560%		

2. Temperature drift

Conditions Vin =115VAC

Iout =100%

Ta	-10°C	+25°C	+50°C	temperature stability	
Vout	5.000V	4.982V	4.970V	0.030V	0.600%

12V

1. Regulation-line and load

condition Ta : 25°C

Iout \ Vin	85VAC	115VAC	230VAC	265VAC	line regulation	
0%	12.040V	12.040V	12.039V	12.038V	0.002V	0.017%
50%	12.032V	12.031V	12.027V	12.021V	0.011V	0.092%
100%	12.024V	12.024V	12.011V	12.000V	0.024V	0.200%
load	0.016V	0.016V	0.028V	0.038V		
regulation	0.133%	0.133%	0.233%	0.317%		

2. Temperature drift

Conditions Vin =115VAC

Iout =100%

Ta	-10°C	+25°C	+50°C	temperature stability	
Vout	12.058V	12.024V	11.997V	0.061V	0.508%

24V

1. Regulation-line and load

condition Ta : 25°C

Iout \ Vin	85VAC	115VAC	230VAC	265VAC	line regulation	
0%	24.048V	24.038V	24.038V	24.034V	0.014V	0.058%
50%	24.034V	24.033V	24.028V	24.025V	0.009V	0.038%
100%	24.033V	24.030V	24.017V	24.012V	0.021V	0.088%
load	0.015V	0.008V	0.021V	0.022V		
regulation	0.062%	0.033%	0.088%	0.092%		

2. Temperature drift

Conditions Vin =115VAC


Iout =100%

Ta	-10°C	+25°C	+50°C	temperature stability	
Vout	24.104V	24.030V	23.975V	0.129V	0.537%


2.1 (2) Output voltage and Ripple voltage v.s. Input voltage

Conditions Iout : 100%
Ta : -10°C -----
: 25°C -.-.-.-
: 50°C _____


5V



12V



24V



2.1 (3) Efficiency and input current v.s. Output current

Conditions Vin : 85VAC


: 115VAC

: 230VAC


: 265VAC

Ta : 25°C


5V



12V



24V



2.2 Over current protection (OCP) characteristics

Conditions


Ta : -10°C

: 25°C


: 50°C

Vin : 115VAC


5V



12V



24V



2.2 Over current protection (OCP) characteristics

Conditions

Ta : -10°C


: 25°C

: 50°C


Vin : 230VAC

- - - - -
—————


5V



12V



24V



2.2 Over current protection (OCP) characteristics

Conditions

Vin : 85VAC


: 115VAC

: 230VAC


: 265VAC

Ta : 25°C


5V



12V






24V






2.3 Over voltage protection (OVP) characteristics

Conditions V_{in} : 230VAC
 I_{out} : 0%
 T_a : 25°C

5V**12V****24V**




2.4 Output rise characteristics

Conditions V_{in} : 85VAC (A)
 : 115VAC (B)
 : 230VAC (C)
 : 265VAC (D)
 I_{out} : 0%
 T_a : 25°C






2.4 Output rise characteristics

Conditions Vin : 85VAC (A)
 : 115VAC (B)
 : 230VAC (C)
 : 265VAC (D)
 Iout : 100%
 Ta : 25°C






2.5 Output fall characteristics

Conditions V_{in} : 85VAC (A)
 : 115VAC (B)
 : 230VAC (C)
 : 265VAC (D)
 I_{out} : 0%
 T_a : 25°C






2.5 Output fall characteristics

Conditions V_{in} : 85VAC (A)
 : 115VAC (B)
 : 230VAC (C)
 : 265VAC (D)
 I_{out} : 100%
 T_a : 25°C



2.6 Hold up time characteristics

Conditions V_{in} : 115VAC -----
 : 230VAC —————
 T_a : 25°C


5V**12V****24V**

2.7 Dynamic load response characteristics


Conditions V_{in} : 115VAC
 T_a : 25°C

5V

$f=100\text{Hz}$



$f=1\text{kHz}$




2.7 Dynamic load response characteristics


Conditions V_{in} : 230VAC
 T_a : 25°C

5V

$f=100\text{Hz}$



$f=1\text{kHz}$




2.7 Dynamic load response characteristics


Conditions V_{in} : 115VAC
 T_a : 25°C

12V

$f=100\text{Hz}$



$f=1\text{kHz}$




2.7 Dynamic load response characteristics


Conditions V_{in} : 230VAC
 T_a : 25°C

12V

$f=100\text{Hz}$



$f=1\text{kHz}$




2.7 Dynamic load response characteristics


Conditions V_{in} : 115VAC
 T_a : 25°C

24V

$f=100\text{Hz}$





$f=1\text{kHz}$



2.7 Dynamic load response characteristics




Conditions V_{in} : 230VAC
 T_a : 25°C

24V

 $f=100\text{Hz}$  $f=1\text{kHz}$ 




2.8 Response to brown out characteristics

Conditions Vin : 115V
Iout : 100%
Ta : 25°C





2.8 Response to brown out characteristics

Conditions V_{in} : 230V
 I_{out} : 100%
 T_a : 25°C




2.9 Inrush current waveform

Conditions V_{in} : 115VAC
 I_{out} : 100%
 T_a : 25°C



2.9 Inrush current waveform


Conditions V_{in} : 230VAC
 I_{out} : 100%
 T_a : 25°C




2.10 Leakage current characteristics

Conditions Iout : 0% -----
 : 100% —————
 Ta : 25°C
 f : 50Hz
Equipment used : MODEL 228 (Simpson)


5V



12V



24V




2.11 Output ripple and noise waveform


Conditions V_{in} : 115VAC
 I_{out} : 100%
 T_a : 25°C

NORMAL MODE


5V



12V



24V




2.11 Output ripple and noise waveform


Conditions V_{in} : 115VAC
 I_{out} : 100%
 T_a : 25°C

NORMAL MODE


5V



12V



24V




2.11 Output ripple and noise waveform


Conditions V_{in} : 230VAC
 I_{out} : 100%
 T_a : 25°C

NORMAL MODE


5V



12V



24V




2.11 Output ripple and noise waveform


Conditions V_{in} : 230VAC
 I_{out} : 100%
 T_a : 25°C

NORMAL MODE


5V



12V



24V



2.12 Electro-Magnetic Interference characteristics

Conducted Emission


5V

Conditions


Vin : 115VAC

Iout : 100%

Ref.	Point A (0.26MHz)	
	Limit (dBuV)	Measure (dBuV)
QP	61.5	53.8
AV	51.5	41.5



Ref.	Point A (0.26MHz)	
	Limit (dBuV)	Measure (dBuV)
QP	61.5	53.3
AV	51.5	40.8



2.12 Electro-Magnetic Interference characteristics

Conducted Emission


5V

Conditions


Vin : 230VAC

Iout : 100%

Ref.	Point A (0.26MHz)	
	Limit (dBuV)	Measure (dBuV)
QP	61.5	54.2
AV	51.5	41.9



Ref.	Point A (0.26MHz)	
	Limit (dBuV)	Measure (dBuV)
QP	61.5	54.3
AV	51.5	42.1



2.12 Electro-Magnetic Interference characteristics

Conducted Emission


12V

Conditions

Vin : 115VAC


Iout : 100%

Ref.	Point A (0.26MHz)	
	Data	Limit (dBuV)
QP	61.5	52.9
AV	51.5	39.2



Phase : L

Ref.	Point A (0.2656MHz)	
	Data	Limit (dBuV)
QP	61.5	51.8
AV	51.5	38.9



Phase : N

2.12 Electro-Magnetic Interference characteristics

Conducted Emission


12V

Conditions


Vin : 230VAC

Iout : 100%

Ref.	Point A (0.26MHz)	
	Data	Limit (dBuV)
QP	61.5	58.6
AV	51.5	48.9



Ref.	Point A (0.26MHz)	
	Data	Limit (dBuV)
QP	61.5	57.3
AV	51.5	47.8




2.12 Electro-Magnetic Interference characteristics

Conducted Emission


24V

Conditions
Vin : 115VAC
Iout : 100%

Ref.	Point A (0.26MHz)	
	Limit (dBuV)	Measure (dBuV)
QP	61.5	49.4
AV	51.5	52.0



Ref.	Point A (0.26MHz)	
	Limit (dBuV)	Measure (dBuV)
QP	61.5	50.1
AV	51.5	33.4




2.12 Electro-Magnetic Interference characteristics

Conducted Emission


24V

Conditions
Vin : 230VAC
Iout : 100%

Ref.	Point A (0.26MHz)	
	Limit (dBuV)	Measure (dBuV)
QP	61.5	56.4
AV	51.5	45.1





Ref.	Point A (0.26MHz)	
	Limit (dBuV)	Measure (dBuV)
QP	61.5	58.3
AV	51.5	47.3



2.12 Electro-Magnetic Interference characteristics

Radiated Emission



2.12 Electro-Magnetic Interference characteristics


Radiated Emission

5V

Conditions
Vin : 230VAC
Iout : 100%


HORIZONTAL:

Point A (298.7MHz)	
Limit (dBuV/m)	Measure (dBuV/m)
46.0	27.0



VERTICAL:

Point B (30.3MHz)	
Limit (dBuV/m)	Measure (dBuV/m)
40.0	33.0



2.12 Electro-Magnetic Interference characteristics


Radiated Emission

12V

Conditions
Vin : 115VAC
Iout : 100%


HORIZONTAL:

Point A (76.9Hz)	
Limit (dBuV/m)	Measure (dBuV/m)
40.0	33.0





VERTICAL:

Point B (51.2MHz)	
Limit (dBuV/m)	Measure (dBuV/m)
40.0	31.0



2.12 Electro-Magnetic Interference characteristics

Radiated Emission



2.12 Electro-Magnetic Interference characteristics


Radiated Emission

24V

Conditions
Vin : 115VAC
Iout : 100%


HORIZONTAL:

Point A (299.7MHz)	
Limit (dBuV/m)	Measure (dBuV/m)
46.0	28.0



VERTICAL:

Point B (299.8MHz)	
Limit (dBuV/m)	Measure (dBuV/m)
46.0	28.5



2.12 Electro-Magnetic Interference characteristics

Radiated Emission

