

Test Report issued under the responsibility of:



TEST REPORT IEC 60950-1 Information technology equipment – Safety – Part 1: General requirements

Report Number: Date of issue Total number of pages	2016-07-14
Applicant's name:	TDK-Lambda UK Ltd.
Address	Kingsley Avenue, Ilfracombe, Devon, EX34 8ES, UK
Test specification:	
Standard	IEC 60950-1:2005 (Second Edition) + Am 1:2009 + Am 2:2013
Test procedure	CB Scheme
Non-standard test method	N/A
Test Report Form No	IEC60950_1F
Test Report Form(s) Originator:	SGS Fimko Ltd
Master TRF:	Dated 2014-02

Copyright $\textcircled{\sc c}$ 2014 IEC System of Conformity Assessment Schemes for Electrotechnical Equipment and Components (IECEE System). All rights reserved.

This publication may be reproduced in whole or in part for non-commercial purposes as long as the IECEE is acknowledged as copyright owner and source of the material. IECEE takes no responsibility for and will not assume liability for damages resulting from the reader's interpretation of the reproduced material due to its placement and context.

If this Test Report Form is used by non-IECEE members, the IECEE/IEC logo and the reference to the CB Scheme procedure shall be removed.

This report is not valid as a CB Test Report unless signed by an approved CB Testing Laboratory and appended to a CB Test Certificate issued by an NCB in accordance with IECEE 02.

General disclaimer:

The test results presented in this report relate only to the object tested.

This report shall not be reproduced, except in full, without the written approval of the Issuing CB Testing Laboratory. The authenticity of this Test Report and its contents can be verified by contacting the NCB, responsible for this Test Report.



Test item description:	DIN rail power supply
Trade Mark:	TDK-Lambda
Manufacturer:	TDK-Lambda UK Ltd. Kingsley Avenue, Ilfracombe, Devon, EX34 8ES, UK
Model/Type reference:	DRL10-12-1-xyz & DRL10-24-1-xyz (Where x, y and z can be any alphanumeric character or blank and is non safety relevant information.)
Ratings:	Input: 100-240 Vac; 0,25 A; 50/60 Hz
	Output: DRL10-12-1-xyz: 12 Vdc; 0,84 A (10,08 W) DRL10-24-1-xyz: 24 Vdc; 0,42 A (10,08 W)



Testing procedure and testing location:			
CB Testing Laboratory:	SIQ Ljubljana		
	Testing Laboratory is accredit LP-009	ted by Slovenian Accreditation, Reg. No.:	
Testing location/ address:	Tržaška c. 2, SI-1000 Lj Slovenia	jubljana	
Associated CB Testing Laboratory:			
Testing location/ address:			
Tested by (name + signature):	Luka Košir	iff	
Approved by (name + signature):	Boštjan Glavič	1/5	
	1	Y	
Testing procedure: TMP/CTF Stage 1:			
Testing location/ address:			
sted by (name + signature):			
Approved by (name + signature):			
Testing procedure: WMT/CTF Stage 2:			
Testing location/ address:			
Tested by (name + signature):			
Witnessed by (name + signature):			
Approved by (name + signature):			
Testing procedure: SMT/CTF Stage 3 or 4:			
Testing location/ address:			
Tested by (name + signature):			
Witnessed by (name + signature):			
Approved by (name + signature):			
Supervised by (name + signature):			



List of Attachments:

- 1. Test Report (77 pages)
- 2. National Differences Enclosure No. 1 (37 pages)
- 3. European Group Differences and National Differences according to EN 60950-1:2006 + A1:2010 + A2:2013 + A11:2009 + A12:2011 Enclosure No. 1a (21 pages)
- 4. Pictures Enclosure No. 2 (5 pages)
- 5. Schematics, Layouts, Transformer data Enclosure No. 3 (27 pages)
- 6. Additional tests performed on manufacturer request Enclosure No. 4 (6 pages)
- 7. Additional testing and evaluation according to UL508 Enclosure No. 5 (46 pages)
- 8. Additional testing and evaluation according to IEC 61010-1 (3rd Edition) Enclosure No. 6 (3 pages)

Summary o	f testing:	
Tests perfo	rmed (name of test and test clause):	Testing location:
1.6.2	Input Test	SIQ Ljubljana, Tržaška c. 2, SI-1000
1.7.11	Durability	Ljubljana, Slovenia
2.1.1.5	Energy hazard Test	
2.1.1.7	Capacitance Discharge Test	
2.2.2 Test	SELV: Hazard Voltage (Circuit) Measurement	
2.2.3	SELV Reliability testing	
2.4 component	Limited Current Circuit (Bridging s)	
2.5	Limited Power Source	
2.9.2	Humidity Test	
2.10.2 Transforme	Working Voltage measurement on PCB and er	
2.10.3/2.10. measureme	4 Clearance and Creepage distance ent	
2.10.5	Distance Through Insulation measurement	
2.10.5.6	Thin Sheet Material (barriers)	
4.2.2-4.2.4	Steady force test, 10N	
4.2.7	Stress relief test; heat test (°C/7 h)	
4.5.2	Heating (Temperature) Test	
4.5.5 test)	Resistance to abnormal heat (Ball pressure	
5.1	Touch Current	
5.2	Electric Strength Test	
5.3 misuse:	Abnormal Operating Tests foreseeable	
SELV reliab	ility and failure in the voltage regulation	



Functional insulation, Component faults Overload and short at the outputs , Air holes closed

Summary of compliance with National Differences

List of countries addressed:

Argentina**, Australia, Austria***, Bahrain**, Belarus**, Belgium***, Brazil**, Bulgaria***, Canada, China, Cyprus***, Colombia**, Croatia**, Czech Republic***, Denmark***, Finland***, France***, Germany***, Greece***, Hungary***, India**, Indonesia**, Iran**, Ireland***, Israel, Italy***, Japan*, Kazakhstan**, Kenya**, Korea, Libya**, Malaysia**, Mexico**, Netherlands***, New Zealand*, Norway***, Pakistan**, Poland***, Portugal***, Romania***, Russian Federation**, Saudi Arabia**, Serbia**, Singapore**, Slovakia***, Slovenia***, South Africa**, Spain***, Sweden, Switzerland, Thailand**, Turkey***, Ukraine**, United Arab Emirates**, United Kingdom, Uruguay**, USA, Vietnam**


* No national differences to IEC 60950-1:2005 (2nd edition) (+ A1 + A2) declared

** No national differences to IEC 60950-1:2005 (2nd edition) + A1 + A2 or IEC 60950-1:2001 (1st edition) declared

*** EU group differences

 \boxtimes The product fulfils the requirements of EN 60950-1:2006 + A1:2010 + A2:2013 + A11:2009 + A12:2011 (see Enclosure No. 1a).






Test item particulars:	
Equipment mobility:	[] movable [] hand-held [] transportable [] stationary [x] for building-in [] direct plug-in
Connection to the mains:	[] pluggable equipment [] type A [] type B [] permanent connection [] detachable power supply cord [] non-detachable power supply cord [x] not directly connected to the mains
Operating condition:	[x] continuous [] rated operating / resting time:
Access location:	[] operator accessible [] restricted access location [x] service access area
Over voltage category (OVC):	[] OVC I [x] OVC II [] OVC III [] OVC IV [] other:
Mains supply tolerance (%) or absolute mains supply values:	85-264 Vac
Tested for IT power systems:	[x] Yes [] No
IT testing, phase-phase voltage (V):	230 V phase-phase (Norway)
Class of equipment:	[] Class I [] Class II [] Class III [x] Not classified (unit for building-in)
Considered current rating of protective device as part of the building installation (A)	16 A (for Europe), 20 A (for Canada and US)
Pollution degree (PD):	[] PD 1 [x] PD 2 [] PD 3
IP protection class	IPX0
Altitude during operation (m):	Up to 3000
Altitude of test laboratory (m):	300
Mass of equipment (kg):	Approx. 0,06

Possible test case verdicts:	
- test case does not apply to the test object:	N/A
- test object does meet the requirement:	P (Pass)
- test object does not meet the requirement::	F (Fail)
Testing:	
Date of receipt of test item:	2014-12-22, 2015-09-03, 2016-05-18
Date(s) of performance of tests:	From 2015-01-30 to 2015-09-24 From 2016-05-31 to 2016-06-10 (Revision No. 2)

General remarks:

"(See Enclosure #)" refers to additional information appended to the report. "(See appended table)" refers to a table appended to the report.

Throughout this report a \boxtimes comma / \square point is used as the decimal separator.





Explanation of the test program:

The component was tested according to the standard IEC 60950-1:2005 (2nd Edition) + A1:2009 + A2:2013 and/or EN 60950-1:2006 + A1:2010 + A2:2013 + A11:2009 + A12:2011.

Additionally the component was also evaluated according to the standards CSA C22.2 No. 60950-1:2007 + A1:2011 + A2:2014 and UL60950-1:2007 (2nd Edition) + A1:2011 + A2:2014 and fulfils the requirements of these standards.

- 1. The products were tested to be suitable for connection to 20 A branch circuit. The unit is approved for TN mains star connections and IT mains with 230 Vac phase to phase voltage.
- 2. The unit provides internally one fuse F1 in line.
- 3. Secondary output is separated from mains by reinforced insulation and rated SELV and is nonhazardous energy levels. Unit is for building-in.
- 4. The disconnect device is end product consideration.
- 5. The input and output terminals and connectors are suitable for factory and field wiring.
- 6. The transformer T1 provides reinforced insulation. These transformers are built up to fulfil the requirement of insulation class F and provide in addition an UR (OBJY3) insulation system (see also list of safety critical components).
- 7. The equipment has been evaluated for use in a Pollution Degree 2 and overvoltage category II environment and a maximum altitude of 3000 m.
- 8. A suitable Electrical and Fire enclosure shall be provided in the end equipment.
- 9. The product was evaluated for rated load operation for temperatures up to 55°C and for derated output load for temperature range from 55°C to 71°C, where output power linearly derates from 100% to 60% of rated load. The temperature test was performed 25 mm above bench, 25 mm below top surface without forced air cooling.

History Sheet:

Date	Report No.	Change/Modification	Rev. No.
2015-11-06	T223-0393/15	Initial report issued.	-
2016-01-08	T223-0393/15 A1	Administrative update of test report only – typo corrections. Page 75 was updated.	1.0
2016-07-14	T223-0357/16	Unit enclosure was modified (blinding of airholes on top cover chassis). Thermal tests & electric strength tests were performed. List of critical components, photos & documentation was updated.	2.0

SI®	Page 1	0 of 231	Report No	. T223-0357/16
Abbreviations used in the re	eport:			
 normal conditions functional insulation double insulation between parts of opposite 	N.C. OP DI	- basic in	ault conditions sulation nentary insulation	S.F.C BI SI
polarity - Equipment under test EUT Indicate used abbreviations	BOP (if any)	- reinforce	ed insulation	RI



	I	EC 60950-1	
Clause	Requirement + Test	Result - Remark	Verdict
1	GENERAL		Р

1.5	Components		
1.5.1	General		Р
	Comply with IEC 60950-1 or relevant component standard	(see appended tables 1.5.1)	Ρ
1.5.2	Evaluation and testing of components	Certified components are used in accordance with their ratings, certifications and they comply with applicable parts of this standard. Components not certified are used in accordance with their ratings and they comply with applicable parts of IEC 60950- 1 and the relevant component standard. Components, for which no relevant IEC-standard exists, have been tested under the conditions occurring in the equipment, using applicable parts of IEC 60950-1.	Ρ
1.5.3	Thermal controls	No thermal controls.	N/A
1.5.4	Transformers	(see list of safety critical components table 1.5.1 and the transformer drawings in the Enclosure No. 3)	Ρ
1.5.5	Interconnecting cables	No interconnecting cables.	N/A
1.5.6	Capacitors bridging insulation	Double / reinforced insulation is bridged by a single capacitor C3. Circuit complies with 2.4; capacitor C3 complies with IEC60384-14 2 nd ed., class Y1.	Ρ
		Line to Neutral is bridged by capacitor C1, type X2 min., complying with IEC 60384-14.	
1.5.7	Resistors bridging insulation	No resistors are bridging basic, double/reinforced insulation. Resistors R101, R102, R103 are bridging functional insulation.	Ρ
1.5.7.1	Resistors bridging functional, basic or supplementary insulation	Only functional insulation briged by resistors. No special precaution required.	N/A

_

	IEC 60950-1				
Clause	Requirement + Test	Result - Remark	Verdict		
1.5.7.2	Resistors bridging double or reinforced insulation between a.c. mains and other circuits		N/A		
1.5.7.3	Resistors bridging double or reinforced insulation between a.c. mains and antenna or coaxial cable	No such resistors are bridging double/reinforced insulation.	N/A		
1.5.8	Components in equipment for IT power systems	No earth connections provided.	N/A		
1.5.9	Surge suppressors	No surge suppressors are used.	N/A		
1.5.9.1	General		N/A		
1.5.9.2	Protection of VDRs		N/A		
1.5.9.3	Bridging of functional insulation by a VDR		N/A		
1.5.9.4	Bridging of basic insulation by a VDR		N/A		
1.5.9.5	Bridging of supplementary, double or reinforced insulation by a VDR	No VDR bridging double or reinforced insulation.	N/A		

1.6	Power interface		Р
1.6.1	AC power distribution systems	TN and IT for 230 Vac.	Р
1.6.2	Input current	(see appended table 1.6.2)	Р
1.6.3	Voltage limit of hand-held equipment	The equipment is not hand- held.	N/A
1.6.4	Neutral conductor	No earth connections provided.	N/A

1.7	Marking and instructions		Р
1.7.1	Power rating and identification markings	The required marking is located on the outside surface of the equipment.	Р
1.7.1.1	Power rating marking		Р
	Multiple mains supply connections	One rated voltage only.	N/A
	Rated voltage(s) or voltage range(s) (V):	100-240 V~	Р
	Symbol for nature of supply, for d.c. only:		N/A
	Rated frequency or rated frequency range (Hz):	50/60 Hz	Р
	Rated current (mA or A):	0,25 A	Р
1.7.1.2	Identification markings		Р
	Manufacturer's name or trade-mark or identification mark:	TDK-Lambda	Р
	Model identification or type reference:	DRL10-12-1 DRL10-24-1	Р

	IEC 60950-1		
Clause	Requirement + Test	Result - Remark	Verdic
	Symbol for Class II equipment only:	Unit for building-in. Classification not possible.	N/A
	Other markings and symbols:	Symbol for electric shock hazard and general danger provided on the marking plate. These symbol does not give rise to miss-understanding.	Р
1.7.1.3	Use of graphical symbols		Р
1.7.2	Safety instructions and marking	Instruction manual provided.	Р
1.7.2.1	General	See manual enclosed.	Р
1.7.2.2	Disconnect devices	External disconnect device required.	N/A
1.7.2.3	Overcurrent protective device	Unit provided with internal protective device (Fuse F1 in Line).	N/A
1.7.2.4	IT power distribution systems	No warning required for Norway.	N/A
1.7.2.5	Operator access with a tool	No operator access area.	N/A
1.7.2.6	Ozone	Unit does not produce ozone.	N/A
1.7.3	Short duty cycles	The equipment is intended for continuous operation.	N/A
1.7.4	Supply voltage adjustment:	No voltage selector.	N/A
	Methods and means of adjustment; reference to installation instructions:		N/A
1.7.5	Power outlets on the equipment:	No standard power outlet.	N/A
1.7.6	Fuse identification (marking, special fusing characteristics, cross-reference):	Fuse located in power supply, designated: F1 and marked T1A 250V on the PCB near fuse.	Р
1.7.7	Wiring terminals		Р
1.7.7.1	Protective earthing and bonding terminals:	No protective earthing or bonding terminals provided.	N/A
1.7.7.2	Terminals for a.c. mains supply conductors	DIN Rail power supply, terminal for neutral conductor marked with letter N and for live conductor marked with letter L.	Р
1.7.7.3	Terminals for d.c. mains supply conductors		N/A
1.7.8	Controls and indicators	There are no controls affecting safety. LED's are only used for indicating the status of the unit.	Р

	IEC 60950-1		
Clause	Requirement + Test	Result - Remark	Verdict
1.7.8.1	Identification, location and marking:	There are no switches in the equipment.	N/A
1.7.8.2	Colours:	For functional indication a Green LED is lit when the output voltage is ON.	Р
1.7.8.3	Symbols according to IEC 60417:	There are no switches in the equipment.	N/A
1.7.8.4	Markings using figures:	No controls in the sense of this clause.	N/A
1.7.9	Isolation of multiple power sources:	Only one connection supplying hazardous voltages and energy levels to the equipment.	N/A
1.7.10	Thermostats and other regulating devices::	No thermostats or other regulating devices.	N/A
1.7.11	Durability	The marking withstands required tests.	Р
1.7.12	Removable parts	No removable parts.	N/A
1.7.13	Replaceable batteries:	No lithium battery in the equipment.	N/A
	Language(s)		
1.7.14	Equipment for restricted access locations: :	Equipment not intended for installation in RAL.	N/A



Report No. T223-0357/16

IEC 60950-1

Clause	Requirement + Test	Result - Remark	Verdict

2	PROTECTION FROM HAZARDS		Р
2.1	Protection from electric shock and energy hazard	ls	Р
2.1.1	Protection in operator access areas	Unit is intended for building-in, not intended to be used in operator access area. The output from the power supply does not present hazardous energy level.	Ρ
2.1.1.1	Access to energized parts	This is a component level power supply. Protection must be checked in the end product.	N/A
	Test by inspection:		N/A
	Test with test finger (Figure 2A):		N/A
	Test with test pin (Figure 2B):		N/A
	Test with test probe (Figure 2C):		N/A
2.1.1.2	Battery compartments	No battery compartment.	N/A
2.1.1.3	Access to ELV wiring	No ELV wiring.	N/A
	Working voltage (Vpeak or Vrms); minimum distance through insulation (mm)		
2.1.1.4	Access to hazardous voltage circuit wiring		N/A
2.1.1.5	Energy hazards:	Output of the unit does not represent an energy hazard.	Ρ
2.1.1.6	Manual controls	No shafts of knobs etc. at ELV or hazardous voltage.	N/A
2.1.1.7	Discharge of capacitors in equipment	The capacitance of the input circuit is > 0,1µF. The measurements were performed in worst-case condition.	Ρ
	Measured voltage (V); time-constant (s):	See appended table 2.1.1.7.	
2.1.1.8	Energy hazards – d.c. mains supply	Unit not connected to DC mains.	N/A
	a) Capacitor connected to the d.c. mains supply:		N/A
	b) Internal battery connected to the d.c. mains supply:		N/A
2.1.1.9	Audio amplifiers:	No audio amplifier within the unit.	N/A

Page 16 of 231

	IEC 60950-	1	
Clause	Requirement + Test	Result - Remark	Verdict
2.1.2	Protection in service access areas	Unit is for built in use. Unintentional contact with hazardous voltages is unlikely during servicing. See also clause 2.1.1.7.	Ρ
2.1.3	Protection in restricted access locations	Equipment not intended for installation in RAL.	N/A

2.2	SELV circuits		Р
2.2.1	General requirements	SELV limits (at output) are not exceeded under normal condition and after a single fault.	Р
2.2.2	Voltages under normal conditions (V)	Within SELV limits. (See appended table 2.2)	Р
2.2.3	Voltages under fault conditions (V):	Within SELV limits. (See appended table 2.2 and 5.3)	Р
2.2.4	Connection of SELV circuits to other circuits:	SELV circuits are only connected to other SELV circuits and protective earth.	Р

2.3	TNV circuits		N/A
2.3.1	Limits	No TNV circuits in the equipment.	N/A
	Type of TNV circuits		
2.3.2	Separation from other circuits and from accessible parts		N/A
2.3.2.1	General requirements		N/A
2.3.2.2	Protection by basic insulation		N/A
2.3.2.3	Protection by earthing		N/A
2.3.2.4	Protection by other constructions		N/A
2.3.3	Separation from hazardous voltages		N/A
	Insulation employed		_
2.3.4	Connection of TNV circuits to other circuits		N/A
	Insulation employed		_
2.3.5	Test for operating voltages generated externally		N/A

2.4	Limited current circuits		Р
2.4.1	General requirements	Refer below:	Р

IEC 60950-1			
Clause	Requirement + Test	Result - Remark	Verdict
2.4.2	Limit values	(see appended Table 2.4)	Р
	Frequency (Hz):	(see appended Table 2.4)	
	Measured current (mA):	(see appended Table 2.4)	
	Measured voltage (V):	(see appended Table 2.4)	
	Measured circuit capacitance (nF or µF):	(see appended Table 2.4)	
2.4.3	Connection of limited current circuits to other circuits	LCC only connected to SELV circuit.	N/A

2.5	Limited power sources		Р
	a) Inherently limited output		N/A
	b) Impedance limited output		N/A
	c) Regulating network limited output under normal operating and single fault condition	See appended table 2.5	Р
	Use of integrated circuit (IC) current limiters		N/A
	d) Overcurrent protective device limited output		N/A
	Max. output voltage (V), max. output current (A), max. apparent power (VA)	See appended table 2.5	
	Current rating of overcurrent protective device (A) .:	N/A	

2.6	Provisions for earthing and bonding		N/A
2.6.1	Protective earthing	The unit is for built in. No protective earthing provided. The enclosure is not intended for operator contact. Enclosure is made of insulating material.	N/A
2.6.2	Functional earthing	No functional earthing is provided.	N/A
	Use of symbol for functional earthing		N/A
2.6.3	Protective earthing and protective bonding conductors	No protective earthing or protective bounding conductors provided.	N/A
2.6.3.1	General		N/A
2.6.3.2	Size of protective earthing conductors		N/A
	Rated current (A), cross-sectional area (mm ²), AWG:		
2.6.3.3	Size of protective bonding conductors		N/A
	Rated current (A), cross-sectional area (mm ²), AWG:		

TRF No. IEC60950_1F



-

IEC 60950-1			
Clause	Requirement + Test	Result - Remark	Verdict
		1	
	Protective current rating (A), cross-sectional area (mm ²), AWG		
2.6.3.4	Resistance of earthing conductors and their terminations; resistance (Ω), voltage drop (V), test current (A), duration (min)		N/A
2.6.3.5	Colour of insulation		N/A
2.6.4	Terminals		N/A
2.6.4.1	General		N/A
2.6.4.2	Protective earthing and bonding terminals		N/A
	Rated current (A), type, nominal thread diameter (mm):		—
2.6.4.3	Separation of the protective earthing conductor from protective bonding conductors		N/A
2.6.5	Integrity of protective earthing		N/A
2.6.5.1	Interconnection of equipment		N/A
2.6.5.2	Components in protective earthing conductors and protective bonding conductors		N/A
2.6.5.3	Disconnection of protective earth		N/A
2.6.5.4	Parts that can be removed by an operator		N/A
2.6.5.5	Parts removed during servicing		N/A
2.6.5.6	Corrosion resistance		N/A
2.6.5.7	Screws for protective bonding		N/A
2.6.5.8	Reliance on telecommunication network or cable distribution system		N/A

2.7	Overcurrent and earth fault protection in primary circuits		Р
2.7.1	Basic requirements	Protective device (Fuse F1) is integrated in the EUT. The EUT is rated to be connected to a mains with 20 A rating.	Р
	Instructions when protection relies on building installation	End product consideration.	N/A
2.7.2	Faults not simulated in 5.3.7	Considered.	Р
2.7.3	Short-circuit backup protection	Adequate protective device.	Р
2.7.4	Number and location of protective devices	One fuse provided in "Live" phase.	Р
2.7.5	Protection by several devices	Only one protective device. See Sub-clause 2.7.4.	N/A
2.7.6	Warning to service personnel		N/A

	IEC 60950-1			
Clause	Requirement + Test	Result - Remark	Verdict	
2.8	Safety interlocks		N/A	
2.8.1	General principles	No safety interlock.	N/A	
2.8.2	Protection requirements		N/A	
2.8.3	Inadvertent reactivation		N/A	
2.8.4	Fail-safe operation		N/A	
	Protection against extreme hazard		N/A	
2.8.5	Moving parts		N/A	
2.8.6	Overriding		N/A	
2.8.7	Switches, relays and their related circuits		N/A	
2.8.7.1	Separation distances for contact gaps and their related circuits (mm):		N/A	
2.8.7.2	Overload test		N/A	
2.8.7.3	Endurance test		N/A	
2.8.7.4	Electric strength test	(see appended table 5.2)	N/A	
2.8.8	Mechanical actuators		N/A	

2.9	Electrical insulation		Р
2.9.1	Properties of insulating materials	Neither natural rubber, materials containing asbestos nor hygroscopic materials are used as insulation. No driving belts or couplings used.	Р
2.9.2	Humidity conditioning		Р
	Relative humidity (%), temperature (°C):	Humidity treatment performed for 48h at 93%.	
2.9.3	Grade of insulation	Insulation is considered to be functional, basic, supplementary, reinforced or double.	Ρ
2.9.4	Separation from hazardous voltages		Р
	Method(s) used:	Accessible conductive parts, SELV circuits or TNV circuits are separated from parts at hazardous voltage by double or reinforced insulation (Method 1).	

2.10	Clearances, creepage distances and distances through insulation		Р
2.10.1	General		Р

IEC 60950-1			
Clause	Requirement + Test	Result - Remark	Verdict
2.10.1.1	Frequency	50/60 Hz (switching frequency >30 kHz)	Р
2.10.1.2	Pollution degrees	Pollution degree 2	Р
2.10.1.3	Reduced values for functional insulation	Functional insulation Line to Neutral before fuse complies with 2.10.3 & 2.10.4. Other functional insulations comply with 5.3.4 c).	Р
2.10.1.4	Intervening unconnected conductive parts	Distance to unconnected conductive parts considered during evaluation of clearances and creepage distances.	P
2.10.1.5	Insulation with varying dimensions	No such transformer used.	N/A
2.10.1.6	Special separation requirements	No TNV circuits.	N/A
2.10.1.7	Insulation in circuits generating starting pulses	No such circuit.	N/A
2.10.2	Determination of working voltage	(see appended table 2.10.2)	Р
2.10.2.1	General	Refer below:	Р
2.10.2.2	RMS working voltage	(see appended table 2.10.2)	Р
2.10.2.3	Peak working voltage	(see appended table 2.10.2)	Р
2.10.3	Clearances	Refer below:	Р
2.10.3.1	General	See the following clauses.	Р
2.10.3.2	Mains transient voltages	Refer below:	Р
	a) AC mains supply:	Overvoltage Category II (2500Vpeak)	Р
	b) Earthed d.c. mains supplies:		N/A
	c) Unearthed d.c. mains supplies		N/A
	d) Battery operation	No battery.	N/A
2.10.3.3	Clearances in primary circuits	(see appended table 2.10.3 and 2.10.4)	Р
2.10.3.4	Clearances in secondary circuits	(see appended table 2.10.3 and 2.10.4)	Р
2.10.3.5	Clearances in circuits having starting pulses		N/A
2.10.3.6	Transients from a.c. mains supply	Secondary circuit is not earthed therefore 2500Va.c. mains transients are considered.	Р
2.10.3.7	Transients from d.c. mains supply		N/A

IEC 60950-1			
Clause	Requirement + Test	Result - Remark	Verdict
2.10.3.8	Transients from telecommunication networks and cable distribution systems:	Unit not intended for connection to telecommunication network or cable distribution system.	N/A
2.10.3.9	Measurement of transient voltage levels	Measurement not relevant.	N/A
	a) Transients from a mains supply		N/A
	For an a.c. mains supply		N/A
	For a d.c. mains supply:		N/A
	b) Transients from a telecommunication network :		N/A
2.10.4	Creepage distances	(see appended table 2.10.3 and 2.10.4)	Р
2.10.4.1	General	Refer below:	Р
2.10.4.2	Material group and comparative tracking index		Р
	CTI tests:	Material group IIIb is assumed to be used.	
2.10.4.3	Minimum creepage distances	(see appended table 2.10.3 and 2.10.4)	Р
2.10.5	Solid insulation		Р
2.10.5.1	General		Р
2.10.5.2	Distances through insulation	(see appended table 2.10.5)	Р
2.10.5.3	Insulating compound as solid insulation	No such potted components.	N/A
2.10.5.4	Semiconductor devices	Approved optical insulators are used. See list of critical components.	Р
2.10.5.5.	Cemented joints	No cemented joints.	N/A
2.10.5.6	Thin sheet material – General		Р
2.10.5.7	Separable thin sheet material	Used inside transformer T1.	Р
	Number of layers (pcs):	T1: One layer of insulation between primary and secondary (TIW) winding for mechanical separation.	
2.10.5.8	Non-separable thin sheet material	No such insulation.	N/A
2.10.5.9	Thin sheet material – standard test procedure		N/A
	Electric strength test		
2.10.5.10	Thin sheet material – alternative test procedure		N/A
	Electric strength test		
2.10.5.11	Insulation in wound components	Transformers provided with triple insulated wire complying with 2.10.5.12.	Р

IEC 60950-1				
Clause	Requirement + Test	Result - Remark	Verdict	
2.10.5.12	Wire in wound components	Approved triple insulated wire is used inside transformer T1. See list of critical components.	Р	
	Working voltage	See appended table 2.10.2.	Р	
	a) Basic insulation not under stress		N/A	
	b) Basic, supplementary, reinforced insulation:	Primary winding wire is approved according to Annex U – reinforced isolation.	Р	
	c) Compliance with Annex U	Approved triple insulated wires used. See list of critical components.	Р	
	Two wires in contact inside wound component; angle between 45° and 90°	No contact between 45°and 90°.	Р	
2.10.5.13	Wire with solvent-based enamel in wound components	No TNV circuits.	N/A	
	Electric strength test	(see appended table 2.10.5)		
	Routine test		N/A	
2.10.5.14	Additional insulation in wound components		N/A	
	Working voltage		N/A	
	- Basic insulation not under stress		N/A	
	- Supplementary, reinforced insulation		N/A	
2.10.6	Construction of printed boards		Р	
2.10.6.1	Uncoated printed boards	See below.	Р	
2.10.6.2	Coated printed boards	No special coating provided in lieu of reducing distances.	N/A	
2.10.6.3	Insulation between conductors on the same inner surface of a printed board	Dual sided PCB laminate provided without inner layers	N/A	
2.10.6.4	Insulation between conductors on different layers of a printed board	Primary and secondary traces do not overlap.	N/A	
	Distance through insulation	(see appended table 2.10.5)	N/A	
	Number of insulation layers (pcs)		N/A	
2.10.7	Component external terminations	Coatings not used over terminations to increase effective creepage and clearance distances.	N/A	
2.10.8	Tests on coated printed boards and coated components		N/A	
2.10.8.1	Sample preparation and preliminary inspection		N/A	
2.10.8.2	Thermal conditioning		N/A	
2.10.8.3	Electric strength test	(see appended table 5.2)	N/A	

TRF No. IEC60950_1F

	IEC 60950-1			
Clause	Requirement + Test	Result - Remark	Verdict	
2.10.8.4	Abrasion resistance test		N/A	
2.10.9	Thermal cycling		N/A	
2.10.10	Test for Pollution Degree 1 environment and insulating compound		N/A	
2.10.11	Tests for semiconductor devices and cemented joints		N/A	
2.10.12	Enclosed and sealed parts		N/A	



IEC 60950-1

Clause Requirement + Test

Result - Remark

Verdict

3	WIRING, CONNECTIONS AND SUPPLY		Р
3.1	General		Р
3.1.1	Current rating and overcurrent protection	Adequate cross sectional areas on internal wiring (PCB traces and internal winding wires of wound components were considered as internal wiring).	Ρ
3.1.2	Protection against mechanical damage	Wire ways are smooth and free from edges. Wires are adequately fixed to prevent excessive strain on wire and terminals and avoiding damage to the insulation of the conductors.	Ρ
3.1.3	Securing of internal wiring	Internal wiring is secured against excessive strain, loosening of terminals and damage to the conductor insulation.	Ρ
3.1.4	Insulation of conductors	No insulated wires used inside the unit.	N/A
3.1.5	Beads and ceramic insulators	Ferrite beads are suitably fixed on components	N/A
3.1.6	Screws for electrical contact pressure	Approved terminals provided.	Р
3.1.7	Insulating materials in electrical connections	No contact pressure through insulating material.	Р
3.1.8	Self-tapping and spaced thread screws	Thread-cutting or space thread screws are not used for electrical connections.	N/A
3.1.9	Termination of conductors	Terminations cannot become displaced so that clearances and Creepage distances can be reduced.	Ρ
	10 N pull test	Considered.	Р
3.1.10	Sleeving on wiring	No sleevings used.	N/A

3.2	Connection to a mains supply		N/A
3.2.1	Means of connection	The EUT is for building-in. Connection to mains supply is to be determined within the end product.	N/A
3.2.1.1	Connection to an a.c. mains supply	See above.	N/A

Report No. T223-0357/16

	IEC 60950-1			
Clause	Requirement + Test	Result - Remark	Verdict	
3.2.1.2	Connection to a d.c. mains supply		N/A	
3.2.2	Multiple supply connections		N/A	
3.2.3	Permanently connected equipment		N/A	
	Number of conductors, diameter of cable and conduits (mm):			
3.2.4	Appliance inlets	No appliance inlet is used.	N/A	
3.2.5	Power supply cords		N/A	
3.2.5.1	AC power supply cords		N/A	
	Туре			
	Rated current (A), cross-sectional area (mm ²), AWG:			
3.2.5.2	DC power supply cords		N/A	
3.2.6	Cord anchorages and strain relief		N/A	
	Mass of equipment (kg), pull (N)			
	Longitudinal displacement (mm)			
3.2.7	Protection against mechanical damage		N/A	
3.2.8	Cord guards		N/A	
	Diameter or minor dimension D (mm); test mass (g)		—	
	Radius of curvature of cord (mm)			
3.2.9	Supply wiring space		N/A	

3.3	Wiring terminals for connection of external cond	uctors	Р
3.3.1	Wiring terminals	DIN Rail PS with pillar type terminals for fixed connection of mains conductors.	Р
3.3.2	Connection of non-detachable power supply cords	Not equipment with special non-detachable power supply cord.	N/A
3.3.3	Screw terminals	Pillar type terminals used.	Р
3.3.4	Conductor sizes to be connected	See below:	Р
	Rated current (A), cord/cable type, cross-sectional area (mm ²)	Terminals allow connection of appropriate conductors.	
		Rated current of the unit: 0,25 A;	
		Terminal allows connection of conductors up to 2,5 mm ² (24-12AWG).	
3.3.5	Wiring terminal sizes	See below:	Р

TRF No. IEC60950_1F

Page 26 of 231

Report No. T223-0357/16

	IEC 60950-1			
Clause	Requirement + Test	Result - Remark	Verdict	
	Rated current (A), type, nominal thread diameter (mm):	Approved Input & Output terminals provided and rated min. 12A. (see list of critical components)	_	
3.3.6	Wiring terminal design	Adequate connection, checked by inspection.	Р	
3.3.7	Grouping of wiring terminals	Terminals located in proximity to each other.	Р	
3.3.8	Stranded wire	Statement in manual provided – wire strip length 5 mm max. Unit was tested according to the specification.	Р	

3.4	Disconnection from the mains supply		N/A
3.4.1	General requirement	The unit is a Power Supply for building-in and does not provide a disconnect device. Should be determined in the end product installation.	N/A
3.4.2	Disconnect devices		N/A
3.4.3	Permanently connected equipment		N/A
3.4.4	Parts which remain energized		N/A
3.4.5	Switches in flexible cords		N/A
3.4.6	Number of poles - single-phase and d.c. equipment		N/A
3.4.7	Number of poles - three-phase equipment		N/A
3.4.8	Switches as disconnect devices		N/A
3.4.9	Plugs as disconnect devices		N/A
3.4.10	Interconnected equipment		N/A
3.4.11	Multiple power sources	One power source only.	N/A

3.5	Interconnection of equipment		Р
3.5.1	General requirements		Р
3.5.2	Types of interconnection circuits	SELV circuit.	Р
3.5.3	ELV circuits as interconnection circuits	No ELV circuits.	N/A
3.5.4	Data ports for additional equipment	No data ports provided in the EUT.	N/A



	IEC 60950-1		
Clause	Requirement + Test	Result - Remark	Verdict

4	PHYSICAL REQUIREMENTS		Р
4.1	Stability		N/A
	Angle of 10°	The unit is for built in use. Therefore, the test is not applicable.	N/A
	Test force (N):	The unit is not floor standing.	N/A

4.2	Mechanical strength		Р
4.2.1	General	EUT complies with the requirement after tests described below were applied.	Р
	Rack-mounted equipment.	(see Annex DD)	N/A
4.2.2	Steady force test, 10 N	No hazard. See appended table 4.2.2.	Ρ
4.2.3	Steady force test, 30 N	The unit is for built in use.	N/A
4.2.4	Steady force test, 250 N	Unit is intended for building-in. Enclosure is end product consideration.	N/A
4.2.5	Impact test	Unit is intended for building-in. Enclosure is end product consideration.	N/A
	Fall test		N/A
	Swing test		N/A
4.2.6	Drop test; height (mm):		N/A
4.2.7	Stress relief test	Enclosure conditioned for 7h on 110°C. No cracks or enclosure deformation occur.	Ρ
4.2.8	Cathode ray tubes	No cathode ray tubes.	N/A
	Picture tube separately certified:		N/A
4.2.9	High pressure lamps		N/A
4.2.10	Wall or ceiling mounted equipment; force (N):	EUT is not intended to be mounted on a wall or ceiling.	N/A

4.3	Design and construction		Р
4.3.1	Edges and corners	All edges and corners are rounded and/or smoothed.	Р
4.3.2	Handles and manual controls; force (N)	No knobs, grips, handles, lever, etc.	N/A
4.3.3	Adjustable controls	No hazardous adjustable controls.	N/A

TRF No. IEC60950_1F

IEC 60950-1			
Clause	Requirement + Test	Result - Remark	Verdict
4.3.4	Securing of parts	No loosening of parts impairing creepage distances or clearances over basic, supplementary or reinforced insulation is likely to occur.	Р
4.3.5	Connection by plugs and sockets	No interchangeable plugs or sockets provided.	N/A
4.3.6	Direct plug-in equipment	The EUT is not direct plug-in equipment.	N/A
	Torque:		
	Compliance with the relevant mains plug standard		N/A
4.3.7	Heating elements in earthed equipment	The equipment does not have any heating elements.	N/A
4.3.8	Batteries	No batteries in the equipment.	N/A
	- Overcharging of a rechargeable battery		N/A
	- Unintentional charging of a non-rechargeable battery		N/A
	- Reverse charging of a rechargeable battery		N/A
	- Excessive discharging rate for any battery		N/A
4.3.9	Oil and grease	Insulation is not exposed to oil, grease etc.	N/A
4.3.10	Dust, powders, liquids and gases	The equipment does not generate dust, powder, does not contain liquid or gas. The unit is specified for office environment.	N/A
4.3.11	Containers for liquids or gases	No containers for liquids or gases in the equipment.	N/A
4.3.12	Flammable liquids		N/A
	Quantity of liquid (I)		N/A
	Flash point (°C):		N/A
4.3.13	Radiation		N/A
4.3.13.1	General		N/A
4.3.13.2	Ionizing radiation		N/A
	Measured radiation (pA/kg):		
	Measured high-voltage (kV):		
	Measured focus voltage (kV):		—
	CRT markings:		
4.3.13.3	Effect of ultraviolet (UV) radiation on materials		N/A

Report No. T223-0357/16

	IEC 60950-1			
Clause	Requirement + Test	Result - Remark	Verdict	
			· · · · · ·	
	Part, property, retention after test, flammability classification		N/A	
4.3.13.4	Human exposure to ultraviolet (UV) radiation:		N/A	
4.3.13.5	Lasers (including laser diodes) and LEDs	The visible indicator is diffuse type LED with low energy.	N/A	
4.3.13.5.1	Lasers (including laser diodes)		N/A	
	Laser class			
4.3.13.5.2	Light emitting diodes (LEDs)	The visible indicator is diffuse type LED with low energy.	N/A	
4.3.13.6	Other types		N/A	

4.4	Protection against hazardous moving parts		N/A
4.4.1	General		N/A
4.4.2	Protection in operator access areas	No hazardous moving parts.	N/A
	Household and home/office document/media shredders	(see Annex EE)	N/A
4.4.3	Protection in restricted access locations		N/A
4.4.4	Protection in service access areas		N/A
4.4.5	Protection against moving fan blades	No fans provided in the EUT.	N/A
4.4.5.1	General		N/A
	Not considered to cause pain or injury. a)		N/A
	Is considered to cause pain, not injury. b)		N/A
	Considered to cause injury. c)		N/A
4.4.5.2	Protection for users		N/A
	Use of symbol or warning		N/A
4.4.5.3	Protection for service persons		N/A
	Use of symbol or warning:		N/A

4.5	Thermal requirements		Р
4.5.1	General		Р
4.5.2	Temperature tests		Р
	Normal load condition per Annex L:	Rated load, as specified by Manufacturer.	
4.5.3	Temperature limits for materials	(see appended table 4.5)	Р
4.5.4	Touch temperature limits	(see appended table 4.5)	Р
4.5.5	Resistance to abnormal heat:	(see appended table 4.5.5)	Р



IEC 60950-1

Clause	Requirement + Test	Result - Remark	Verdict

4.6	Openings in enclosures		N/A
4.6.1	Top and side openings	Equipment for building-in. This clause should be evaluated for the final system.	N/A
	Dimensions (mm):		
4.6.2	Bottoms of fire enclosures	Must be considered in the end product.	N/A
	Construction of the bottom, dimensions (mm):		
4.6.3	Doors or covers in fire enclosures	No doors or covers in the enclosure.	N/A
4.6.4	Openings in transportable equipment	The unit is not regarded as transportable equipment.	N/A
4.6.4.1	Constructional design measures	See sub-clause 4.6.4.1	N/A
	Dimensions (mm):		
4.6.4.2	Evaluation measures for larger openings	See sub-clause 4.6.4.1	N/A
4.6.4.3	Use of metallized parts	See sub-clause 4.6.4.1	N/A
4.6.5	Adhesives for constructional purposes		N/A
	Conditioning temperature (°C), time (weeks):		

4.7	Resistance to fire		Р
4.7.1	Reducing the risk of ignition and spread of flame	Method 1 is used.	Р
	Method 1, selection and application of components wiring and materials	See appended table 4.7.	Р
	Method 2, application of all of simulated fault condition tests	Method 1 is used.	N/A
4.7.2	Conditions for a fire enclosure	See below:	Р
4.7.2.1	Parts requiring a fire enclosure	Component power supply for building-in, fire enclosure must be considered for the end product.	Р
4.7.2.2	Parts not requiring a fire enclosure	The fire enclosure is required to cover all parts. Must be considered for the end product installation.	Р
4.7.3	Materials		Р
4.7.3.1	General	Components and materials have adequate flammability classification. Refer to "List of Critical Components".	Р



	IEC 60950-1				
Clause	Requirement + Test	Result - Remark	Verdict		
4.7.3.2	Materials for fire enclosures	Enclosure of EUT is made of plastic material with flammability rating V-0. EUT is component level power supply for building-in. Fire enclosure must be considered within the end product.	N/A		
4.7.3.3	Materials for components and other parts outside fire enclosures	EUT for building-in, must be considered in the end product.	N/A		
4.7.3.4	Materials for components and other parts inside fire enclosures	Other materials inside fire enclosure are minimum V-2 material or mounted on PCB rated minimum V-0.	Р		
4.7.3.5	Materials for air filter assemblies	No air filters in the equipment.	N/A		
4.7.3.6	Materials used in high-voltage components	No parts exceeding 4kV.	N/A		



Page 32 of 231

IEC 60950-1

Clause Requirement + Test R

Result - Remark

Verdict

5	ELECTRICAL REQUIREMENTS AND SIMULATED	ABNORMAL CONDITIONS	Ρ
5.1	Touch current and protective conductor current		Р
5.1.1	General	Test conducted in accordance with 5.1.2 to 5.1.7.	Р
5.1.2	Configuration of equipment under test (EUT)	Refer below:	Р
5.1.2.1	Single connection to an a.c. mains supply	Considered.	Р
5.1.2.2	Redundant multiple connections to an a.c. mains supply	Single connection to the mains.	N/A
5.1.2.3	Simultaneous multiple connections to an a.c. mains supply	No multiple connections to the mains.	N/A
5.1.3	Test circuit	According to Fig. 5A	Р
5.1.4	Application of measuring instrument	Measuring instrument D1 was used.	Ρ
5.1.5	Test procedure		Р
5.1.6	Test measurements		Р
	Supply voltage (V)	264 Va.c.; 60 Hz	—
	Measured touch current (mA)	(see appended table 5.1)	
	Max. allowed touch current (mA)	(see appended table 5.1)	
	Measured protective conductor current (mA):	No protective earthing provided.	
	Max. allowed protective conductor current (mA) :		
5.1.7	Equipment with touch current exceeding 3,5 mA		N/A
5.1.7.1	General:		N/A
5.1.7.2	Simultaneous multiple connections to the supply		N/A
5.1.8	Touch currents to telecommunication networks and cable distribution systems and from telecommunication networks	EUT not connected to a telecommunication network nor a cable distribution system.	N/A
5.1.8.1	Limitation of the touch current to a telecommunication network or to a cable distribution system		N/A
	Supply voltage (V)		
	Measured touch current (mA)		
	Max. allowed touch current (mA)		
5.1.8.2	Summation of touch currents from telecommunication networks		N/A
	a) EUT with earthed telecommunication ports :		N/A



	IEC 60950-1		
Clause	Requirement + Test	Result - Remark	Verdict
	b) EUT whose telecommunication ports have no reference to protective earth		N/A

5.2	Electric strength		Р
5.2.1	General	(see appended table 5.2)	Р
5.2.2	Test procedure		Р

5.3	Abnormal operating and fault conditions		Р
5.3.1	Protection against overload and abnormal operation	(see appended table 5.3)	Ρ
5.3.2	Motors	No motors in the power supply.	N/A
5.3.3	Transformers	See Annex C and appended Table C.2.	Р
5.3.4	Functional insulation:	Complies with a), b) and c)	Р
5.3.5	Electromechanical components	No electromechanical components.	N/A
5.3.6	Audio amplifiers in ITE:	No audio amplifiers.	N/A
5.3.7	Simulation of faults	(see appended table 5.3)	Р
5.3.8	Unattended equipment	The unit is intended for continuous operation. There is no thermal sensor or cut-off for operational condition.	N/A
5.3.9	Compliance criteria for abnormal operating and fault conditions		Ρ
5.3.9.1	During the tests	No fire, emission of molten metal or deformation was noted during the tests.	Ρ
5.3.9.2	After the tests	The tested units passed the dielectric strength test.	Р



Page 34 of 231

IEC 60950-1 Clause Requirement + Test Result - Remark Verdict

6	CONNECTION TO TELECOMMUNICATION NETWORKS		N/A
6.1	Protection of telecommunication network service persons, and users of other equipment connected to the network, from hazards in the equipment		N/A
6.1.1	Protection from hazardous voltages		N/A
6.1.2	Separation of the telecommunication network from earth		N/A
6.1.2.1	Requirements	(see appended table 5.2)	N/A
	Supply voltage (V)		
	Current in the test circuit (mA):		
6.1.2.2	Exclusions:		N/A

6.2	Protection of equipment users from overvoltages on telecommunication networks		N/A
6.2.1	Separation requirements		N/A
6.2.2	Electric strength test procedure		N/A
6.2.2.1	Impulse test	(see appended table 5.2)	N/A
6.2.2.2	Steady-state test	(see appended table 5.2)	N/A
6.2.2.3	Compliance criteria		N/A

6.3	Protection of the telecommunication wiring system from overheating	
	Max. output current (A)	
	Current limiting method	_



IEC 60950-1					
Clause	Requirement + Test		Result - Remark	Verdi	ct

7	CONNECTION TO CABLE DISTRIBUTION SYSTE	EMS	N/A
7.1	General	EUT not intended for connection to cable distribution systems.	N/A
7.2	Protection of cable distribution system service persons, and users of other equipment connected to the system, from hazardous voltages in the equipment		N/A
7.3	Protection of equipment users from overvoltages on the cable distribution system		N/A
7.4	Insulation between primary circuits and cable distribution systems		N/A
7.4.1	General		N/A
7.4.2	Voltage surge test	(see appended table 5.2)	N/A
7.4.3	Impulse test	(see appended table 5.2)	N/A



Page 36 of 231

IEC 60950-1						
Clause	Requirement + Test		Result - Remark		Verdict	

Α	ANNEX A, TESTS FOR RESISTANCE TO HEAT A	ND FIRE	N/A
A.1	Flammability test for fire enclosures of movable equipment having a total mass exceeding 18 kg, and of stationary equipment (see 4.7.3.2)	Approved materials are used. See list of critical components.	N/A
A.1.1	Samples:		_
	Wall thickness (mm)		_
A.1.2	Conditioning of samples; temperature (°C)		N/A
A.1.3	Mounting of samples		N/A
A.1.4	Test flame (see IEC 60695-11-3)		N/A
	Flame A, B, C or D		
A.1.5	Test procedure		N/A
A.1.6	Compliance criteria		N/A
	Sample 1 burning time (s)		
	Sample 2 burning time (s)		_
	Sample 3 burning time (s)		_
A.2	Flammability test for fire enclosures of movable mass not exceeding 18 kg, and for material and o fire enclosures (see 4.7.3.2 and 4.7.3.4)		N/A
A.2.1	Samples, material		
	Wall thickness (mm)		
A.2.2	Conditioning of samples; temperature (°C)		N/A
A.2.3	Mounting of samples		N/A
A.2.4	Test flame (see IEC 60695-11-4)		N/A
	Flame A, B or C		—
A.2.5	Test procedure		N/A
A.2.6	Compliance criteria		N/A
	Sample 1 burning time (s)		_
	Sample 2 burning time (s)		
	Sample 3 burning time (s)		
A.2.7	Alternative test acc. to IEC 60695-11-5, cl. 5 and 9		N/A
	Sample 1 burning time (s)		
	Sample 2 burning time (s)		
	Sample 3 burning time (s)		
A.3	Hot flaming oil test (see 4.6.2)		N/A
A.3.1	Mounting of samples		N/A



	IEC 60950-1			
Clause	Requirement + Test	Result - Remark	Verdict	
A.3.2	Test procedure		N/A	
A.3.3	Compliance criterion		N/A	

В	ANNEX B, MOTOR TESTS UNDER ABNORMAL (5.3.2)	CONDITIONS (see 4.7.2.2 and	N/A
B.1	General requirements	No fans or other motors are used in the EUT.	N/A
	Position:		—
	Manufacturer:		
	Туре:		_
	Rated values:		
B.2	Test conditions		N/A
B.3	Maximum temperatures	(see appended table 5.3)	N/A
B.4	Running overload test	(see appended table 5.3)	N/A
B.5	Locked-rotor overload test		N/A
	Test duration (days):		
	Electric strength test: test voltage (V):		
B.6	Running overload test for d.c. motors in secondary circuits		N/A
B.6.1	General		N/A
B.6.2	Test procedure		N/A
B.6.3	Alternative test procedure		N/A
B.6.4	Electric strength test; test voltage (V):		N/A
B.7	Locked-rotor overload test for d.c. motors in secondary circuits		N/A
B.7.1	General		N/A
B.7.2	Test procedure		N/A
B.7.3	Alternative test procedure		N/A
B.7.4	Electric strength test; test voltage (V)		N/A
B.8	Test for motors with capacitors	(see appended table 5.3)	N/A
B.9	Test for three-phase motors	(see appended table 5.3)	N/A
B.10	Test for series motors		N/A
	Operating voltage (V):		

С

ANNEX C, TRANSFORMERS (see 1.5.4 and 5.3.3)

Ρ



Clause	Requirement + Test	Result - Remark	Verdict
	Position:	Primary to secondary transformer T1.	—
	Manufacturer:	Trio	—
	Туре:	DRL10-12-1: CA81602 DRL10-24-1: CA81601	_
	Rated values	See list of critical components.	
	Method of protection	Primary current regulation.	
C.1	Overload test	(see appended table 5.3)	Р
C.2	Insulation	(see appended tables 5.2 and C2)	Р
	Protection from displacement of windings:	Triple insulated wire is used. No special precaution is required.	Р

D	ANNEX D, MEASURING INSTRUMENTS FOR TOUCH-CURRENT TESTS (see 5.1.4)		Р
D.1	Measuring instrument	Measuring instrument D1 was used.	Р
D.2	Alternative measuring instrument		N/A

	E	ANNEX E, TEMPERATURE RISE OF A WINDING (see 1.4.13)	N/A	
--	---	---	-----	--

F	ANNEX F, MEASUREMENT OF CLEARANCES AND CREEPAGE DISTANCES	Р
	(see 2.10 and Annex G)	

G	ANNEX G, ALTERNATIVE METHOD FOR DETERMINING MINIMUM CLEARANCES	N/A
G.1	Clearances	N/A
G.1.1	General	N/A
G.1.2	Summary of the procedure for determining minimum clearances	N/A
G.2	Determination of mains transient voltage (V)	N/A
G.2.1	AC mains supply	N/A
G.2.2	Earthed d.c. mains supplies	N/A
G.2.3	Unearthed d.c. mains supplies	N/A
G.2.4	Battery operation	N/A
G.3	Determination of telecommunication network transient voltage (V)	N/A
G.4	Determination of required withstand voltage (V)	N/A

TRF No. IEC60950_1F

Report No. T223-0357/16

	IEC 60950-1				
Clause	Requirement + Test	Result - Remark	Verdict		
G.4.1	Mains transients and internal repetitive peaks:		N/A		
G.4.2	Transients from telecommunication networks:		N/A		
G.4.3	Combination of transients		N/A		
G.4.4	Transients from cable distribution systems		N/A		
G.5	Measurement of transient voltages (V)		N/A		
	a) Transients from a mains supply		N/A		
	For an a.c. mains supply		N/A		
	For a d.c. mains supply		N/A		
	b) Transients from a telecommunication network		N/A		
G.6	Determination of minimum clearances:		N/A		

Н	ANNEX H, IONIZING RADIATION (see 4.3.13)	N/A
---	--	-----

J	ANNEX J, TABLE OF ELECTROCHEMICAL POTENTIALS (see 2.6.5.6)	N/A
	Metal(s) used	

Κ	ANNEX K, THERMAL CONTROLS (see 1.5.3 and 5.3.8)	
K.1	Making and breaking capacity	N/A
K.2	Thermostat reliability; operating voltage (V):	N/A
K.3	Thermostat endurance test; operating voltage (V)	N/A
K.4	Temperature limiter endurance; operating voltage (V):	N/A
K.5	Thermal cut-out reliability	N/A
K.6	Stability of operation (see appended table 5.3	3) N/A

L	ANNEX L, NORMAL LOAD CONDITIONS FOR SOME TYPES OF ELECTRICAL BUSINESS EQUIPMENT (see 1.2.2.1 and 4.5.2)		Ρ
L.1	Typewriters		N/A
L.2	Adding machines and cash registers		N/A
L.3	Erasers		N/A
L.4	Pencil sharpeners		N/A
L.5	Duplicators and copy machines		N/A
L.6	Motor-operated files		N/A
L.7		Rated load, as specified by Manufacturer.	Р



		IEC 60950-1		
Clause	Requirement + Test		Result - Remark	Verdict

М	ANNEX M, CRITERIA FOR TELEPHONE RINGING SIGNALS (see 2.3.1)	N/A
M.1	Introduction	N/A
M.2	Method A	N/A
M.3	Method B	N/A
M.3.1	Ringing signal	N/A
M.3.1.1	Frequency (Hz)	
M.3.1.2	Voltage (V)	
M.3.1.3	Cadence; time (s), voltage (V):	
M.3.1.4	Single fault current (mA)	
M.3.2	Tripping device and monitoring voltage	N/A
M.3.2.1	Conditions for use of a tripping device or a monitoring voltage	N/A
M.3.2.2	Tripping device	N/A
M.3.2.3	Monitoring voltage (V)	N/A

N	ANNEX N, IMPULSE TEST GENERATORS (see 1.4 7.3.2, 7.4.3 and Clause G.5)	5.7.2, 1.5.7.3, 2.10.3.9, 6.2.2.1,	N/A
N.1	ITU-T impulse test generators		N/A
N.2	IEC 60065 impulse test generator		N/A

P ANNEX P, NORMATIVE REFERENCES

Q	ANNEX Q, Voltage dependent resistors (VDRs) (see 1.5.9.1)	
	a) Preferred climatic categories	N/A
	b) Maximum continuous voltage	N/A
	c) Combination pulse current:	N/A
	Body of the VDR Test according to IEC60695-11-5:	N/A
	Body of the VDR. Flammability class of material (min V-1):	N/A

R	ANNEX R, EXAMPLES OF REQUIREMENTS FOR QUALITY CONTROL PROGRAMMES	N/A
R.1	Minimum separation distances for unpopulated coated printed boards (see 2.10.6.2)	N/A
R.2	Reduced clearances (see 2.10.3)	N/A



S.3

N/A

	IEC 60950-1			
Clause	Requirement + Test	Result - Remark	Verdict	
S	ANNEX S, PROCEDURE FOR IMPULSE	E TESTING (see 6.2.2.3)	N/A	
S.1	Test equipment		N/A	
S.2	Test procedure		N/A	

Т	ANNEX T, GUIDANCE ON PROTECTION AGAINST INGRESS OF WATER (see 1.1.2)	N/A
	See separate test report.	

Examples of waveforms during impulse testing

U	ANNEX U, INSULATED WINDING WIRES FOR USE WITHOUT INTERLEAVED INSULATION (see 2.10.5.4)	
	See list of critical components. All used triple insulated wires are already approved to Annex U. No additional tests considered required.	

V	ANNEX V, AC POWER DISTRIBUTION SYSTEMS	(see 1.6.1)	Р
V.1	Introduction		Р
V.2	TN power distribution systems		Р

W	ANNEX W, SUMMATION OF TOUCH CURRENTS	N/A
W.1	Touch current from electronic circuits	N/A
W.1.1	Floating circuits	N/A
W.1.2	Earthed circuits	N/A
W.2	Interconnection of several equipments	N/A
W.2.1	Isolation	N/A
W.2.2	Common return, isolated from earth	N/A
W.2.3	Common return, connected to protective earth	N/A

X	ANNEX X, MAXIMUM HEATING EFFECT IN TRANSFORMER TESTS (see clause C.1)		Р
X.1	Determination of maximum input current	Input current was measured and recorded (see appended table 5.3).	Р
X.2	Overload test procedure		Р

Y ANNEX Y, ULTRAVIOLET LIGHT CONDITIONING TEST (see 4.3.13.3) N/A

Page 42 of 231

Report No. T223-0357/16

	IEC 60950-1		
Clause	Requirement + Test	Result - Remark	Verdict
Y.1	Test apparatus	:	N/A
Y.2	Mounting of test samples	:	N/A
Y.3	Carbon-arc light-exposure apparatus	:	N/A
Y.4	Xenon-arc light exposure apparatus		N/A

Z	ANNEX Z, OVERVOLTAGE CATEGORIES (see 2.10.3.2 and Clause G.2)

Р

AA

ANNEX AA, MANDREL TEST (see 2.10.5.8)

N/A

BB ANNEX BB, CHANGES IN THE SECOND EDITION ____

CC	ANNEX CC, Evaluation of integrated circuit (IC) c	urrent limiters	N/A
CC.1	General		N/A
CC.2	Test program 1		N/A
CC.3	Test program 2		N/A

DD	ANNEX DD, Requirements for the mounting mean equipment	ns of rack-mounted	N/A
DD.1	General		N/A
DD.2	Mechanical strength test, variable N		N/A
DD.3	Mechanical strength test, 250N, including end stops		N/A
DD.4	Compliance		N/A

EE	ANNEX EE, Household and home/office document/media shredders	N/A
EE.1	General	N/A
EE.2	Markings and instructions	N/A
	Use of markings or symbols	N/A
	Information of user instructions, maintenance and/or servicing instructions	N/A
EE.3	Inadvertent reactivation test	N/A
EE.4	Disconnection of power to hazardous moving parts:	N/A
	Use of markings or symbols	N/A
EE.5	Protection against hazardous moving parts	N/A
	Test with test finger (Figure 2A)	N/A
	Test with wedge probe (Figure EE1 and EE2):	N/A