CUS200M

IMMUNITY DATA

I N D E X

1.0	Summary of Immunity Test Result	R-1
1.0	Summary of minimum Pest Result	IC I
	IEC61000 Series Test Data	
2.0	IEC61000 Series Test Data · · · · · · · · · · · · · · · · · ·	R-2
2.1	Electrostatic Discharge Immunity Test (IEC61000-4-2)	R-2
2.2	Radiated Radio-Frequency Electromagnetic Field Immunity Test (IEC61000-4-3)	R-3
2.3	Electrical Fast Transient / Burst Immunity Test (IEC61000-4-4)	R-4
2.4	Surge Immunity Test (IEC61000-4-5)	R-5
2.5	Conducted Disturbances Induced by Radio-Frequency Field Immunity Test (IEC61000-4-6) · · · · · · · · · · · · · · · · · · ·	R-6
2.6	Power Frequency Magnetic Field Immunity Test (IEC61000-4-8)	R-7
2.7	Voltage Dips, Short Interruptions Immunity Test (IEC61000-4-11) · · · · · · · · · · · · · · · · · ·	R-8
	IEC60601-1-2 Series Test Data	
	IEC60601-1-2 Series Test Data	
3.1	Electrostatic Discharge Immunity Test (IEC60601-1-2 Ed.4.1)	R-9
3.2	Radiated Radio-Frequency Electromagnetic Field Immunity Test (IEC60601-1-2 Ed.4.1)	R-10
3.3	Electrical Fast Transient / Burst Immunity Test (IEC60601-1-2 Ed.4.1)	R-11
3.4	Surge Immunity Test (IEC60601-1-2 Ed.4.1)	R-12
3.5	Conducted Disturbances Induced by Radio-Frequency Field Immunity Test (IEC60601-1-2 Ed.4.1) · · · · ·	R-13
3.6	Power Frequency Magnetic Field Immunity Test (IEC60601-1-2 Ed.4.1)	R-14
3.7	Voltage Dips, Voltage Interruptions Immunity Test (IEC60601-1-2 Ed.4.1)	R-15
3.8	Radiated Field In Close Proximity Immunity Test (IEC60601-1-2 Ed.4.1)	R-16
	Terminology Used	
	FG · · · · · Frame GND ± · · · · · Earth (±) terminal L · · · · · Live line N · · · · · Neutral line /// · · · · Earth +V · · · · + Output -V · · · · · Output	

^{*} Test results are reference data based on our standard measurement condition.

MODEL: CUS200M

(1) IEC61000 Series Test Result:

Item	Standard	Test level	Criteria	Result	Page	Notes & Conditions
Electrostatic Discharge Immunity Test	IEC61000-4-2	1,2,(3)	A	PASS	R-2	Level3 : Air discharge only
Radiated Radio-Frequency Electromagnetic Field Immunity Test	IEC61000-4-3	1,2,3	A	PASS	R-3	
Electrical Fast Transient / Burst Immunity Test	IEC61000-4-4	1,2,3	A	PASS	R-4	
Surge Immunity Test	IEC61000-4-5	1,2,3,(4)	A	PASS	R-5	Level4 : Common mode only
Conducted Disturbances Induced by Radio-Frequency Field Immunity Test	IEC61000-4-6	1,2,3	A	PASS	R-6	
Power Frequency Magnetic Field Immunity Test	IEC61000-4-8	1,2,3,4	A	PASS	R-7	
Voltage Dips Immunity Test	IEC61000-4-11	Class 3	В	PASS	R-8	
Short Interruptions Immunity Test	IEC61000-4-11	Class 3	В	PASS	R-8	

Detail of test condition refer to each test page.

(2) IEC60601-1-2 Series Test Result:

Item	Standard	Test level	Criteria	Result	Page	Notes & Conditions
Electrostatic Discharge Immunity Test	IEC60601-1-2 Ed.4.1	1,2,3,4	A	PASS	R-9	Enclosure port
Radiated Radio-Frequency Electromagnetic Field Immunity Test	IEC60601-1-2 Ed.4.1	1,2,3	A	PASS	R-10	Enclosure port
Electrical Fast Transient / Burst Immunity Test	IEC60601-1-2 Ed.4.1	1,2,3	A	PASS	R-11	Input a.c. power PORT
Surge Immunity Test	IEC60601-1-2 Ed.4.1	1,2	A	PASS	R-12	Input a.c. power PORT
Conducted Disturbances Induced by Radio-Frequency Field Immunity Test	IEC60601-1-2 Ed.4.1	1,2	A	PASS	R-13	Input a.c. power PORT
Power Frequency Magnetic Field Immunity Test	IEC60601-1-2 Ed.4.1	1,2,3,4	A	PASS	R-14	Enclosure port
Voltage Dips Immunity Test	IEC60601-1-2	Class 2	A $(200\text{VAC} \sim 240\text{VAC}$ and $(\text{Po} \leq 160\text{W}))$	PASS	R-15	Input a.c. power PORT
	Ed.4.1	Class 2	B (100VAC~ 120VAC or (Po > 160W))	PASS	K-13	
Voltage Interruptions Immunity Test	IEC60601-1-2 Ed.4.1	Class 2	В	PASS	R-15	Input a.c. power PORT
Radiated Field In Close Proximity Immunity Test	IEC60601-1-2 Ed.4.1	-	A	PASS	R-16	Enclosure port
Datail of toot condition refer to each toot many	_					

Detail of test condition refer to each test page.

Criteria A

- 1. The regulation of output voltage must not exceed 5% of initial value during test.
- 2. The output voltage must be within the regulation of specification after the test.
- 3. Smoke and fire are not allowed.

Criteria B

- 1. Must not have temporary function degradation that requires input restart.
- $2. The \ output \ voltage \ must \ be \ within \ the \ regulation \ of \ specification \ after \ the \ test.$
- 3. Smoke and fire are not allowed.

2.0 IEC61000 Series Data

2.1 Electrostatic Discharge Immunity Test (IEC61000-4-2)

MODEL: CUS200M

(1) Equipment Used

Electro Static Discharge Simulator : NSG435 (SCHAFFNER)

Discharge Resistance :330Ω Capacity :150pF

(2) Test Conditions

•Input Voltage :115, 230VAC •Output Voltage :Rated


•Output Current :0%, 100% •Polarity :+,-

•Test Times :10 times •Discharge Interval :>1 second

• Ambient Temperature :25°C

(3) Test Method and Device Test Point

Contact Discharge : + , Mounting screw



(4) Acceptable Conditions

- 1. Output voltage regulation not to exceed $\pm 5\%$ of initial (before test) value during test.
- 2. Output voltage to be within regulation specification after the test.
- 3. Along with 1 and 2, without the occurrence of smoke and fire, as well as no output failure.

Contact Discharge (kV)	CUS200M-12/18/24/36/48	Air Discharge(kV)	CUS200M-12/18/24/36/48
2	PASS	2	PASS
4	PASS	4	PASS
		8	PASS

2.2 Radiated Radio-Frequency Electromagnetic Field Immunity Test (IEC61000-4-3)

MODEL: CUS200M

(1) Equipment Used

SML 03(RS CORPORATION) HL 046(RS CORPORATION) AR500W 1000A(AR CORPORATION) FM5004(AR CORPORATION) FP6001(AR CORPORATION)

(2) Test Conditions

•Input Voltage : 115, 230VAC •Output Voltage : Rated

•Output Current : 0%, 100% •Amplitude Modulated : 80%, 1kHz


•Electromagnetic Frequency: 80~1000MHz •Ambient Temperature: 25°C

•Wave Angle : Horizontal and Vertical •Distance : 3.0m

• Sweep Condition : 1.0%Step Up, 2.8 Seconds Hold

•Test Angle : Top/Bottom, Both Sides, Front/Back

(3) Test Method



(4) Acceptable Conditions

- 1. Output voltage regulation not to exceed $\pm 5\%$ of initial (before test) value during test.
- 2. Output voltage to be within regulation specification after the test.
- 3. Along with 1 and 2, without the occurrence of smoke and fire, as well as no output failure.

Radiation Field Strength (V/m)	CUS200M-12/18/24/36/48
1	PASS
3	PASS
10	PASS

2.3 Electrical Fast Transient / Burst Immunity Test (IEC61000-4-4)

MODEL: CUS200M

(1) Equipment Used

EFT/B Generator : FNS-100L (NOISEKEN)

(2) Test Conditions

•Input Voltage :115, 230VAC •Output Voltage :Rated


•Output Current :0%, 100% •Test Time :1 minute

• Polarity : +,- • Ambient Temperature : 25° C

•Number of Tests : 3 times

(3) Test Method and Device Test Point

Apply to $(N, L, \pm), (N, L), (N), (L), (\pm).$



(4) Acceptable Conditions

- 1. Output voltage regulation not to exceed $\pm 5\%$ of initial (before test) value during test.
- 2. Output voltage to be within output voltage regulation specification after the test.
- 3. Along with 1 and 2, without the occurrence of smoke and fire, as well as no output failure.

Test Voltage (kV)	Repetition Rate (kHz)	CUS200M-12/18/24/36/48
0.5	5 / 100	PASS
1	5 / 100	PASS
2	5 / 100	PASS

2.4 Surge Immunity Test (IEC61000-4-5)

MODEL: CUS200M

(1) Equipment Used

Surge Generator :6100 (SCHAFFNER)

Coupling Impedance : Common 12Ω Coupling Capacitance : Common $9\mu F$

Normal 2Ω Normal $18\mu F$

(2) Test Conditions

•Input Voltage :115, 230VAC •Output Voltage :Rated


•Output Current :0, 100% •Number of Tests :3 times

•Polarity :+,- •Mode : Common, Normal

•Phase :0, 90 deg •Ambient Temperature :25°C

(3) Test Method and Device Test Points

Apply to Common mode $(N-\pm, L-\pm)$ and Normal mode (N-L).



(4) Acceptable Conditions

- 1. Output voltage regulation not to exceed $\pm 5\%$ of initial (before test) value during test.
- 2. Output voltage to be within regulation specification after the test.
- 3. Along with 1 and 2, without the occurrence of smoke and fire, as well as no output failure.

Co	ommon	Normal		
Test Voltage (kV)	CUS200M-12/18/24/36/48	Test Voltage (kV)	CUS200M-12/18/24/36/48	
0.5	PASS	0.5	PASS	
1	PASS	1	PASS	
2	PASS	2	PASS	
4	PASS			

2.5 Conducted Disturbances Induced by Radio-Frequency Field Immunity Test (IEC61000-4-6)

MODEL: CUS200M

(1) Equipment Used

RF POWER AMPLIFIER : (AR U.S.A)

SIGNAL GENERATOR : IFR 2023A (IFR U.K)

(2) Test Conditions


•Input Voltage :115, 230VAC •Output Voltage :Rated

•Output Current :100% •Electromagnetic Frequency :150kHz~80MHz

•Ambient Temperature :25°C

• Sweep Condition : 1.0% Step Up, 2.8 Seconds Hold

(3) Test Method



(4) Acceptable Conditions

- 1. Output voltage regulation not to exceed $\pm 5\%$ of initial (before test) value during test.
- 2. Output voltage to be within regulation specification after the test.
- 3. Along with 1 and 2, without the occurrence of smoke and fire, as well as no output failure.

Voltage Level (V)	CUS200M-12/18/24/36/48
1	PASS
3	PASS
10	PASS

2.6 Power Frequency Magnetic Field Immunity Test (IEC61000-4-8)

MODEL: CUS200M

(1) Equipment Used

AC Power Source : 1501L (California Instrument)

Helmholts Coil : HHS5215 (Spulen)

(2) Test Conditions


•Input Voltage :115, 230VAC •Output Voltage :Rated

•Output Current :100% •Magnetic Frequency :50Hz

•Ambient Temperature :25 $^{\circ}$ C •Direction :X, Y, Z

•Test Time : More than 10 seconds(Each direction)

(3) Test Method and Device Test Point



(4) Acceptable Conditions

- 1. Output voltage regulation not to exceed $\pm 5\%$ of initial (before test) value during test.
- 2. Output voltage to be within regulation specification after the test.
- 3. Along with 1 and 2, without the occurrence of smoke and fire, as well as no output failure.

Magnetic Field Strength (A/m)	CUS200M-12/18/24/36/48
1	PASS
3	PASS
10	PASS
30	PASS

2.7 Voltage Dips, Short Interruptions Immunity Test (IEC61000-4-11)

MODEL: CUS200M

(1) Equipment Used

Test Generator : PCR2000L (KIKUSUI)


(2) Test Conditions

•Input Voltage :115, 230VAC •Output Voltage :Rated

•Output Current :100% •Ambient Temperature :25°C

•Number of Tests : 3 times • Test interval : More than 10 seconds

(3) Test Method and Device Test Point



(4) Acceptable Conditions

- 1. Output voltage to be within output voltage regulation specification after the test.
- 2. Smoke and fire do not occur.

Test Lev	vel Dip rate	Continue Time	CUS200M-12/18/24/36/48
70%	30%	500ms	PASS
40%	60%	200ms	PASS
0%	100%	20ms	PASS
0%	100%	5000ms	PASS

3.0 IEC60601-1-2 Series Test Data

3.1 Electrostatic Discharge Immunity Test (IEC60601-1-2 Ed.4.1)

MODEL: CUS200M

(1) Equipment Used

Electro Static Discharge Simulator : NSG435 (SCHAFFNER)

Discharge Resistance : 330Ω Capacity : 150pF

(2) Test Conditions

•Input Voltage :100, 240VAC •Output Voltage :Rated


•Output Current :0%, Full load •Polarity :+,-

•Number of Tests :10 times •Discharge Interval :>1 second

•Ambient Temperature :25°C

(3) Test Method and Device Test Point (IEC61000-4-2, ENCLOSURE PORT)

Air Discharge $: \pm$, Mounting screw, and Input (L, N).



(4) Acceptable Conditions

- 1. The regulation of output voltage must not exceed 5% of initial value during test.
- 2. The output voltage must be within the regulation of specification after the test.
- 3. Smoke and fire are not allowed.

Contact Discharge (kV) (Level 4)	CUS200M-12/18/24/36/48	Air Discharge(kV) (Level 4)	CUS200M-12/18/24/36/48
2	PASS	2	PASS
4	PASS	4	PASS
6	PASS	8	PASS
8	PASS	15	PASS

3.2 Radiated Radio-Frequency Electromagnetic Field Immunity Test (IEC60601-1-2 Ed.4.1)

MODEL: CUS200M

(1) Equipment Used

:MG3692B (Anritsu) Signal generator Power amplifier system : AP32 SW210 (PRANA)

: AP32 MT255 (PRANA)

Electric field sensor :HI-6105 (ETS-Lindgren)

:AT4510 (AR) Bilog antenna

:VULP9118E(SCHWARZBECK)

(2) Test Conditions

·Input Voltage :100, 240VAC ·Output Voltage :Rated

 Output Current :0%, Full load •Distance(AM) :3.0m

·Wave An : Horizontal and Vertical :0.3m •Distance(FM,PM)

:Top/Bottom, Both Sides, Front/Back •Ambient Temperature :25°C ·Test Angle

• Amplitude Modulated(AM): 80%, 1kHz, 1.0% step up,

0.5 seconds hold.


•Pulse Modulated(PM) :18Hz, 217Hz,

0.5 seconds hold

•Frequency Modulated(FM) :5kHz deviation, 1kHz sine,

0.5 seconds hold.

(3) Test Method (IEC61000-4-3, ENCLOSURE PORT)



(4) Acceptable Conditions

- 1. The regulation of output voltage must not exceed 5% of initial value during test.
- 2. The output voltage must be within the regulation of specification after the test.
- 3. Smoke and fire are not allowed.

Modulation	Radiation Field Strength (V/m) (Level 3)	Electromagnetic Frequency	CUS200M-12/18/24/36/48
AM	10	80MHz ∼2.7GHz	PASS
PM	27	385MHz	PASS
(18Hz)	28	810,870,930MHz	PASS
PM	9	710,745,780,5240,5500,5785MHz	PASS
(217Hz)	28	1720,1845,1970,2450MHz	PASS
FM	28	450MHz	PASS

3.3 Electrical Fast Transient / Burst Immunity Test (IEC60601-1-2 Ed.4.1)

MODEL: CUS200M

(1) Equipment Used

EFT/B Generator : FNS-100L (NOISEKEN)

(2) Test Conditions

•Input Voltage :100, 240VAC •Output Voltage :Rated

•Output Current : 0%, Full load •Test Time : 1 minute


• Polarity : +,- • Ambient Temperature : 25° C

•Number of Tests : 1 time •Pulse Frequency : 100kHz

•Burst Time :15msec •Number of Pulse :75pcs

•Burst Cycle :300msec

(3) Test Method and Device Test Point (IEC61000-4-4, Input a.c. power PORT) Apply to (N, L, \pm) .



(4) Acceptable Conditions

- 1. The regulation of output voltage must not exceed 5% of initial value during test.
- 2. The output voltage must be within the regulation of specification after the test.
- 3. Smoke and fire are not allowed.

Test Voltage (kV) (Level 3)	CUS200M-12/18/24/36/48		
0.5	PASS		
1	PASS		
2	PASS		

3.4 Surge Immunity Test (IEC60601-1-2 Ed.4.1)

MODEL: CUS200M

(1) Equipment Used

Surge Generator : NSG3040 (TESEQ)

Coupling Impedance : Common 12Ω Coupling Capacitance : Common $9\mu F$

Normal 2Ω Normal $18\mu F$

(2) Test Conditions

•Input Voltage :100, 240VAC •Output Voltage :Rated


•Output Current :0%, Full load •Number of Tests :5 times

•Polarity :+,- •Mode :Common and Normal

•Phase :0, 90deg •Ambient Temperatur :25°C

(3) Test Method and Device Test Point (IEC61000-4-5, Input a.c. power PORT)

Apply to Common mode $(N-\frac{1}{2}, L-\frac{1}{2})$ and Normal mode (N-L).



(4) Acceptable Conditions

- 1. The regulation of output voltage must not exceed 5% of initial value during test.
- 2. The output voltage must be within the regulation of specification after the test.
- 3. Smoke and fire are not allowed.

Common(Level 3)		Normal(Level 2)		
Test Voltage (kV)	CUS200M-12/18/24/36/48	Test Voltage (kV)	CUS200M-12/18/24/36/48	
0.5	PASS	0.5	PASS	
1	PASS	1	PASS	
2	PASS			

3.5 Conducted Disturbances Induced by Radio-Frequency Field Immunity Test (IEC60601-1-2 Ed.4.1)

MODEL: CUS200M

(1) Equipment Used

Compact RF Simulator : NSG 4070-30 (TESEQ)

Coupling-Decoupling Network : CDN L-801 M2/M3 (Liithi)

(2) Test Conditions

•Input Voltage :100, 240VAC •Output Voltage :Rated


•Output Current :0%, Full load •Electromagnetic Frequenc :150kHz~80MHz

•Ambient Temperature :25 $^{\circ}$ C

• Sweep Condition :1.0% step up, 0.5 seconds hold

(3) Test Method and Device Test Point (IEC61000-4-6, Input a.c. power PORT)

Apply to (N, L, \pm) .



(4) Acceptable Conditions

- 1. The regulation of output voltage must not exceed 5% of initial value during test.
- 2. The output voltage must be within the regulation of specification after the test.
- 3. Smoke and fire are not allowed.

Voltage Level (V) (Level 2)	CUS200M-12/18/24/36/48		
1	PASS		
3	PASS		

3.6 Power Frequency Magnetic Field Immunity Test (IEC60601-1-2 Ed.4.1)

MODEL: CUS200M

(1) Equipment Used

AC Power Source : NSG 1007(SCHAFFNER)

Helmholts Coil : R-1000-4-8/9-L-1M (TESEQ)

(2) Test Conditions


•Input Voltage :100, 240VAC •Output Voltage :Rated

•Output Current :0%, Full load •Magnetic Frequency :50Hz

•Ambient Temperatur : 25° C •Direction : X, Y, Z

•Test Time : More than 10 seconds (each direction)

(3) Test Method (IEC61000-4-8, ENCLOSURE PORT)



(4) Acceptable Conditions

- 1. The regulation of output voltage must not exceed 5% of initial value during test.
- 2. The output voltage must be within the regulation of specification after the test.
- 3. Smoke and fire are not allowed.

Magnetic Field Strength (A/m) (Level 4)	CUS200M-12/18/24/36/48		
1	PASS		
3	PASS		
10	PASS		
30	PASS		

3.7 Voltage Dips, Voltage Interruptions Immunity Test (IEC60601-1-2 Ed.4.1)

MODEL: CUS200M

(1) Equipment Used

Test generator : PCR2000LA(KIKUSUI)


(2) Test Conditions

•Input Voltage :100, 240VAC •Output Voltage :Rated

•Output Current :Full load •Ambient Temperature :25°C

•Number of Tests : 1time •Test Interval : More than 10 seconds

(3) Test Method (IEC61000-4-11, Class 2, Input a.c. power PORT)



(4) Acceptable Conditions

Criteria A

- 1. The regulation of output voltage must not exceed 5% of initial value during test.
- 2. The output voltage must be within the regulation of specification after the test.
- 3. Smoke and fire are not allowed.

Criteria B

- 1. Must not have temporary function degradation that requires input restart.
- 2. The output voltage must be within the regulation of specification after the test.
- 3. Smoke and fire are not allowed.

Phenomenon		Continue	Phase Angles	Criteria				CUS200M-
		Time		$100VAC{\sim}120VAC$ and Po \leqslant 160W	200VAC~240VAC and Po≤160W	100VAC~120VAC and Po > 160W	200VAC~240VAC and Po>160W	12/18/24/36/48
Voltage dips	70%	500ms	0 deg	В	A	В	A	PASS
	0%	10ms	0,45,90,135,180, 225,270,315 deg	A	A	A	A	PASS
	0%	20ms	0 deg	A	A	В	В	PASS
Voltage interruptions	0%	5000ms	0 deg	В	В	В	В	PASS

3.8 Radiated Field In Close Proximity Immunity Test (IEC60601-1-2 Ed.4.1)

MODEL: CUS200M

(1) Equipment Used

Signal generator : SMC100A (R&S)
Power amplifier system : BBA150-AB200 (R&S)

:NFCN9734 (SCHWARZBECK)
loop sensor
:FESP5134-40 (SCHWARZBECK)
Radiating loop
:FESP5132 (SCHWARZBECK)
:FESP5139 (SCHWARZBECK)


(2) Test Conditions

Input Voltage : 100, 240VAC Output Voltage : Rated

Output Current : Full load : 50mm

Test Angle : Top/Bottom, Both Sides, Front/Back Ambient Temperature : 25°C

Test Time : 2sec for each coil position



(4) Acceptable Conditions

- 1. The regulation of output voltage must not exceed 5% of initial value during test.
- 2. The output voltage must be within the regulation of specification after the test.
- 3. Smoke and fire are not allowed.

Test Frequency	Immunity test level (A/m)	Modulation	CUS200M-12/18/24/36/48
30kHz	8	Continuous waves	PASS
134.2kHz	65	Pulse Modulation 50%, 2.1kHz	PASS
13.56MHz	7.5	Pulse Modulation 50%, 50kHz	PASS