

PAE50S24-*

EVALUATION DATA

型式データ

DWG.No. C245-53-01		
承認	査閲	担当
T. Suzuki 28.Mar.'06	J. Hayama 10.Mar.'06	K. Yokoyama 10.Mar.'06

DENSEI-LAMBDA

INDEX


1. 測定方法	Evaluation Method	PAGE
1.1	測定回路 Circuits used for determination	T-1~5
	(1) 静特性 Steady state data	
	(2) 通電ドリフト特性 Warm up voltage drift characteristics	
	(3) 過電流保護特性 Over current protection (OCP) characteristics	
	(4) 過電圧保護特性 Over voltage protection (OVP) characteristics	
	(5) 出力立ち上がり特性 Output rise characteristics	
	(6) 出力立ち下がり特性 Output fall characteristics	
	(7) 出力立ち上がり特性 (ON/OFFコントロール時) Output rise characteristics with ON/OFF CONTROL	
	(8) 出力立ち下がり特性 (ON/OFFコントロール時) Output fall characteristics with ON/OFF CONTROL	
	(9) 過渡応答 (負荷急変) 特性 Dynamic load response characteristics	
	(10) 入力サージ電流 (突入電流) 特性 Inrush current characteristics	
	(11) 出力リップル、ノイズ波形 Output ripple and noise waveform	
	(12) EMI特性 Electro-Magnetic Interference characteristics	
1.2	使用測定機器 List of equipments used	T-6
2.	特性データ Characteristics	
2.1	(1) 入力・負荷・温度変動 Regulation - line and load, temperature drift	T-7
	(2) 出力電圧・リップル電圧対入力電圧 Output voltage and ripple voltage v.s. input voltage	T-8
	(3) 効率・入力電流対出力電流 Efficiency and input current v.s. output current	T-9
	(4) 効率対入力電圧 Efficiency v.s. input voltage	T-10
	(5) 効率対周囲温度 Efficiency v.s. ambient temperature	T-11
2.2	通電ドリフト特性 Warm up voltage drift characteristics	T-12
2.3	過電流保護特性 Over current protection (OCP) characteristics	T-13~14
2.4	過電圧保護特性 Over voltage protection (OVP) characteristics	T-15
2.5	出力立ち上がり特性 Output rise characteristics	T-16~17
2.6	出力立ち下がり特性 Output fall characteristics	T-18~19
2.7	出力立ち上がり特性 (ON/OFFコントロール時) Output rise characteristics with ON/OFF CONTROL	T-20~21
2.8	出力立ち下がり特性 (ON/OFFコントロール時) Output fall characteristics with ON/OFF CONTROL	T-22~23

2.9	過渡応答（負荷急変）特性	Dynamic load response characteristics	T-24
2.10	入力サージ電流（突入電流）特性	Inrush current waveform	T-25
2.11	出力リップル、ノイズ波形	Output ripple and noise waveform	T-26
2.12	EMI特性	Electro-Magnetic Interference characteristics	
	VCCI class A 対応アプリケーションシステム		
	VCCI class A application system		T-27~29

使用記号 Terminology used

	Definition	
Vin 入力電圧	Input Voltage
Vout 出力電圧	Output Voltage
VCNT CNT電圧	CNT Voltage
Iin 入力電流	Input Current
Iout 出力電流	Output Current
Ta 周囲温度	Ambient Temperature


- 1. 測定方法 Evaluation Method
- 1.1 測定回路 Circuits used for determination
- (1) 静特性 Steady state characteristics




- (2) 通電ドリフト Warm up voltage drift characteristics

静特性と同じ
 Same as Steady state data


- (3) 過電流保護特性 Over current protection (OCP) characteristics



(4) 過電圧保護特性 Over voltage protection (OVP) characteristics



(5) 出力立ち上がり特性 Output rise characteristics




(6) 出力立ち下がり Output fall characteristics

出力立ち上がり特性と同じ
 Same as output rise characteristics

(7) 出力立ち上がり特性 (ON/OFFコントロール時)

Output rise characteristics with ON/OFF CONTROL




(8) 出力立ち下がり特性 (ON/OFFコントロール時)

Output fall characteristics with ON/OFF CONTROL


出力立ち上がり特性 (ON/OFFコントロール時) と同じ

Same as output rise characteristics with ON/OFF CONTROL

(9) 過渡応答(負荷急変)特性 Dynamic load response characteristics




(10) 入力サージ電流 (突入電流) 特性 Inrush current characteristics




- C1: 4.7uF Ceramic Capacitor × 7para
- C2: 1uF Ceramic Capacitor
- C3: 10uF Tantalum Capacitor
- C4: 15000uF Electrolytic Capacitor
- R1: 0.01Ω
- l: 50mm

(11) 出力リップル、ノイズ波形 Output ripple and noise waveform




- C1: 4.7uF Ceramic Capacitor × 7para
- C2: 1uF Ceramic Capacitor
- C3: 10uF Tantalum Capacitor
- C4: 4700pF Ceramic Capacitor
- R1: 50Ω
- l: 50mm

(12) EMI 特性 Electro-Magnetic Interference characteristics




(a) 雑音端子電圧 (掃還ノイズ) Conducted Emission Noise



(b) 雑音電界強度 (輻射ノイズ) Radiated Emission Noise

(1) VCC class A 対応アプリケーションシステム

VCCI class A application system



- L1: 680uH
- C1,C2: 1uF Ceramic Capacitor
- C3: 470uF Electrolytic Capacitor × 2para
- C4: 1uF Ceramic Capacitor
- C5: 10uF Tantalum Capacitor
- C6,C7: 0.1uF Ceramic Capacitor
- C8,C9: 0.047uF Ceramic Capacitor
- I : 50mm

1.2 使用測定機器 List of equipment used

	EQUIPMENT USED	MANUFACTURER	MODEL NO.
1	OSCILLO SCOPE	HITACHI DENSHI	V-1100A
2	DIGITAL STORAGE OSCILLOSCOPE	TEKTRONIX	TDS540
3	DIGITAL MULTIMETER	AGILENT	34970A
4	CURRENT PROBE/AMPLIFIER	TEKTRONIX	A6303/AM503
5	SHUNT RESISTOR	YOKOGAWA ELECT.	2215
6	X-Y RECORDER	GRAPHTEC	WX4309
7	CONTROLLED TEMP. CHANBER	TABAI ESPEC	SH-240
8	SPECTRUM ANALYZER	ROHDE & SCHWARZ	FSA
9	EMI TEST RECEIVER	ROHDE & SCHWARZ	ESHS10
10	EMI TEST RECEIVER	ROHDE & SCHWARZ	ESVS10
11	RF RELAY MATRIX	ROHDE & SCHWARZ	PSU
12	AMN	KYORITSU	KNW-242
13	ANTENNA(BICONICAL ANTENNA)	SCHWARZBECK	BBA9106
14	DYNAMIC DUMMY LOAD	TAKASAGO	FK-400L
15	AC POWER SUPPLY	TAKASAGO	AA2000XG

2. 特性データ

2.1 静特性 Steady state data

(1) 入力、負荷、温度変動 Regulation - line and load, temperature drift

5V

1. Regulation - line and load

condition Ta : 25°C

Air Velocity: 2m/s

Iout \ Vin	18VDC	24VDC	36VDC	line regulation	
0%	5.0239V	5.0243V	5.0239V	0.4mV	0.008%
50%	5.0238V	5.0242V	5.0243V	0.5mV	0.010%
100%	5.0239V	5.0243V	5.0245V	0.6mV	0.012%
load regulation	0.1mV	0.1mV	0.6mV		
	0.002%	0.002%	0.012%		

2. Temperature drift

conditions Vin : 24VDC

Iout : 100%

Air Velocity: 2m/s

Ta	-40°C	25°C	85°C	temperature stability	
Vout	4.9909V	5.0243V	5.0424V	51.5mV	1.030%

6V

1. Regulation - line and load

condition Ta : 25°C

Air Velocity: 2m/s

Iout \ Vin	18VDC	24VDC	36VDC	line regulation	
0%	6.0254V	6.0256V	6.0259V	0.5mV	0.008%
50%	6.0251V	6.0252V	6.0256V	0.5mV	0.008%
100%	6.0249V	6.0251V	6.0256V	0.7mV	0.012%
load regulation	0.5mV	0.5mV	0.3mV		
	0.008%	0.008%	0.005%		

2. Temperature drift

conditions Vin : 24VDC

Iout : 100%

Air Velocity: 2m/s

Ta	-40°C	25°C	85°C	temperature stability	
Vout	5.9907V	6.0251V	6.0468V	56.1mV	0.935%

2.1 (2) 出力電圧、リップル電圧対入力電圧

Output voltage and ripple voltage vs input voltage

Conditions Iout : 100 %


Ta : -40 °C -----

25 °C - - - - -

85 °C _____

Air Velocity : 2m/s

5V




Ta : -40 °C -----

25 °C - - - - -

85 °C _____

Air Velocity : 2m/s

6V



2.1 (3) 効率、入力電流対出力電流

Efficiency and input current vs output current

Conditions V_{in} : 18 VDC -----


: 24 VDC - - - - -

: 36 VDC ————


T_a : 25 °C

Air Velocity : 2m/s

5V



6V



2.1 (4) 効率対入力電圧
Efficiency vs input voltage

Conditions Ta : 25 °C


Iout : 50 % -----

80 % - - - - -


100 % _____

Air Velocity : 2m/s

5V



6V




2.1 (5) 効率対周囲温度
Efficiency vs ambient temperature

Conditions Vin : 24 VDC


Iout : 100 %

Air Velocity : 2m/s

5V




6V




2.2 通電ドリフト特性
Warm up voltage drift characteristics

Conditions Vin : 24 VDC
Iout : 100 %
Ta : 25 °C
Air Velocity : 2 m/s

5V




6V




2.3 過電流保護特性
Over current protection (OCP) characteristics

Conditions Vin : 18 VDC -----
 : 24 VDC - - - - -
 : 36 VDC ————
 Ta : 25 °C

5V




6V




2.3 過電流保護特性
Over current protection (OCP) characteristics

Conditions Ta : -40 °C -----
 : 25 °C - - - - -
 : 85 °C _____
 Vin : 24 VDC

5V




6V




2.4 過電圧保護特性
Over voltage protection (OVP) characteristics

Conditions Vin : 24 VDC
Iout : 0 %
Ta : 25 °C

5V



6V




2.5 出力立ち上がり特性
Output rise characteristics


PAE50S24-*

Conditions Vin : 24 VDC
Iout : 0 %
Ta : 25 °C

5V



6V




出力立ち上がり特性
Output rise characteristics


PAE50S24-*

Conditions V_{in} : 24 VDC
 I_{out} : 100 %
 T_a : 25 °C

5V



6V




2.6 出力立ち下がり特性
Output fall characteristics


PAE50S24-*

Conditions Vin : 24 VDC
Iout : 0 %
Ta : 25 °C

5V



6V




出力立ち下がり特性
Output rise characteristics


PAE50S24-*

Conditions Vin : 24 VDC
Iout : 100 %
Ta : 25 °C

5V



6V




2.7 出力立ち上がり特性 (ON/OFFコントロール時)
Output rise characteristics with ON/OFF CONTROL


PAE50S24-*

Conditions Vin : 24 VDC
Iout : 0 %
Ta : 25 °C

5V



6V




出力立ち上がり特性 (ON/OFFコントロール時)
Output rise characteristics with ON/OFF CONTROL


PAE50S24-*

Conditions Vin : 24 VDC
Iout : 100 %
Ta : 25 °C

5V



6V




2.8 出力立ち下がり特性 (ON/OFFコントロール時)
Output fall characteristics with ON/OFF CONTROL


PAE50S24-*

Conditions Vin : 24 VDC
Iout : 0 %
Ta : 25 °C

5V




6V




出力立ち下がり特性 (ON/OFFコントロール時)
Output fall characteristics with ON/OFF CONTROL

Conditions Vin : 24 VDC
Iout : 100 %
Ta : 25 °C

5V





6V



2.9 過渡応答（負荷急変）特性
Dynamic load response characteristics


Conditions V_{in} : 24 VDC
 T_a : 25 °C



2.10 入力サージ電流 (突入電流) 特性
Inrush current waveform

Conditions Vin : 24 VDC
Iout : 100 %
Ta : 25 °C

6V



2.11 出力リップル、ノイズ波形
Output ripple and noise waveform


PAE50S24-*

Conditions V_{in} : 24 VDC


I_{out} : 100 %

T_a : 25 °C

5V



6V



2.12 EMI特性

Electro-Magnetic Interference characteristics

(a) 雑音端子電圧 (帰還ノイズ)

Conditions Vin : 24 VDC

Conducted Emission


Iout : 100 %

(1) VCCI class A 対応アプリケーションシステム


Ta : 25 °C

VCCI class A application system

5V



6V



EMI特性

Electro-Magnetic Interference characteristics

(b) 雑音電界強度 (輻射ノイズ)

Conditions Vin : 24 VDC

Radiated Emission

Iout : 100 %


(1) VCCI class A 対応アプリケーションシステム

Ta : 25 °C


VCCI class A application system

5V

HORIZONTAL:



VERTICAL:



EMI特性

Electro-Magnetic Interference characteristics

(b) 雑音電界強度 (輻射ノイズ)

Radiated Emission

(1) VCCI class A 対応アプリケーションシステム

VCCI class A application system


Conditions Vin : 24 VDC

Iout : 100 %

Ta : 25 °C

6V

HORIZONTAL:



VERTICAL:

