

PAH100S48-*

**QUALITY
TEST DATA**



POWER MODULE

| | | |
|---------------------------|--------------------|-----------------------|
| DRAWING NO. : PA551-53-01 | | |
| NLS R&D | | |
| PREPARED | CHECKED | APPROVED |
| <i>Chew 8/9/99</i> | <i>Thom 8/9/99</i> | <i>Jeffrey 8/9/99</i> |
| DATE ISSUE : | 8 Sept 99 | |

INDEX

PAH100S48-*

| | |
|--|-------------|
| 1. Evaluation Method | PAGE |
| 1 - 1 Circuit used for determination | T - 1 |
| (1) Steady state data | |
| (2) Warm up voltage drift characteristics | |
| (3) Over current protection (O.C.P.) characteristics | |
| (4) Over voltage protection (O.V.P.) characteristics | |
| (5) Output rise characteristics | |
| (6) Output fall characteristics | |
| (7) Output rise characteristics with ON / OFF control (negative logic) | |
| (8) Output fall characteristics with ON / OFF control (negative logic) | |
| (9) Dynamic load response characteristics | |
| (10) Inrush current waveform | |
| (11) Output-ripple , noise waveform | |
| (12) Leakage current characteristics | |
| (13) Dynamic line response characteristics | |
| (14) AC input response | |
| (15) Input reflected current | |
| 1 - 2 List of equipment used | T - 6 |
| 2. Characteristics | |
| 2 - 1 Steady state data | T - 7 |
| (1) Regulation - line and load , temp. drift | |
| (2) Output voltage and ripple voltage v.s. input voltage | |
| (3) Efficiency and input current v.s.output current | |
| (4) Efficiency v.s. input voltage | |
| 2 - 2 Warm up voltage drift characteristics | T - 11 |
| 2 - 3 Over current protection (O.C.P.) characteristics | T - 12 |
| 2 - 4 Over voltage protection (O.V.P.) characteristics | T - 14 |
| 2 - 5 Output rise characteristics | T - 15 |
| 2 - 6 Output fall characteristics | T - 17 |
| 2 - 7 Output rise characteristics with ON / OFF control (negative logic) | T - 19 |
| 2 - 8 Output fall characteristics with ON / OFF control (negative logic) | T - 21 |
| 2 - 9 Dynamic load response characteristics | T - 23 |
| 2 - 10 Inrush current waveform | T - 26 |
| 2 - 11 Output-ripple , noise waveform | T - 27 |
| 2 - 12 Leakage current characteristics | T - 30 |
| 2 - 13 Dynamic line response characteristics | T - 31 |
| 2 - 14 AC input response | T - 32 |
| 2 - 15 Input reflected current | T - 33 |


Terminology used

| | | | |
|--------|----------------|--------|------------------------|
| Vin - | Input Voltage | Iout - | Output Current |
| Vout - | Output Voltage | Tp - | Base-Plate Temperature |
| Iin - | Input Current | Tr - | Load Rise-Time |
| | | Tf - | Load Fall-Time |

1. EVALUATION METHOD

1 - 1 Circuit used for determination

(1) Steady state data



(i) $T_p = -20^\circ\text{C} \sim 100^\circ\text{C}$


C1 : 33 μF Electrolytic Capacitor
 C2 : 4700pF Ceramic Capacitor
 C3 : 1 μF Ceramic Capacitor

C4 : 3.3V&5V - 2200 μF Electrolytic Capacitor
 12V&15V - 470 μF Electrolytic Capacitor
 24V&28V - 220 μF Electrolytic Capacitor

(ii) $T_p = -40^\circ\text{C} \sim 100^\circ\text{C}$

C1 : 33 μF Ceramic Capacitor or equivalent capacitor such as 100V 6.8 μF x 5 pcs
 C4 : 2 pieces of the above recommended value

(2) Warm up voltage drift characteristics




C1 : 33 μF Electrolytic Capacitor
 C2 : 4700pF Ceramic Capacitor
 C3 : 1 μF Ceramic Capacitor

C4 : 3.3V&5V - 2200 μF Electrolytic Capacitor
 12V&15V - 470 μF Electrolytic Capacitor
 24V&28V - 220 μF Electrolytic Capacitor


(3) Over current protection (O.C.P.) characteristics

Same as steady state data

(4) Over voltage protection (O.V.P.) characteristics




(5) Output rise characteristics



(6) Output fall characteristics

Same as Output rise characteristics


(7) Output rise characteristics with on/off control




(8) Output fall characteristics with on/off control

Same as Output rise characteristics with on/off control

(9) Dynamic load response characteristics




(10) Inrush current waveform




(11) Output-ripple , noise waveform

NORMAL MODE (EIAJ Standard RC-9002A)




(11) Output-ripple , noise waveform


NORMAL + COMMON MODE




(12) Leakage current characteristics



(13) Dynamic line characteristics



(14) AC input response characteristics



C1 : 33μF Electrolytic Capacitor

C2 : 4700pF Ceramic Capacitor

C3 : 1μF Ceramic Capacitor


C5 : 560μF Electrolytic Capacitor

C4 : 3.3V&5V - 2200μF Electrolytic Capacitor

12V&15V - 470μF Electrolytic Capacitor

24V&28V - 220μF Electrolytic Capacitor

(15) Input Reflected current characteristics



C1 : 33μF Electrolytic Capacitor

C2 : 4700pF Ceramic Capacitor

C3 : 1μF Ceramic Capacitor

C5 : 220μF Electrolytic Capacitor

C4 : 3.3V&5V - 2200μF Electrolytic Capacitor

12V&15V - 470μF Electrolytic Capacitor

24V&28V - 220μF Electrolytic Capacitor

1-2 List of equipment used

| No | Description | Manufacturer | Model No. |
|----|----------------------------|-----------------|------------|
| 1 | Oscilloscope | TEKTRONIX | 2465B |
| 2 | | HITACHI | V-1050F |
| 3 | Digital oscilloscope | YEW | DL2140 |
| 4 | | HITACHI | VC-6041 |
| 5 | Digital volt meter | IWATSU | VDAC 7411 |
| 6 | DC ampere meter | YOKOGAWA ELEC. | 2051 |
| 7 | Dynamic dummy load | TAKAMIZAWA | PSA-150D |
| 8 | Variable resistive load | MATSUNAGA | 44/11Ω |
| 9 | Variable resistive load | MATSUNAGA | 2.4/0.6Ω |
| 10 | Controlled temp . chamber | TABAI | PL-2GM |
| 11 | Shunt resistor | KUWANO | 100mV , 1A |
| 12 | Current probe amplifier | TEKTRONIX | TM503 |
| 13 | Current probe | TEKTRONIX | A6303 |
| 14 | AC power source / Analyzer | HEWLETT PACKARD | 6813A |
| 15 | Leakage current tester | SIMPSON | 229-2 |

2. CHARACTERISTICS

2-1 Steady State Data

(1) Regulation - Line and Load, Temperature Drift

5 V

Regulation - Line and Load

Tp = 25°C

| Iout | Vin | 36 VDC | 48 VDC | 76 VDC | Line Regulation | |
|-----------------|---------|---------|---------|--------|-----------------|--|
| 0% | 4.994 V | 4.994 V | 4.995 V | 1 mV | 0.02% | |
| 50% | 4.992 V | 4.994 V | 4.995 V | 3 mV | 0.06% | |
| 100% | 4.994 V | 4.995 V | 4.996 V | 2 mV | 0.04% | |
| Load Regulation | | 2 mV | 1 mV | 1mV | | |
| | | 0.04% | 0.02% | 0.02% | | |

Temperature Drift

Vin = 48VDC

Iout = 100%

| Tp | -40°C | 25°C | 100°C | Temp. Stability |
|------|--------|--------|--------|-----------------|
| Vout | 4.997V | 5.020V | 5.010V | 23 mV |

12 V

Regulation - Line and Load

Tp = 25°C

| Iout | Vin | 36 VDC | 48 VDC | 76 VDC | Line Regulation | |
|-----------------|---------|---------|---------|--------|-----------------|--|
| 0% | 12.036V | 12.029V | 12.028V | 8 mV | 0.066% | |
| 50% | 12.038V | 12.037V | 12.036V | 2 mV | 0.017% | |
| 100% | 12.038V | 12.037V | 12.036V | 2 mV | 0.017% | |
| Load Regulation | | 2 mV | 8 mV | 8 mV | | |
| | | 0.017% | 0.066% | 0.066% | | |

Temperature Drift

Vin = 48VDC

Iout = 100%

| Tp | -40°C | 25°C | 100°C | Temp. Stability |
|------|---------|---------|---------|-----------------|
| Vout | 12.059V | 12.044V | 11.993V | 66 mV |

24 V

Regulation - Line and Load

Tp = 25°C

| Iout | Vin | 36 VDC | 48 VDC | 76 VDC | Line Regulation | |
|-----------------|---------|---------|---------|--------|-----------------|--|
| 0% | 24.058V | 24.053V | 24.050V | 8 mV | 0.033% | |
| 50% | 24.062V | 24.060V | 24.060V | 2 mV | 0.008% | |
| 100% | 24.059V | 24.060V | 24.060V | 1 mV | 0.004% | |
| Load Regulation | | 4 mV | 7 mV | 10 mV | | |
| | | 0.017% | 0.029% | 0.042% | | |

Temperature Drift

Vin = 48VDC

Iout = 100%

| Tp | -40°C | 25°C | 100°C | Temp. Stability |
|------|---------|---------|---------|-----------------|
| Vout | 24.052V | 24.071V | 24.025V | 46 mV |

2. CHARACTERISTICS

2-1 Steady State Data

(2) Output Voltage And Ripple Voltage V.S. Input Voltage


Condition : Iout = 100%

T_p = -40°C —————


T_p = 25°C -----

T_p = 100°C -·-----


5 V



12 V



24 V






2. CHARACTERISTICS

2-1 Steady State Data

(3) Efficiency And Input Current V.S. Output Current

Condition : Vin = 36 VDC _____
 = 48VDC -----
 = 76VDC - - - -
 Tp = 25°C



2. CHARACTERISTICS


2-1 Steady State Data

(4) Efficiency v.s. Input Voltage


Condition : Iout = 100%

Tp = 25°C


5 V



12 V




24 V




2-2 Warm Up Voltage Drift Characteristics

Condition : Vin = 48 V DC
Iout = 100 %
Tp = 25°C


5 V



12 V




24 V




2-3 O.C.P. Characteristics

Condition : Vin = 36 VDC —————
 Vin = 48 VDC -----
 Vin = 76 VDC - - - - -
 Tp = 25°C


5 V



12 V




24 V




O.C.P. Characteristics

Condition :
Tp = -40°C
Tp = 25°C
Tp = 100°C
Vin = 48 VDC


5V



12V



24 V






2-4 O.V.P. Characteristics

Condition : Vin = 48 V DC




Iout = 0 %

Tp = 25°C






2-5 Output Rise Characteristics

Condition : Vin = 48 V DC
 Iout = 0 %
 Tp = 25°C






Output Rise Characteristics

Condition : Vin = 48 V DC
Iout = 100 %
Tp = 25°C

5 V**12 V****24 V**




2-6 Output Fall Characteristics

Condition : Vin = 48 V DC
 Iout = 0 %
 Tp = 25°C



Output Fall Characteristics

Condition : Vin = 48 V DC
 Iout = 100 %
 Tp = 25°C






2-7 Output Rise With On/Off Characteristics

(Negative logic)

Condition : Vin = 48 V DC

Iout = 0 %




Tp = 25°C



Output Rise With On/Off Characteristics

(Negative logic)

Condition :
 Vin = 48 V DC
 Iout = 100 %
 Tp = 25°C






2-8 Output Fall With On/Off Characteristics

(Negative logic)

Condition : Vin = 48 V DC

Iout = 0 %

Tp = 25°C






Output Fall With On/Off Characteristics

(Negative logic)

Condition : Vin = 48 V DC



Iout = 100 %

Tp = 25°C





2-9 Dynamic Load Response Characteristics

Condition : Vin = 48 VDC
Tp = 25°C





Dynamic Load Response Characteristics

Condition : Vin = 48 VDC
Tp = 25°C




Dynamic Load Response Characteristics

Condition : Vin = 48 VDC
Tp = 25°C



2-10 Inrush Current Waveform

Condition : Vin = 48 V DC
Iout = 100 %
Tp = 25°C




2-11 Output - Ripple & Noise Waveform


Condition : Vin = 48V DC
Iout = 100%
Tp = 25°C

5 V

NORMAL MODE



NORMAL + COMMON MODE




Output - Ripple & Noise Waveform


Condition : Vin = 48V DC
Iout = 100%
Tp = 25°C

12 V

NORMAL MODE



NORMAL + COMMON MODE




Output - Ripple & Noise Waveform


Condition : Vin = 48V DC
Iout = 100%
Tp = 25°C

24 V

NORMAL MODE




NORMAL + COMMON MODE




2-12 Leakage Current Characteristics

Condition : Iout = 100%
Tp= 25°C


5V



12V



24V




PAH100S48-*

2-13 Dynamic Line Response Characteristics

Condition : Vin = 43 <=> 53VDC

Iout = 100%

Tp= 25°C






2-14 AC Input Response

Condition :

Vin = 48 VDC



Iout = 100%

Tp = 25°C





2-15 INPUT REFLECTED CURRENT

Condition : Vin = 48 VDC
Iout = 100%
Tp= 25°C



2-15 INPUT REFLECTED CURRENT

Condition : Vin = 48 VDC
 Iout = 100%
 Tp= 25°C



2-15 INPUT REFLECTED CURRENT

Condition Vin = 48 VDC
Iout = 100%
Tp = 25°C

