

RDS50-110

EVALUATION DATA

型式データ

DWG No. B043-53-01		
APPD	CHK	DWG
N. Uehara	Y. Kuroi Sawa	Y. Takahashi
17. Jan. '12	13. Jan. '12	13. Jan. '12

INDEX

1. 測定方法	Evaluation Method	PAGE
1.1 測定回路	Measurement Circuit	
測定回路1	Measurement Circuit 1	T-1
	静特性	Steady state characteristics
	過電流保護特性	Over current protection (OCP) characteristics
	過電圧保護特性	Over voltage protection (OVP) characteristics
	出力立ち上がり・立ち下がり特性	Output rise and fall characteristics
	出力保持時間特性	Hold up time characteristics
測定回路2	Measurement Circuit 2	T-1
	過渡応答（負荷急変）特性	Dynamic load response characteristics
測定回路3	Measurement Circuit 3	T-1
	入力サージ電流（突入電流）特性	Inrush current characteristics
測定回路4	Measurement Circuit 4	T-2
	出力リップル、ノイズ波形	Output ripple and noise waveform
測定構成図	Configuration used for determination.....	T-2
	EMI特性	Electro-Magnetic Interference Characteristics
	雑音端子電圧（帰還ノイズ）	Conducted Emission
	雑音電界強度（輻射ノイズ）	Radiated Emission
1.2 使用測定機器	List of equipment used	T-3
2. 特性データ	Characteristics Data	
2.1 静特性	Steady state characteristics	
(1) 入力・負荷・温度変動	Regulation - Line and Load , Temperature drift	T-4
(2) 入力電流・効率 対 出力電流	Input current and Efficiency vs. Output current	T-5～6
(3) 効率 対 入力電流	Efficiency vs. Input voltage	T-7～8
(4) 起動・停止電圧特性	Start and Stop voltage characteristics	T-9～10
2.2 過電流保護特性	Over current protection (OCP) characteristics	T-11～12
2.3 過電圧保護特性	Over voltage protection (OVP) characteristics	T-13
2.4 出力立ち上がり・立ち下がり特性	Output rise and fall characteristics	T-14～15
2.5 出力立ち上がり・立ち下がり特性 (ON/OFFコントロール時)	Output rise and fall characteristics with ON/OFF CONTROL	T-16～17
2.6 出力保持時間特性	Hold up time characteristics	T-18
2.7 過渡応答（負荷急変）特性	Dynamic load response characteristics	T-19～20
2.8 入力サージ電流（突入電流）特性	Inrush current characteristics	T-21
2.9 出力リップル、ノイズ波形	Output ripple and noise waveform	T-22
2.10 EMI特性	Electro-Magnetic Interference characteristics	T-23～26
略称記号説明	Abbreviation Symbol Description	
V _{in} 入力電圧	Input voltage
V _o 出力電圧	Output voltage
I _{in} 入力電流	Input current
I _o 出力電流	Output current
T _a 周囲温度	Ambient temperature
f 周波数	Frequency
CNT (RC) ON/OFF制御	ON/OFF control

1. 測定方法 Evaluation Method


1.1 測定回路 Measurement Circuit

測定回路 1

- 静特性
- 過電流保護特性
- 過電圧保護特性
- 出力立ち上がり・立ち下がり特性
- 出力保持時間特性

Measurement Circuit 1

- Steady state data
- Over current protection (OCP) characteristics
- Over voltage protection (OVP) characteristics
- Output rise and fall characteristics
- Hold up time characteristics




測定回路 2


- 過渡応答 (負荷急変) 特性

Measurement Circuit 2

- Dynamic load response characteristics



Output current waveform
Iout 50% ↔ 100%




測定回路 3

- 入力サージ電流 (突入電流) 特性

Measurement Circuit 3

- Inrush current characteristics




測定回路 4

- 出力リップル、ノイズ波形

Measurement Circuit 4

Output ripple and noise waveform




測定構成図

- EMI特性
- 雑音端子電圧 (帰還ノイズ)


Configuration used for determination

Electro-Magnetic Interference characteristics
Conducted Emission



雑音電界強度 (輻射ノイズ)

Radiated Emission



1.2 使用測定機器 List of equipment used

	EQUIPMENT USED	MANUFACTURER	MODEL NO.
1	DIGITAL STORAGE OSCILLOSCOPE	YOKOGAWA ELECTRIC	DL1740EL
2	DIGITAL MULTIMETER	AGILENT	34970A
3	DIGITAL POWER METER	YOKOGAWA ELECTRIC	WT110
4	CURRENT PROBE/AMPLIFIER	YOKOGAWA ELECTRIC	701932
5	CURRENT PROBE/AMPLIFIER	TEKTRONIX	A6303
6	DUMMY LOAD	TAKASAGO	FK-400L
7	CVCF (AC/DC POWER SUPPLY)	KIKUSUI	PCR4000L
8	DYNAMIC DIP SIMULATOR	TAKAMIZAWA	PSA-210
9	CONTROLLED TEMP. CHAMBER	ESPEC	SU-240
10	SPECTRUM ANALYZER EMI TEST RECEIVER	ROHDE & SCHWARZ	ESCI
11	RF SELECTOR	TOYO CORPOLATION	NS4900
12	AMN	SCHWARZBECK	NNLK8121
13	ANTENNA (BICONICAL ANTENNA)	TESEQ	CBL6111D

2. 特性データ

Characteristics Data

2.1 静特性 Steady state data

(1) 入力・負荷・温度変動

Regulation - Line and Load , Temperature drift

1. Regulation - Line and Load

Condition : Ta=25°C

5V	Io \ Vin	60VDC	110VDC	160VDC	Line regulation	
	0%	5.004V	5.005V	5.005V	1mV	0.020%
50%	5.002V	5.002V	5.002V	0mV	0.000%	
100%	5.000V	5.000V	4.999V	1mV	0.020%	
Load regulation	4mV	5mV	6mV			
	0.080%	0.100%	0.120%			

12V	Io \ Vin	60VDC	110VDC	160VDC	Line regulation	
	0%	12.014V	12.014V	12.014V	0mV	0.000%
50%	12.014V	12.013V	12.013V	1mV	0.008%	
100%	12.013V	12.013V	12.012V	1mV	0.008%	
Load regulation	1mV	1mV	2mV			
	0.008%	0.008%	0.017%			

15V	Io \ Vin	60VDC	110VDC	160VDC	Line regulation	
	0%	14.995V	14.996V	14.996V	1mV	0.007%
50%	14.994V	14.995V	14.995V	1mV	0.007%	
100%	14.994V	14.994V	14.994V	0mV	0.000%	
Load regulation	1mV	2mV	2mV			
	0.007%	0.013%	0.013%			

24V	Io \ Vin	60VDC	110VDC	160VDC	Line regulation	
	0%	23.994V	23.994V	23.995V	1mV	0.004%
50%	23.993V	23.994V	23.994V	1mV	0.004%	
100%	23.993V	23.994V	23.994V	1mV	0.004%	
Load regulation	1mV	0mV	1mV			
	0.004%	0.000%	0.004%			

2. Temperature drift

Conditions : Vin=110VDC, Iout=100%


5V	Ta	-20°C	+25°C	+71°C	Temperature stability	
	Vo	5.005V	5.000V	4.998V	7mV	0.140%
12V	Vo	12.039V	12.013V	11.994V	45mV	0.375%
15V	Vo	15.033V	14.994V	14.970V	63mV	0.420%
24V	Vo	24.025V	23.994V	23.988V	37mV	0.154%

(2) 入力電流・効率 対 出力電流


Input current and Efficiency vs. Output current

Conditions Vin : 60 VDC ---
 : 110 VDC - - -
 : 160 VDC ———
 Ta : 25 °C

5V



12V




(2) 入力電流・効率 対 出力電流


Input current and Efficiency vs. Output current

Conditions Vin : 60 VDC -----
 : 110 VDC -.-.-.-
 : 160 VDC ————
 Ta : 25 °C

15V




24V




(3) 効率対入力電圧
Efficiency vs. Input voltage

Conditions Io : 50 % ----
 : 100 % ——
 Ta : 25 °C

5V




12V




(3) 効率対入力電圧
Efficiency vs. Input voltage

Conditions Io : 50 % - - - -
 : 100 % ————
 Ta : 25 °C

15V



24V







(4) 起動・停止電圧特性
Start and Stop voltage characteristics

出力電圧 対 入力電圧
Output voltage vs. Input voltage

Conditions I_o : 100 %
 T_a : 25 °C

入力電流 対 入力電圧
Input current vs. Input voltage

Conditions I_o : 100 %
 T_a : 25 °C







(4) 起動・停止電圧特性
Start and Stop voltage characteristics

出力電圧 対 入力電圧
Output voltage vs. Input voltage

Conditions I_o : 100 %
 T_a : 25 °C

入力電流 対 入力電圧
Input current vs. Input voltage

Conditions I_o : 100 %
 T_a : 25 °C



2.2 過電流保護特性

Over current protection (OCP) characteristics

入力電圧依存性

Input voltage dependence



Conditions Vin : 60 VDC -----
 : 110 VDC -.-.-.-
 : 160 VDC ————
 Ta : 25 °C

温度依存性



Temperature dependence

Conditions Vin : 110 VDC
 Ta : -20 °C -----
 : 25 °C -.-.-.-
 : 71 °C ————

5V



12V



2.2 過電流保護特性

Over current protection (OCP) characteristics

入力電圧依存性

Input voltage dependence



Conditions Vin : 60 VDC -----
 : 110 VDC -.-.-.-.
 : 160 VDC ————
 Ta : 25 °C

温度依存性



Temperature dependence

Conditions Vin : 110 VDC
 Ta : -20 °C -----
 : 25 °C -.-.-.-.
 : 71 °C ————

15V







24V



2.3 過電圧保護特性

Over voltage protection (OVP) characteristics



Conditions V_{in} : 110 VDC
 I_o : 0 %
 T_a : 25 °C





2.4 出力立ち上がり、立ち下がり特性
Output rise and fall characteristics

Conditions
 Vin : 110 VDC
 Io : 100 %
 Ta : 25°C

5V





12V





2.4 出力立ち上がり、立ち下がり特性
Output rise and fall characteristics

Conditions Vin : 110 VDC
Io : 100 %
Ta : 25°C

15V



24V



2.5 出力立ち上がり、立ち下がり特性 (ON/OFFコントロール時)

Output rise and fall characteristics with ON/OFF CONTROL



Conditions

Vin : 110 VDC



Io : 100 %

Ta : 25°C

5V



12V



2.5 出力立ち上がり、立ち下がり特性 (ON/OFFコントロール時)

Output rise and fall characteristics with ON/OFF CONTROL



Conditions

Vin : 110 VDC



Io : 100 %

Ta : 25°C

15V




24V




2.6 出力保持時間特性
Hold up time Characteristics

Conditions Vin : 110 VDC
Ta : 25 °C


5V




12V



15V



24V




2.7 過渡応答 (負荷急変) 特性

Dynamic load response characteristics


Conditions V_{in} : 110 VDC
 I_o : 50% \leftrightarrow 100 %
 (tr = tf = 100us)
 T_a : 25 °C

5V

f = 100Hz




f = 1kHz




12V

f = 100Hz




f = 1kHz




2.7 過渡応答 (負荷急変) 特性
Dynamic load response characteristics

Conditions Vin : 110 VDC
Io : 50% ↔ 100 %
(tr = tf = 100us)
Ta : 25 °C

15V




24V




2.8 入力サージ電流（突入電流）特性
Inrush current characteristics

Conditions Vin : 110 VDC
Io : 100 %
Ta : 25 °C

24V







↓ 拡大
Zoom in



本特性は、いずれの出力電圧モデルにおいても同様となります。
This characteristics is same for each output model.

2.9 出力リップル、ノイズ波形
Output ripple and noise waveform

Conditions Vin : 110 VDC
Io : 100 %
Ta : 25 °C



2.10 EMI特性

Electro-Magnetic Interference characteristics

雑音端子電圧



Conducted Emission

Conditions



Vin : 110 VDC

Io : 100 %

5V



12V



EN55011-A,EN55022-Aの限界値はVCCI class Aの限界値と同じです。
Limit of EN55011-A,EN55022-A are same as its VCCI class A.

表示はピーク値です。
Indication is peak values.

2.10 EMI特性

Electro-Magnetic Interference characteristics

雑音端子電圧



Conducted Emission

Conditions



Vin : 110 VDC

Io : 100 %

15V



24V



EN55011-A,EN55022-Aの限界値はVCCI class Aの限界値と同じです。
Limit of EN55011-A,EN55022-A are same as its VCCI class A.

表示はピーク値です。
Indication is peak values.

2.10 EMI特性

Electro-Magnetic Interference characteristics

雑音電界強度

Radiated Emission


Conditions

Vin : 110 VDC


Io : 100 %

5V

HORIZONTAL




VERTICAL




12V

HORIZONTAL



VERTICAL



EN55011-A,EN55022-Aの限界値はVCCI class Aの限界値と同じです。
Limit of EN55011-A,EN55022-A are same as its VCCI class A.

表示はピーク値です。
Indication is peak values.

2.10 EMI特性

Electro-Magnetic Interference characteristics

雑音電界強度

Radiated Emission


Conditions

Vin : 110 VDC


Io : 100 %

15V

HORIZONTAL




VERTICAL




24V

HORIZONTAL



VERTICAL



EN55011-A,EN55022-Aの限界値はVCCI class Aの限界値と同じです。
Limit of EN55011-A,EN55022-A are same as its VCCI class A.

表示はピーク値です。
Indication is peak values.