UL TEST REPORT AND PROCEDURE

Standard:	UL 62368-1, 2nd Ed, 2014-12-01 (Audio/video, information and communication technology equipment Part 1: Safety requirements) CAN/CSA C22.2 No. 62368-1-14, 2nd Ed-(Audio/video, information and communication technology equipment Part 1: Safety requirements)			
Certification Type:	Component Recognition			
CCN: QQJQ2, QQJQ8 (Power Supplies for Use in Audio/Video, Info and Communication Technology Equipment)				
Complementary CCN:	N/A			
Product:	DC-To-DC Converters			
	iE(A/C) Series			
Model:				
	See Model Matrix, under Misc Enclosure 7-01 for details.			
	Input: DC 18 - 75 V, max. 5 A			
Rating:	Output: DC 1.2 -28 V, max. 25 A, max. 82.5 W (SELV) Refer to Appendix 3			
	TDK-LAMBDA AMERICAS INC			
	SUITE 100			
Applicant Name and Address:	3320 MATRIX DR			
	RICHARDSON TX 75082			
	UNITED STATES			

This is to certify that representative samples of the products covered by this Test Report have been investigated in accordance with the above referenced Standards. The products have been found to comply with the requirements covering the category and the products are judged to be eligible for Follow-Up Service under the indicated Test Procedure. The manufacturer is authorized to use the UL Mark on such products which comply with this Test Report and any other applicable requirements of UL LLC ('UL') in accordance with the Follow-Up Service under the indicated Test Procedure as being covered by UL's Follow-Up Service under the indicated Test Procedure.

The applicant is authorized to reproduce the referenced Test Report provided it is reproduced in its entirety.

UL authorizes the applicant to reproduce the latest pages of the referenced Test Report consisting of the first page of the Specific Technical Criteria through to the end of the Conditions of Acceptability.

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL.

Prepared By:

Mengis Tesfay / Project Handler

Reviewed By:

Scott Shepler / Reviewer

Supporting Documentation

The following documents located at the beginning of this Procedure supplement the requirements of this Test Report:

A. Authorization - The Authorization page may include additional Factory Identification Code markings.

B. Generic Inspection Instructions -

- i. Part AC details important information which may be applicable to products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of this Test Report.
- ii. Part AE details any requirements which may be applicable to all products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of each Test Report.
- iii. Part AF details the requirements for the UL Certification Mark which is not controlled by the technical standard used to investigate these products. Products are permitted to bear only the Certification Mark(s) corresponding to the countries for which it is certified, as indicated in each Test Report.

Product Description

The product is a component type DC to DC power module with a planar power transformer. The converter is provided with input terminal pins for factory installation onto a printed wiring board with a connection to a dc source of supply and output terminal pins. These models have been evaluated as having Basic insulation from input to output. The product employs a multilayer PWB planar transformer.

Model Differences

All models within the iE(A/C) Series, are similar in construction and employ identical mechanical configuration, using the same PWB, same transformer core set, and inductor core set, except for rating.

Test Item Particulars

Classification of use by	Instructed person
Supply Connection	External Circuit - not Mains connected ES2
Supply % Tolerance	None
Supply Connection – Type	Not connected to Mains. For building in
Considered current rating of protective device as part of building or equipment installation	N/A (For building in) A; equipment
Equipment mobility	for building-in
Over voltage category (OVC)	other: Not directly connected to Mains
Class of equipment	Not classified
Access location	N/A
Pollution degree (PD)	PD 2
Manufacturer's specified maximum operating ambient (°C)	25°C
IP protection class	IPX0
Power Systems	N/A
Altitude during operation (m)	2000 m or less
Altitude of test laboratory (m)	app 180 m m
Mass of equipment (kg)	0.10
Technical Considerations	-

- The product was submitted and evaluated for use at the maximum ambient temperature (Tma) permitted by the manufacturer's specification of : 25°C
- The product is intended for use on the following power systems : No direct connection
- Considered current rating of protective device as part of the building installation (A) : For building in. An external input line normal blow fuse with a maximum value of 10A is required, see the Safety Considerations section of the data sheet. (see Appendix)
- Mains supply tolerance (%) or absolute mains supply values : No direct connection
- The equipment disconnect device is considered to be : N/A
- The following are available from the Applicant upon request : Installation (Safety) Instructions / Manual
- The product was investigated to the following additional standard : EN 62368-1:2014 + A11:2017

Engineering Conditions of Acceptability

For use only in or with complete equipment where the acceptability of the combination is determined by UL LLC. When installed in an end-product, consideration must be given to the following:

- The following product-line tests are conducted for this product : Electric Strength
- The following output circuits are at ES1 energy levels : All
- The following output circuits are at PS3 energy levels : Output Terminal
- The maximum investigated branch circuit rating is : EUT is for building in. 10 A external fuse is to be provided in the end product.
- The investigated Pollution Degree is : 2
- The following end-product enclosures are required : Electrical, Fire
- Heating Test shall be evaluated in end product.
- This component has been evaluated in 'control of fire spread' method assuming appropriate fire enclosure is provided in end product. Unless the fire enclosure is made of non-combustible or V-0 material, the separation from the PIS shall be considered
- Classification of PIS has not been conducted. Therefore, all electrical components and conductors including printed wirings were assumed to be arcing/resistive PIS.
- Unit intended for building-in and supplied power from secondary circuit which is isolated from primary circuit by double or reinforced insulation.
- This product was tested with external cooling at a minimum of 250 LFM @ 36V input and 400 LFM @ 75V input. Additional testing should be considered in the end product investigation if external cooling is different than these values. Except no airflow for model IE(A/C)4W004A120V-0##[R]

Additional Information

This report is based on VDE CB report reference 218758-Cl3-2, with its respective CB Test Certificate Ref. DE1-56443 respectively which was previously evaluated to UL/CSA/IEC 60950-1, 2nd edition, + Amendment 1 & 2.

Testing conducted in accordance with IEC 60950-1:2005 (Second Edition), Am1:2009 + Am2:2013; UL 60950-1, 2nd Edition, 2014-10-14; and CAN/CSA C22.2 No. 60950-1-07, 2nd Edition, 2014-10, and was deemed equivalent to the test required by IEC62368-1, 2nd Edition, CAN/CSA-C22.2 NO. 62368-1 2nd Ed, Issued December 1, 2014, and UL 62368-1 2nd Ed, Issued December 1, 2014. Testing correlation explanation provided in Enclosure.

All original sample and test dates are noted in the testing portion of this report. Additionally, limited testing was deemed necessary for this investigation to IEC 62368-1. The following tests were performed under this investigation:

ELECTRIC STRENGTH TEST (5.4.9)

The nameplate included in the report is representative of all models covered under this report. The label

includes: Optional "-R" appended to product code to indicate ROHS compliance.

Additional Standards

The product fulfills the requirements of: EN 62368-1:2014 + A11:2017

Markings and Instructions

•					
Clause Title	Marking or Instruction Details				
Equipment identification marking – Manufacturer identification	Listees or Recognized companys name, Trade Name, Trademark or File Number				
Equipment identification marking – model identification	Model Number				
Special Instructions to UL Representative N/A					

BD1.0	TABLE: Production-Line Testing Requirements							
BD1.1	Electric Strength	Electric Strength Test Special Constructions – Refer to Generic Inspection Instructions,						
		Part AC	for further infor	mation.				
Model	Component Removable parts Test probe Test V rms Test V							
			location		dc	Time, s		
N/A	-	-	-	-	-	-		
BD1.2	Earthing Continuity Test Exemptions – This test is not required for the following models:							
	All Models							
BD1.3	Electric Strengt	h Test Exemptions -	 This test is not 	t required for th	e following	g models:		
		-		-				
BD1.4	Electric Strength Test Component Exemptions – The following solid-state components							
	may be disconnected from the remainder of the circuitry during the performance of this							
	test.							
	N/A							

BE1.0	3E1.0 Sample and Test Specifics for Follow-Up Tests at UL						
Model	Component	Component Material Test Sample (s)					

Issue Date: 2020-04-29

Page 6 of 7

Report Reference #

4.1.2	TABLE: List of critic	Pass				
Object / part No.	Manufacturer/ trademark	Type / model	Technical data	Product Category CCN(s)	Mark(s) of conformity	Supplement ID
PWB	Interchangeable	Interchangeable	Min. V-1, 130°C	ZPMV2	UL	
Main isolating (T1) or (T101) Planar Transformer Printed Wiring Board (PWB): Top and Bottom	Interchangeable	Interchangeable	PWB rated V-1, 130 C, Multiple layered PWB.	ZPMV2	UL	
Optocoupler (U100 – U200)	NEC	PS2911-1 or PS2801	Minimum 1500 V isolation voltage	FPQU2	UL	
Optocoupler (U100 U200)-Alternate	Interchangeable	Interchangeable	Minimum 1500 V isolation voltage	FPQU2	UL	
Inductor (L1 or L201))	Interchangeable	Interchangeable, Integral to PWB. Planar type	94V-1 minimum, rated 130 °C			
Capacitor (C400)	TDK	C4520X7R 3DXX XKT	2000 V Ceramic Capacitor			
Capacitor (C400) - Alternate	Interchangeable	Interchangeable	2000 V Ceramic Capacitor			
Label	Identco International Corp	TTL139-401-10	Max temperature 175°C, Indoor use only	PGDQ2 or PGJI2	UL	
Alternate Label	Interchangeable	Interchangeable	Suitable for application to enclosure	PGDQ2 or PGJI2	UR	

Enclosures

Туре	Supplement Id	Description
Photographs	03-01	iEA Series Top
Photographs	03-02	iEA4W Series back side
Photographs	03-03	iEA4W Series PWB top Side
Schematics + PWB	05-01	Circuit diagram (Schematics), Layout, Data sheets
Miscellaneous	07-01	Model Matrix
Miscellaneous	07-02	Test correlation
Miscellaneous	07-03	Test Equipment

Test Record No. 1

The manufacturer submitted representative production sample(s) of Models iEA series. Testing was mainly based on VDE CB report reference 218758-Cl3-2, with its respective CB Test Certificate Ref. DE1-56443 which was previously evaluated to UL/CSA/IEC 60950-1, 2nd edition, + Amendment 1, and Amendment 2. . Test was also considered covered under E220248-A4. Testing conducted in accordance with IEC 60950-1:2005 (Second Edition), Am1:2009 + Am2:2013; UL 60950-1, 2nd Edition, 2014-10-14; and CAN/CSA C22.2 No. 60950-1-07, 2nd Edition, 2014-10, was deemed equivalent to the test required per IEC62368-1, 2nd Edition, CAN/CSA-C22.2 NO. 62368-1 2nd Ed, Issued December 1, 2014, and UL 62368-1 2nd Ed, Issued December 1, 2014. Testing correlation explanation is provided in Enclosure. Only Electric Strength test was repeated.

The following tests were conducted:

Tests performed (name of test and test clause):	Testing location: TDK-LAMBDA AMERICAS INC SUITE 100 3320 MATRIX DR RICHARDSON TX 75082 UNITED STATES
DETERMINATION OF WORKING VOLTAGE (5.4.1.8)	Testing conducted under IEC 60950- 1:2005 (Second Edition); Am1:2009 + Am2:2013 evaluation was considered equivalent. Test was covered under on VDE CB report reference 218758-Cl3-2, with its respective CB Test Certificate Ref. DE1-56443 respectively which were previously evaluated to UL/CSA/IEC 60950-1, 2nd edition, + Amendment 1 & 2 by VDE Testing and Certification Institute. See correlation page under miscellaneous enclosure for details.
ELECTRIC STRENGTH TEST (5.4.9)	Testing conducted under IEC 60950- 1:2005 (Second Edition); Am1:2009 + Am2:2013 evaluation was considered equivalent. Test was covered under on VDE CB report reference 218758-Cl3-2, with its respective CB Test Certificate Ref. DE1-56443 respectively which were previously evaluated to UL/CSA/IEC 60950-1, 2nd edition, + Amendment 1 & 2 by VDE Testing and Certification Institute. See correlation page under miscellaneous enclosure for details. Test was also repeated per UL/CSA/IEC 62368-1
INPUT TEST: SINGLE PHASE (B.2.5)	Testing conducted under IEC 60950- 1:2005 (Second Edition); Am1:2009 + Am2:2013 evaluation was considered equivalent. Test was covered under on VDE CB report reference 218758-Cl3-2, with its respective CB Test Certificate Ref. DE1-56443 respectively which

	were previously evaluated to UL/CSA/IEC 60950-1, 2nd edition, + Amendment 1 & 2 by VDE Testing and Certification Institute. See correlation page under miscellaneous enclosure for details.
NORMAL OPERATING CONDITIONS TEMPERATURE MEASUREMENT (B.2.6)	Testing conducted under IEC 60950- 1:2005 (Second Edition); Am1:2009 + Am2:2013 evaluation was considered equivalent. Test was covered under on VDE CB report reference 218758-Cl3-2, with its respective CB Test Certificate Ref. DE1-56443 respectively which were previously evaluated to UL/CSA/IEC 60950-1, 2nd edition, + Amendment 1 & 2 by VDE Testing and Certification Institute. See correlation page under miscellaneous enclosure for details.
SIMULATED ABNORMAL OPERATING CONDITIONS (B.3)	Testing conducted under IEC 60950- 1:2005 (Second Edition); Am1:2009 + Am2:2013 evaluation was considered equivalent. Test was covered under on VDE CB report reference 218758-Cl3-2, with its respective CB Test Certificate Ref. DE1-56443 respectively which were previously evaluated to UL/CSA/IEC 60950-1, 2nd edition, + Amendment 1 & 2 by VDE Testing and Certification Institute. See correlation page under miscellaneous enclosure for details.
SIMULATED SINGLE FAULT CONDITIONS (B.4)	Testing conducted under IEC 60950- 1:2005 (Second Edition); Am1:2009 + Am2:2013 evaluation was considered equivalent. Test was covered under on VDE CB report reference 218758-Cl3-2, with its respective CB Test Certificate Ref. DE1-56443 respectively which were previously evaluated to UL/CSA/IEC 60950-1, 2nd edition, + Amendment 1 & 2 by VDE Testing and Certification Institute. See correlation page under miscellaneous enclosure for details.
The following tests were waived:	Rationale for Waiving
TEST FOR THE PERMANENCE OF MARKINGS (ANNEX F.3.10)	Testing conducted under IEC 60950- 1:2005 (Second Edition); Am1:2009 + Am2:2013 evaluation was considered equivalent. Test was covered under E220248-A6002-CB.

Test results are valid only for the tested equipment. These tests are considered representative of the products covered by this Test Report. The test methods and results of the above tests have been reviewed and found

to be in accordance with the requirements in the Standard(s) referenced at the beginning of this Test Report.

The following supplements are provided as part of this Test Record. NOTE: These supplements are only available to the Applicant via the myUL[™] Client Portal.

Туре	Supplement Id	Description
Datasheet	02-01	Datasheet
Attachment	02-02	French CRD

Supplementary information:

ssue Date:	2020-04	2020-04-29 Page 1 of 13 Report Reference # E			E22024	E220248-A6014-UL	
		IEC 623	68-1				
Clause		Requirement + Test	Result - Remark			Verdict	
4.8.4, 4.8.5	TABLE: Lit	hium coin/button cell batteries	mechanical tests			N/A	
(The follow	ing mechani	cal tests are conducted in the s	eque	nce noted.)			
4.8.4.2	TABLE: Str	ess Relief test				—	
Ра	art	Material		Oven Temperature (°C)	C	omments	
4.8.4.3	TABLE: Ba	ttery replacement test				—	
Battery part	no	:				—	
Battery Insta	allation/withd	rawal	В	attery Installation/Removal Cycle	С	omments	
				1			
				2			
				3			
				4			
				5			
				6			
				8			
				9			
				10			
.8.4.4	TABLE: Dro	p test				—	
mpact Area	•	Drop Distance		Drop No.	Obse	ervations	
				1			
				2			
				3			
4.8.4.5	TABLE: Imp	pact				_	
Impacts p	er surface	Surface tested		Impact energy (Nm)	C	omments	
4.8.4.6	TABLE: Cru	ish test				_	
Test position		Surface tested		Crushing Force (N)		ation force	

TABLE: Lithium coin/button cell batteries mechanical test result 4.8.5 N/A Duration force applied (s) Test position Surface tested Force (N)

--

--

designation)

Normal

Abnormal

Single fault – SC/OC

--

Issue	Date: 2020	Date: 2020-04-29 Page 2 of		age 2 of 13 Report		rt Reference #	
			IEC	62368-1			
Clau	use	Requirer	nent + Test		Resu	lt - Remark	<
Supple	ementary inform	nation:					
5.2	Table: C	lassification of	electrical energy	sources			
-		e Voltage and Cu					
	Supply	Location (e.g.			Param	eters	
No.	Voltage	circuit designation)	Test conditions	U (Vrms or V	l (Apk or	Arms)	Hz
1	75 VDC	Input (E(A/C) Series, all	Normal	75 VDC		DC	>
		models except IE(A/C)4W00 4A120V-0##)	Abnormal Single fault – SC/OC				
2	60 VDC	Input	Normal	60 VDC			
		(IE(A/C)4W00 4A120V-0##)	Abnormal				
		,	Single fault – SC/OC				
3	75 VDC	Output	Normal	28 VDC			
		(E(A/C) Series, all	Abnormal				
		models except IE(A/C)4W00 4A120V-0##)	Single fault – SC/OC				
4	60 VDC		Normal	12 VDC			
		(IE(A/C)4W00 4A120V-0##)	Abnormal				
			Single fault – SC/OC				
5	60 or 75		Normal	60 or 75 VI	DC		
	VDC	iE(A/C) Series, all	Abnormal				
		models	Single fault – SC/OC				
5.2.2.3	3 - Capacitance	Limits					
No.	Supply Voltage	Location (e.g. circuit designation)	Test conditions	Capacit	Param ance, nF		k (V)

48-A6014-UL

Verdict

Pass

ES Class

ES2

ES1

ES1

ES1

ES2

ES Class

--

Upk (V)

--

Capacitance, nF

--

--

--

Issue Date:	2020-04-29

	IEC 62368-1		
Clause	Requirement + Test	Result - Remark	Verdict

5.2	Table:	Table: Classification of electrical energy sources							
5.2.2.4	4 - Single Puls	es							
	Supply	Location (e.g.	_		Parameters				
No.	Voltage	circuit designation)	Test conditions	Duration (ms)	Upk (V)	lpk (mA)	ES Class		
			Normal						
			Abnormal]		
			Single fault – SC/OC						
5.2.2.	5 - Repetitive F	Pulses							
	Supply	Location (e.g.			Parameters				
No.	Voltage		Test conditions	Off time (ms)	Upk (V)	lpk (mA)	ES Class		
			Normal						
			Abnormal						
			Single fault – SC/OC						
Test C	Test Conditions:								
	Normal –								
Abnormal -									
Supple	Supplementary information: SC=Short Circuit, OC=Open Circuit								

Page 3 of 13

Report Reference #

			EC 62368-1				
Clause		Requirement + Test	R	lesult - Rem	ark	Verdict	
5.4.1.4, 6.3.2, 9.0, B.2.6	TA	ABLE: Temperature measurement	S				Pass
		Supply voltage (V):	36 VDC	75 VDC			—
		Ambient T _{min} (°C):	26.9	25.0			
		Ambient T _{max} (°C):	26.9	25.0			
		Tma (°C)	26.9	25.0			
Maximum n	neas	sured temperature T of part/at:		T	(°C)		Allowed T _{max} (°C)
Ambient			26.9	25.0			
T1 - PWB, t	ор		88.3	78.6			130
T1 - PWB, I	Bott	om	83.1	76.1			130
L2 - PWB, 1	Гор		83.8	85.3			130
L2 - PWB, E	Botto	om	72.6	71.4			130
PWB, near	Q3(00	97.6	87.2			130
PWB, near	CR	303	85.2	90.9			130
C400, case			70.9	66.6			
U100, case			34.7	28.9			
Q303			93.4	97.9			
See Below			18 VDC	48 VDC	60 VDC		
IE(A/C)4W0	04/	A120V-0##[R	See below ambient 25.6	See below ambient 24.8	See below ambient 25.5		
IC101 body			72.8	66.7	73		130
CR102 bod	у		66.3	61.9	69.1		105
U1 body			64.9	61	65.9		130
T1 winding			79.6	72.9	79.2		130
Q200 drain			75.6	72	77.6		130
CR206 body		68.4	64.1	69.1		130	
CR201 body		53.3	52.5	55.5		130	
Q305 Pin 2		84.7	70.7	80.3		130	
R125 body			84.1	68.6	74.9		130
Q104 pin 2			77.7	71	79.8		130
T1 core			79.5	73.9	80.4		130
Q203 pin 7			72.6	74.7	80.9		130
L1 near win	ding]	74.2	75.4	81.4		130

			IEC 623	68-1						
Clause	Require	ment + Test		Result - Remark					Verdict	
Supply voltage	ge - NO FORCED AIR		48Vdo abnori		60Vda overla		60Vdc short circuit			
Maximum m	easured temperature T	of part/at:	T (°C)		T (°C)		T (°C)			
Ambient			24.4		25.1		23.6			
IC101 body			69.8		102.7		68.8		-	
CR102 body			63.8		94.7		66.7		-	
U1 body			65		97		72.4			
T1 winding			75.9		115.1		79.7			
Q200 drain			75.2		115.1		89			
CR206 body			66.7		99.9		76.2		-	
CR201 body			54.6		77.7		63.2			
Q305 Pin 2			75.2		118.8		76.3			
R125 body			71.6		108.7		69.5			
Q104 pin 2			74.2		112.9		73.8			
T1 core			77.1		117.4		81.4			
Q203 pin 7			78.8		123.3		109.9			
L1 near wind	ling		79		123.9		103.5			
Supplementa	ary information:									
External Coc	ling fan used follows:									
Condition 1: Condition 2:										
Temperature	T of winding:	t ₁ (°C)	R ₁ (Ω)	t2 (°	C)	R ₂ (2) T ((°C)	Allowed T _{max} (°C)	Insulation class
Supplementa	ary information:									
	should be considered a	s directed h	v applicab	le rea	uireme	ent				
	is not included in asses			•			9)			
11010 2. Tilla				Gratur	03 (01	ause	5)			

5.4.1.10.2	TABLE: Vicat softening temperature of thermoplastics				
Penetration	(mm):		_		
Object/ Part	No./Material	Manufacturer/t rademark	C)		
supplementary information:					

5.4.4.2,

5.4.4.5 c) 5.4.4.9

insulation di at/of:

Clearance	distanced between:	Required withstand voltage	Required cl (mm)	Measured cl (mm)
Supplemen	ntary information:			
5.4.2.4	TABLE: Clearances bas	ed on electric strength	n test	N/A
Test voltage applied between:		Required cl (mm)	Test voltage (kV) peak/ r.m.s. / d.c.	Breakdown Yes / No
Supplemer		•		

Frequency

(kHz)

Material

Required DTI

(mm)

TABLE: Distance through insulation measurements

Peak voltage

(V)

5.4.2.4 and 5.4.3							
Clearance (cl) and creepage distance (cr) at/of/between:	Up (V)	U r.m.s. (V)	Frequency (kHz) ¹	Required cl (mm)	cl (mm) ²	Required ³ cr (mm)	cr (mm)
Primary to Secondary	75 VDC		<30 Khz	0.2	1.2	1.3	1.8
Supplementary information:							
Note 1: Only for frequency above 30 kHz							
Note 2: See table 5.4.2.4 if this is based on electric strength test							
Note 3: Provide Material Group							

TABLE: Minimum Clearances distances using required withstand voltage

5.4.1.10.3	TABLE: Ball pressure test of thermoplastics					
Allowed imp	ression diameter					
Object/Part	No./Material	Manufacturer/trademark	Test temperature (°C)	Impression dia	meter (mm)	
Supplement	ary information:					

IEC 62368-1

TABLE: Minimum Clearances/Creepage distance

Overvoltage Category (OV):

Pollution Degree:

IEC 62368-1						
Clause	Requirement + Test	Result - Remark	Verdict			

Report Reference #

5.4.2.2,

5.4.2.3

Pass

N/A

N/A

DTI

(mm)

Page 6 of 13

Issue Date:	2020-04-29

IEC 62368-1									
Clause	Requirement + Test		Result - Remark			Verdict			
Supplementary information:									

5.4.9	TABLE: Electric strength tests				Pass
Test voltage	applied between:	Voltage shape (AC, DC)	Test voltage (V)	Breakdown Yes / No	
Functional:					
Basic/suppl	ementary:				
Input and O	utput	DC	1500	No	
Input and O	utput (62368-1)	DC	1500	00 No	
Input and O	utput (62368-1 Reverse Polarity)	DC	1500	No	
Reinforced:					
Routine Tes	sts:				
Supplement	tary information:				

5.5.2.2	5.5.2.2 TABLE: Stored discharge on capacitors N/A							
Supply Volt	Ipply Voltage (V), HzTest LocationOperating Condition (N, S)Switch position On or offMeasured Voltage (after 2 seconds)ES		ES Clas	ssification				
Supplemen	tary informat	ion:						
X-capacitor	s installed fo	r testing are:						
[] bleedin	g resistor rat	ing:						
[] ICX:								
Notes:								
A. Test Loc	ation:							
Phase to N	eutral; Phase	e to Phase; Pha	ase to Earth; a	nd/or Neutral to	o Earth			
B. Operatin	g condition a	bbreviations:						
N – Normal	N – Normal operating condition (e.g., normal operation, or open fuse); S –Single fault condition							

IEC 62368-1								
Clause	Requirement + Test			Result - Remark				
5.6.6.2 TABLE: Resistance of protective conductors and terminations N/A								
Accessible part		Test current (A)	Duration (min)	Voltage drop (V)	Resistance (Ω)			
Supplemen	tary information:							

5.7.2.2, 5.7.4					
Supply volt	age:				
Location		Test conditions specified in 6.1 of IEC 60990 or Fault Condition No in IEC 60990 clause 6.2.2.1 through 6.2.2.8, except for 6.2.2.7	Touch current (mA)		
		1			
		2*			
		3			
		4			
		5			
		6			
		8			
Supplemen	tary Information:	·			
Notes:					

[1] Supply voltage is the anticipated maximum Touch Voltage

[2] Earthed neutral conductor [Voltage differences less than 1% or more]

[3] Specify method used for measurement as described in IEC 60990 sub-clause 4.3

[4] IEC60990, sub-clause 6.2.2.7, Fault 7 not applicable.

[5] (*) IEC60990, sub-clause 6.2.2.2 is not applicable if switch or disconnect device (e.g., appliance coupler) provided.

E220248-A6014-UL

IEC 62368-1						
Clause	Requirement + Test	Result - Remark	Verdict			

6.2.2	Table: Electrical power sources (PS) measurements for classification						
Source	Description	Measurement	Max Power after 3 s	Max Power after 5 s*)	PS Classification		
75 VDC		Power (W) :			PS3 (To be		
	All circuits	V _A (V) :			employed in an end product)		
		I _A (A) :					
Supplementary Information:							
(*) Measurement taken only when limits at 3 seconds exceed PS1 limits							

6.2.3.1	Table: Determination of Potential Ignition Sources (Arcing PIS)					
	Location	Open circuit voltage After 3 s (Vp)	Measured r.m.s current (Irms)	Calculated value (V _p x I _{rms})		ing PIS? es / No
All Circuitss				addre		To be ssed in the roduct
Supplementary information:						
An Arcing PIS requires a minimum of 50 V (peak) a.c. or d.c. An Arcing PIS is established when the product of						

An Arcing PIS requires a minimum of 50 V (peak) a.c. or d.c. An Arcing PIS is established when the product of the open circuit voltage (Vp) and normal operating condition rms current (Irms) is greater than 15.

6.2.3.2	Table: Dete	able: Determination of Potential Ignition Sources (Resistive PIS)					
Circuit Location (x-y)		Operating Condition (Normal / Describe Single Fault)	Measured wattage or VA During first 30 s (W / VA)	Measured wattage or VA After 30 s (W / VA)	Protective Circuit, Regulator, or PTC Operated? Yes / No (Comment)	Resistive PIS? Yes/No	
All circuits						Yes. To be addressed in the end product	
Supplemen	Supplementary Information:						

A combination of voltmeter, VA and ammeter IA may be used instead of a wattmeter.

If a separate voltmeter and ammeter are used, the product of (VA x IA) is used to determine Resistive PIS classification.

A Resistive PIS: (a) dissipates more than 15 W, measured after 30 s of normal operation,

or (b) under single fault conditions has either a power exceeding 100 W measured immediately after the introduction of the fault if electronic circuits,

regulators or PTC devices are used, or has an available power exceeding 15 W measured 30 s after introduction of the fault.

IEC 62368-1						
Clause	Requirement + Test	Result - Remark	Verdict			

8.5.5	TABLE: High Pressure Lamp			N/A
Description		Values	Energy Source Classifica	
Lamp type .	:		_	
Manufacture	er:		_	
Cat no			_	
Pressure (c	old) (MPa):		MS_	
Pressure (o	perating) (MPa):		MS_	
Operating ti	me (minutes):		_	
Explosion m	nethod:		_	
Max particle	e length escaping enclosure (mm).:		MS_	
Max particle length beyond 1 m (mm):			MS_	
Overall resu	ılt:			
Supplement	tary information:			

B.2.5 T	ABLE: Inp	out test							Pass	
U (V)	Hz	I (A)	I rated (A)	P (W)	P rated (W)	Fuse No	l fuse (A)	Conditi	on/status	
36V	DC	2.8A	2A	100.8				Normal		
75V	DC	1.34A	2A	100.5				Normal		
								as follow of new m IE(A/C)4 ^V V-0##[R]	097) scope s: addition odel W004A120 and upgrade to	
18V dc	DC	3.032A	5A	54.574				mnl @ ou 12Vdc, 4		
48V dc	DC	1.212A	5A	53.823				mnl @ ou 12Vdc, 4		
60V dc	DC	0.913A	5A	54.766				mnl @ ou 12Vdc, 4		
Supplem	entary info	rmation:			1	<u> </u>				
Equipme	quipment may be have rated current or rated power or both. Both should be measured									

B.3

TABLE: Abnormal operating condition tests

Pass

E220248-A6014-UL

	IEC 62368-1							
Clause	Requirement + Test	Result - Remark	Verdict					

Ambient temperature (°C) 25									
EUT: Manufa	acturer, model	TDK, DC 36							
No. Abnormal Supply Test time Fuse Fuse Condition Voltage, (V) (ms) No. Condition (°C)				Observat	tion				
Short	75 VDC	10 minutes	Exter nal	10 A		See temperat ure data		Unit went hiccup mc no output, hazard. N NC, NT	ode, , no
OutputOver load36 VDC43 minutesExter nal10 ASee temperat ure dataT101 Temp. 109 °C. NB, NC, NT									
Supplementary information:									
	EUT: Manufa Abnormal Condition Short Over load	EUT: Manufacturer, model. Abnormal Condition Supply voltage, (V) Short 75 VDC Over load 36 VDC	EUT: Manufacturer, model/type, outputAbnormal ConditionSupply voltage, (V)Test time (ms)Short75 VDC10 minutesOver load36 VDC43 minutes	EUT: Manufacturer, model/type, output ratingAbnormal ConditionSupply voltage, (V)Test time (ms)Fuse no.Short75 VDC10 minutesExter nalOver load36 VDC43 minutesExter nal	EUT: Manufacturer, model/type, output rating:Abnormal ConditionSupply voltage, (V)Test time (ms)Fuse no.Fu currerShort75 VDC10 minutesExter nal10 A nalOver load36 VDC43 minutesExter nal10 A nal	EUT: Manufacturer, model/type, output rating: TDK, DC 36 Abnormal Condition Supply voltage, (V) Test time (ms) Fuse no. Fuse current, (A) Short 75 VDC 10 minutes Exter nal 10 A Over load 36 VDC 43 minutes Exter nal 10 A	EUT: Manufacturer, model/type, output rating: TDK, DC 36 – 75 V, m Abnormal Condition Supply voltage, (V) Test time (ms) Fuse no. Fuse current, (A) T-couple Short 75 VDC 10 minutes Exter nal 10 A See temperat ure data Over load 36 VDC 43 minutes Exter nal 10 A See temperat ure data	EUT: Manufacturer, model/type, output rating:TDK, DC 36 – 75 V, max. 4 AAbnormal ConditionSupply voltage, (V)Test time (ms)Fuse no.Fuse current, (A)T-coupleTemp. (°C)Short75 VDC10 minutesExter nal10 A see ture dataSee temperat ure dataOver load36 VDC43 minutesExter nal10 A see ture dataSee temperat ure data	EUT: Manufacturer, model/type, output rating: TDK, DC 36 - 75 V, max. 4 A Abnormal Condition Supply voltage, (V) Test time (ms) Fuse no. T-couple current, (A) Test time (°C) Observation Short 75 VDC 10 minutes Exter nal 10 A See temperat ure data Unit went hiccup mono output, hazard. N NC, NT Over load 36 VDC 43 minutes Exter nal 10 A See temperat ure data T101 Tem 109 °C. N NC, NT

Test table is provided to record abnormal and fault conditions for all applicable energy sources including Thermal burn injury. Column "Abnormal/Fault." Specify if test condition by indicating "Abnormal" then the condition for a Clause B.3 test or "Single Fault" then the condition for Clause B.4.

B.4	TAB	LE: Fault co	ondition tests								Pass
Ambient terr	npera	ture (°C)				:	25				_
Power source for EUT: Manufacturer, model/type, output rating:											
Component	Component No.FaultSupply voltage, (V)Test time (ms)Fuse no.Fuse current, (A)T-coupleTemp. (°C)O						bservation				
T101 (Prima to Secondar		Short	75 VDC	10 Minutes	Exter nal	10 A				tha to DC	itput is less an or equal 42.4 Vpk or 2 60 V, no zard
Q305 (D-S)		Short	75 VDC	60 Sec	Exter nal	10 A				tha to DC	itput is less an or equal 42.4 Vpk or 2 60 V, no zard
C350	C350Short75 VDC1 secExter nal10 AExternal fuse 10 A open										
Supplement	Supplementary information:										
F1 is externa	al fus	e with 10 A c	on test fixture s	pecified in	manufa	cturer s	specific	ation for er	nd use app	olica	ation

E220248-A6014-UL

				II	EC 62368-	1				
Clause			Requirem	nent + Test			Result -	Remark		Verdict
Annex M	ТА	BLE: Batte	eries							N/A
The tests of	The tests of Annex M are applicable only when appropriate battery data is not available									
Is it possible	e to i	install the b	pattery in a	reverse polari	ity position	?	:			
		Non-re	chargeable	e batteries		F	Rechargeal	ble batterie	es	
		Disch	arging	Un-	Cha	rging	Disch	arging	Reverse	d charging
	Meas. Manuf. current Specs. intentiona				Meas. current	Manuf. Specs.	Meas. current	Manuf. Specs.	Meas. current	Manuf. Specs.
Max. curren during norm condition										
Max. curren during fault condition	ıt									
Test results	:									Verdict
- Chemical	leak	S								
- Explosion	of th	e battery								
- Emission	of fla	me or exp	ulsion of m	olten metal						
- Electric str	eng	th tests of	equipment	after completi	on of tests					

Supplementary information:

Annex M.4	Table: Addi	tional safe	guards for equi	ipment con	taining seconda	ry lithium batte	eries	N/A
Batter	•	Test	conditions		Measurements	3	Oł	oservation
No	Э.			U	I (A)	I (A) Temp (°C)		
		Normal						
		Abnormal						
		Single fau	lt –SC/OC					
Supplementa	ary Informatio	on:						
Battery identificatio	n T	rging at ^{Tlowest} (°C)	Observa	ition	Charging at T _{highest} (°C)	Obs	ervati	on
Supplementa	ary Informatio	on:						

Clause

Clause	Require	ement + Test		Result -	Remark	Verdict			
Annex Q.1	TABLE: Circuits inter	nded for interco	nnection wit	h building wiring	g (LPS)	N/A			
Note: Meas	sured UOC (V) with all load circuits disconnected:								
Output	Components	U _{oc} (V)	l	sc (A)	S (\	/A)			
Circuit			Meas.	Limit	Meas.	Limit			
Supplemen	tary Information:								
SC=Short c	ircuit, OC=Open circuit								

IEC 62368-1

T.2, T.3, T.4, T.5	TABL	ABLE: Steady force test						
Part/Locat	tion	Material	Thickness (mm)	Force (N)	Test Duration (sec)	Obser	vation	
Supplement	onvinf	ormation:						
Supplement	ary inio							

T.6, T.9	ТАВ	LE: Impact tests				N/A
Part/Locat	ion	Material	Thickness (mm)	Vertical distance (mm)	Observation	
Supplementa	ary inf	ormation:				

T.7	TAB	3LE: Drop tests							
Part/Locati	t/Location Material		Thickness (mm)	Drop Height (mm)	Observation				
Supplementa	ary inf	ormation:							

T.8	TAB	LE: Stress relief t	est				N/A
Part/Locat	ion	Material	Thickness (mm)	Oven Temperature (°C)	Duration (h)	Observ	vation
Supplement	ary inf	ormation:					

Result - Remark

IEC 62368-1								
Clause	Requirement + Test	Result - Remark	Verdict					

4	GENERAL REQUIREMENTS		Pass
4.1.1	Acceptance of materials, components and subassemblies		Pass
4.1.2	Use of components		Pass
4.1.3	Equipment design and construction		Pass
4.1.15	Markings and instructions	(See Annex F)	Pass
4.4.4	Safeguard robustness	Unit intended for building-in. Additional Safeguards to be determined in the end product.	Pass
4.4.4.2	Steady force tests		N/A
4.4.4.3	Drop tests		N/A
4.4.4.4	Impact tests:		N/A
4.4.4.5	Internal accessible safeguard enclosure and barrier tests		N/A
4.4.4.6	Glass Impact tests		N/A
4.4.4.7	Thermoplastic material tests		N/A
4.4.4.8	Air comprising a safeguard		N/A
4.4.4.9	Accessibility and safeguard effectiveness		N/A
4.5	Explosion		N/A
4.6	Fixing of conductors		N/A
4.6.1	Fix conductors not to defeat a safeguard		N/A
4.6.2	10 N force test applied to		N/A
4.7	Equipment for direct insertion into mains socket - outlets		N/A
4.7.2	Mains plug part complies with the relevant standard		N/A
4.7.3	Torque (Nm):		N/A
4.8	Products containing coin/button cell batteries	Product does not contain lithium coin / button cell batteries.	N/A
4.8.2	Instructional safeguard		N/A
4.8.3	Battery Compartment Construction		N/A
	Means to reduce the possibility of children removing the battery		—
4.8.4	Battery Compartment Mechanical Tests:		N/A
4.8.5	Battery Accessibility		N/A
4.9	Likelihood of fire or shock due to entry of conductive object	This component is DC to DC converter intended for building in. To be determined in the end product.	N/A

Page 2 of 27

Report Reference #

IEC 62368-1			
Clause	Requirement + Test	Result - Remark	Verdict

5	ELECTRICALLY-CAUSED INJURY		Pass
5.2.1	Electrical energy source classifications:	(See appended table 5.2)	Pass
5.2.2	ES1, ES2 and ES3 limits	Input is ES2 and Output circuit is classified as ES1.	Pass
5.2.2.2	Steady-state voltage and current	(See appended table 5.2)	Pass
5.2.2.3	Capacitance limits		N/A
5.2.2.4	Single pulse limits		N/A
5.2.2.5	Limits for repetitive pulses:		N/A
5.2.2.6	Ringing signals		N/A
5.2.2.7	Audio signals:		N/A
5.3	Protection against electrical energy sources	Unit is for building-in. To be provided in the end product.	Pass
5.3.1	General Requirements for accessible parts to ordinary, instructed and skilled persons	Unit is for building-in.	Pass
5.3.2.1	Accessibility to electrical energy sources and safeguards	Unit is for building in. Accessible to Instructed or Skilled person.	Pass
5.3.2.2	Contact requirements	To be considered in end product.	N/A
	a) Test with test probe from Annex V		N/A
	b) Electric strength test potential (V)		N/A
	c) Air gap (mm):		N/A
5.3.2.4	Terminals for connecting stripped wire		N/A
5.4	Insulation materials and requirements		Pass
5.4.1.2	Properties of insulating material	Natural rubber, asbestos or hygroscopic materials are not used.	Pass
5.4.1.3	Humidity conditioning:	See sub-clause 5.4.8	Pass
5.4.1.4	Maximum operating temperature for insulating materials	(See appended table 5.4.1.4)	Pass
5.4.1.5	Pollution degree:	PD-2	
5.4.1.5.2	Test for pollution degree 1 environment and for an insulating compound		N/A
5.4.1.5.3	Thermal cycling		N/A
5.4.1.6	Insulation in transformers with varying dimensions		N/A

	IEC 62368-1		
Clause	Requirement + Test	Result - Remark	Verdict
		1	
5.4.1.7	Insulation in circuits generating starting pulses		N/A
5.4.1.8	Determination of working voltage		Pass
5.4.1.9	Insulating surfaces		N/A
5.4.1.10	Thermoplastic parts on which conductive metallic parts are directly mounted		N/A
5.4.1.10.2	Vicat softening temperature:		N/A
5.4.1.10.3	Ball pressure:		N/A
5.4.2	Clearances		Pass
5.4.2.2	Determining clearance using peak working voltage	See appended 5.4.2.2	Pass
5.4.2.3	Determining clearance using required withstand voltage:	No direct connection to Mains	N/A
	a) a.c. mains transient voltage		
	b) d.c. mains transient voltage:		
	c) external circuit transient voltage:		
	d) transient voltage determined by measurement		_
5.4.2.4	Determining the adequacy of a clearance using an electric strength test		N/A
5.4.2.5	Multiplication factors for clearances and test voltages:		N/A
5.4.3	Creepage distances:	See appended table 5.4.3	Pass
5.4.3.1	General		Pass
5.4.3.3	Material Group:	Material Group IIIb 100 ≤ CTI <175	_
5.4.4	Solid insulation		Pass
5.4.4.2	Minimum distance through insulation:		N/A
5.4.4.3	Insulation compound forming solid insulation		N/A
5.4.4.4	Solid insulation in semiconductor devices		N/A
5.4.4.5	Cemented joints		N/A
5.4.4.6	Thin sheet material		N/A
5.4.4.6.1	General requirements		N/A
5.4.4.6.2	Separable thin sheet material		N/A
	Number of layers (pcs):		N/A
5.4.4.6.3	Non-separable thin sheet material		N/A
5.4.4.6.4	Standard test procedure for non-separable thin sheet material		N/A
5.4.4.6.5	Mandrel test		N/A
5.4.4.7	Solid insulation in wound components		N/A

	IEC 62368-1		
Clause	Requirement + Test	Result - Remark	Verdict
5.4.4.9	Solid insulation at frequencies >30 kHz		N/A
5.4.5	Antenna terminal insulation		N/A
5.4.5	General		N/A
5.4.5.1	Voltage surge test		N/A
5.4.5.2	Insulation resistance (MΩ)		IN/A
5.4.6	Insulation of internal wire as part of supplementary safeguard		N/A
5.4.7	Tests for semiconductor components and for cemented joints	Planar transformer	Pass
5.4.8	Humidity conditioning		Pass
	Relative humidity (%):	95 %	—
	Temperature (°C):	25 °C	
	Duration (h):	72 hours	
5.4.9	Electric strength test:	(See appended table 5.4.9)	Pass
5.4.9.1	Test procedure for a solid insulation type test		Pass
5.4.9.2	Test procedure for routine tests		N/A
5.4.10	Protection against transient voltages between external circuit	Equipment is for building in. To be considered in the end product.	N/A
5.4.10.1	Parts and circuits separated from external circuits		N/A
5.4.10.2	Test methods		N/A
5.4.10.2.1	General		N/A
5.4.10.2.2	Impulse test:		N/A
5.4.10.2.3	Steady-state test:		N/A
5.4.11	Insulation between external circuits and earthed circuitry:		N/A
5.4.11.1	Exceptions to separation between external circuits and earth		N/A
5.4.11.2	Requirements		N/A
	Rated operating voltage U _{op} (V):		
	Nominal voltage U _{peak} (V):		
	Max increase due to variation Usp		—
	Max increase due to ageing ΔU_{sa} :		—
	U_{op} = U_{peak} + ΔU_{sp} + ΔU_{sa} :		—
5.5	Components as safeguards		Pass
5.5.1	General		Pass
5.5.2	Capacitors and RC units		N/A
5.5.2.1	General requirement		N/A

	IEC 62368-1		
Clause	Requirement + Test	Result - Remark	Verdict
5.5.2.2	Safeguards against capacitor discharge after disconnection of a connector:		N/A
5.5.3	Transformers	See Annex G.5.3	Pass
5.5.4	Optocouplers	See Annex G.12	Pass
5.5.5	Relays		N/A
5.5.6	Resistors		N/A
5.5.7	SPD's		N/A
5.5.7.1	Use of an SPD connected to reliable earthing		N/A
5.5.7.2	Use of an SPD between mains and protective earth		N/A
5.5.8	Insulation between the mains and external circuit consisting of a coaxial cable:		N/A
5.6	Protective conductor	•	N/A
5.6.2	Requirement for protective conductors		N/A
5.6.2.1	General requirements		N/A
5.6.2.2	Colour of insulation		N/A
5.6.3	Requirement for protective earthing conductors		N/A
	Protective earthing conductor size (mm ²)		
5.6.4	Requirement for protective bonding conductors		N/A
5.6.4.1	Protective bonding conductors		N/A
	Protective bonding conductor size (mm ²)		
	Protective current rating (A):		
5.6.4.3	Current limiting and overcurrent protective devices		N/A
5.6.5	Terminals for protective conductors		N/A
5.6.5.1	Requirement		N/A
	Conductor size (mm ²), nominal thread diameter (mm).		N/A
5.6.5.2	Corrosion		N/A
5.6.6	Resistance of the protective system		N/A
5.6.6.1	Requirements		N/A
5.6.6.2	Test Method Resistance (Ω):		N/A
5.6.7	Reliable earthing		N/A
5.7	Prospective touch voltage, touch current and prot	ective conductor current	Pass
5.7.2	Measuring devices and networks		Pass
5.7.2.1	Measurement of touch current:		N/A

Page 6 of 27

Report Reference #

	IEC 62368-1		
Clause	Requirement + Test	Result - Remark	Verdict
		•	
5.7.2.2	Measurement of prospective touch voltage	Outputs meet ES1 based on Voltages	Pass
5.7.3	Equipment set-up, supply connections and earth connections		N/A
	System of interconnected equipment (separate connections/single connection):		—
	Multiple connections to mains (one connection at a time/simultaneous connections)		—
5.7.4	Earthed conductive accessible parts		N/A
5.7.5	Protective conductor current		N/A
	Supply Voltage (V)		_
	Measured current (mA):		—
	Instructional Safeguard		N/A
5.7.6	Prospective touch voltage and touch current due to external circuits		N/A
5.7.6.1	Touch current from coaxial cables		N/A
5.7.6.2	Prospective touch voltage and touch current from external circuits		N/A
5.7.7	Summation of touch currents from external circuits		N/A
	a) Equipment with earthed external circuits Measured current (mA):		N/A
	b) Equipment whose external circuits are not referenced to earth. Measured current (mA):		N/A

6	ELECTRICALLY- CAUSED FIRE		Pass
6.2	.2 Classification of power sources (PS) and potential ignition sources (PIS)		Pass
6.2.2	Power source circuit classifications		Pass
6.2.2.1	General	(See appended table 6.2.2)	Pass
6.2.2.2	Power measurement for worst-case load fault :	(See appended table 6.2.2)	Pass
6.2.2.3	Power measurement for worst-case power source fault:	(See appended table 6.2.2)	Pass
6.2.2.4	PS1:		N/A
6.2.2.5	PS2:		N/A
6.2.2.6	PS3:	Input and outputs are PS3 classified	Pass
6.2.3	Classification of potential ignition sources	All parts in the internal circuits were considered as Arcing PIS and Resistive PIS.	Pass

Page 7 of 27 Report Reference # E220248-A6014-UL

	IEC 62368-1		
Clause	Requirement + Test	Result - Remark	Verdict
6.2.3.1	Arcing PIS:	All parts in the internal circuits were considered as Arcing PIS and Resistive PIS. (See appended table 6.2.3.1)	Pass
6.2.3.2	Resistive PIS:	All parts in the internal circuits were considered as Arcing PIS and Resistive PIS. (See appended table 6.2.3.1)	Pass
6.3	Safeguards against fire under normal operating and	abnormal operating conditions	Pass
6.3.1 (a)	No ignition and attainable temperature value less than 90 % defined by ISO 871 or less than 300 °C for unknown materials:	(See appended table 5.4.1.5, 6.3.2, 9.0, B.2.6)	Pass
6.3.1 (b)	Combustible materials outside fire enclosure	No combustible material.	N/A
6.4	Safeguards against fire under single fault conditions		Pass
6.4.1	Safeguard Method	"Control fire spread" method applied. The suitability of a fire enclosure should be considered in the end-product.	Pass
6.4.2	Reduction of the likelihood of ignition under single fault conditions in PS1 circuits		N/A
6.4.3	Reduction of the likelihood of ignition under single fault conditions in PS2 and PS3 circuits	Test was conducted with a 10 A external fuse during single fault test. Additional testing may be considered in an end product.	Pass
6.4.3.1	General		N/A
6.4.3.2	Supplementary Safeguards	Fire enclosure to be provided in the end product.	N/A
	Special conditions if conductors on printed boards are opened or peeled		N/A
6.4.3.3	Single Fault Conditions:	See B.2	Pass
	Special conditions for temperature limited by fuse		N/A
6.4.4	Control of fire spread in PS1 circuits		N/A
6.4.5	Control of fire spread in PS2 circuits		Pass
6.4.5.2	Supplementary safeguards:	All parts are mounted on a min. V- 1 PWB.	Pass
6.4.6	Control of fire spread in PS3 circuit	All parts are mounted on a min. V- 1 PWB.	Pass
6.4.7	Separation of combustible materials from a PIS	To be considered in the end application	Pass
6.4.7.1	General:	Supplementary Safeguard provided such as PWB min. V-1. Fire enclosure should be considered in the end-product.	Pass
6.4.7.2	Separation by distance		N/A

Page 8 of 27

Report Reference #

	IEC 62368-1		
Clause	Requirement + Test	Result - Remark	Verdict
6.4.7.3	Separation by a fire barrier		N/A
6.4.8	Fire enclosures and fire barriers	Fire enclosure should be considered in the end-product.	Pass
6.4.8.1	Fire enclosure and fire barrier material properties	Fire enclosure should be considered in the end-product.	N/A
6.4.8.2.1	Requirements for a fire barrier	Provided in the end-product	N/A
6.4.8.2.2	Requirements for a fire enclosure		N/A
6.4.8.3	Constructional requirements for a fire enclosure and a fire barrier		N/A
6.4.8.3.1	Fire enclosure and fire barrier openings		N/A
6.4.8.3.2	Fire barrier dimensions		N/A
6.4.8.3.3	Top Openings in Fire Enclosure: dimensions (mm):		N/A
	Needle Flame test		N/A
6.4.8.3.4	Bottom Openings in Fire Enclosure, condition met a), b) and/or c) dimensions (mm)		N/A
	Flammability tests for the bottom of a fire enclosure:		N/A
6.4.8.3.5	Integrity of the fire enclosure, condition met: a), b) or c):		N/A
6.4.8.4	Separation of PIS from fire enclosure and fire barrier distance (mm) or flammability rating:		N/A
6.5	Internal and external wiring		N/A
6.5.1	Requirements		N/A
6.5.2	Cross-sectional area (mm ²):		
6.5.3	Requirements for interconnection to building wiring:		N/A
6.6	Safeguards against fire due to connection to additional equipment		N/A
	External port limited to PS2 or complies with Clause Q.1		N/A

7	INJURY CAUSED BY HAZARDOUS SUBSTANCES	
7.2	Reduction of exposure to hazardous substances	N/A
7.3	Ozone exposure	N/A
7.4	Use of personal safeguards (PPE)	N/A
	Personal safeguards and instructions	—
7.5	Use of instructional safeguards and instructions	N/A
	Instructional safeguard (ISO 7010):	—

IEC 62368-1			
Clause	Requirement + Test	Result - Remark	Verdict

7.6

Batteries:

N/A

8	MECHANICALLY-CAUSED INJURY	N/A
8.1	General	N/A
8.2	Mechanical energy source classifications	N/A
8.3	Safeguards against mechanical energy sources	N/A
8.4	Safeguards against parts with sharp edges and corners	N/A
8.4.1	Safeguards	N/A
8.5	Safeguards against moving parts	N/A
8.5.1	MS2 or MS3 part required to be accessible for the function of the equipment	N/A
8.5.2	Instructional Safeguard :	—
8.5.4	Special categories of equipment comprising moving parts	N/A
8.5.4.1	Large data storage equipment	N/A
8.5.4.2	Equipment having electromechanical device for destruction of media	N/A
8.5.4.2.1	Safeguards and Safety Interlocks	N/A
8.5.4.2.2	Instructional safeguards against moving parts	N/A
	Instructional Safeguard	—
8.5.4.2.3	Disconnection from the supply	N/A
8.5.4.2.4	Probe type and force (N)	N/A
8.5.5	High Pressure Lamps	N/A
8.5.5.1	Energy Source Classification	N/A
8.5.5.2	High Pressure Lamp Explosion Test	N/A
8.6	Stability	N/A
8.6.1	Product classification	N/A
	Instructional Safeguard	—
8.6.2	Static stability	N/A
8.6.2.2	Static stability test	N/A
	Applied Force:	—
8.6.2.3	Downward Force Test	N/A
8.6.3	Relocation stability test	N/A
	Unit configuration during 10° tilt:	_
8.6.4	Glass slide test	N/A

Report Reference # E220248-A6014-UL

IEC 62368-1			
Clause	Requirement + Test	Result - Remark	Verdict
8.6.5	Horizontal force test (Applied Force):		N/A
	Position of feet or movable parts		_
8.7	Equipment mounted to wall or ceiling		N/A
8.7.1	Mounting Means (Length of screws (mm) and mounting surface):		N/A
8.7.2	Direction and applied force:		N/A
8.8	Handles strength		N/A
8.8.1	Classification		N/A
8.8.2	Applied Force:		N/A
8.9	Wheels or casters attachment requirements		N/A
8.9.1	Classification		N/A
8.9.2	Applied force:		
8.10	Carts, stands and similar carriers		N/A
8.10.1	General		N/A
8.10.2	Marking and instructions		N/A
	Instructional Safeguard:		
8.10.3	Cart, stand or carrier loading test and compliance		N/A
	Applied force:		
8.10.4	Cart, stand or carrier impact test		N/A
8.10.5	Mechanical stability		N/A
	Applied horizontal force (N):		
8.10.6	Thermoplastic temperature stability (°C):		N/A
8.11	Mounting means for rack mounted equipment		N/A
8.11.1	General		N/A
8.11.2	Product Classification		N/A
8.11.3	Mechanical strength test, variable N:		N/A
8.11.4	Mechanical strength test 250N, including end stops		N/A
8.12	Telescoping or rod antennas		N/A
	Button/Ball diameter (mm)		

9	THERMAL BURN INJURY		Pass
9.2	Thermal energy source classifications	TS3	Pass
9.3	Safeguard against thermal energy sources	Unit is for building-in - shall be considered in the final end-use	N/A
9.4	Requirements for safeguards		N/A
9.4.1	Equipment safeguard		N/A

	IEC 62368-1			
Clause Requirement + Test Result - Remark	Verdict			

|--|

Instructional safeguard:

N/A

10	RADIATION	N/A
10.2	Radiation energy source classification	N/A
10.2.1	General classification	N/A
10.3	Protection against laser radiation	N/A
	Laser radiation that exists in the equipment:	_
	Normal, abnormal, single-fault	N/A
	Instructional safeguard	_
	Tool	_
10.4	Protection against visible, infrared, and UV radiation	N/A
10.4.1	General	N/A
10.4.1.a)	RS3 for Ordinary and instructed persons	N/A
10.4.1.b)	RS3 accessible to a skilled person	N/A
	Personal safeguard (PPE) instructional safeguard:	—
10.4.1.c)	Equipment visible, IR, UV does not exceed RS1:	N/A
10.4.1.d)	Normal, abnormal, single-fault conditions:	N/A
10.4.1.e)	Enclosure material employed as safeguard is opaque 	N/A
10.4.1.f)	UV attenuation	N/A
10.4.1.g)	Materials resistant to degradation UV	N/A
10.4.1.h)	Enclosure containment of optical radiation	N/A
10.4.1.i)	Exempt Group under normal operating conditions	N/A
10.4.2	Instructional safeguard	N/A
10.5	Protection against x-radiation	N/A

	IEC 62368-1			
Clause	Requirement + Test	Result - Remark	Verdict	
10.5.1	X- radiation energy source that exists equipment:		N/A	
10.0.1	Normal, abnormal, single fault conditions		N/A	
	Equipment safeguards		N/A N/A	
	Instructional safeguard for skilled person:		N/A N/A	
10.5.3	Most unfavourable supply voltage to give maximum radiation			
	Abnormal and single-fault condition:		N/A	
	Maximum radiation (pA/kg):		N/A	
10.6	Protection against acoustic energy sources		N/A	
10.6.1	General		N/A	
10.6.2	Classification		N/A	
	Acoustic output, dB(A):		N/A	
	Output voltage, unweighted r.m.s.		N/A	
10.6.4	Protection of persons		N/A	
	Instructional safeguards:		N/A	
	Equipment safeguard prevent ordinary person to RS2:		—	
	Means to actively inform user of increase sound pressure:		—	
	Equipment safeguard prevent ordinary person to RS2:		—	
10.6.5	Requirements for listening devices (headphones, earphones, etc.)		N/A	
10.6.5.1	Corded passive listening devices with analog input		N/A	
	Input voltage with 94 dB(A) <i>L_{Aeq}</i> acoustic pressure output:		—	
10.6.5.2	Corded listening devices with digital input		N/A	
	Maximum dB(A)			
10.6.5.3	Cordless listening device		N/A	
	Maximum dB(A)			

В	NORMAL OPERATING CONDITION TESTS, ABNORMAL OPERATING CONDITION TESTS AND SINGLE FAULT CONDITION TESTS		Pass
B.2	Normal Operating Conditions		Pass
B.2.1	General requirements	(See Test Item Particulars and appended test tables)	Pass
	Audio Amplifiers and equipment with audio amplifiers		N/A

Page 13 of 27 Report Reference # E220248-A6014-UL

	IEC 62368-1		
Clause	Requirement + Test	Result - Remark	Verdict
			N1/A
B.2.3	Supply voltage and tolerances		N/A
B.2.5	Input test	(See appended table B.2.5)	Pass
B.3	Simulated abnormal operating conditions		Pass
B.3.1	General requirements	(See appended table B.3)	Pass
B.3.2	Covering of ventilation openings	No ventilation openings.	N/A
B.3.3	D.C. mains polarity test	Not DC mains.	N/A
B.3.4	Setting of voltage selector:		N/A
B.3.5	Maximum load at output terminals	(See appended table B.3)	Pass
B.3.6	Reverse battery polarity	No batteries.	N/A
B.3.7	Abnormal operating conditions as specified in Clause E.2.		N/A
B.3.8	Safeguards functional during and after abnormal operating conditions		Pass
B.4	Simulated single fault conditions		Pass
B.4.2	Temperature controlling device open or short- circuited		N/A
B.4.3	Motor tests		N/A
B.4.3.1	Motor blocked or rotor locked increasing the internal ambient temperature		N/A
B.4.4	Short circuit of functional insulation		Pass
B.4.4.1	Short circuit of clearances for functional insulation		Pass
B.4.4.2	Short circuit of creepage distances for functional insulation		Pass
B.4.4.3	Short circuit of functional insulation on coated printed boards		N/A
B.4.5	Short circuit and interruption of electrodes in tubes and semiconductors		N/A
B.4.6	Short circuit or disconnect of passive components		N/A
B.4.7	Continuous operation of components		Pass
B.4.8	Class 1 and Class 2 energy sources within limits during and after single fault conditions		N/A
B.4.9	Battery charging under single fault conditions :		N/A
С	UV RADIATION		N/A
C.1	Protection of materials in equipment from UV radiation		N/A
C.1.2	Requirements		N/A
C.1.3	Test method		N/A
C.2	UV light conditioning test		N/A
C.2.1	Test apparatus		N/A

IEC 62368-1				
Clause	Requirement + Test	Result - Remark	Verdict	
0.0.0				
C.2.2	Mounting of test samples		N/A	
C.2.3	Carbon-arc light-exposure apparatus		N/A	
C.2.4	Xenon-arc light exposure apparatus		N/A	
D	TEST GENERATORS		N/A	
D.1	Impulse test generators		N/A	
D.2	Antenna interface test generator		N/A	
D.3	Electronic pulse generator		N/A	
E	TEST CONDITIONS FOR EQUIPMENT CONTAIN	ING AUDIO AMPLIFIERS	N/A	
E.1	Audio amplifier normal operating conditions		N/A	
	Audio signal voltage (V):			
	Rated load impedance (Ω) :		—	
E.2	Audio amplifier abnormal operating conditions		N/A	
F	EQUIPMENT MARKINGS, INSTRUCTIONS, AND	INSTRUCTIONAL SAFEGUARDS	Pass	
F.1	General requirements		Pass	
	Instructions – Language:	Unit intended for building-in. No means for direct connection to AC mains supply. Electrical rating is not mandatorily required.	—	
F.2	Letter symbols and graphical symbols		N/A	
F.2.1	Letter symbols according to IEC60027-1		N/A	
F.2.2	Graphic symbols IEC, ISO or manufacturer specific		N/A	
F.3	Equipment markings	·	Pass	
F.3.1	Equipment marking locations		Pass	
F.3.2	Equipment identification markings		Pass	
F.3.2.1	Manufacturer identification:	Refer to the Model information at the beginning of this Test Report.	—	
F.3.2.2	Model identification:	Refer to the Rating information at the beginning of this Test Report.	—	
F.3.3	Equipment rating markings	Unit intended for building-in. No marking on unit.	Pass	
F.3.3.1	Equipment with direct connection to mains		N/A	
F.3.3.2	Equipment without direct connection to mains	Unit intended for building-in.	Pass	
F.3.3.3	Nature of supply voltage:			
F.3.3.4	Rated voltage		_	
F.3.3.5	Rated frequency			

Page 15 of 27 Report Reference # E220248-A6014-UL

	IEC 62368-1		
Clause	Requirement + Test	Result - Remark	Verdict
F 0 0 0	Data da marca da da cara da		
F.3.3.6	Rated current or rated power	Unit intended for building-in.	
F.3.3.7	Equipment with multiple supply connections		N/A
F.3.4	Voltage setting device		N/A
F.3.5	Terminals and operating devices		N/A
F.3.5.1	Mains appliance outlet and socket-outlet markings		N/A
F.3.5.2	Switch position identification marking:		N/A
F.3.5.3	Replacement fuse identification and rating markings		N/A
F.3.5.4	Replacement battery identification marking :		N/A
F.3.5.5	Terminal marking location		N/A
F.3.6	Equipment markings related to equipment classification		N/A
F.3.6.1	Class I Equipment		N/A
F.3.6.1.1	Protective earthing conductor terminal		N/A
F.3.6.1.2	Neutral conductor terminal		N/A
F.3.6.1.3	Protective bonding conductor terminals		N/A
F.3.6.2	Class II equipment (IEC60417-5172)		N/A
F.3.6.2.1	Class II equipment with or without functional earth		N/A
F.3.6.2.2	Class II equipment with functional earth terminal marking		N/A
F.3.7	Equipment IP rating marking:		
F.3.8	External power supply output marking		N/A
F.3.9	Durability, legibility and permanence of marking		N/A
F.3.10	Test for permanence of markings		N/A
F.4	Instructions	1	N/A
	a) Equipment for use in locations where children not likely to be present - marking		N/A
	b) Instructions given for installation or initial use		N/A
	c) Equipment intended to be fastened in place		N/A
	d) Equipment intended for use only in restricted access area		N/A
	e) Audio equipment terminals classified as ES3 and other equipment with terminals marked in accordance F.3.6.1		N/A
	f) Protective earthing employed as safeguard		N/A
	g) Protective earthing conductor current exceeding ES 2 limits		N/A
	h) Symbols used on equipment		N/A

	IEC 62368-1		
Clause	Requirement + Test	Result - Remark	Verdict
		Γ	
	i) Permanently connected equipment not provided with all-pole mains switch		N/A
	 j) Replaceable components or modules providing safeguard function 		N/A
F.5	Instructional safeguards		N/A
	Where "instructional safeguard" is referenced in the test report it specifies the required elements, location of marking and/or instruction		N/A
G	COMPONENTS		Pass
G.1	Switches		N/A
G.1.1	General requirements		N/A
G.1.2	Ratings, endurance, spacing, maximum load		N/A
G.2	Relays		N/A
G.2.1	General requirements		N/A
G.2.2	Overload test		N/A
G.2.3	Relay controlling connectors supply power		N/A
G.2.4	Mains relay, modified as stated in G.2		N/A
G.3	Protection Devices		Pass
G.3.1	Thermal cut-offs		N/A
G.3.1.1a) &b)	Thermal cut-outs separately approved according to IEC 60730 with conditions indicated in a) & b)		N/A
G.3.1.1c)	Thermal cut-outs tested as part of the equipment as indicated in c)		N/A
G.3.1.2	Thermal cut-off connections maintained and secure		N/A
G.3.2	Thermal links		N/A
G.3.2.1a)	Thermal links separately tested with IEC 60691		N/A
G.3.2.1b)	Thermal links tested as part of the equipment		N/A
	Aging hours (H)		
	Single Fault Condition		
	Test Voltage (V) and Insulation Resistance (Ω). :		
G.3.3	PTC Thermistors		Pass
G.3.4	Overcurrent protection devices	External Fuse used. See Engineering Conditions of Acceptability.	Pass
G.3.5	Safeguards components not mentioned in G.3.1 to	G.3.5	N/A
G.3.5.1	Non-resettable devices suitably rated and marking provided		N/A
G.3.5.2	Single faults conditions		N/A

IEC 62368-1			
Clause	Requirement + Test	Result - Remark	Verdict

G.4	Connectors		N/A
G.4.1	Spacings		N/A
G.4.2	Mains connector configuration:		N/A
G.4.3	Plug is shaped that insertion into mains socket- outlets or appliance coupler is unlikely		N/A
G.5	Wound Components		Pass
G.5.1	Wire insulation in wound components		N/A
G.5.1.2 a)	Two wires in contact inside wound component, angle between 45° and 90°		N/A
G.5.1.2 b)	Construction subject to routine testing		N/A
G.5.2	Endurance test on wound components		N/A
G.5.2.1	General test requirements		N/A
G.5.2.2	Heat run test		N/A
	Time (s):		_
	Temperature (°C):		—
G.5.2.3	Wound Components supplied by mains		N/A
G.5.3	Transformers		Pass
G.5.3.1	Requirements applied (IEC61204-7, IEC61558- 1/-2, and/or IEC62368-1):		N/A
	Position:	Planar type construction	—
	Method of protection:		—
G.5.3.2	Insulation		Pass
	Protection from displacement of windings	Planar type construction	
G.5.3.3	Overload test:	(See appended table B.3)	Pass
G.5.3.3.1	Test conditions		Pass
G.5.3.3.2	Winding Temperatures testing in the unit		N/A
G.5.3.3.3	Winding Temperatures - Alternative test method		N/A
G.5.4	Motors		N/A
G.5.4.1	General requirements		N/A
	Position:		—
G.5.4.2	Test conditions		N/A
G.5.4.3	Running overload test		N/A
G.5.4.4	Locked-rotor overload test		N/A
	Test duration (days):		—
G.5.4.5	Running overload test for d.c. motors in secondary circuits		N/A
G.5.4.5.2	Tested in the unit		N/A

	IEC 62368-1		
Clause	Requirement + Test	Result - Remark	Verdict
_	Electric strength test (V):		
G.5.4.5.3	Tested on the Bench - Alternative test method; test time (h)		N/A
	Electric strength test (V):		
G.5.4.6	Locked-rotor overload test for d.c. motors in secondary circuits		N/A
G.5.4.6.2	Tested in the unit		N/A
	Maximum Temperature:		N/A
	Electric strength test (V):		N/A
G.5.4.6.3	Tested on the bench - Alternative test method; test time (h):		N/A
	Electric strength test (V):		N/A
G.5.4.7	Motors with capacitors		N/A
G.5.4.8	Three-phase motors		N/A
G.5.4.9	Series motors		N/A
	Operating voltage:		
G.6	Wire Insulation		N/A
G.6.1	General		N/A
G.6.2	Solvent-based enamel wiring insulation		N/A
G.7	Mains supply cords		N/A
G.7.1	General requirements		N/A
	Туре:		
	Rated current (A):		
	Cross-sectional area (mm ²), (AWG):		
G.7.2	Compliance and test method		N/A
G.7.3	Cord anchorages and strain relief for non- detachable power supply cords		N/A
G.7.3.2	Cord strain relief		N/A
G.7.3.2.1	Requirements		N/A
	Strain relief test force (N):		
G.7.3.2.2	Strain relief mechanism failure		N/A
G.7.3.2.3	Cord sheath or jacket position, distance (mm):		
G.7.3.2.4	Strain relief comprised of polymeric material		N/A
G.7.4	Cord Entry:		N/A
G.7.5	Non-detachable cord bend protection		N/A
G.7.5.1	Requirements		N/A

	IEC 62368-1		
Clause	Requirement + Test	Result - Remark	Verdict
G.7.5.2	Mass (g):		_
	Diameter (m)		
	Temperature (°C):		
G.7.6	Supply wiring space		N/A
G.7.6.2	Stranded wire		N/A
G.7.6.2.1	Test with 8 mm strand		N/A
G.8	Varistors		N/A
G.8.1	General requirements		N/A
G.8.2	Safeguard against shock		N/A
G.8.3	Safeguard against fire		N/A
G.8.3.2	Varistor overload test		N/A
G.8.3.3	Temporary overvoltage		N/A
G.9	Integrated Circuit (IC) Current Limiters		N/A
G.9.1 a)	Manufacturer defines limit at max. 5A.		N/A
G.9.1 b)	Limiters do not have manual operator or reset		N/A
G.9.1 c)	Supply source does not exceed 250 VA:		_
G.9.1 d)	IC limiter output current (max. 5A):		
G.9.1 e)	Manufacturers' defined drift		
G.9.2	Test Program 1		N/A
G.9.3	Test Program 2		N/A
G.9.4	Test Program 3		N/A
G.10	Resistors		N/A
G.10.1	General requirements		N/A
G.10.2	Resistor test		N/A
G.10.3	Test for resistors serving as safeguards between the mains and an external circuit consisting of a coaxial cable		N/A
G.10.3.1	General requirements		N/A
G.10.3.2	Voltage surge test		N/A
G.10.3.3	Impulse test		N/A
G.11	Capacitor and RC units		N/A
G.11.1	General requirements		N/A
G.11.2	Conditioning of capacitors and RC units		N/A
G.11.3	Rules for selecting capacitors		N/A
G.12	Optocouplers		Pass

	IEC 62368-1		
Clause	Requirement + Test	Result - Remark	Verdict
	·	1	
	Optocouplers comply with IEC 60747-5-5:2007 Spacing or Electric Strength Test (specify option and test results)		Pass
	Type test voltage Vini:	1500 VDC isolation	—
	Routine test voltage, Vini,b:	1500 VDC isolation	
G.13	Printed boards		Pass
G.13.1	General requirements		Pass
G.13.2	Uncoated printed boards		Pass
G.13.3	Coated printed boards		N/A
G.13.4	Insulation between conductors on the same inner surface		N/A
	Compliance with cemented joint requirements (Specify construction):		—
G.13.5	Insulation between conductors on different surfaces		N/A
	Distance through insulation		N/A
	Number of insulation layers (pcs)		
G.13.6	Tests on coated printed boards		N/A
G.13.6.1	Sample preparation and preliminary inspection		N/A
G.13.6.2a)	Thermal conditioning		N/A
G.13.6.2b)	Electric strength test		N/A
G.13.6.2c)	Abrasion resistance test		N/A
G.14	Coating on components terminals		N/A
G.14.1	Requirements		N/A
G.15	Liquid filled components		N/A
G.15.1	General requirements		N/A
G.15.2	Requirements		N/A
G.15.3	Compliance and test methods		N/A
G.15.3.1	Hydrostatic pressure test		N/A
G.15.3.2	Creep resistance test		N/A
G.15.3.3	Tubing and fittings compatibility test		N/A
G.15.3.4	Vibration test		N/A
G.15.3.5	Thermal cycling test		N/A
G.15.3.6	Force test		N/A
G.15.4	Compliance		N/A
G.16	IC including capacitor discharge function (ICX)		N/A

	IEC 62368-1		
Clause	Requirement + Test R	Result - Remark	Verdict
G.16 a)	Humidity treatment in accordance with sc 5.4.8 – 120 hours		N/A
G.16 b)	Impulse test using circuit 2 with Uc = to transient voltage:		N/A
G.16 C1)	Application of ac voltage at 110% of rated voltage for 2.5 minutes		N/A
G.16 C2)	Test voltage:		
G.16 D1)	10,000 cycles on and off using capacitor with smallest capacitance resistor with largest resistance specified by manufacturer		N/A
G.16 D2)	Capacitance:		
G.16 D3)	Resistance:		
Н	CRITERIA FOR TELEPHONE RINGING SIGNALS		N/A
H.1	General		N/A
H.2	Method A		N/A
H.3	Method B		N/A
H.3.1	Ringing signal		N/A
H.3.1.1	Frequency (Hz)		
H.3.1.2	Voltage (V)		
H.3.1.3	Cadence; time (s) and voltage (V)		
H.3.1.4	Single fault current (mA):		
H.3.2	Tripping device and monitoring voltage:		N/A
H.3.2.1	Conditions for use of a tripping device or a monitoring voltage complied with		N/A
H.3.2.2	Tripping device		N/A
H.3.2.3	Monitoring voltage (V):		—
J	INSULATED WINDING WIRES FOR USE WITHOUT	FINTERLEAVED INSULATION	N/A
	General requirements		N/A
К	SAFETY INTERLOCKS		N/A
K.1	General requirements		N/A
K.2	Components of safety interlock safeguard mechanism		N/A
K.3	Inadvertent change of operating mode		N/A
K.4	Interlock safeguard override		N/A
K.5	Fail-safe		N/A
	Compliance:		N/A
K.6	Mechanically operated safety interlocks		N/A
K.6.1	Endurance requirement		N/A

IEC 62368-1			
Clause	Requirement + Test	Result - Remark	Verdict
K.6.2	Compliance and Test method		N/A
K.7	Interlock circuit isolation		N/A
K.7.1	Separation distance for contact gaps & interlock circuit elements (type and circuit location)		N/A
K.7.2	Overload test, Current (A)		N/A
K.7.3	Endurance test		N/A
K.7.4	Electric strength test		N/A
L	DISCONNECT DEVICES		N/A
L.1	General requirements		N/A
L.2	Permanently connected equipment		N/A
L.3	Parts that remain energized		N/A
L.4	Single phase equipment		N/A
L.5	Three-phase equipment		N/A
L.6	Switches as disconnect devices		N/A
L.7	Plugs as disconnect devices		N/A
L.8	Multiple power sources		N/A
М	EQUIPMENT CONTAINING BATTERIES AND TH	EIR PROTECTION CIRCUITS	N/A
M.1	General requirements		N/A
M.2	Safety of batteries and their cells		N/A
M.2.1	Requirements		N/A
M.2.2	Compliance and test method (identify method) :		N/A
M.3	Protection circuits		N/A
M.3.1	Requirements		N/A
M.3.2	Tests		N/A
	- Overcharging of a rechargeable battery		N/A
	- Unintentional charging of a non-rechargeable battery		N/A
	- Reverse charging of a rechargeable battery		N/A
	- Excessive discharging rate for any battery		N/A
M.3.3	Compliance:		N/A
M.4	Additional safeguards for equipment containing secondary lithium battery		N/A
M.4.1	General		N/A
M.4.2	Charging safeguards		N/A
M.4.2.1	Charging operating limits		N/A
M.4.2.2a)	Charging voltage, current and temperature:		

Page 23 of 27 Report Reference # E220248-A6014-UL

_

	IEC 62368-1		
Clause	Requirement + Test	Result - Remark	Verdict
M.4.2.2 b)	Single faults in charging circuitry		
M.4.3	Fire Enclosure		N/A
M.4.4	Endurance of equipment containing a secondary lithium battery		N/A
M.4.4.2	Preparation		N/A
M.4.4.3	Drop and charge/discharge function tests		N/A
	Drop		N/A
	Charge		N/A
	Discharge		N/A
M.4.4.4	Charge-discharge cycle test		N/A
M.4.4.5	Result of charge-discharge cycle test		N/A
M.5	Risk of burn due to short circuit during carrying		N/A
M.5.1	Requirement		N/A
M.5.2	Compliance and Test Method (Test of P.2.3)		N/A
M.6	Prevention of short circuits and protection from other effects of electric current		N/A
M.6.1	Short circuits		N/A
M.6.1.1	General requirements		N/A
M.6.1.2	Test method to simulate an internal fault		N/A
M.6.1.3	Compliance (Specify M.6.1.2 or alternative method)		N/A
M.6.2	Leakage current (mA):		N/A
M.7	Risk of explosion from lead acid and NiCd batteries		N/A
M.7.1	Ventilation preventing explosive gas concentration		N/A
M.7.2	Compliance and test method		N/A
M.8	Protection against internal ignition from external spark sources of lead acid batteries		N/A
M.8.1	General requirements		N/A
M.8.2	Test method		N/A
M.8.2.1	General requirements		N/A
M.8.2.2	Estimation of hypothetical volume Vz (m ³ /s):		
M.8.2.3	Correction factors:		_
M.8.2.4	Calculation of distance d (mm)		
M.9	Preventing electrolyte spillage		N/A
M.9.1	Protection from electrolyte spillage		N/A

	IEC 62368-1		
Clause	Requirement + Test	Result - Remark	Verdict
	1- - - - - - - - - -		
M.9.2	Tray for preventing electrolyte spillage		N/A
M.10	Instructions to prevent reasonably foreseeable misuse (Determination of compliance: inspection, data review; or abnormal testing)		N/A
N	ELECTROCHEMICAL POTENTIALS	• •	N/A
	Metal(s) used:		—
0	MEASUREMENT OF CREEPAGE DISTANCES A	ND CLEARANCES	N/A
	Figures O.1 to O.20 of this Annex applied:		
Р	SAFEGUARDS AGAINST ENTRY OF FOREIGN	OBJECTS AND SPILLAGE OF	N/A
P.1	General requirements		N/A
P.2.2	Safeguards against entry of foreign object		N/A
	Location and Dimensions (mm):		
P.2.3	Safeguard against the consequences of entry of foreign object		N/A
P.2.3.1	Safeguards against the entry of a foreign object		N/A
	Openings in transportable equipment		N/A
	Transportable equipment with metalized plastic parts:		N/A
P.2.3.2	Openings in transportable equipment in relation to metallized parts of a barrier or enclosure (identification of supplementary safeguard):		N/A
P.3	Safeguards against spillage of internal liquids		N/A
P.3.1	General requirements		N/A
P.3.2	Determination of spillage consequences		N/A
P.3.3	Spillage safeguards		N/A
P.3.4	Safeguards effectiveness		N/A
P.4	Metallized coatings and adhesive securing parts		N/A
P.4.2 a)	Conditioning testing		N/A
	Tc (°C):		—
	Tr (°C):		
	Ta (°C):		—
P.4.2 b)	Abrasion testing:		N/A
P.4.2 c)	Mechanical strength testing:		N/A
Q	CIRCUITS INTENDED FOR INTERCONNECTION	I WITH BUILDING WIRING	N/A
Q.1	Limited power sources		N/A
Q.1.1 a)	Inherently limited output		N/A
Q.1.1 b)	Impedance limited output		N/A

	IEC 62368-1		
Clause	Requirement + Test	Result - Remark	Verdict
	- Regulating network limited output under normal operating and simulated single fault condition		N/A
Q.1.1 c)	Overcurrent protective device limited output		N/A
Q.1.1 d)	IC current limiter complying with G.9		N/A
Q.1.2	Compliance and test method		N/A
Q.2	Test for external circuits – paired conductor cable		N/A
	Maximum output current (A):		
	Current limiting method:		
R	LIMITED SHORT CIRCUIT TEST		N/A
R.1	General requirements		N/A
R.2	Determination of the overcurrent protective device and circuit		N/A
R.3	Test method Supply voltage (V) and short-circuit current (A)):		N/A
S	TESTS FOR RESISTANCE TO HEAT AND FIRE	·	N/A
S.1	Flammability test for fire enclosures and fire barrier materials of equipment where the steady state power does not exceed 4 000 W		N/A
	Samples, material:		
	Wall thickness (mm):		
	Conditioning (°C)		
	Test flame according to IEC 60695-11-5 with conditions as set out		N/A
	- Material not consumed completely		N/A
	- Material extinguishes within 30s		N/A
	- No burning of layer or wrapping tissue		N/A
S.2	Flammability test for fire enclosure and fire barrier integrity		N/A
	Samples, material:		
	Wall thickness (mm):		
	Conditioning (°C):		
	Test flame according to IEC 60695-11-5 with conditions as set out		N/A
	Test specimen does not show any additional hole		N/A
S.3	Flammability test for the bottom of a fire enclosure		N/A
	Samples, material:		
	Wall thickness (mm):		

Report Reference # E220248-A6014-UL

IEC 62368-1				
Clause	Requirement + Test Result - Remark	Verdict		
		N1/A		
<u> </u>	Cheesecloth did not ignite	N/A		
S.4	Flammability classification of materials	N/A		
S.5	Flammability test for fire enclosures and fire barrier materials of equipment where the steady state power does not exceed 4 000 W	N/A		
	Samples, material			
	Wall thickness (mm):			
	Conditioning (test condition), (°C)			
	Test flame according to IEC 60695-11-20 with conditions as set out	N/A		
	After every test specimen was not consumed completely	N/A		
	After fifth flame application, flame extinguished within 1 min	N/A		
т	MECHANICAL STRENGTH TESTS	N/A		
T.1	General requirements	N/A		
T.2	Steady force test, 10 N	N/A		
Т.З	Steady force test, 30 N	N/A		
T.4	Steady force test, 100 N	N/A		
T.5	Steady force test, 250 N	N/A		
T.6	Enclosure impact test	N/A		
	Fall test	N/A		
	Swing test	N/A		
T.7	Drop test:	N/A		
T.8	Stress relief test	N/A		
Т.9	Impact Test (glass)	N/A		
T.9.1	General requirements	N/A		
T.9.2	Impact test and compliance	N/A		
	Impact energy (J)			
	Height (m)			
T.10	Glass fragmentation test	N/A		
T.11	Test for telescoping or rod antennas	N/A		
	Torque value (Nm)			
U	MECHANICAL STRENGTH OF CATHODE RAY TUBES (CRT) AND PROTECTION AGAINST THE EFECTS OF IMPLOSION	N/A		
U.1	General requirements	N/A		

	IEC 62368-1		
Clause	Requirement + Test	Result - Remark	Verdict
[
U.2	Compliance and test method for non-intrinsically protected CRTs		N/A
U.3	Protective Screen:		N/A
v	DETERMINATION OF ACCESSIBLE PARTS (FINC	GERS, PROBES AND WEDGES)	N/A
V.1	Accessible parts of equipment		N/A
V.2	Accessible part criterion		N/A

Enclosure National Differences

USA / Canada

E220248-A6014-UL

IEC62368_1B - ATTACHMENT

Clause

Requirement + Test

Result - Remark

Verdict

ATTACHMENT TO TEST REPORT IEC 62368-1 2th Ed. U.S.A. NATIONAL DIFFERENCES

Audio/video, information and communication technology equipment - Part 1: Safety requirements

Differences according to	CSA/UL 62368-1:2014
Attachment Form No.	US&CA_ND_IEC623681B
Attachment Originator	UL(US)
Master Attachment	Date 2015-06
Converight @ 2015 IEC System	for Conformity Tooting and Cortification of Electrical Equipment (IECEE)

Copyright © 2015 IEC System for Conformity Testing and Certification of Electrical Equipment (IECEE), Geneva, Switzerland. All rights reserved.

	IEC 62368-1 - US and Canadian National Differences Special National Conditions based on Regulations and Other National Differences				
1.1	All equipment is to be designed to allow installation according to the National Electrical Code (NEC), ANSI/NFPA 70, the Canadian Electrical Code (CEC), Part I, CAN/CSA C22.1, and when applicable, the National Electrical Safety Code, IEEE C2. Also, for such equipment marked or otherwise identified, installation is allowed per the Standard for the Protection of Information Technology Equipment, ANSI/NFPA 75.	Noted	Pass		
1.4	Additional requirements apply to some forms of power distribution equipment, including sub-assemblies.		N/A		
4.1.17	For lengths exceeding 3.05 m, external interconnecting flexible cord and cable assemblies are required to be a suitable cable type (e.g., DP, CL2) specified in the NEC.		N/A		
	For lengths 3.05 m or less, external interconnecting flexible cord and cable assemblies that are not types specified in the NEC generally are required to have special construction features and identification markings.		N/A		
4.8	Lithium coin / button cell batteries have modified special construction and performance requirements.		N/A		
5.6.3	Protective earthing conductors comply with the minimum conductor sizes in Table G.5, except as required by Table G.7ADV.1 for cord connected equipment, or Annex DVH for permanently connected equipment		N/A		
5.7.7	Equipment intended to receive telecommunication ringing signals complies with a special touch current measurement tests.		N/A		
6.5.1	PS3 wiring outside a fire enclosure complies with single fault testing in B.4, or be current limited per one of the permitted methods.		N/A		

	IEC62368_1B - ATTACI	HMENT	
Clause	Requirement + Test	Result - Remark	Verdict
Annex F (F.3.3.8)	Output terminals provided for supply of other equipment, except mains, supply are marked with a maximum rating or references to which equipment it is permitted to be connected.		N/A
Annex G (G.7.1)	Permanent connection of equipment to the mains supply by a power supply cord is not permitted, except for certain equipment, such as ATMs.		N/A
Annex G (G.7.3)	Power supply cords are required to have attachment plugs rated not less than 125 percent of the rated current of the equipment.		N/A
	Flexible power supply cords are required to be compatible with Article 400 of the NEC, and Tables 11 and 12 of the CEC.		N/A
Annex G (G.7.5)	Minimum cord length is required to be 1.5 m, with certain constructions such as external power supplies allowed to consider both input and output cord lengths into the requirement. Power supply cords are required to be no longer than 4.5 m in length if used in ITE Rooms.		N/A
Annex H.2	Continuous ringing signals under normal operating conditions up to 16 mA only are permitted if the equipment is subjected to special installation and performance restrictions.		N/A
Annex H.4	For circuits with other than ringing signals and with voltages exceeding 42.4 Vpeak or 60 V d.c., the maximum acceptable current through a 2000 ohm resistor (or greater) connected across the voltage source with other loads disconnected is 7.1 mA peak or 30 mA d.c. under normal operating conditions.		N/A
Annex M	Battery packs for stationary applications comply with special component requirements.		N/A
Annex DVA (1)	Equipment intended for use in spaces used for environmental air are subjected to special flammability requirements for heat and visible smoke release.		N/A
	For ITE room applications, automated information storage systems with combustible media greater than 0.76 m3 (27 cu ft) have a provision for connection of either automatic sprinklers or a gaseous agent extinguishing system with an extended discharge.		N/A
	Consumer products designed or intended primarily for children 12 years of age or younger are subject to additional requirements in accordance with U.S. & Canadian Regulations.		N/A
	Baby monitors additionally comply with ASTM F2951, Consumer Safety Specification for Baby Monitors.		N/A

Report Reference #

IEC62368_1B - ATTACHMENT				
Clause	Requirement + Test	Result - Remark	Verdict	
Annex DVA (5.6.3)	For Pluggable Equipment Type A, the protection in the installation is assumed to be 20A.		N/A	
Annex DVA (6.3)	The maximum quantity of flammable liquid stored in equipment complies with NFPA 30.		N/A	
Annex DVA (6.4.8)	For ITE room applications, enclosures with combustible material measuring greater than 0.9 m2 (10 sq ft) or a single dimension greater than 1.8 m (6 ft) have a flame spread rating of 50 or less. For equipment with the same dimensions for other applications, an external surface that is not a fire enclosure requires a min. flammability classification of V-1.		N/A	
Annex DVA (10.3.1)	Equipment with lasers meets the U.S. Code of Federal Regulations 21 CFR 1040 (and the Canadian Radiation Emitting Devices Act, REDR C1370).		N/A	
Annex DVA (10.5.1)	Equipment that produces ionizing radiation complies with the U.S. Code of Federal Regulations, 21 CFR 1020 (and the Canadian Radiation Emitting Devices Act, REDR C1370).		N/A	
Annex DVA (F.3.3.3)	Equipment for use on a.c. mains supply systems with a neutral and more than one phase conductor (e.g. 120/240 V, 3-wire) require a special marking format for electrical ratings. Additional considerations apply for voltage ratings that exceed the attachment cap rating or are lower than the "Normal Operating Condition" in Table 2 of CAN/CSA C22.2 No. 235."		N/A	
Annex DVA (F.3.3.5)	Equipment identified for ITE (computer) room installation is marked with the rated current		N/A	
Annex DVA (G.1)	Vertically-mounted disconnect switches and circuit breakers have the "on" position indicated by the handle in the up position		N/A	
Annex DVA (G.3.4)	Suitable NEC/CEC branch circuit protection rated at the maximum circuit rating is required for all standard supply outlets and receptacles (such as supplied in power distribution units) if the supply branch circuit protection is not suitable.		N/A	
Annex DVA (G.4.2)	Equipment with isolated ground (earthing) receptacles complies with NEC 250.146(D) and CEC 10-112 and 10-906(8).		N/A	
Annex DVA (G.4.3)	Where a fuse is used to provide Class 2 or Class 3 current limiting, it is not operator-accessible unless it is non- interchangeable.		N/A	
Annex DVA (G.5.3)	Power distribution transformers distributing power at 100 volts or more, and rated 10 kVA or more, require special transformer overcurrent protection.		N/A	

IEC62368_1B - ATTACHMENT				
Clause	Requirement + Test	Result - Remark	Verdict	
Annex DVA (G.5.4)	Motor control devices are required for cord- connected equipment with a mains-connected motor if the equipment is rated more than 12 A, or if the equipment has a nominal voltage rating greater than 120 V, or if the motor is rated more than 1/3 hp (locked rotor current over 43 A).		N/A	
Annex DVA (Annex M)	For ITE room applications, equipment with battery systems capable of supplying 750 VA for five minutes have a battery disconnect means that may be connected to the ITE room remote power- off circuit.		N/A	
Annex DVA (Q)	Wiring terminals intended to supply Class 2 outputs according to the NEC or CEC Part 1are marked with the voltage rating and "Class 2" or equivalent; marking is located adjacent to the terminals and visible during wiring.		N/A	
Annex DVB (1)	Additional requirements apply for equipment used for entertainment purposes intended for installation in general patient care areas of health care facilities.		N/A	
Annex DVC (1)	Additional requirements apply for equipment intended for mounting under kitchen cabinets.		N/A	
Annex DVE (4.1.1)	Some equipment, components, sub-assemblies and materials associated with the risk of fire, electric shock, or personal injury have component or material ratings in accordance with the applicable national (U.S. and Canadian) component or material requirements. Components required to comply include: appliance couplers, attachment plugs, battery back-up systems, battery packs, circuit breakers, communication circuit accessories, connectors (used for current interruption of non-LPS circuits), power supply cords, direct plug-in equipment, electrochemical capacitor modules (energy storage modules with ultra-capacitors), enclosures (outdoor), flexible cords and cables, fuses (branch circuit), ground-fault current interrupters, interconnecting cables, data storage equipment, printed wiring, protectors for communications circuits, receptacles, surge protective devices, vehicle battery adapters, wire connectors, and wire and cables.		Pass	
Annex DVH	Equipment for permanent connection to the mains supply is subjected to additional requirements.		N/A	
Annex DVH (DVH.1)	Wiring methods (terminals, leads, etc.) used for the connection of the equipment to the mains are in accordance with the NEC/CEC.		N/A	

	IEC62368_1B - ATTACHMENT				
Clause	Requirement + Test	Result - Remark	Verdict		
Annex DVH (DVH.3.2)	Terminals for permanent wiring, including protective earthing terminals, are suitable for U.S./Canadian wire gauge sizes, rated 125 percent of the equipment rating, and are specially marked when specified.		N/A		
Annex DVH (DVH.3.2)	Wire binding screws are not permitted to attach conductors larger than 10 AWG (5.3 mm2).		N/A		
Annex DVH (DVH.4)	Permanently connected equipment is required to have a suitable wiring compartment and wire bending space.		N/A		
Annex DVH (DVH 5.5)	Equipment connected to a centralized d.c. power system, and having one pole of the DC mains input terminal connected to the main protective earthing terminal in the equipment, complies with special earthing, wiring, marking and installation instruction requirements.		N/A		
Annex DVI (6.7)	Equipment intended for connection to telecommunication network outside plant cable is required to be protected against overvoltage from power line crosses.		N/A		
Annex DVJ (10.6.1)	Equipment connected to a telecommunication and cable distribution networks and supplied with an earphone intended to be held against, or in the ear is required to comply with special acoustic pressure requirements.		N/A		

Enclosures

MODEL #	Input Voltage	Max Input Current*	Output Voltage**	Output Current	Max. Output Power
IE(A/C)48003A280V-0##	36-75	4	28	2.8	78W
IE(A/C)48003A240V-0##	36-75	4	24	3.3	78W
IE(A/C)48004A200V-0##	36-75	4	20	3.9	78W
IE(A/C)48004A180V-0##	36-75	4	18	4.3	78W
IE(A/C)48005A150V-0##	36-75	4	15	5.2	78W
IE(A/C)48007A120V-0##	36-75	4	12	6.5	78W
IE(A/C)48008A050V-0##	36-75	2	5	8	40W
IE(A/C)48013A050V-0##	36-75	4	5	13	65W
IE(A/C)48015A050V-0##	36-75	4	5	15	75W
IE(A/C)48010A033V-0##	36-75	2	3.3	10	33W
IE(A/C)48025A033V-0##	36-75	4	3.3	25	82.5W
IE(A/C)48020A033V-0##	36-75	4	3.3	20	66W
IE(A/C)48010A025V-0##	36-75	2	2.5	10	25W
IE(A/C)48025A025V-0##	36-75	4	2.5	25	62.5W
IE(A/C)48020A025V-0##	36-75	4	2.5	20	50W
IE(A/C)48010A020V-0##	36-75	2	2.0	10	20W
IE(A/C)48025A020V-0##	36-75	4	2.0	25	50W
IE(A/C)48020A020V-0##	36-75	4	2.0	20	40W
IE(A/C)48010A018V-0##	36-75	2	1.8	10	18W
IE(A/C)48025A018V-0##	36-75	4	1.8	25	45W
IE(A/C)48020A018V-0##	36-75	4	1.8	20	36W
IE(A/C)48010A015V-0##	36-75	2	1.5	10	15W
IE(A/C)48025A015V-0##	36-75	4	1.5	25	37.5W
IE(A/C)48020A015V-0##	36-75	4	1.5	20	30W
IE(A/C)48010A012V-0##	36-75	2	1.2	10	12W
IE(A/C)48025A012V-0##	36-75	4	1.2	25	30W
IE(A/C)48020A012V-0##	36-75	4	1.2	20	24W
IE(A/C)48015A012V-0##	36-75	4	1.2	15	18W
IE(A/C)48015A015V-0##	36-75	4	1.5	15	22.5W
IE(A/C)48015A018V-0##	36-75	4	1.8	15	27W
IE(A/C)48015A020V-0##	36-75	4	2	15	30W
IE(A/C)48015A025V-0##	36-75	4	2.5	15	37.5W
IE(A/C)48015A033V-0##	36-75	4	3.3	15	49.5W
IE(A/C)4W004A120V-0##	18-60	5	12	4	48W

Miscellaneous ID 07-01