



# EV3303-0400-A EVALUATION BOARD USER GUIDE

## Introduction

This user guide describes the evaluation board provided for the FS3303  $\mu$ POL™ product.

The board generates an output voltage ( $V_{OUT}$ ) of 1.2V\* for loads of 0–3A from an input voltage ( $V_{IN}$ ) of 3.3V.

## Specifications

- Input voltage ( $V_{IN}$ ) = +3.3V
- Output voltage ( $V_{OUT}$ ) = +1.2V
- Output load ( $I_{OUT}$ ) = 0–3A
- Switching frequency ( $F_{SW}$ ) = 1.44MHz
- Output capacitance ( $C_O$ ) = 1x22 $\mu$ F (MLCC)
- Input capacitance ( $C_{IN}$ ) = 1x22 $\mu$ F (MLCC)
- Power Solution Size (width x length x height) = 6 x 6 x 1.2mm

## Operation

The board is configured for a single input supply. The Enable (EN) input is connected to  $V_{IN}$  through a resistor divider, so that no Enable signal is needed. If an independent Enable Control is required, use Enable header. Pgood status can be checked at PG header.


To use the evaluation board:

1. Connect a well-regulated +3.3V input supply to  $V_{IN}$  (Red Connector) and Gnd (Black Connector).
2. Connect a load of 0–3A to  $V_{OUT}$  (Green Connector) and Gnd (Black Connector).

**\*NOTE – Output Voltages from 0.4V to 3.3V can be obtained by changing the values of Resistor Divider Components. Refer Page 7.**


## Description

The evaluation board consists of a 4-layer PCB made from FR4 glass-reinforced epoxy laminate material. All layers use 1oz copper. The EV3303-0400-A is a single sided board, with all components, including the FS3303, mounted on the top side of the board.




**Figure 1 Board Picture**


Figure 2 to Figure 5 show the pictures of the board layers and Figure 6 shows a schematic of the electric circuit.




**Figure 2 Board Layout – layer 1**



**Figure 3 Board Layout – layer 2**





**Figure 4** Board Layout – layer 3



**Figure 5** Board Layout – layer 4

Part reference	Quantity	Type	Description
FS3303 $\mu$ POL	1	–	FS3303 Module
C2, C4	2	22 $\mu$ F	0805, 10V, X5R
R1, R4	2	0 $\Omega$	0402 case size
R2	1	4.02k $\Omega$	0402 case size
R3	1	2k $\Omega$	0402 case size
R5	1	49.9k $\Omega$	0402 case size
R6	1	38.3k $\Omega$	0402 case size
R7	1	49.9	0402 case size
J8	1	–	Coaxial Connector



$V_{OUT}$ (V)	$R_{TOP}/R_{BOTTOM}$	$V_{OUT}$ (V)	$R_{TOP}/R_{BOTTOM}$
0.625	0.5622	1.05	1.6145
0.65	0.6194	1.1	1.7328
0.7	0.7500	1.2	2.0100
0.8	1.0000	1.5	2.7347
0.85	1.1261	1.7	3.2419
0.9	1.2407	1.8	3.4957
0.95	1.3673	2.5	5.2344
1	1.5056	3.3	7.3224

Figure 6 Schematic\*

\*NOTE – Modify  $R_3$  ( $R_{BOTTOM}$ ) for different  $V_{OUT}$  as per the included table.  $R_2$  ( $R_{TOP}$ ) = 4.02 k $\Omega$  is recommended. For  $V_{OUT}$  = 0.4V;  $R_2$  = 0 $\Omega$ .

## Typical performance

Figure 7 to Figure 23 show typical operating waveforms for the evaluation board, while Figure 24 shows thermal image of the board in operation. In all cases, the board is operating at room temperature with no airflow;  $V_{IN}$  is 3.3V,  $V_{OUT}$  is 1.2V and  $I_O$  is 0–3A.




Figure 7 Startup with no load (Ch1:  $V_{IN}$ , Ch2:  $V_{OUT}$ , Ch3: PGOOD, Ch4: EN)




Figure 8 Startup with 3A load (Ch1:  $V_{IN}$ , Ch2:  $V_{OUT}$ , Ch3: PGOOD, Ch4: EN)






Figure 9  $V_{in}$  Shutdown at 0A load (Ch1:  $V_{IN}$ , Ch2:  $V_{OUT}$ , Ch3: PGOOD, Ch4: EN)




Figure 10  $V_{in}$  Shutdown at 3A load (Ch1:  $V_{IN}$ , Ch2:  $V_{OUT}$ , Ch3: PGOOD, Ch4: EN)




Figure 11 Turn on with Enable at 3A load (Ch1:VIN, Ch2: VOUT, Ch3: PGOOD, Ch4: EN)




Figure 12 Enable Shutdown at 3A load (Ch1:VIN, Ch2: VOUT, Ch3: PGOOD, Ch4: EN)



Figure 13 Startup into pre-bias (Ch1:  $V_{IN}$ , Ch2:  $V_{OUT}$ , Ch3: PGOOD, Ch4: EN)




Figure 14 Recovery from OCP (Ch1:  $V_{IN}$ , Ch2:  $V_{OUT}$ , Ch3: PGOOD, Ch4: EN)




Figure 15 Sw at 0A (Ch5: Sw, Ch8: IOUT),  $F_{SW} = 1.44\text{MHz}$



Figure 16 Sw at 3A (Ch5: Sw, Ch8: IOUT),  $F_{SW} = 1.67\text{MHz}$




Figure 17  $V_{OUT}$  ripple at 0A (Ch7: $V_{OUT}$ , Ch8:  $I_{OUT}$ ), Peak-Peak  $V_{OUT}$  ripple = 8.68mV







Figure 18  $V_{OUT}$  ripple at 3A (Ch7: $V_{OUT}$ , Ch8:  $I_{OUT}$ ), Peak-Peak  $V_{OUT}$  ripple = 9.17mV




**Figure 19** Transient response 0A to 1.5A @ 2.5A/μs from Chroma Load (Ch7:V<sub>OUT</sub>, Ch8: I<sub>OUT</sub>), peak-peak deviation = 29.1 mV



**Figure 20** Transient response 1.5A to 3A @ 2.5A/μs from Chroma Load (Ch7:V<sub>OUT</sub>, Ch8: I<sub>OUT</sub>), peak-peak deviation = 28.1 mV



**Figure 21** *Efficiency*



**Figure 22** *Power loss*






Figure 23 Load regulation –  $<\pm 0.2\%$  ( $I_{OUT} = 0-3A$ )




Figure 24 Thermal image ( $V_{IN}=3.3V$ ,  $I_{OUT}=3A$ ) – maximum temperature rise =  $32^{\circ}C$



## Disclaimer

### IMPORTANT NOTICE AND DISCLAIMER

TDK PROVIDES THIS POWER DESIGN USER GUIDE (“Resources”) “AS IS” AND WITH ALL FAULTS, AND DISCLAIMS. ALL WARRANTIES, EXPRESS AND IMPLIED, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

These Resources are intended for skilled developers designing with TDK products. You are solely responsible for (1) selecting the appropriate TDK products for your application, (2) designing, validating and testing your application, (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements, and (4) ensuring your application complies with all applicable laws and regulations. These Resources are subject to change without notice and TDK assumes no responsibility for any notices or lack thereof. TDK grants you permission to use these Resources solely for development of an application that uses the TDK products described in the Resource.

This permission may be revoked at any time by TDK or any of its affiliates. Your use of these Resources shall be in compliance with all applicable laws and regulations including applicable export/import controls. Reproduction and display of these Resources is prohibited. No license is granted to any other TDK intellectual property right or to any third party intellectual property right. TDK disclaims responsibility for, and you agree to fully indemnify TDK, its affiliates and its representatives against, any claims, damages, costs, losses, and liabilities arising out of your use of these Resources.

### REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

#### SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using these products.

The products listed on this specification sheet are intended for use in general electric equipment (AV equipment, telecommunication equipment,

**REMINDER**

home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal condition and use condition.

The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to sociality, person or property. Please understand that we are not responsible for any damage or liability caused by use of the products in any of the applications below or for any other use exceeding the range or conditions set forth in this specification sheet.

1. Aerospace/Aviation equipment
2. Transportation equipment (cars, electric trains, ships, etc.)
3. Medical equipment
4. Power-generation control equipment
5. Atomic energy related equipment
6. Seabed equipment
7. Transportation control equipment
8. Public Information-processing equipment
9. Military equipment
10. Electric heating apparatus, burning equipment
11. Disaster prevention/crime prevention equipment
12. Safety equipment
13. Other applications that are not considered general-purpose applications

When using this product in general-purpose application, you are kindly requested to take into consideration securing protection circuit/ equipment or providing backup circuits, etc., to ensure higher safety.